

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854304

Luminaire Tested: SQ2-PW1-125U-050D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854304
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PW1-125U-050D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7065.6 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.22
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854304

CATALOG NUMBER: SQ2-PW1-125U-050D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854304

CATALOG NUMBER: SQ2-PW1-125U-050D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34	27
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29	24
3	79	70	63	57	70	63	57	52	51	46	43	39	36	34	28	27	25	20
4	72	62	54	49	65	56	50	45	45	40	37	35	32	29	25	24	22	18
5	66	55	47	42	59	50	43	38	40	36	32	31	28	26	23	21	19	16
6	61	49	42	36	55	45	38	33	36	32	28	28	25	22	21	19	17	14
7	56	45	37	32	51	41	34	29	33	28	25	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16306	16306	16306
5°	16196	16321	16477
10°	16226	16415	16620
15°	16222	16527	16720
20°	16228	16509	16393
25°	16140	16158	15232
30°	16032	15224	13772
35°	15906	14010	12435
40°	15588	12770	10987
45°	14979	11485	9597
50°	13941	10268	8214
55°	12752	9070	6660
60°	11428	7889	5745
65°	9994	6797	5108
70°	8172	6038	4631
75°	6363	5221	4261
80°	4742	4472	3756
85°	3205	3390	2130

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14979 cd/sqm



TEST NUMBER: P854304

CATALOG NUMBER: SQ2-PW1-125U-050D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.2	1.4
10°-20°	278.6	3.9
20°-30°	410.0	5.8
30°-40°	448.3	6.3
40°-50°	402.2	5.7
50°-60°	300.0	4.2
60°-70°	189.6	2.7
70°-80°	93.9	1.3
80°-90°	22.8	0.3
90°-100°	299.1	4.2
100°-110°	973.7	13.8
110°-120°	963.2	13.6
120°-130°	787.1	11.1
130°-140°	643.3	9.1
140°-150°	501.1	7.1
150°-160°	361.2	5.1
160°-170°	220.8	3.1
170°-180°	74.5	1.1
0°-30°	784.8	11.1
0°-40°	1233.1	17.5
0°-60°	1935.3	27.4
0°-90°	2241.7	31.7
90°-120°	2236.0	31.6
90°-150°	4167.5	59.0
90°-180°	4824.0	68.3
0°-180°	7065.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1010	1010	1010	1010	1010	
5°	999	1015	1007	1008	1017	95
15°	970	989	989	996	1000	274
25°	906	926	907	869	855	417
35°	807	798	711	649	631	503
45°	656	603	503	440	420	503
55°	453	410	322	253	237	405
65°	262	240	178	143	134	259
75°	102	110	84	70	68	112
85°	17	22	18	12	12	22
90°	0	3	7	6	6	3
95°	40	123	548	195	120	47
105°	165	239	965	1842	1744	176
115°	306	365	786	1619	1905	303
125°	425	474	775	1278	1507	378
135°	514	567	771	1103	1244	397
145°	600	644	769	950	1040	376
155°	685	707	774	851	883	315
165°	747	754	776	805	814	210
175°	779	779	779	785	783	74
180°	782	782	782	782	782	

TEST NUMBER: P854304

CATALOG NUMBER: SQ2-PW1-125U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1009.9	1009.9	1009.9	1009.9	1009.9
2.5°	1003.0	1015.8	1007.6	1008.4	1010.7
5°	999.3	1015.3	1007.0	1008.2	1016.6
7.5°	994.3	1010.5	1004.3	1007.8	1016.1
10°	989.7	1006.6	1001.2	1006.2	1013.7
12.5°	983.5	1001.2	997.4	1003.1	1010.7
15°	970.5	989.3	988.7	995.6	1000.3
17.5°	955.3	974.1	973.2	974.9	977.2
20°	944.5	963.3	960.8	954.1	954.1
22.5°	929.1	949.4	943.1	924.7	918.7
25°	906.0	925.8	907.0	869.2	855.0
27.5°	879.1	895.1	857.4	803.6	784.1
30°	859.9	872.1	816.6	757.5	738.7
32.5°	839.9	844.6	775.0	713.6	693.3
35°	807.0	798.5	710.8	648.8	630.9
37.5°	768.1	742.9	649.0	584.1	564.4
40°	739.6	703.9	605.9	541.0	521.3
42.5°	708.1	663.3	565.2	500.3	479.8
45°	656.0	603.3	503.0	440.1	420.3
47.5°	597.3	545.0	444.9	384.0	367.0
50°	555.0	504.2	408.8	347.7	327.0
52.5°	511.9	466.4	373.4	310.6	282.4
55°	453.0	409.8	322.2	252.6	236.6
57.5°	392.4	355.0	275.8	212.6	199.5
60°	353.9	321.0	244.3	191.1	177.9
62.5°	317.0	287.9	213.5	171.1	160.2
65°	261.6	240.0	177.9	143.1	133.7
67.5°	207.8	195.7	147.9	117.4	111.2
70°	173.1	169.4	127.9	102.8	98.1
72.5°	143.1	144.6	108.7	89.0	85.8
75°	102.0	109.5	83.7	70.2	68.3
77.5°	69.4	80.7	61.9	51.9	50.4
80°	51.0	62.3	48.1	40.4	40.4
82.5°	35.6	44.6	34.2	30.4	30.4
85°	17.3	22.0	18.3	12.5	11.5
87.5°	4.6	7.4	4.4	3.5	3.5
90°	0.0	2.8	6.7	5.8	5.8
92.5°	13.8	49.8	159.1	52.4	40.4
95°	40.4	123.1	548.2	195.4	120.2
97.5°	76.0	160.2	930.3	566.6	345.8
100°	99.1	181.8	1074.2	957.9	621.3
102.5°	125.2	205.0	1056.5	1417.1	1077.5
105°	165.4	238.8	964.6	1842.3	1744.5
107.5°	208.9	277.9	877.3	1879.2	1982.8
110°	240.4	303.4	835.7	1833.4	2020.5



TEST NUMBER: P854304

CATALOG NUMBER: SQ2-PW1-125U-050D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	266.6	328.8	809.5	1750.8	1992.0
115°	305.8	365.1	785.7	1619.2	1905.1
117.5°	346.2	399.6	776.5	1498.8	1783.4
120°	369.3	421.9	774.2	1424.8	1700.3
122.5°	391.6	443.5	774.9	1360.5	1617.2
125°	425.1	474.0	775.1	1278.5	1507.0
127.5°	453.7	503.7	774.9	1217.0	1407.5
130°	472.2	523.0	774.2	1181.9	1352.1
132.5°	488.3	541.4	773.4	1149.4	1309.0
135°	513.5	567.1	771.3	1103.4	1244.4
137.5°	538.2	592.1	769.2	1056.7	1181.9
140°	555.9	607.6	768.4	1025.0	1143.4
142.5°	572.8	622.2	768.4	994.7	1100.4
145°	600.1	644.3	769.4	950.3	1040.5
147.5°	626.6	665.0	770.7	912.5	982.3
150°	644.3	678.2	772.2	889.9	949.2
152.5°	662.0	689.9	773.0	872.7	920.0
155°	684.7	707.3	774.2	850.9	882.8
157.5°	706.3	722.4	775.3	834.7	857.1
160°	719.3	732.5	776.1	824.6	842.4
162.5°	730.9	741.0	776.1	816.0	829.4
165°	747.2	753.8	776.1	805.1	814.5
167.5°	758.8	762.9	776.3	797.0	801.9
170°	766.5	768.3	777.0	791.5	793.4
172.5°	771.9	773.0	778.6	788.4	788.0
175°	779.0	779.0	779.0	784.7	782.8
177.5°	781.9	781.1	780.3	784.1	781.1
180°	781.9	781.9	781.9	781.9	781.9



TEST NUMBER: P854304

CATALOG NUMBER: SQ2-PW1-125U-050D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.75	15.45	15.86	16.55	18.06	11.24	11.93	12.34	13.03	14.54
	3H	16.06	16.68	17.18	17.79	19.32	12.43	13.05	13.54	14.16	15.69
	4H	16.43	17.02	17.55	18.12	19.66	12.87	13.46	13.99	14.57	16.10
	6H	16.62	17.16	17.75	18.27	19.82	13.18	13.72	14.31	14.83	16.38
	8H	16.65	17.17	17.79	18.29	19.83	13.25	13.76	14.38	14.89	16.43
	12H	16.64	17.13	17.78	18.25	19.81	13.25	13.74	14.39	14.86	16.43
4H	2H	14.83	15.42	15.97	16.53	18.07	11.90	12.49	13.03	13.60	15.13
	3H	16.36	16.85	17.50	17.99	19.54	13.27	13.76	14.41	14.90	16.44
	4H	16.87	17.32	18.01	18.44	20.01	13.81	14.26	14.95	15.39	16.95
	6H	17.19	17.58	18.34	18.72	20.28	14.21	14.59	15.35	15.74	17.30
	8H	17.27	17.62	18.41	18.76	20.34	14.31	14.67	15.46	15.81	17.38
	12H	17.27	17.60	18.44	18.75	20.33	14.32	14.65	15.49	15.80	17.38
8H	4H	16.89	17.25	18.04	18.39	19.97	14.13	14.49	15.27	15.62	17.20
	6H	17.32	17.62	18.49	18.80	20.37	14.63	14.92	15.79	16.10	17.68
	8H	17.47	17.73	18.64	18.89	20.48	14.79	15.05	15.96	16.21	17.80
	12H	17.53	17.76	18.70	18.91	20.54	14.84	15.07	16.02	16.23	17.85
12H	4H	16.85	17.17	18.01	18.32	19.90	14.14	14.46	15.30	15.61	17.19
	6H	17.32	17.57	18.49	18.73	20.32	14.69	14.95	15.86	16.11	17.70
	8H	17.47	17.70	18.64	18.85	20.48	14.87	15.10	16.05	16.25	17.88