

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854379

Luminaire Tested: SQ2-WBM-100U-075D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854379
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G3-2104-222-6)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-WBM-100U-075D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6935.8 lumens
Efficiency: N/A
Efficacy: 115.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.18 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854379

CATALOG NUMBER: SQ2-WBM-100U-075D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854379

CATALOG NUMBER: SQ2-WBM-100U-075D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	98	95	91	88	90	87	84	82	73	71	69	60	59	58	48	48	47	41
2	91	85	79	75	83	78	74	70	66	63	60	55	53	51	45	43	42	37
3	84	76	70	65	77	70	65	61	60	56	53	50	48	45	41	39	38	34
4	78	68	62	56	72	64	58	53	54	50	47	46	43	40	38	36	34	31
5	72	62	55	50	66	58	51	47	50	45	41	42	39	36	35	33	31	28
6	67	56	49	44	62	53	46	42	45	41	37	39	35	33	33	30	28	25
7	62	51	44	39	58	48	42	37	42	37	33	36	32	30	30	28	26	23
8	58	47	40	35	54	44	38	33	38	34	30	33	29	27	28	26	24	21
9	54	43	36	32	50	41	34	30	35	31	27	31	27	25	26	24	22	20
10	51	40	33	29	47	37	32	28	33	28	25	29	25	22	24	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	32411	32411	32411
5°	32707	32302	32692
10°	33037	32723	33023
15°	33588	33153	32991
20°	33747	32953	32459
25°	33054	32076	31545
30°	31362	30464	29496
35°	28206	27618	26613
40°	23123	22778	21905
45°	14458	16459	13579
50°	5657	9595	5172
55°	2790	4470	2764
60°	1305	2144	1182
65°	1177	1249	1104
70°	1138	1180	1090
75°	1142	1142	1023
80°	1069	1069	986
85°	1074	889	889

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 16459 cd/sqm



TEST NUMBER: P854379

CATALOG NUMBER: SQ2-WBM-100U-075D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.9	2.8
10°-20°	561.2	8.1
20°-30°	829.8	12.0
30°-40°	858.6	12.4
40°-50°	516.4	7.4
50°-60°	123.6	1.8
60°-70°	33.8	0.5
70°-80°	18.9	0.3
80°-90°	7.0	0.1
90°-100°	254.6	3.7
100°-110°	770.1	11.1
110°-120°	751.8	10.8
120°-130°	614.3	8.9
130°-140°	501.5	7.2
140°-150°	390.4	5.6
150°-160°	281.4	4.1
160°-170°	172.3	2.5
170°-180°	58.2	0.8
0°-30°	1582.9	22.8
0°-40°	2441.5	35.2
0°-60°	3081.5	44.4
0°-90°	3141.2	45.3
90°-120°	1776.6	25.6
90°-150°	3282.7	47.3
90°-180°	3795.0	54.7
0°-180°	6935.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2007	2007	2007	2007	2007	
5°	2018	2011	1993	2020	2017	192
15°	2009	2024	1983	1983	1974	566
25°	1855	1870	1800	1781	1771	848
35°	1431	1429	1401	1369	1350	878
45°	633	719	721	685	595	490
55°	99	111	159	106	98	99
65°	31	32	33	31	29	31
75°	18	18	18	17	16	19
85°	6	6	5	5	5	6
90°	0	2	12	7	6	2
95°	32	100	480	178	112	37
105°	134	188	756	1436	1365	141
115°	238	284	612	1266	1486	236
125°	333	370	603	1000	1176	296
135°	399	441	599	862	970	309
145°	466	501	599	742	811	292
155°	531	549	603	665	690	244
165°	581	588	606	629	636	164
175°	608	608	609	614	612	58
180°	610	610	610	610	610	



TEST NUMBER: P854379

CATALOG NUMBER: SQ2-WBM-100U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2007.4	2007.4	2007.4	2007.4	2007.4
2.5°	2017.4	2012.2	1995.9	2012.7	2009.0
5°	2018.0	2011.4	1993.0	2019.9	2017.1
7.5°	2015.9	2013.1	1999.0	2019.3	2014.9
10°	2015.1	2016.1	1995.9	2017.0	2014.2
12.5°	2014.4	2022.1	1992.8	2009.2	2002.6
15°	2009.4	2024.4	1983.4	1983.2	1973.7
17.5°	1988.0	2005.9	1951.0	1936.0	1924.5
20°	1964.1	1982.0	1917.9	1893.8	1889.1
22.5°	1926.4	1945.8	1877.1	1850.6	1842.9
25°	1855.4	1870.4	1800.5	1781.0	1770.7
27.5°	1760.7	1769.0	1703.3	1681.1	1666.8
30°	1682.2	1685.9	1634.0	1604.7	1582.1
32.5°	1589.0	1592.8	1547.0	1519.3	1501.2
35°	1431.0	1429.1	1401.2	1369.0	1350.2
37.5°	1233.3	1236.0	1213.9	1188.4	1169.4
40°	1097.1	1098.9	1080.7	1044.0	1039.3
42.5°	930.8	959.0	934.4	905.8	883.8
45°	633.2	718.8	720.8	685.1	594.7
47.5°	357.6	455.1	511.4	408.8	299.1
50°	225.2	291.1	382.0	242.6	205.9
52.5°	159.7	193.2	288.1	170.7	151.3
55°	99.1	111.4	158.8	105.7	98.2
57.5°	58.9	71.5	90.3	71.5	59.7
60°	40.4	50.8	66.4	46.9	36.6
62.5°	35.0	39.4	52.5	37.1	33.5
65°	30.8	31.7	32.7	30.8	28.9
67.5°	27.1	28.1	27.3	27.1	25.4
70°	24.1	25.0	25.0	24.0	23.1
72.5°	21.7	22.7	21.9	21.7	20.0
75°	18.3	18.3	18.3	17.3	16.4
77.5°	13.9	14.8	13.9	13.8	12.9
80°	11.5	12.5	11.5	11.5	10.6
82.5°	9.2	9.4	9.2	9.2	8.3
85°	5.8	5.8	4.8	4.8	4.8
87.5°	1.5	2.7	3.8	2.9	2.7
90°	0.0	1.9	11.5	6.7	5.7
92.5°	10.7	43.3	155.4	51.6	37.1
95°	31.6	99.9	480.5	177.5	112.0
97.5°	61.1	127.1	757.3	501.1	305.1
100°	79.4	144.0	846.1	818.0	549.4
102.5°	100.1	162.4	827.8	1147.3	914.7
105°	134.0	188.3	756.2	1436.0	1364.9
107.5°	166.2	218.0	687.2	1464.6	1547.0
110°	187.6	237.2	652.8	1428.6	1578.4



TEST NUMBER: P854379

CATALOG NUMBER: SQ2-WBM-100U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	208.3	256.4	632.1	1368.3	1557.7
115°	238.3	284.2	611.6	1265.6	1486.5
117.5°	268.2	311.6	604.4	1169.4	1395.5
120°	288.1	329.3	602.1	1113.3	1330.5
122.5°	306.5	345.4	602.1	1063.9	1264.6
125°	333.1	369.6	603.0	999.5	1176.3
127.5°	354.7	392.5	602.1	950.8	1101.7
130°	368.5	407.8	602.1	922.9	1059.6
132.5°	380.8	420.8	601.3	897.4	1023.6
135°	399.1	441.3	599.2	862.0	969.6
137.5°	419.6	459.7	599.2	824.1	923.8
140°	432.6	471.9	599.2	799.5	894.0
142.5°	445.7	483.5	598.4	777.0	859.5
145°	466.1	500.8	599.2	741.5	810.7
147.5°	486.6	516.0	600.3	712.2	765.3
150°	499.6	526.8	601.1	695.9	740.8
152.5°	511.9	536.0	601.9	681.9	718.6
155°	531.2	549.0	603.0	664.8	690.1
157.5°	548.1	562.5	604.2	652.2	669.8
160°	558.0	570.2	604.9	644.5	657.6
162.5°	568.0	577.1	605.7	637.5	648.4
165°	581.0	587.5	605.9	629.0	636.5
167.5°	592.1	595.5	607.0	622.4	625.6
170°	598.2	600.1	607.8	619.3	620.2
172.5°	602.1	603.2	607.8	616.2	616.4
175°	607.8	607.8	608.8	613.5	611.6
177.5°	610.5	609.7	608.9	611.2	609.7
180°	609.7	609.7	609.7	609.7	609.7



TEST NUMBER: P854379

CATALOG NUMBER: SQ2-WBM-100U-075D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.52	5.22	5.55	6.23	7.58	4.18	4.87	5.20	5.88	7.23
	3H	5.02	5.63	6.05	6.66	8.03	4.68	5.30	5.72	6.32	7.69
	4H	5.28	5.86	6.33	6.89	8.27	4.92	5.50	5.97	6.53	7.91
	6H	5.51	6.04	6.56	7.07	8.46	5.13	5.66	6.18	6.69	8.08
	8H	5.58	6.09	6.65	7.13	8.52	5.19	5.70	6.25	6.74	8.12
	12H	5.63	6.11	6.70	7.15	8.56	5.22	5.70	6.29	6.74	8.14
4H	2H	4.52	5.10	5.58	6.13	7.51	4.21	4.79	5.26	5.81	7.19
	3H	5.23	5.71	6.29	6.76	8.15	4.93	5.41	5.99	6.46	7.85
	4H	5.63	6.07	6.69	7.11	8.53	5.30	5.74	6.37	6.79	8.20
	6H	6.01	6.38	7.08	7.45	8.86	5.65	6.02	6.72	7.09	8.50
	8H	6.15	6.50	7.22	7.56	8.98	5.77	6.12	6.84	7.18	8.60
	12H	6.24	6.55	7.33	7.63	9.05	5.83	6.15	6.92	7.22	8.64
8H	4H	5.71	6.06	6.79	7.12	8.54	5.41	5.76	6.48	6.82	8.24
	6H	6.22	6.51	7.31	7.61	9.03	5.88	6.17	6.98	7.27	8.69
	8H	6.45	6.70	7.55	7.78	9.22	6.08	6.33	7.18	7.42	8.86
	12H	6.62	6.84	7.72	7.92	9.40	6.22	6.44	7.32	7.52	9.00
12H	4H	5.68	6.00	6.77	7.07	8.50	5.39	5.70	6.48	6.78	8.20
	6H	6.24	6.49	7.34	7.57	9.01	5.91	6.16	7.01	7.25	8.69
	8H	6.49	6.71	7.59	7.79	9.27	6.13	6.35	7.24	7.44	8.91