

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855126

Luminaire Tested: SQ2-PP3-125U-050D-835-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855126
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PP3-125U-050D-835-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8372.9 lumens
Efficiency: N/A
Efficacy: 135.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855126

CATALOG NUMBER: SQ2-PP3-125U-050D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855126

CATALOG NUMBER: SQ2-PP3-125U-050D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32				32
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				28
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	30	29	24				24
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25	21				21
4	72	62	54	48	65	56	50	45	45	40	37	35	32	29	26	24	22	18				18
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19	16				16
6	61	49	41	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14				14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12				12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	17	18	15	14	11				11
9	48	37	29	25	43	33	27	23	27	23	19	22	18	16	16	14	12	10				10
10	45	33	26	22	41	31	24	20	25	20	17	20	16	14	15	13	11	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17286	17286	17286
5°	17149	17297	17460
10°	17236	17365	17588
15°	17195	17366	17630
20°	17072	17481	17986
25°	16976	17701	18930
30°	16878	18060	19326
35°	16640	18112	19362
40°	16195	18080	17888
45°	15712	17262	13618
50°	15094	14724	11341
55°	14049	12391	8155
60°	12096	10634	5848
65°	10204	8214	5750
70°	8493	6463	5504
75°	7199	5577	5153
80°	6100	4844	4630
85°	4817	3983	2519

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 17262 cd/sqm



TEST NUMBER: P855126

CATALOG NUMBER: SQ2-PP3-125U-050D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	1.2
10°-20°	295.0	3.5
20°-30°	462.2	5.5
30°-40°	570.2	6.8
40°-50°	536.8	6.4
50°-60°	380.1	4.5
60°-70°	216.6	2.6
70°-80°	107.1	1.3
80°-90°	27.2	0.3
90°-100°	351.9	4.2
100°-110°	1145.7	13.7
110°-120°	1133.3	13.5
120°-130°	926.1	11.1
130°-140°	756.9	9.0
140°-150°	589.6	7.0
150°-160°	425.0	5.1
160°-170°	259.7	3.1
170°-180°	87.6	1.0
0°-30°	859.1	10.3
0°-40°	1429.3	17.1
0°-60°	2346.2	28.0
0°-90°	2697.1	32.2
90°-120°	2630.9	31.4
90°-150°	4903.5	58.6
90°-180°	5676.0	67.8
0°-180°	8372.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1071	1071	1071	1071	1071	
5°	1058	1077	1067	1070	1077	101
15°	1029	1043	1039	1049	1055	290
25°	953	977	994	1034	1063	439
35°	844	867	919	971	982	526
45°	688	740	756	641	596	530
55°	499	529	440	332	290	440
65°	267	281	215	152	150	268
75°	115	128	89	84	83	125
85°	26	24	22	17	14	30
90°	0	3	8	7	7	3
95°	48	145	645	230	142	55
105°	195	281	1135	2168	2053	208
115°	360	430	924	1905	2242	356
125°	500	558	912	1504	1773	445
135°	604	667	908	1298	1464	467
145°	706	758	905	1118	1224	442
155°	806	832	911	1001	1039	371
165°	879	887	913	947	958	248
175°	916	916	916	923	921	87
180°	920	920	920	920	920	



TEST NUMBER: P855126

CATALOG NUMBER: SQ2-PP3-125U-050D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1070.6	1070.6	1070.6	1070.6	1070.6
2.5°	1062.4	1077.5	1067.8	1069.6	1071.5
5°	1058.1	1076.9	1067.2	1069.6	1077.3
7.5°	1054.0	1073.3	1063.8	1067.8	1077.3
10°	1051.3	1068.0	1059.2	1065.1	1072.8
12.5°	1043.2	1058.9	1051.1	1058.7	1065.6
15°	1028.7	1043.1	1038.9	1049.2	1054.7
17.5°	1009.0	1026.5	1026.4	1041.0	1046.8
20°	993.6	1014.6	1017.4	1035.7	1046.8
22.5°	977.3	1001.9	1006.5	1034.1	1053.1
25°	952.9	977.2	993.6	1033.9	1062.6
27.5°	924.3	948.4	982.3	1027.4	1050.2
30°	905.3	928.5	968.7	1015.6	1036.6
32.5°	881.8	905.9	948.8	999.3	1018.5
35°	844.2	867.4	918.9	971.2	982.3
37.5°	801.0	827.4	885.0	914.2	914.8
40°	768.4	802.7	857.8	863.1	848.7
42.5°	736.7	780.7	819.8	795.9	732.0
45°	688.1	740.1	756.0	640.6	596.4
47.5°	636.2	687.6	662.2	537.3	506.8
50°	600.9	649.6	586.2	480.3	451.5
52.5°	561.1	604.4	518.3	425.6	381.8
55°	499.1	528.9	440.2	331.8	289.7
57.5°	424.4	445.4	376.4	249.1	201.9
60°	374.6	391.2	329.3	204.3	181.1
62.5°	329.3	344.1	280.4	177.4	169.3
65°	267.1	281.4	215.0	151.6	150.5
67.5°	212.5	228.3	165.0	132.4	131.0
70°	179.9	196.6	136.9	118.8	116.6
72.5°	152.8	168.5	116.1	104.3	103.0
75°	115.4	127.7	89.4	83.7	82.6
77.5°	83.7	91.4	66.5	63.6	62.5
80°	65.6	68.9	52.1	50.9	49.8
82.5°	49.3	48.2	39.4	38.3	36.2
85°	26.0	23.8	21.5	16.9	13.6
87.5°	8.1	8.8	5.2	4.1	4.1
90°	0.0	3.3	7.9	6.8	6.8
92.5°	16.3	58.5	187.2	61.7	47.5
95°	47.5	144.9	644.9	230.0	141.5
97.5°	89.4	188.5	1094.7	666.7	406.9
100°	116.6	213.9	1264.0	1127.0	730.9
102.5°	147.3	241.2	1243.1	1667.4	1267.8
105°	194.6	280.9	1134.9	2167.7	2052.6
107.5°	245.8	326.9	1032.2	2211.0	2333.0
110°	282.9	357.0	983.3	2157.2	2377.4



TEST NUMBER: P855126

CATALOG NUMBER: SQ2-PP3-125U-050D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.7	386.9	952.5	2060.0	2343.9
115°	359.9	429.6	924.5	1905.3	2241.6
117.5°	407.4	470.2	913.6	1763.5	2098.3
120°	434.6	496.5	910.9	1676.3	2000.6
122.5°	460.8	521.8	911.8	1600.7	1902.8
125°	500.1	557.7	912.0	1504.2	1773.1
127.5°	533.8	592.8	911.8	1432.0	1656.1
130°	555.5	615.3	910.9	1390.7	1590.9
132.5°	574.5	637.0	910.0	1352.3	1540.2
135°	604.2	667.3	907.5	1298.2	1464.3
137.5°	633.2	696.8	905.0	1243.2	1390.7
140°	654.0	714.9	904.1	1206.0	1345.4
142.5°	673.9	732.2	904.1	1170.4	1294.7
145°	706.0	758.1	905.2	1118.1	1224.3
147.5°	737.3	782.4	906.8	1073.6	1155.8
150°	758.1	797.9	908.6	1047.1	1116.8
152.5°	778.9	811.7	909.5	1026.9	1082.4
155°	805.6	832.2	910.9	1001.2	1038.8
157.5°	831.0	850.0	912.2	982.1	1008.4
160°	846.4	861.9	913.1	970.2	991.2
162.5°	860.0	871.9	913.1	960.1	975.8
165°	879.2	887.0	913.1	947.3	958.4
167.5°	892.8	897.6	913.4	937.7	943.5
170°	901.8	904.1	914.3	931.4	933.5
172.5°	908.2	909.5	916.1	927.6	927.2
175°	916.5	916.5	916.5	923.3	921.1
177.5°	919.9	919.0	918.1	922.5	919.0
180°	919.9	919.9	919.9	919.9	919.9



TEST NUMBER: P855126

CATALOG NUMBER: SQ2-PP3-125U-050D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.51	16.21	16.61	17.31	18.81	11.91	12.61	13.01	13.70	15.21
	3H	16.59	17.22	17.70	18.32	19.85	13.00	13.62	14.11	14.73	16.25
	4H	16.93	17.52	18.05	18.63	20.16	13.45	14.05	14.57	15.15	16.68
	6H	17.13	17.68	18.26	18.79	20.33	13.79	14.34	14.92	15.44	16.98
	8H	17.18	17.70	18.31	18.82	20.35	13.87	14.39	15.00	15.51	17.05
	12H	17.19	17.68	18.32	18.80	20.35	13.88	14.37	15.02	15.49	17.05
4H	2H	15.60	16.19	16.72	17.30	18.83	12.60	13.19	13.73	14.30	15.83
	3H	16.89	17.38	18.02	18.52	20.06	13.83	14.33	14.97	15.46	17.00
	4H	17.36	17.81	18.49	18.93	20.49	14.38	14.84	15.52	15.96	17.52
	6H	17.69	18.08	18.83	19.22	20.77	14.81	15.20	15.96	16.35	17.90
	8H	17.78	18.14	18.92	19.27	20.84	14.93	15.29	16.07	16.43	18.00
	12H	17.81	18.13	18.97	19.28	20.85	14.95	15.28	16.11	16.43	18.00
8H	4H	17.36	17.73	18.51	18.86	20.43	14.64	15.01	15.79	16.14	17.71
	6H	17.79	18.09	18.95	19.27	20.83	15.18	15.48	16.35	16.66	18.23
	8H	17.95	18.21	19.12	19.36	20.95	15.37	15.63	16.54	16.79	18.37
	12H	18.03	18.26	19.20	19.41	21.03	15.44	15.67	16.61	16.82	18.44
12H	4H	17.32	17.65	18.48	18.79	20.37	14.64	14.97	15.80	16.12	17.69
	6H	17.78	18.04	18.95	19.20	20.78	15.24	15.50	16.41	16.65	18.24
	8H	17.94	18.17	19.11	19.33	20.95	15.44	15.67	16.61	16.82	18.44