

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854475

Luminaire Tested: SQ2-WBN-125U-075D-930-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854475
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G3-2308-130-2)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-WBN-125U-075D-930-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7955.8 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.58 / 0.63
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 71.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854475
CATALOG NUMBER: SQ2-WBN-125U-075D-930-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854475

CATALOG NUMBER: SQ2-WBN-125U-075D-930-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40				
1	97	94	91	88	89	86	83	81	71	69	67	57	56	55	44	43	43	37				
2	90	84	79	75	82	77	73	70	64	61	59	52	50	49	41	40	39	34				
3	84	76	70	65	77	70	65	61	59	55	52	48	46	44	39	37	36	32				
4	78	69	63	58	71	64	58	54	54	50	47	45	42	40	36	35	33	30				
5	73	63	56	51	67	58	53	48	50	46	42	42	39	37	34	32	31	28				
6	68	58	51	46	62	54	48	44	46	42	39	39	36	34	32	30	29	26				
7	64	53	46	42	59	50	44	40	43	39	35	36	33	31	31	29	27	25				
8	60	49	43	38	55	46	40	36	40	36	33	34	31	29	29	27	25	23				
9	56	46	39	35	52	43	37	33	37	33	30	32	29	27	27	25	24	22				
10	53	43	36	32	49	40	35	31	35	31	28	31	27	25	26	24	23	21				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	87669	87669	87669
5°	84647	83804	84741
10°	73166	72818	73339
15°	58221	56386	56612
20°	41361	40814	41111
25°	29756	29172	28967
30°	22736	22124	22070
35°	17848	17542	17087
40°	13521	13340	12688
45°	7567	9040	6752
50°	2663	5564	2346
55°	1627	3037	1545
60°	1243	1586	1150
65°	1142	1177	1066
70°	1090	1090	1001
75°	1023	1023	961
80°	893	893	893
85°	889	722	722

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 9040 cd/sqm



TEST NUMBER: P854475

CATALOG NUMBER: SQ2-WBN-125U-075D-930-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	471.3	5.9
10°-20°	936.7	11.8
20°-30°	775.7	9.8
30°-40°	558.1	7.0
40°-50°	284.3	3.6
50°-60°	74.0	0.9
60°-70°	30.7	0.4
70°-80°	17.0	0.2
80°-90°	5.9	0.1
90°-100°	297.7	3.7
100°-110°	969.3	12.2
110°-120°	958.8	12.1
120°-130°	783.5	9.8
130°-140°	640.4	8.0
140°-150°	498.8	6.3
150°-160°	359.5	4.5
160°-170°	219.7	2.8
170°-180°	74.1	0.9
0°-30°	2183.8	27.4
0°-40°	2741.9	34.5
0°-60°	3100.2	39.0
0°-90°	3153.9	39.6
90°-120°	2225.8	28.0
90°-150°	4148.5	52.1
90°-180°	4802.0	60.4
0°-180°	7955.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5430	5430	5430	5430	5430	
5°	5223	5215	5171	5246	5228	471
15°	3483	3444	3373	3397	3387	946
25°	1670	1667	1638	1623	1626	786
35°	906	911	890	875	867	568
45°	331	381	396	368	296	265
55°	58	67	108	62	55	57
65°	30	31	31	29	28	30
75°	16	16	16	15	15	17
85°	5	5	4	5	4	5
90°	0	3	7	6	6	2
95°	40	123	546	194	120	47
105°	165	238	960	1834	1737	176
115°	304	363	782	1612	1896	301
125°	423	472	772	1273	1500	377
135°	511	565	768	1098	1239	395
145°	597	641	766	946	1036	374
155°	682	704	771	847	879	314
165°	744	750	772	802	811	209
175°	775	775	775	781	779	74
180°	778	778	778	778	778	



TEST NUMBER: P854475

CATALOG NUMBER: SQ2-WBN-125U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5429.8	5429.8	5429.8	5429.8	5429.8
2.5°	5421.3	5412.3	5360.5	5403.4	5392.8
5°	5222.7	5215.2	5170.7	5245.5	5228.5
7.5°	4812.6	4819.0	4792.9	4859.0	4840.9
10°	4462.7	4479.7	4441.5	4537.4	4473.3
12.5°	4076.7	4065.7	4039.3	4054.1	4018.7
15°	3483.1	3443.5	3373.3	3397.1	3386.8
17.5°	2805.6	2820.8	2759.9	2757.3	2745.6
20°	2407.2	2411.9	2375.4	2394.6	2392.7
22.5°	2086.6	2087.5	2040.9	2069.1	2052.1
25°	1670.3	1667.4	1637.5	1623.1	1626.0
27.5°	1369.7	1358.1	1335.4	1344.9	1337.9
30°	1219.5	1210.1	1186.7	1192.3	1183.8
32.5°	1084.6	1085.0	1061.1	1058.3	1052.1
35°	905.5	911.1	890.0	875.4	866.9
37.5°	745.6	750.8	733.0	711.7	704.5
40°	641.5	645.3	632.9	607.7	602.0
42.5°	528.2	544.1	531.9	508.1	495.7
45°	331.4	381.3	395.9	368.2	295.7
47.5°	167.6	236.7	282.4	208.6	137.4
50°	106.0	154.0	221.5	125.5	93.4
52.5°	81.3	106.0	176.9	92.6	74.9
55°	57.8	67.2	107.9	62.4	54.9
57.5°	44.7	50.0	64.5	47.3	42.6
60°	38.5	42.3	49.1	40.3	35.6
62.5°	34.7	36.9	39.9	34.3	32.6
65°	29.9	30.8	30.8	28.9	27.9
67.5°	25.4	26.4	26.2	25.2	24.3
70°	23.1	24.1	23.1	22.1	21.2
72.5°	20.0	21.0	20.0	19.8	18.9
75°	16.4	16.4	16.4	15.4	15.4
77.5°	12.7	12.9	11.9	11.9	11.2
80°	9.6	10.6	9.6	9.6	9.6
82.5°	8.1	8.3	7.3	7.3	7.3
85°	4.8	4.8	3.9	4.8	3.9
87.5°	1.5	2.1	2.9	2.7	2.7
90°	0.0	2.8	6.7	5.7	5.7
92.5°	13.8	49.5	158.3	52.2	40.2
95°	40.2	122.6	545.7	194.5	119.7
97.5°	75.6	159.5	926.1	564.0	344.2
100°	98.6	181.0	1069.3	953.5	618.4
102.5°	124.6	204.0	1051.7	1410.7	1072.6
105°	164.7	237.7	960.2	1833.9	1736.6
107.5°	207.9	276.6	873.3	1870.6	1973.8
110°	239.3	302.0	831.9	1825.0	2011.3



TEST NUMBER: P854475

CATALOG NUMBER: SQ2-WBN-125U-075D-930-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	265.4	327.3	805.9	1742.8	1983.0
115°	304.4	363.4	782.1	1611.9	1896.4
117.5°	344.6	397.8	772.9	1492.0	1775.2
120°	367.6	420.0	770.6	1418.3	1692.5
122.5°	389.8	441.5	771.4	1354.3	1609.8
125°	423.1	471.8	771.6	1272.6	1500.1
127.5°	451.7	501.5	771.4	1211.5	1401.1
130°	470.0	520.6	770.6	1176.5	1346.0
132.5°	486.1	538.9	769.9	1144.1	1303.1
135°	511.2	564.6	767.8	1098.3	1238.8
137.5°	535.7	589.4	765.7	1051.8	1176.5
140°	553.3	604.8	764.9	1020.3	1138.2
142.5°	570.2	619.4	764.9	990.1	1095.3
145°	597.4	641.4	765.8	945.9	1035.8
147.5°	623.8	662.0	767.2	908.3	977.8
150°	641.4	675.1	768.7	885.9	944.9
152.5°	659.0	686.7	769.5	868.8	915.8
155°	681.6	704.1	770.6	847.0	878.8
157.5°	703.0	719.1	771.8	830.9	853.1
160°	716.1	729.2	772.5	820.8	838.6
162.5°	727.6	737.7	772.5	812.3	825.6
165°	743.8	750.4	772.5	801.5	810.8
167.5°	755.3	759.4	772.7	793.3	798.2
170°	763.0	764.8	773.5	787.9	789.8
172.5°	768.3	769.5	775.0	784.8	784.4
175°	775.4	775.4	775.4	781.1	779.2
177.5°	778.3	777.5	776.8	780.5	777.5
180°	778.3	778.3	778.3	778.3	778.3



TEST NUMBER: P854475

CATALOG NUMBER: SQ2-WBN-125U-075D-930-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.34	1.98	2.41	3.03	4.46	0.95	1.59	2.02	2.64	4.07
	3H	2.38	2.95	3.47	4.02	5.46	1.94	2.52	3.03	3.58	5.02
	4H	2.81	3.35	3.90	4.41	5.86	2.36	2.91	3.46	3.97	5.42
	6H	3.12	3.61	4.22	4.68	6.14	2.69	3.19	3.79	4.26	5.72
	8H	3.21	3.68	4.32	4.77	6.22	2.79	3.26	3.90	4.35	5.80
	12H	3.28	3.72	4.38	4.80	6.27	2.84	3.29	3.95	4.36	5.84
4H	2H	1.55	2.09	2.65	3.16	4.61	1.22	1.76	2.32	2.82	4.27
	3H	2.85	3.29	3.95	4.39	5.85	2.46	2.91	3.56	4.00	5.46
	4H	3.41	3.82	4.52	4.90	6.39	3.02	3.43	4.12	4.51	5.99
	6H	3.86	4.21	4.98	5.32	6.79	3.47	3.82	4.59	4.93	6.40
	8H	4.02	4.34	5.13	5.44	6.93	3.63	3.96	4.74	5.05	6.54
	12H	4.12	4.41	5.25	5.52	7.02	3.71	4.01	4.84	5.12	6.61
8H	4H	3.55	3.88	4.67	4.97	6.46	3.20	3.52	4.31	4.62	6.11
	6H	4.14	4.40	5.27	5.54	7.03	3.78	4.05	4.91	5.19	6.67
	8H	4.38	4.62	5.52	5.74	7.24	4.03	4.26	5.16	5.38	6.89
	12H	4.57	4.77	5.71	5.89	7.43	4.19	4.40	5.33	5.51	7.06
12H	4H	3.52	3.82	4.65	4.93	6.42	3.18	3.47	4.31	4.58	6.08
	6H	4.16	4.39	5.30	5.51	7.02	3.82	4.05	4.96	5.17	6.68
	8H	4.43	4.63	5.57	5.75	7.30	4.09	4.29	5.23	5.40	6.95