

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853657

Luminaire Tested: SQ2-F-025U-050D-835-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853657
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-025U-050D-835-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3476.6 lumens
Efficiency: N/A
Efficacy: 138.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 25.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853657

CATALOG NUMBER: SQ2-F-025U-050D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853657

CATALOG NUMBER: SQ2-F-025U-050D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67		
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	62	60	56		
2	92	84	78	73	87	80	74	69	71	66	63	63	59	56	55	53	50	47		
3	84	74	66	60	79	70	63	58	62	57	52	55	51	47	49	46	43	39		
4	77	65	57	51	72	62	55	49	55	49	45	49	44	41	44	40	37	33		
5	70	58	50	44	66	55	48	42	50	43	38	44	39	35	39	35	32	29		
6	65	52	44	38	61	50	42	36	45	38	33	40	35	31	35	31	28	25		
7	60	47	39	33	56	45	37	32	40	34	30	36	31	27	32	28	25	22		
8	56	43	35	29	52	41	33	28	37	31	26	33	28	24	30	25	22	20		
9	52	39	32	26	49	37	30	25	34	28	24	31	25	22	27	23	20	18		
10	49	36	29	24	46	34	27	23	31	25	21	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13411	13411	13411
5°	13316	13353	13462
10°	13285	13321	13414
15°	13203	13242	13374
20°	13125	13144	13261
25°	13003	13003	13083
30°	12870	12870	12913
35°	12713	12670	12759
40°	12547	12499	12547
45°	12351	12300	12351
50°	12167	12052	12082
55°	11882	11851	11786
60°	11583	11512	11438
65°	11240	11110	10980
70°	10579	10523	10310
75°	9956	9744	9457
80°	8842	8629	8312
85°	7132	6502	6076

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 12426 cd/sqm



TEST NUMBER: P853657

CATALOG NUMBER: SQ2-F-025U-050D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	2.3
10°-20°	224.4	6.5
20°-30°	337.5	9.7
30°-40°	403.9	11.6
40°-50°	416.7	12.0
50°-60°	375.9	10.8
60°-70°	286.9	8.3
70°-80°	164.9	4.7
80°-90°	43.5	1.3
90°-100°	74.6	2.1
100°-110°	232.1	6.7
110°-120°	227.1	6.5
120°-130°	185.4	5.3
130°-140°	151.7	4.4
140°-150°	118.4	3.4
150°-160°	85.4	2.5
160°-170°	52.2	1.5
170°-180°	17.6	0.5
0°-30°	640.4	18.4
0°-40°	1044.3	30.0
0°-60°	1836.9	52.8
0°-90°	2332.2	67.1
90°-120°	533.8	15.4
90°-150°	989.2	28.5
90°-180°	1144.0	32.9
0°-180°	3476.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	831	831	831	831	831	
5°	822	833	824	825	831	78
15°	790	800	792	796	800	223
25°	730	738	730	731	734	336
35°	645	650	643	645	647	403
45°	541	544	539	540	541	417
55°	422	424	421	419	419	377
65°	294	293	291	289	287	289
75°	160	158	156	153	152	168
85°	38	36	35	32	33	45
90°	0	1	3	3	3	2
95°	10	30	137	50	33	12
105°	41	57	228	436	416	43
115°	72	86	186	383	448	71
125°	101	112	183	301	353	89
135°	121	134	182	260	292	94
145°	142	152	182	224	244	89
155°	162	167	183	202	208	75
165°	178	179	184	190	192	50
175°	184	184	184	186	184	17
180°	184	184	184	184	184	



TEST NUMBER: P853657

CATALOG NUMBER: SQ2-F-025U-050D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	830.6	830.6	830.6	830.6	830.6
2.5°	825.2	834.9	827.0	828.8	829.7
5°	821.6	832.7	823.9	825.1	830.6
7.5°	814.8	826.8	817.1	819.2	825.4
10°	810.3	821.4	812.5	813.8	818.2
12.5°	803.0	814.1	805.3	807.4	811.9
15°	789.9	799.9	792.2	795.7	800.1
17.5°	774.7	785.4	776.8	779.8	783.6
20°	763.9	772.7	765.0	766.2	771.8
22.5°	750.3	759.1	752.3	752.7	757.3
25°	729.9	737.6	729.9	731.2	734.4
27.5°	706.6	713.3	706.6	707.9	710.7
30°	690.3	697.0	690.3	691.4	692.6
32.5°	672.2	678.0	671.3	672.5	675.4
35°	645.0	649.5	642.8	645.0	647.3
37.5°	616.1	619.4	613.8	614.9	617.0
40°	595.3	598.5	593.0	594.1	595.3
42.5°	574.4	576.9	571.3	572.4	574.4
45°	540.9	544.2	538.7	539.8	540.9
47.5°	507.0	509.0	504.3	503.4	505.4
50°	484.4	485.5	479.8	479.8	481.0
52.5°	459.9	461.0	457.2	455.4	456.5
55°	422.1	424.4	421.0	418.7	418.7
57.5°	384.1	386.1	381.8	380.7	380.5
60°	358.7	359.9	356.5	355.3	354.2
62.5°	333.4	333.6	330.2	329.1	328.0
65°	294.2	293.1	290.8	288.6	287.4
67.5°	250.3	251.5	249.2	245.6	245.6
70°	224.1	225.2	222.9	218.4	218.4
72.5°	198.7	198.0	196.7	193.1	191.3
75°	159.6	158.4	156.2	152.8	151.6
77.5°	120.4	119.3	118.1	113.8	114.8
80°	95.1	93.9	92.8	89.4	89.4
82.5°	72.4	70.4	69.3	65.9	65.9
85°	38.5	36.2	35.1	31.7	32.8
87.5°	10.9	10.2	9.7	7.9	7.9
90°	0.0	1.1	3.4	3.4	3.4
92.5°	3.6	12.7	43.2	14.1	11.5
95°	10.2	30.1	136.9	50.5	32.8
97.5°	18.6	39.2	226.7	141.1	88.9
100°	24.9	43.7	255.6	239.1	159.6
102.5°	31.2	49.1	250.2	341.5	268.1
105°	40.7	57.4	228.5	436.3	416.3
107.5°	50.2	65.7	207.7	443.5	465.5
110°	56.6	72.1	196.8	433.1	476.3



TEST NUMBER: P853657

CATALOG NUMBER: SQ2-F-025U-050D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	62.9	77.5	191.4	414.4	469.1
115°	72.4	85.7	185.5	382.7	448.0
117.5°	81.7	93.8	183.0	352.4	419.3
120°	87.1	99.2	182.1	335.2	399.4
122.5°	92.6	104.7	183.0	320.6	379.4
125°	100.7	111.7	183.2	301.0	353.0
127.5°	107.3	118.5	183.2	286.3	330.6
130°	110.9	123.0	183.2	278.0	317.9
132.5°	115.4	127.5	182.3	270.8	307.9
135°	121.1	134.3	182.1	259.8	291.9
137.5°	127.7	139.8	182.1	248.9	278.0
140°	131.3	143.4	182.1	241.6	268.1
142.5°	135.8	147.0	182.1	234.3	258.1
145°	141.5	152.4	182.1	224.4	244.3
147.5°	148.2	157.8	183.2	215.4	231.0
150°	152.8	160.5	183.2	210.7	222.8
152.5°	156.4	163.2	183.2	206.1	216.5
155°	161.8	167.3	183.2	201.5	208.1
157.5°	167.3	171.4	183.2	197.4	201.5
160°	170.9	174.2	183.2	194.6	197.9
162.5°	173.5	176.0	183.2	192.8	195.2
165°	177.6	178.7	184.3	190.1	192.3
167.5°	180.0	180.3	183.2	188.5	189.6
170°	181.0	182.1	183.2	186.7	187.7
172.5°	182.8	183.0	184.1	185.8	185.9
175°	184.3	184.3	184.3	185.5	184.3
177.5°	184.3	184.3	184.3	184.3	184.3
180°	184.3	184.3	184.3	184.3	184.3



TEST NUMBER: P853657

CATALOG NUMBER: SQ2-F-025U-050D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.42	19.48	19.22	20.30	21.30	18.35	19.40	19.14	20.22	21.22
	3H	20.22	21.17	21.02	21.99	23.03	20.10	21.05	20.90	21.87	22.91
	4H	20.89	21.78	21.71	22.62	23.66	20.73	21.63	21.56	22.46	23.51
	6H	21.37	22.19	22.20	23.04	24.09	21.18	22.01	22.02	22.85	23.91
	8H	21.51	22.30	22.35	23.16	24.22	21.31	22.10	22.15	22.96	24.01
	12H	21.59	22.34	22.44	23.20	24.28	21.37	22.12	22.22	22.97	24.06
4H	2H	19.00	19.89	19.82	20.73	21.77	18.94	19.83	19.76	20.67	21.71
	3H	21.00	21.75	21.84	22.62	23.68	20.89	21.64	21.73	22.51	23.57
	4H	21.80	22.48	22.65	23.35	24.44	21.66	22.34	22.51	23.21	24.29
	6H	22.40	22.99	23.27	23.88	24.97	22.22	22.81	23.09	23.70	24.79
	8H	22.59	23.15	23.47	24.03	25.13	22.39	22.94	23.26	23.83	24.93
	12H	22.71	23.20	23.60	24.11	25.22	22.48	22.98	23.37	23.88	24.99
8H	4H	22.06	22.62	22.94	23.50	24.60	21.94	22.49	22.81	23.37	24.48
	6H	22.79	23.25	23.69	24.17	25.28	22.62	23.08	23.52	24.01	25.11
	8H	23.06	23.47	23.97	24.39	25.51	22.87	23.27	23.78	24.19	25.31
	12H	23.24	23.59	24.15	24.51	25.68	23.01	23.37	23.92	24.28	25.45
12H	4H	22.07	22.57	22.96	23.47	24.58	21.95	22.44	22.84	23.35	24.46
	6H	22.83	23.24	23.74	24.16	25.28	22.68	23.08	23.59	24.00	25.12
	8H	23.14	23.50	24.05	24.41	25.58	22.95	23.31	23.86	24.22	25.39