

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853681

Luminaire Tested: SQ2-F-075U-050D-835-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853681
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-075U-050D-835-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5716.1 lumens
Efficiency: N/A
Efficacy: 139.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 41.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853681
CATALOG NUMBER: SQ2-F-075U-050D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853681

CATALOG NUMBER: SQ2-F-075U-050D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	87	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	73	68	79	73	67	63	60	56	53	48	45	43	37	35	33	28
3	79	70	62	57	72	64	57	52	53	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	56	50	44	47	41	37	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	18
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	21	18	15
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	19	16	14
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	20	17	15	12
9	49	36	29	24	44	34	27	22	28	23	19	23	19	16	18	15	13	11
10	45	33	26	21	41	31	24	20	26	21	17	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13411	13411	13411
5°	13316	13353	13462
10°	13285	13321	13414
15°	13203	13242	13374
20°	13125	13144	13261
25°	13003	13003	13083
30°	12870	12870	12913
35°	12713	12670	12759
40°	12547	12499	12547
45°	12351	12300	12351
50°	12167	12052	12082
55°	11882	11851	11786
60°	11583	11512	11438
65°	11240	11110	10980
70°	10579	10523	10310
75°	9956	9744	9457
80°	8842	8629	8312
85°	7132	6502	6076

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 12426 cd/sqm



TEST NUMBER: P853681

CATALOG NUMBER: SQ2-F-075U-050D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	1.4
10°-20°	224.4	3.9
20°-30°	337.5	5.9
30°-40°	403.9	7.1
40°-50°	416.7	7.3
50°-60°	375.9	6.6
60°-70°	286.9	5.0
70°-80°	164.9	2.9
80°-90°	43.6	0.8
90°-100°	206.7	3.6
100°-110°	685.2	12.0
110°-120°	680.0	11.9
120°-130°	553.9	9.7
130°-140°	450.2	7.9
140°-150°	349.6	6.1
150°-160°	251.9	4.4
160°-170°	154.3	2.7
170°-180°	52.1	0.9
0°-30°	640.4	11.2
0°-40°	1044.3	18.3
0°-60°	1836.9	32.1
0°-90°	2332.3	40.8
90°-120°	1571.9	27.5
90°-150°	2925.6	51.2
90°-180°	3384.0	59.2
0°-180°	5716.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	831	831	831	831	831	
5°	822	833	824	825	831	78
15°	790	800	792	796	800	223
25°	730	738	730	731	734	336
35°	645	650	643	645	647	403
45°	541	544	539	540	541	417
55°	422	424	421	419	419	377
65°	294	293	291	289	287	289
75°	160	158	156	153	152	168
85°	38	36	35	32	33	45
90°	0	1	3	4	4	3
95°	29	87	375	134	89	34
105°	120	171	686	1294	1210	127
115°	214	256	552	1150	1344	211
125°	299	332	542	903	1065	266
135°	358	394	537	775	875	277
145°	415	446	536	667	730	261
155°	474	491	540	596	618	218
165°	520	526	542	564	569	147
175°	544	544	545	549	548	52
180°	546	546	546	546	546	



TEST NUMBER: P853681

CATALOG NUMBER: SQ2-F-075U-050D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	830.6	830.6	830.6	830.6	830.6
2.5°	825.2	834.9	827.0	828.8	829.7
5°	821.6	832.7	823.9	825.1	830.6
7.5°	814.8	826.8	817.1	819.2	825.4
10°	810.3	821.4	812.5	813.8	818.2
12.5°	803.0	814.1	805.3	807.4	811.9
15°	789.9	799.9	792.2	795.7	800.1
17.5°	774.7	785.4	776.8	779.8	783.6
20°	763.9	772.7	765.0	766.2	771.8
22.5°	750.3	759.1	752.3	752.7	757.3
25°	729.9	737.6	729.9	731.2	734.4
27.5°	706.6	713.3	706.6	707.9	710.7
30°	690.3	697.0	690.3	691.4	692.6
32.5°	672.2	678.0	671.3	672.5	675.4
35°	645.0	649.5	642.8	645.0	647.3
37.5°	616.1	619.4	613.8	614.9	617.0
40°	595.3	598.5	593.0	594.1	595.3
42.5°	574.4	576.9	571.3	572.4	574.4
45°	540.9	544.2	538.7	539.8	540.9
47.5°	507.0	509.0	504.3	503.4	505.4
50°	484.4	485.5	479.8	479.8	481.0
52.5°	459.9	461.0	457.2	455.4	456.5
55°	422.1	424.4	421.0	418.7	418.7
57.5°	384.1	386.1	381.8	380.7	380.5
60°	358.7	359.9	356.5	355.3	354.2
62.5°	333.4	333.6	330.2	329.1	328.0
65°	294.2	293.1	290.8	288.6	287.4
67.5°	250.3	251.5	249.2	245.6	245.6
70°	224.1	225.2	222.9	218.4	218.4
72.5°	198.7	198.0	196.7	193.1	191.3
75°	159.6	158.4	156.2	152.8	151.6
77.5°	120.4	119.3	118.1	113.8	114.8
80°	95.1	93.9	92.8	89.4	89.4
82.5°	72.4	70.4	69.3	65.9	65.9
85°	38.5	36.2	35.1	31.7	32.8
87.5°	10.9	10.2	9.7	8.1	8.1
90°	0.0	1.1	3.4	4.5	4.5
92.5°	9.1	35.0	103.0	33.4	28.1
95°	29.4	86.9	374.6	133.6	89.4
97.5°	54.1	114.3	653.8	381.3	241.0
100°	71.3	128.8	757.0	650.1	431.2
102.5°	90.3	146.1	750.6	993.6	750.6
105°	120.0	170.9	685.7	1293.7	1209.6
107.5°	150.3	195.7	623.4	1324.2	1388.1
110°	167.5	212.9	591.7	1294.1	1423.4



TEST NUMBER: P853681

CATALOG NUMBER: SQ2-F-075U-050D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	185.6	230.1	572.7	1240.5	1405.3
115°	213.9	255.9	552.1	1149.5	1344.3
117.5°	241.9	279.3	544.7	1062.6	1266.9
120°	259.2	295.6	542.0	1008.2	1206.2
122.5°	274.5	310.2	542.0	963.5	1146.5
125°	298.8	331.9	542.0	903.2	1064.8
127.5°	318.7	351.2	540.6	857.7	995.8
130°	330.4	364.7	539.7	831.1	955.0
132.5°	341.3	376.5	538.8	809.1	920.6
135°	357.6	394.0	537.4	775.1	874.7
137.5°	375.3	410.3	536.1	742.3	830.1
140°	387.0	421.3	535.2	720.3	801.1
142.5°	397.9	431.3	536.1	698.5	770.3
145°	415.3	446.2	536.3	666.8	729.8
147.5°	434.1	459.9	536.5	640.0	686.8
150°	445.9	469.1	537.4	624.3	664.2
152.5°	456.6	479.0	538.3	611.6	643.4
155°	474.1	490.7	539.7	595.7	617.8
157.5°	491.0	503.9	541.0	584.5	600.1
160°	500.1	511.2	542.0	576.2	588.4
162.5°	509.1	517.6	542.0	570.7	580.2
165°	520.5	526.0	542.0	563.6	569.1
167.5°	530.9	533.8	543.1	557.2	560.1
170°	536.3	537.4	543.1	554.5	555.5
172.5°	539.9	541.0	544.0	551.7	551.9
175°	544.2	544.2	545.3	548.7	547.6
177.5°	546.5	546.5	545.6	547.4	545.6
180°	546.5	546.5	546.5	546.5	546.5



TEST NUMBER: P853681

CATALOG NUMBER: SQ2-F-075U-050D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.08	16.87	17.11	17.91	19.31	16.00	16.79	17.03	17.83	19.23
	3H	17.85	18.56	18.89	19.61	21.03	17.73	18.44	18.77	19.49	20.91
	4H	18.51	19.18	19.56	20.23	21.66	18.36	19.03	19.41	20.08	21.50
	6H	18.97	19.60	20.04	20.65	22.08	18.79	19.41	19.85	20.46	21.90
	8H	19.11	19.70	20.18	20.77	22.20	18.91	19.50	19.97	20.57	22.00
	12H	19.18	19.74	20.25	20.81	22.26	18.96	19.52	20.03	20.58	22.04
4H	2H	16.62	17.29	17.68	18.34	19.77	16.56	17.23	17.62	18.28	19.70
	3H	18.60	19.16	19.67	20.24	21.68	18.49	19.06	19.56	20.13	21.57
	4H	19.39	19.90	20.46	20.97	22.43	19.24	19.76	20.32	20.83	22.29
	6H	19.97	20.42	21.06	21.51	22.96	19.79	20.24	20.87	21.33	22.78
	8H	20.16	20.57	21.24	21.66	23.13	19.96	20.37	21.04	21.46	22.92
	12H	20.26	20.63	21.36	21.73	23.20	20.03	20.41	21.13	21.50	22.98
8H	4H	19.63	20.04	20.71	21.13	22.60	19.50	19.92	20.59	21.00	22.47
	6H	20.34	20.69	21.45	21.81	23.28	20.18	20.52	21.28	21.65	23.11
	8H	20.61	20.91	21.72	22.02	23.50	20.42	20.72	21.53	21.83	23.31
	12H	20.78	21.04	21.89	22.14	23.67	20.55	20.81	21.66	21.92	23.44
12H	4H	19.62	19.99	20.72	21.09	22.56	19.50	19.87	20.60	20.97	22.44
	6H	20.39	20.69	21.50	21.80	23.28	20.23	20.53	21.34	21.64	23.12
	8H	20.68	20.94	21.79	22.04	23.57	20.49	20.75	21.61	21.86	23.38