

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853720

Luminaire Tested: SQ2-F-125U-075D-835-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853720
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-125U-075D-835-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9014.7 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 70.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853720
CATALOG NUMBER: SQ2-F-125U-075D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853720

CATALOG NUMBER: SQ2-F-125U-075D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	49	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	51	46	43	41	34	33	31	26
3	79	69	62	56	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	61	53	47	65	56	49	44	45	40	36	36	32	29	27	25	23	19
5	66	54	46	40	59	50	43	37	40	35	31	32	28	25	24	22	20	16
6	60	49	41	35	55	44	37	32	36	31	27	29	25	22	22	19	17	14
7	56	44	36	30	50	40	33	28	33	28	24	26	22	19	20	17	15	12
8	52	40	32	27	47	36	29	25	30	25	21	24	20	17	18	16	14	11
9	48	36	29	24	43	33	26	22	27	22	19	22	18	15	17	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19346	19346	19346
5°	19209	19263	19420
10°	19164	19218	19351
15°	19047	19102	19293
20°	18933	18962	19129
25°	18759	18759	18875
30°	18567	18567	18627
35°	18343	18277	18404
40°	18099	18029	18099
45°	17817	17744	17817
50°	17550	17384	17427
55°	17140	17095	17005
60°	16711	16604	16498
65°	16218	16027	15840
70°	15257	15182	14875
75°	14361	14055	13649
80°	12757	12450	11994
85°	10282	9374	8762

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 17927 cd/sqm



TEST NUMBER: P853720

CATALOG NUMBER: SQ2-F-125U-075D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.3	1.3
10°-20°	323.6	3.6
20°-30°	486.9	5.4
30°-40°	582.6	6.5
40°-50°	601.1	6.7
50°-60°	542.3	6.0
60°-70°	413.8	4.6
70°-80°	237.9	2.6
80°-90°	63.1	0.7
90°-100°	350.3	3.9
100°-110°	1140.4	12.7
110°-120°	1128.1	12.5
120°-130°	921.9	10.2
130°-140°	753.5	8.4
140°-150°	586.9	6.5
150°-160°	423.0	4.7
160°-170°	258.6	2.9
170°-180°	87.2	1.0
0°-30°	923.8	10.2
0°-40°	1506.5	16.7
0°-60°	2649.9	29.4
0°-90°	3364.7	37.3
90°-120°	2618.8	29.1
90°-150°	4881.1	54.1
90°-180°	5650.0	62.7
0°-180°	9014.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1198	1198	1198	1198	1198	
5°	1185	1201	1188	1190	1198	113
15°	1140	1154	1143	1148	1154	321
25°	1053	1064	1053	1055	1060	485
35°	931	937	927	931	934	582
45°	780	785	777	779	780	602
55°	609	612	607	604	604	544
65°	424	423	420	416	415	417
75°	230	229	225	220	219	243
85°	56	52	51	46	47	64
90°	0	3	8	7	7	4
95°	47	144	642	229	141	55
105°	194	280	1130	2158	2043	207
115°	358	428	920	1897	2231	355
125°	498	555	908	1497	1765	443
135°	602	664	903	1292	1458	465
145°	703	755	901	1113	1219	440
155°	802	828	907	996	1034	369
165°	875	883	909	943	954	246
175°	912	912	912	919	917	87
180°	916	916	916	916	916	



TEST NUMBER: P853720

CATALOG NUMBER: SQ2-F-125U-075D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1198.2	1198.2	1198.2	1198.2	1198.2
2.5°	1190.4	1204.4	1193.0	1195.7	1197.0
5°	1185.2	1201.1	1188.5	1190.3	1198.2
7.5°	1175.3	1192.7	1178.6	1181.8	1190.7
10°	1168.9	1184.9	1172.2	1173.9	1180.3
12.5°	1158.4	1174.4	1161.7	1164.8	1171.2
15°	1139.5	1153.8	1142.8	1147.8	1154.2
17.5°	1117.6	1132.9	1120.6	1124.9	1130.3
20°	1101.9	1114.7	1103.6	1105.4	1113.3
22.5°	1082.3	1095.1	1085.3	1085.7	1092.5
25°	1053.0	1064.1	1053.0	1054.7	1059.5
27.5°	1019.3	1028.9	1019.3	1021.1	1025.2
30°	995.9	1005.4	995.9	997.4	999.1
32.5°	969.7	978.0	968.4	970.2	974.2
35°	930.6	936.9	927.3	930.6	933.7
37.5°	888.7	893.6	885.4	887.1	890.1
40°	858.7	863.5	855.4	857.1	858.7
42.5°	828.6	832.2	824.1	825.8	828.6
45°	780.3	785.1	777.1	778.7	780.3
47.5°	731.4	734.2	727.4	726.2	729.1
50°	698.7	700.3	692.1	692.2	693.8
52.5°	663.5	665.1	659.5	656.9	658.5
55°	608.9	612.1	607.3	604.1	604.1
57.5°	554.1	556.9	550.8	549.2	548.9
60°	517.5	519.1	514.2	512.5	510.9
62.5°	481.0	481.3	476.3	474.7	473.1
65°	424.5	422.9	419.5	416.2	414.6
67.5°	361.1	362.7	359.5	354.2	354.2
70°	323.2	324.8	321.6	315.1	315.1
72.5°	286.7	285.7	283.7	278.5	275.9
75°	230.2	228.6	225.3	220.3	218.8
77.5°	173.7	172.1	170.4	164.2	165.6
80°	137.2	135.6	133.9	129.0	129.0
82.5°	104.5	101.6	99.9	95.1	95.1
85°	55.5	52.3	50.6	45.7	47.3
87.5°	15.6	15.1	14.6	11.8	11.8
90°	0.0	3.3	7.9	6.8	6.8
92.5°	16.2	58.3	186.3	61.4	47.3
95°	47.3	144.2	642.0	228.9	140.8
97.5°	88.9	187.6	1089.7	663.6	405.0
100°	116.0	213.0	1258.2	1121.9	727.7
102.5°	146.7	240.0	1237.5	1659.8	1262.0
105°	193.7	279.6	1129.7	2157.7	2043.2
107.5°	244.7	325.5	1027.4	2201.0	2322.4
110°	281.6	355.3	978.8	2147.3	2366.5



TEST NUMBER: P853720

CATALOG NUMBER: SQ2-F-125U-075D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	312.2	385.1	948.2	2050.6	2333.2
115°	358.2	427.5	920.3	1896.6	2231.3
117.5°	405.5	468.1	909.4	1755.4	2088.7
120°	432.5	494.2	906.7	1668.8	1991.4
122.5°	458.7	519.4	907.6	1593.5	1894.1
125°	497.8	555.1	907.8	1497.4	1765.1
127.5°	531.4	590.0	907.6	1425.4	1648.6
130°	553.0	612.6	906.7	1384.4	1583.7
132.5°	571.9	634.1	905.8	1346.2	1533.2
135°	601.5	664.3	903.4	1292.4	1457.6
137.5°	630.3	693.5	900.9	1237.6	1384.4
140°	651.0	711.6	900.0	1200.5	1339.2
142.5°	670.9	728.8	900.0	1165.0	1288.9
145°	702.9	754.6	901.1	1113.0	1218.7
147.5°	734.0	778.9	902.7	1068.7	1150.4
150°	754.7	794.3	904.4	1042.4	1111.7
152.5°	775.4	808.0	905.3	1022.2	1077.5
155°	802.0	828.4	906.7	996.5	1034.0
157.5°	827.2	846.1	908.0	977.6	1003.8
160°	842.5	857.9	909.0	965.8	986.7
162.5°	856.0	868.0	909.0	955.8	971.4
165°	875.2	882.9	909.0	943.0	954.0
167.5°	888.7	893.6	909.2	933.4	939.2
170°	897.7	899.9	910.1	927.1	929.2
172.5°	904.1	905.3	911.9	923.4	923.0
175°	912.3	912.3	912.3	919.0	916.9
177.5°	915.7	914.8	913.9	918.3	914.8
180°	915.7	915.7	915.7	915.7	915.7



TEST NUMBER: P853720

CATALOG NUMBER: SQ2-F-125U-075D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.97	17.73	18.02	18.79	20.23	16.89	17.65	17.94	18.71	20.16
	3H	18.74	19.43	19.81	20.50	21.96	18.62	19.31	19.69	20.38	21.84
	4H	19.39	20.04	20.47	21.12	22.58	19.24	19.89	20.32	20.96	22.43
	6H	19.86	20.46	20.95	21.53	23.01	19.67	20.27	20.76	21.35	22.83
	8H	19.99	20.56	21.09	21.66	23.13	19.79	20.36	20.88	21.45	22.93
	12H	20.06	20.61	21.16	21.69	23.19	19.84	20.38	20.94	21.47	22.96
4H	2H	17.51	18.16	18.59	19.23	20.69	17.44	18.09	18.53	19.17	20.63
	3H	19.48	20.03	20.58	21.13	22.61	19.38	19.92	20.47	21.02	22.50
	4H	20.27	20.77	21.37	21.86	23.36	20.13	20.63	21.22	21.72	23.21
	6H	20.85	21.28	21.96	22.40	23.89	20.67	21.10	21.78	22.22	23.71
	8H	21.04	21.44	22.14	22.54	24.05	20.84	21.24	21.94	22.34	23.85
	12H	21.14	21.50	22.26	22.62	24.13	20.91	21.27	22.03	22.39	23.90
8H	4H	20.51	20.91	21.61	22.01	23.52	20.38	20.78	21.49	21.89	23.40
	6H	21.22	21.55	22.35	22.70	24.21	21.06	21.39	22.18	22.53	24.04
	8H	21.49	21.78	22.62	22.91	24.43	21.30	21.59	22.43	22.71	24.24
	12H	21.65	21.91	22.79	23.03	24.59	21.42	21.68	22.56	22.80	24.37
12H	4H	20.50	20.86	21.62	21.98	23.49	20.38	20.74	21.50	21.86	23.37
	6H	21.27	21.56	22.40	22.68	24.21	21.11	21.40	22.24	22.52	24.05
	8H	21.55	21.81	22.69	22.93	24.49	21.37	21.62	22.50	22.75	24.31