

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853717

Luminaire Tested: SQ2-F-125U-050D-935-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P853717  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-F-125U-050D-935-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7076.9 lumens  
Efficiency: N/A  
Efficacy: 114.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 61.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853717  
CATALOG NUMBER: SQ2-F-125U-050D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853717

CATALOG NUMBER: SQ2-F-125U-050D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29
1	93	89	85	82	83	80	77	74	63	60	59	47	46	44	32	32	31	24
2	85	77	71	66	76	70	64	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	46	63	54	47	42	43	38	34	32	29	26	22	20	19	15
5	64	53	45	39	57	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	17	14	13	10
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	25	21	25	21	17	20	16	14	14	12	10	8
10	44	32	25	20	39	29	23	19	23	19	16	18	15	12	13	11	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11851	11851	11851
5°	11767	11799	11896
10°	11739	11772	11854
15°	11667	11701	11818
20°	11598	11615	11718
25°	11491	11491	11562
30°	11373	11373	11410
35°	11235	11196	11274
40°	11086	11044	11086
45°	10914	10869	10914
50°	10751	10650	10675
55°	10500	10472	10415
60°	10236	10172	10107
65°	9933	9819	9704
70°	9347	9300	9111
75°	8796	8609	8359
80°	7810	7624	7345
85°	6299	5743	5372

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 10981 cd/sqm



TEST NUMBER: P853717

CATALOG NUMBER: SQ2-F-125U-050D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.4	1.0
10°-20°	198.2	2.8
20°-30°	298.3	4.2
30°-40°	356.9	5.0
40°-50°	368.2	5.2
50°-60°	332.2	4.7
60°-70°	253.5	3.6
70°-80°	145.7	2.1
80°-90°	38.9	0.5
90°-100°	311.0	4.4
100°-110°	1012.4	14.3
110°-120°	1001.4	14.2
120°-130°	818.4	11.6
130°-140°	668.9	9.5
140°-150°	521.0	7.4
150°-160°	375.5	5.3
160°-170°	229.5	3.2
170°-180°	77.4	1.1
0°-30°	565.9	8.0
0°-40°	922.8	13.0
0°-60°	1623.2	22.9
0°-90°	2061.4	29.1
90°-120°	2324.8	32.9
90°-150°	4333.0	61.2
90°-180°	5015.0	70.9
0°-180°	7076.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	734	734	734	734	734	
5°	726	736	728	729	734	69
15°	698	707	700	703	707	197
25°	645	652	645	646	649	297
35°	570	574	568	570	572	356
45°	478	481	476	477	478	369
55°	373	375	372	370	370	333
65°	260	259	257	255	254	256
75°	141	140	138	135	134	149
85°	34	32	31	28	29	39
90°	0	3	7	6	6	3
95°	42	128	570	203	125	49
105°	172	248	1003	1916	1814	183
115°	318	380	817	1684	1981	315
125°	442	493	806	1329	1567	393
135°	534	590	802	1147	1294	412
145°	624	670	800	988	1082	391
155°	712	735	805	885	918	328
165°	777	784	807	837	847	219
175°	810	810	810	816	814	77
180°	813	813	813	813	813	



TEST NUMBER: P853717

CATALOG NUMBER: SQ2-F-125U-050D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	734.0	734.0	734.0	734.0	734.0
2.5°	729.2	737.8	730.8	732.4	733.2
5°	726.0	735.8	728.0	729.1	734.0
7.5°	720.0	730.6	722.0	723.9	729.4
10°	716.0	725.8	718.0	719.1	723.0
12.5°	709.6	719.4	711.6	713.5	717.4
15°	698.0	706.8	700.0	703.1	707.0
17.5°	684.6	694.0	686.4	689.1	692.4
20°	675.0	682.8	676.0	677.1	682.0
22.5°	663.0	670.8	664.8	665.1	669.2
25°	645.0	651.8	645.0	646.1	649.0
27.5°	624.4	630.3	624.4	625.5	628.0
30°	610.0	615.9	610.0	611.0	612.0
32.5°	594.0	599.1	593.2	594.3	596.8
35°	570.0	573.9	568.0	570.0	572.0
37.5°	544.4	547.3	542.4	543.4	545.2
40°	526.0	528.9	524.0	525.0	526.0
42.5°	507.6	509.8	504.8	505.8	507.6
45°	478.0	480.9	476.0	477.0	478.0
47.5°	448.0	449.8	445.6	444.8	446.6
50°	428.0	429.0	424.0	424.0	425.0
52.5°	406.4	407.4	404.0	402.4	403.4
55°	373.0	375.0	372.0	370.0	370.0
57.5°	339.4	341.2	337.4	336.4	336.2
60°	317.0	318.0	315.0	314.0	313.0
62.5°	294.6	294.8	291.8	290.8	289.8
65°	260.0	259.0	257.0	255.0	254.0
67.5°	221.2	222.2	220.2	217.0	217.0
70°	198.0	199.0	197.0	193.0	193.0
72.5°	175.6	175.0	173.8	170.6	169.0
75°	141.0	140.0	138.0	135.0	134.0
77.5°	106.4	105.4	104.4	100.6	101.4
80°	84.0	83.0	82.0	79.0	79.0
82.5°	64.0	62.2	61.2	58.2	58.2
85°	34.0	32.0	31.0	28.0	29.0
87.5°	9.6	9.4	9.4	7.6	7.6
90°	0.0	2.9	7.0	6.0	6.0
92.5°	14.4	51.7	165.4	54.5	42.0
95°	42.0	128.0	569.9	203.2	125.0
97.5°	79.0	166.6	967.3	589.1	359.6
100°	103.0	189.0	1116.9	995.9	645.9
102.5°	130.2	213.1	1098.5	1473.4	1120.3
105°	172.0	248.2	1002.9	1915.5	1813.8
107.5°	217.2	288.9	912.1	1953.8	2061.6
110°	250.0	315.5	868.9	1906.2	2100.8



TEST NUMBER: P853717

CATALOG NUMBER: SQ2-F-125U-050D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	277.2	341.9	841.7	1820.3	2071.2
115°	318.0	379.6	816.9	1683.6	1980.8
117.5°	360.0	415.5	807.3	1558.3	1854.2
120°	384.0	438.7	804.9	1481.3	1767.8
122.5°	407.2	461.1	805.7	1414.5	1681.4
125°	441.9	492.8	805.9	1329.2	1566.8
127.5°	471.7	523.8	805.7	1265.4	1463.4
130°	490.9	543.7	804.9	1228.9	1405.8
132.5°	507.7	562.9	804.1	1195.0	1361.0
135°	533.9	589.7	801.9	1147.2	1293.9
137.5°	559.5	615.7	799.7	1098.6	1228.9
140°	577.9	631.7	798.9	1065.7	1188.9
142.5°	595.5	647.0	798.9	1034.2	1144.1
145°	623.9	669.9	799.9	988.0	1081.9
147.5°	651.5	691.4	801.3	948.7	1021.3
150°	669.9	705.1	802.9	925.3	986.9
152.5°	688.3	717.3	803.7	907.4	956.5
155°	711.9	735.4	804.9	884.7	917.9
157.5°	734.3	751.1	806.1	867.8	891.1
160°	747.9	761.6	806.9	857.3	875.9
162.5°	759.9	770.5	806.9	848.4	862.3
165°	776.9	783.8	806.9	837.1	846.9
167.5°	788.9	793.2	807.1	828.6	833.7
170°	796.9	798.9	807.9	823.0	824.9
172.5°	802.5	803.7	809.5	819.7	819.3
175°	809.9	809.9	809.9	815.9	813.9
177.5°	812.9	812.1	811.3	815.2	812.1
180°	812.9	812.9	812.9	812.9	812.9

TEST NUMBER: P853717

CATALOG NUMBER: SQ2-F-125U-050D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.23	14.94	15.35	16.05	17.59	14.15	14.86	15.27	15.97	17.51
	3H	16.00	16.63	17.13	17.75	19.31	15.88	16.51	17.01	17.63	19.19
	4H	16.65	17.25	17.79	18.37	19.94	16.50	17.10	17.63	18.22	19.78
	6H	17.11	17.67	18.26	18.79	20.36	16.93	17.48	18.07	18.61	20.18
	8H	17.25	17.77	18.39	18.91	20.48	17.05	17.57	18.19	18.71	20.28
	12H	17.32	17.82	18.47	18.95	20.54	17.09	17.59	18.24	18.73	20.31
4H	2H	14.76	15.37	15.91	16.49	18.05	14.70	15.30	15.84	16.42	17.99
	3H	16.74	17.24	17.89	18.39	19.96	16.63	17.13	17.78	18.28	19.85
	4H	17.52	17.98	18.67	19.12	20.71	17.38	17.84	18.53	18.97	20.57
	6H	18.10	18.50	19.26	19.66	21.24	17.92	18.32	19.08	19.48	21.06
	8H	18.29	18.65	19.44	19.80	21.41	18.08	18.45	19.24	19.60	21.20
	12H	18.38	18.71	19.55	19.88	21.48	18.15	18.49	19.32	19.65	21.25
8H	4H	17.76	18.12	18.91	19.27	20.88	17.63	18.00	18.78	19.15	20.75
	6H	18.47	18.77	19.64	19.96	21.56	18.30	18.60	19.48	19.80	21.39
	8H	18.73	19.00	19.91	20.17	21.79	18.54	18.80	19.72	19.97	21.59
	12H	18.89	19.13	20.08	20.29	21.94	18.66	18.90	19.85	20.07	21.72
12H	4H	17.74	18.08	18.91	19.24	20.84	17.62	17.96	18.79	19.12	20.72
	6H	18.51	18.77	19.69	19.94	21.56	18.35	18.61	19.53	19.79	21.40
	8H	18.79	19.03	19.98	20.19	21.85	18.61	18.84	19.79	20.01	21.66