

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855165

Luminaire Tested: SQ2-PH1-075U-075D-835-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855165
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PH1-075U-075D-835-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7164.1 lumens
Efficiency: N/A
Efficacy: 143.3 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 50
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855165
CATALOG NUMBER: SQ2-PH1-075U-075D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855165

CATALOG NUMBER: SQ2-PH1-075U-075D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53				
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50	45				
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38				
3	82	73	65	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32				
4	75	64	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28				
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	33	30	27	24				
6	64	52	43	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21				
7	59	47	39	33	54	44	36	31	38	32	28	33	28	25	28	24	21	19				
8	55	42	35	29	51	40	33	28	35	29	25	30	25	22	25	22	19	17				
9	51	39	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15				
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27703	27703	27703
5°	27861	26195	25321
10°	27220	23846	23017
15°	27343	22430	22567
20°	26366	21739	22747
25°	25883	21638	22219
30°	25322	21580	22400
35°	25131	21333	26256
40°	25151	21195	20818
45°	25160	20390	17931
50°	24810	20791	16814
55°	24493	22565	16130
60°	24251	19769	15129
65°	23828	16027	13161
70°	22504	13638	9404
75°	20062	10287	7130
80°	16392	6685	6685
85°	10282	6058	4520

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25160 cd/sqm



TEST NUMBER: P855165

CATALOG NUMBER: SQ2-PH1-075U-075D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.0	2.1
10°-20°	397.1	5.5
20°-30°	582.3	8.1
30°-40°	705.1	9.8
40°-50°	693.5	9.7
50°-60°	603.7	8.4
60°-70°	419.7	5.9
70°-80°	199.0	2.8
80°-90°	44.4	0.6
90°-100°	205.8	2.9
100°-110°	682.1	9.5
110°-120°	676.9	9.4
120°-130°	551.4	7.7
130°-140°	448.1	6.3
140°-150°	348.0	4.9
150°-160°	250.7	3.5
160°-170°	153.6	2.1
170°-180°	51.9	0.7
0°-30°	1130.4	15.8
0°-40°	1835.5	25.6
0°-60°	3132.6	43.7
0°-90°	3795.6	53.0
90°-120°	1564.8	21.8
90°-150°	2912.3	40.7
90°-180°	3368.0	47.0
0°-180°	7164.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1716	1716	1716	1716	1716	
5°	1719	1717	1616	1566	1562	162
15°	1636	1457	1342	1332	1350	456
25°	1453	1236	1215	1252	1247	668
35°	1275	1031	1082	1176	1332	799
45°	1102	816	893	924	785	847
55°	870	635	802	578	573	777
65°	624	437	420	344	344	613
75°	322	223	165	118	114	341
85°	56	36	33	26	24	74
90°	0	1	3	4	4	3
95°	29	87	373	133	89	34
105°	119	170	683	1288	1204	126
115°	213	255	550	1144	1338	210
125°	297	330	540	899	1060	264
135°	356	392	535	772	871	275
145°	413	444	534	664	726	259
155°	472	488	537	593	615	217
165°	518	524	540	561	566	146
175°	542	542	543	546	545	51
180°	544	544	544	544	544	



TEST NUMBER: P855165

CATALOG NUMBER: SQ2-PH1-075U-075D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1715.8	1715.8	1715.8	1715.8	1715.8
2.5°	1711.9	1729.7	1689.7	1674.0	1671.4
5°	1719.0	1717.4	1616.2	1565.5	1562.3
7.5°	1687.7	1638.2	1517.2	1461.3	1458.8
10°	1660.3	1585.2	1454.5	1403.9	1403.9
12.5°	1653.7	1535.3	1403.6	1366.3	1374.0
15°	1635.8	1457.0	1341.9	1332.5	1350.1
17.5°	1576.4	1383.8	1293.9	1315.3	1335.7
20°	1534.5	1344.6	1265.2	1304.8	1323.9
22.5°	1499.3	1306.8	1244.3	1287.6	1297.9
25°	1452.9	1235.9	1214.6	1252.1	1247.2
27.5°	1397.4	1170.8	1184.9	1207.8	1210.7
30°	1358.2	1131.6	1157.5	1180.8	1201.5
32.5°	1320.4	1086.1	1127.4	1182.7	1230.2
35°	1275.0	1030.7	1082.3	1175.7	1332.1
37.5°	1227.3	965.5	1036.9	1115.5	1165.3
40°	1193.3	918.8	1005.6	1102.6	987.7
42.5°	1156.8	882.2	958.6	1083.8	889.7
45°	1101.9	816.3	893.0	924.1	785.3
47.5°	1037.3	765.0	848.6	770.7	716.3
50°	987.7	730.7	827.7	704.5	669.4
52.5°	939.4	695.2	813.3	649.8	626.3
55°	870.1	635.4	801.6	577.8	573.0
57.5°	796.7	574.8	708.9	515.1	523.4
60°	751.0	535.5	612.2	478.1	468.5
62.5°	702.7	497.4	522.0	431.1	421.5
65°	623.7	436.8	419.5	344.5	344.5
67.5°	536.7	373.9	339.8	281.9	243.5
70°	476.7	333.0	288.9	224.7	199.2
72.5°	412.7	289.5	236.7	184.1	154.8
75°	321.6	222.6	164.9	117.5	114.3
77.5°	232.4	160.4	111.0	87.1	87.5
80°	176.3	122.0	71.9	70.3	71.9
82.5°	124.0	83.9	53.5	55.8	56.1
85°	55.5	36.3	32.7	26.0	24.4
87.5°	11.8	10.8	7.2	7.5	7.5
90°	0.0	1.1	3.4	4.5	4.5
92.5°	9.1	34.7	102.5	33.3	28.0
95°	29.3	86.6	372.9	133.1	88.9
97.5°	53.9	113.7	650.8	379.6	239.9
100°	71.0	128.2	753.6	647.2	429.1
102.5°	89.9	145.4	747.2	989.1	747.2
105°	119.4	170.1	682.6	1287.8	1204.1
107.5°	149.6	194.8	620.6	1318.2	1381.9
110°	166.7	211.8	589.1	1288.1	1417.0



TEST NUMBER: P855165

CATALOG NUMBER: SQ2-PH1-075U-075D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	184.7	229.0	570.1	1234.9	1399.0
115°	212.9	254.7	549.6	1144.3	1338.1
117.5°	240.8	278.0	542.2	1057.8	1261.1
120°	257.9	294.2	539.6	1003.6	1200.7
122.5°	273.3	308.7	539.6	959.1	1141.3
125°	297.4	330.4	539.6	899.1	1059.9
127.5°	317.2	349.6	538.2	853.7	991.2
130°	328.9	363.0	537.3	827.2	950.6
132.5°	339.7	374.7	536.4	805.4	916.4
135°	355.9	392.2	535.1	771.6	870.7
137.5°	373.4	408.5	533.7	738.9	826.3
140°	385.2	419.4	532.8	717.0	797.5
142.5°	396.1	429.2	533.7	695.3	766.8
145°	413.4	444.2	533.9	663.7	726.5
147.5°	432.1	457.9	534.1	637.0	683.8
150°	443.8	466.9	535.1	621.5	661.2
152.5°	454.6	476.9	536.0	608.7	640.4
155°	471.9	488.4	537.3	593.0	614.9
157.5°	488.9	501.7	538.7	581.8	597.4
160°	497.8	508.9	539.6	573.6	585.7
162.5°	506.9	515.2	539.6	568.1	577.6
165°	518.1	523.6	539.6	561.1	566.5
167.5°	528.5	531.3	540.7	554.7	557.6
170°	533.9	535.1	540.7	551.9	553.0
172.5°	537.5	538.6	541.5	549.2	549.4
175°	541.7	541.7	542.9	546.3	545.1
177.5°	544.0	544.0	543.1	544.9	543.1
180°	544.0	544.0	544.0	544.0	544.0



TEST NUMBER: P855165

CATALOG NUMBER: SQ2-PH1-075U-075D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.14	20.02	20.07	20.97	22.20	17.81	18.69	18.75	19.64	20.87
	3H	21.17	21.96	22.11	22.91	24.17	18.85	19.64	19.79	20.60	21.85
	4H	21.90	22.64	22.86	23.61	24.87	19.06	19.81	20.02	20.77	22.03
	6H	22.39	23.07	23.36	24.04	25.31	19.21	19.90	20.18	20.86	22.14
	8H	22.51	23.16	23.49	24.15	25.42	19.24	19.90	20.22	20.88	22.15
	12H	22.56	23.18	23.54	24.16	25.45	19.24	19.86	20.22	20.84	22.14
4H	2H	19.52	20.26	20.48	21.23	22.49	18.46	19.20	19.42	20.17	21.43
	3H	21.63	22.25	22.60	23.24	24.51	19.64	20.26	20.61	21.25	22.53
	4H	22.44	23.01	23.43	23.99	25.29	19.92	20.48	20.90	21.47	22.77
	6H	23.03	23.51	24.02	24.52	25.82	20.12	20.61	21.12	21.62	22.92
	8H	23.20	23.65	24.20	24.66	25.97	20.18	20.64	21.18	21.64	22.95
	12H	23.27	23.68	24.28	24.70	26.01	20.19	20.60	21.21	21.62	22.94
8H	4H	22.46	22.92	23.46	23.92	25.23	20.13	20.59	21.13	21.59	22.90
	6H	23.11	23.49	24.14	24.53	25.84	20.41	20.78	21.43	21.83	23.14
	8H	23.34	23.67	24.37	24.70	26.03	20.51	20.84	21.54	21.87	23.20
	12H	23.45	23.74	24.49	24.77	26.14	20.55	20.84	21.59	21.87	23.24
12H	4H	22.41	22.82	23.43	23.84	25.16	20.13	20.54	21.15	21.56	22.88
	6H	23.09	23.42	24.12	24.45	25.78	20.44	20.77	21.47	21.80	23.13
	8H	23.32	23.61	24.36	24.64	26.01	20.55	20.84	21.59	21.87	23.24