

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853852

Luminaire Tested: SQ2-FB-075U-075D-935-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853852
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-075U-075D-935-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5942.0 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 50
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853852
CATALOG NUMBER: SQ2-FB-075U-075D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853852

CATALOG NUMBER: SQ2-FB-075U-075D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	42				
2	89	81	75	69	81	75	69	65	63	59	56	53	50	47	43	41	39	34				
3	80	71	63	57	74	65	59	53	55	50	46	46	42	39	38	35	33	28				
4	73	62	54	48	67	58	50	45	49	43	39	41	37	33	33	30	28	24				
5	67	55	47	41	61	51	44	38	43	38	33	36	32	28	30	26	24	20				
6	62	49	41	35	56	46	38	33	39	33	29	32	28	24	27	23	20	18				
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18	15				
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16	13				
9	49	36	28	23	45	34	27	22	29	23	19	24	20	17	20	17	14	12				
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4845	4845	4845
5°	4723	6546	8580
10°	4423	12677	16698
15°	4003	16493	19218
20°	3545	18144	20127
25°	3135	19402	20457
30°	2770	19982	20709
35°	2474	20329	22263
40°	2251	20523	23655
45°	2076	20621	24770
50°	1957	21017	25219
55°	1909	21562	25422
60°	1957	21849	25294
65°	2040	21547	24581
70°	2110	20837	18590
75°	2339	18721	10262
80°	2417	9661	9521
85°	2408	6688	4001

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 25650 cd/sqm



TEST NUMBER: P853852

CATALOG NUMBER: SQ2-FB-075U-075D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	0.8
10°-20°	229.5	3.9
20°-30°	403.7	6.8
30°-40°	522.6	8.8
40°-50°	576.4	9.7
50°-60°	538.2	9.1
60°-70°	415.9	7.0
70°-80°	191.8	3.2
80°-90°	37.1	0.6
90°-100°	181.8	3.1
100°-110°	602.7	10.1
110°-120°	598.2	10.1
120°-130°	487.2	8.2
130°-140°	396.0	6.7
140°-150°	307.5	5.2
150°-160°	221.6	3.7
160°-170°	135.7	2.3
170°-180°	45.8	0.8
0°-30°	683.5	11.5
0°-40°	1206.1	20.3
0°-60°	2320.6	39.1
0°-90°	2965.5	49.9
90°-120°	1382.7	23.3
90°-150°	2573.4	43.3
90°-180°	2977.0	50.1
0°-180°	5942.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	300	300	300	300	300	
5°	291	334	404	493	529	27
15°	240	472	987	1105	1150	67
25°	176	634	1089	1137	1148	81
35°	126	612	1031	1068	1130	79
45°	91	469	903	1037	1085	70
55°	68	279	766	880	903	61
65°	53	158	564	632	643	52
75°	38	97	300	162	164	38
85°	13	28	36	24	22	14
90°	0	1	3	4	4	2
95°	26	76	330	118	79	30
105°	106	150	603	1138	1064	111
115°	188	225	486	1011	1182	186
125°	263	292	477	794	937	234
135°	314	347	473	682	769	243
145°	365	392	472	586	642	229
155°	417	432	475	524	543	192
165°	458	463	477	496	501	129
175°	479	479	480	483	482	45
180°	481	481	481	481	481	



TEST NUMBER: P853852

CATALOG NUMBER: SQ2-FB-075U-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	300.1	300.1	300.1	300.1	300.1
2.5°	297.7	310.2	324.3	340.6	347.4
5°	291.4	333.7	403.9	492.8	529.4
7.5°	280.1	366.2	587.4	825.1	898.4
10°	269.8	389.7	773.2	979.0	1018.5
12.5°	258.2	421.0	889.8	1034.4	1075.0
15°	239.5	472.2	986.7	1104.6	1149.7
17.5°	220.1	529.9	1031.7	1148.0	1172.5
20°	206.3	570.2	1056.0	1155.9	1171.4
22.5°	193.6	600.4	1073.3	1149.0	1165.6
25°	176.0	634.4	1089.1	1137.0	1148.3
27.5°	159.0	643.3	1082.2	1113.6	1124.6
30°	148.6	640.9	1071.8	1095.3	1110.8
32.5°	139.4	633.9	1056.8	1079.5	1113.1
35°	125.5	612.1	1031.4	1067.5	1129.5
37.5°	113.7	577.2	998.0	1071.8	1131.6
40°	106.8	551.1	973.7	1071.5	1122.3
42.5°	99.8	520.4	946.0	1060.0	1110.8
45°	90.9	468.9	903.1	1036.9	1084.8
47.5°	82.5	410.9	863.2	1004.8	1039.8
50°	77.9	371.3	836.7	975.8	1004.0
52.5°	73.3	332.8	810.2	941.2	967.1
55°	67.8	279.4	766.0	880.5	903.1
57.5°	62.9	233.6	715.8	813.5	831.8
60°	60.6	208.7	676.6	765.0	783.3
62.5°	57.1	186.0	632.7	714.2	731.4
65°	53.4	157.8	564.0	632.1	643.4
67.5°	48.2	136.8	491.1	532.7	511.5
70°	44.7	126.5	441.4	454.5	393.8
72.5°	42.4	115.2	387.2	352.8	238.0
75°	37.5	96.7	300.1	161.6	164.5
77.5°	30.6	74.9	197.3	124.1	126.7
80°	26.0	61.2	103.9	101.0	102.4
82.5°	21.4	47.6	71.6	74.4	72.4
85°	13.0	28.5	36.1	24.5	21.6
87.5°	4.6	10.5	6.4	6.6	6.6
90°	0.0	1.0	3.0	4.0	4.0
92.5°	8.0	30.7	90.6	29.4	24.7
95°	25.9	76.5	329.5	117.6	78.6
97.5°	47.6	100.5	575.1	335.4	212.0
100°	62.7	113.3	665.9	571.9	379.2
102.5°	79.4	128.5	660.3	874.0	660.3
105°	105.5	150.3	603.2	1138.0	1064.0
107.5°	132.2	172.1	548.4	1164.8	1221.1
110°	147.3	187.2	520.6	1138.2	1252.1



TEST NUMBER: P853852

CATALOG NUMBER: SQ2-FB-075U-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	163.2	202.4	503.8	1091.2	1236.2
115°	188.1	225.1	485.7	1011.2	1182.4
117.5°	212.8	245.7	479.1	934.7	1114.4
120°	227.9	260.0	476.8	886.8	1061.0
122.5°	241.5	272.8	476.8	847.5	1008.5
125°	262.8	292.0	476.8	794.5	936.6
127.5°	280.3	308.9	475.6	754.4	875.9
130°	290.6	320.8	474.8	731.0	840.0
132.5°	300.2	331.1	474.0	711.7	809.8
135°	314.5	346.6	472.8	681.8	769.4
137.5°	330.0	361.0	471.6	652.9	730.2
140°	340.4	370.6	470.8	633.6	704.7
142.5°	350.0	379.3	471.6	614.4	677.6
145°	365.3	392.5	471.8	586.5	642.0
147.5°	381.8	404.6	472.0	562.9	604.2
150°	392.2	412.6	472.8	549.2	584.3
152.5°	401.7	421.4	473.6	537.9	565.9
155°	417.0	431.6	474.8	524.0	543.4
157.5°	432.0	443.3	476.0	514.1	527.9
160°	439.9	449.7	476.8	506.9	517.6
162.5°	447.9	455.3	476.8	502.0	510.4
165°	457.8	462.7	476.8	495.8	500.6
167.5°	467.0	469.5	477.8	490.2	492.7
170°	471.8	472.8	477.8	487.7	488.7
172.5°	475.0	475.9	478.5	485.3	485.5
175°	478.7	478.7	479.7	482.7	481.7
177.5°	480.7	480.7	479.9	481.5	479.9
180°	480.7	480.7	480.7	480.7	480.7



TEST NUMBER: P853852

CATALOG NUMBER: SQ2-FB-075U-075D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.54	13.42	13.49	14.40	15.67	21.27	22.16	22.23	23.13	24.40
	3H	13.27	14.07	14.23	15.05	16.34	22.90	23.69	23.86	24.67	25.97
	4H	13.57	14.32	14.55	15.31	16.61	23.08	23.83	24.06	24.82	26.12
	6H	13.79	14.48	14.78	15.47	16.79	23.17	23.86	24.16	24.85	26.17
	8H	13.85	14.51	14.84	15.52	16.83	23.17	23.83	24.17	24.84	26.15
	12H	13.88	14.51	14.88	15.51	16.84	23.14	23.77	24.15	24.77	26.11
4H	2H	16.94	17.69	17.92	18.68	19.98	21.72	22.47	22.70	23.46	24.76
	3H	17.87	18.50	18.87	19.52	20.83	23.55	24.18	24.54	25.19	26.51
	4H	18.16	18.73	19.16	19.74	21.08	23.79	24.36	24.79	25.37	26.71
	6H	18.29	18.79	19.31	19.82	21.15	23.93	24.43	24.95	25.46	26.79
	8H	18.31	18.77	19.33	19.80	21.15	23.96	24.42	24.98	25.44	26.80
	12H	18.31	18.72	19.34	19.76	21.12	23.93	24.35	24.97	25.39	26.75
8H	4H	19.34	19.80	20.35	20.82	22.17	23.91	24.37	24.92	25.39	26.74
	6H	19.57	19.95	20.62	21.02	22.37	24.11	24.49	25.16	25.56	26.91
	8H	19.65	19.98	20.70	21.03	22.40	24.18	24.51	25.22	25.56	26.93
	12H	19.67	19.97	20.73	21.01	22.42	24.17	24.46	25.22	25.51	26.92
12H	4H	19.36	19.77	20.39	20.81	22.17	23.86	24.28	24.90	25.32	26.67
	6H	19.67	20.00	20.72	21.06	22.42	24.10	24.43	25.15	25.48	26.85
	8H	19.77	20.07	20.83	21.11	22.53	24.17	24.46	25.22	25.51	26.92