

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855150

Luminaire Tested: SQ2-PH1-150U-050D-835-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855150
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-14, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PH1-150U-050D-835-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9427.7 lumens
Efficiency: N/A
Efficacy: 126.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 74.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855150
CATALOG NUMBER: SQ2-PH1-150U-050D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855150

CATALOG NUMBER: SQ2-PH1-150U-050D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	85	82	83	80	77	74	62	60	58	46	45	44	32	31	30	24				
2	85	78	72	67	76	70	65	61	55	51	48	41	39	37	28	27	26	20				
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17				
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	15				
5	65	54	46	40	58	48	42	37	38	33	30	29	26	23	20	18	16	13				
6	59	48	40	35	53	43	36	32	34	29	26	26	23	20	18	16	14	11				
7	55	43	35	30	49	39	32	28	31	26	23	24	20	18	17	14	13	10				
8	51	39	32	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9				
9	47	35	28	23	42	32	26	22	26	21	18	20	16	14	14	12	10	8				
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19204	19204	19204
5°	19313	18157	17553
10°	18869	16531	15956
15°	18954	15549	15644
20°	18278	15069	15770
25°	17943	15000	15403
30°	17553	14958	15528
35°	17420	14789	18201
40°	17435	14693	14431
45°	17443	14134	12428
50°	17199	14413	11655
55°	16980	15640	11181
60°	16811	13705	10488
65°	16516	11110	9123
70°	15597	9456	6519
75°	13905	7130	4941
80°	11362	4630	4630
85°	7132	4187	3149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17443 cd/sqm



TEST NUMBER: P855150

CATALOG NUMBER: SQ2-PH1-150U-050D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.7	1.1
10°-20°	275.3	2.9
20°-30°	403.6	4.3
30°-40°	488.8	5.2
40°-50°	480.7	5.1
50°-60°	418.5	4.4
60°-70°	290.9	3.1
70°-80°	137.9	1.5
80°-90°	31.6	0.3
90°-100°	419.5	4.4
100°-110°	1373.7	14.6
110°-120°	1358.1	14.4
120°-130°	1110.2	11.8
130°-140°	906.0	9.6
140°-150°	705.1	7.5
150°-160°	507.7	5.4
160°-170°	310.6	3.3
170°-180°	104.9	1.1
0°-30°	783.6	8.3
0°-40°	1272.4	13.5
0°-60°	2171.6	23.0
0°-90°	2632.0	27.9
90°-120°	3151.3	33.4
90°-150°	5872.5	62.3
90°-180°	6796.0	72.1
0°-180°	9427.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1189	1189	1189	1189	1189	
5°	1192	1190	1120	1085	1083	112
15°	1134	1010	930	924	936	316
25°	1007	857	842	868	865	463
35°	884	714	750	815	923	554
45°	764	566	619	641	544	587
55°	603	441	556	400	397	539
65°	432	303	291	239	239	425
75°	223	154	114	82	79	236
85°	38	25	23	18	17	52
90°	1	3	9	8	9	4
95°	59	170	763	272	176	67
105°	239	340	1364	2591	2461	252
115°	430	514	1108	2289	2688	425
125°	599	667	1092	1805	2121	533
135°	721	797	1083	1557	1755	558
145°	843	905	1081	1339	1468	528
155°	961	993	1087	1198	1245	442
165°	1049	1059	1092	1134	1146	296
175°	1096	1096	1098	1106	1103	104
180°	1101	1101	1101	1101	1101	



TEST NUMBER: P855150

CATALOG NUMBER: SQ2-PH1-150U-050D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1189.4	1189.4	1189.4	1189.4	1189.4
2.5°	1186.7	1199.1	1171.3	1160.4	1158.6
5°	1191.6	1190.5	1120.3	1085.3	1083.0
7.5°	1169.9	1135.6	1051.8	1013.1	1011.3
10°	1150.9	1099.0	1008.3	973.2	973.2
12.5°	1146.4	1064.3	973.0	947.1	952.4
15°	1133.9	1010.0	930.2	923.8	935.9
17.5°	1092.7	959.3	897.0	911.8	925.9
20°	1063.8	932.2	877.0	904.5	917.8
22.5°	1039.3	905.9	862.6	892.5	899.7
25°	1007.2	856.7	842.0	867.9	864.6
27.5°	968.7	811.6	821.4	837.2	839.2
30°	941.5	784.5	802.3	818.5	832.9
32.5°	915.3	752.9	781.5	819.9	852.8
35°	883.8	714.5	750.3	815.0	923.4
37.5°	850.8	669.3	718.8	773.3	807.8
40°	827.2	636.9	697.1	764.3	684.7
42.5°	801.9	611.6	664.5	751.3	616.8
45°	763.9	565.8	619.0	640.6	544.3
47.5°	719.1	530.3	588.2	534.1	496.6
50°	684.7	506.5	573.8	488.3	464.0
52.5°	651.2	481.9	563.8	450.5	434.1
55°	603.2	440.6	555.6	400.5	397.2
57.5°	552.3	398.5	491.4	357.0	362.8
60°	520.6	371.2	424.4	331.5	324.8
62.5°	487.1	344.8	361.9	298.9	292.2
65°	432.3	302.8	290.8	238.8	238.8
67.5°	372.1	259.3	235.6	195.4	168.8
70°	330.4	230.9	200.3	155.7	138.1
72.5°	286.1	200.6	164.1	127.7	107.3
75°	222.9	154.4	114.3	81.5	79.2
77.5°	161.1	111.1	77.0	60.4	60.7
80°	122.2	84.6	49.8	48.7	49.8
82.5°	86.0	58.2	37.1	38.7	38.9
85°	38.5	25.2	22.6	18.1	17.0
87.5°	8.4	7.9	6.3	6.1	6.3
90°	1.1	3.4	9.1	7.9	9.1
92.5°	19.2	70.2	215.5	70.0	56.1
95°	58.8	170.5	762.7	271.7	176.5
97.5°	106.8	225.0	1308.5	791.6	490.7
100°	140.3	253.2	1514.1	1352.1	896.2
102.5°	178.4	288.6	1491.4	1992.3	1544.4
105°	238.8	340.5	1363.5	2590.6	2461.1
107.5°	298.3	391.7	1238.8	2646.6	2788.9
110°	337.2	428.0	1179.1	2581.4	2845.9



TEST NUMBER: P855150

CATALOG NUMBER: SQ2-PH1-150U-050D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.4	462.4	1142.9	2468.2	2807.0
115°	430.0	514.1	1107.8	2289.2	2687.5
117.5°	484.1	562.7	1094.4	2113.3	2517.7
120°	519.4	593.6	1090.8	2010.7	2404.6
122.5°	551.1	623.4	1090.8	1922.2	2287.9
125°	598.7	667.2	1091.9	1805.2	2120.6
127.5°	638.9	708.8	1090.6	1719.0	1993.4
130°	664.3	735.0	1089.7	1666.8	1914.7
132.5°	686.9	759.5	1087.0	1621.9	1846.8
135°	720.9	797.1	1082.9	1557.1	1755.1
137.5°	756.6	832.2	1080.4	1489.4	1668.4
140°	781.9	855.0	1079.5	1446.6	1615.9
142.5°	807.2	875.9	1079.5	1401.0	1554.3
145°	843.0	905.0	1080.6	1339.3	1467.7
147.5°	880.5	932.2	1082.2	1285.7	1382.6
150°	904.1	949.5	1084.0	1254.6	1336.4
152.5°	927.6	967.7	1084.9	1228.9	1296.5
155°	960.7	992.8	1087.4	1198.3	1244.7
157.5°	990.3	1013.6	1089.9	1174.2	1207.8
160°	1009.3	1028.2	1090.8	1160.5	1187.0
162.5°	1025.6	1040.9	1090.8	1149.4	1168.9
165°	1048.9	1058.9	1091.9	1134.2	1146.3
167.5°	1068.6	1073.5	1093.3	1122.3	1128.8
170°	1079.5	1081.8	1094.2	1115.8	1118.0
172.5°	1087.6	1089.0	1096.9	1111.2	1111.6
175°	1096.5	1096.5	1097.6	1105.5	1103.3
177.5°	1101.0	1100.1	1099.2	1104.6	1101.0
180°	1101.0	1101.0	1101.0	1101.0	1101.0



TEST NUMBER: P855150

CATALOG NUMBER: SQ2-PH1-150U-050D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.09	15.78	16.21	16.89	18.45	13.76	14.45	14.89	15.57	17.12
	3H	17.10	17.71	18.23	18.84	20.41	14.78	15.40	15.92	16.52	18.09
	4H	17.82	18.41	18.97	19.53	21.11	14.99	15.57	16.13	16.70	18.27
	6H	18.30	18.83	19.45	19.96	21.55	15.12	15.66	16.27	16.79	18.38
	8H	18.42	18.93	19.57	20.07	21.65	15.15	15.66	16.30	16.80	18.39
	12H	18.46	18.94	19.62	20.08	21.68	15.14	15.63	16.30	16.76	18.37
4H	2H	15.44	16.03	16.59	17.15	18.73	14.38	14.96	15.53	16.09	17.67
	3H	17.53	18.02	18.69	19.17	20.76	15.54	16.03	16.70	17.18	18.77
	4H	18.34	18.79	19.50	19.93	21.54	15.81	16.26	16.97	17.40	19.01
	6H	18.91	19.30	20.08	20.46	22.06	16.01	16.39	17.17	17.56	19.15
	8H	19.08	19.44	20.24	20.59	22.21	16.06	16.42	17.23	17.57	19.19
	12H	19.14	19.46	20.32	20.63	22.25	16.06	16.38	17.24	17.55	19.17
8H	4H	18.34	18.70	19.51	19.85	21.47	16.01	16.37	17.18	17.53	19.14
	6H	18.99	19.28	20.17	20.48	22.09	16.28	16.57	17.46	17.77	19.38
	8H	19.21	19.47	20.40	20.64	22.28	16.38	16.64	17.57	17.81	19.44
	12H	19.32	19.54	20.51	20.71	22.38	16.42	16.64	17.61	17.81	19.48
12H	4H	18.28	18.61	19.47	19.78	21.40	16.00	16.32	17.18	17.49	19.11
	6H	18.96	19.21	20.15	20.39	22.02	16.31	16.56	17.50	17.74	19.37
	8H	19.18	19.41	20.38	20.58	22.25	16.41	16.64	17.61	17.81	19.48