

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855105

Luminaire Tested: SQ2-PR1-0U-075D-835-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P855105  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PR1-0U-075D-835-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3852.7 lumens  
Efficiency: N/A  
Efficacy: 144.3 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P855105

CATALOG NUMBER: SQ2-PR1-0U-075D-835-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P855105

CATALOG NUMBER: SQ2-PR1-OU-075D-835-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	90	89	87				
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77	75				
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67	65				
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52	50				
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				
7	69	56	48	42	67	55	47	42	54	47	42	52	46	41	51	45	41	39				
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35				
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	25858	25858	25858
5°	25825	25982	26300
10°	26096	26765	27166
15°	26088	26223	26444
20°	25667	26060	26928
25°	25593	26320	28035
30°	25568	26905	28305
35°	25324	27480	26355
40°	24740	26460	23191
45°	23409	23222	18338
50°	21283	18985	14230
55°	18702	15626	11077
60°	16185	12494	9122
65°	13967	10353	7985
70°	12562	9172	7091
75°	11510	7941	6519
80°	10014	6378	6378
85°	7262	5743	3020

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 25304 cd/sqm

TEST NUMBER: P855105

CATALOG NUMBER: SQ2-PR1-OU-075D-835-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.7	4.0
10°-20°	447.7	11.6
20°-30°	692.0	18.0
30°-40°	832.4	21.6
40°-50°	747.4	19.4
50°-60°	500.7	13.0
60°-70°	291.3	7.6
70°-80°	149.6	3.9
80°-90°	36.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1294.4	33.6
0°-40°	2126.8	55.2
0°-60°	3374.9	87.6
0°-90°	3852.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3852.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1602	1602	1602	1602	1602	
5°	1593	1620	1603	1607	1623	152
15°	1561	1624	1569	1574	1582	438
25°	1437	1494	1477	1532	1574	663
35°	1285	1296	1394	1367	1337	801
45°	1025	1108	1017	858	803	784
55°	664	690	555	429	394	597
65°	366	374	271	220	209	370
75°	184	180	127	108	104	196
85°	39	31	31	21	16	50
90°	0	0	0	0	0	



TEST NUMBER: P855105

CATALOG NUMBER: SQ2-PR1-OU-075D-835-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1601.5	1601.5	1601.5	1601.5	1601.5
2.5°	1595.0	1614.1	1596.3	1597.7	1601.5
5°	1593.4	1620.4	1603.1	1606.7	1622.7
7.5°	1593.0	1631.6	1623.4	1633.3	1654.4
10°	1591.7	1638.0	1632.5	1634.7	1657.0
12.5°	1583.9	1637.9	1613.0	1610.9	1623.0
15°	1560.7	1624.5	1568.8	1573.9	1582.0
17.5°	1519.8	1586.6	1533.6	1551.6	1567.2
20°	1493.8	1559.2	1516.7	1540.1	1567.2
22.5°	1470.3	1535.7	1500.9	1533.7	1571.1
25°	1436.6	1494.0	1477.4	1532.3	1573.7
27.5°	1401.3	1435.2	1454.9	1528.4	1557.4
30°	1371.4	1393.6	1443.1	1507.0	1518.2
32.5°	1338.6	1352.1	1427.5	1460.8	1446.4
35°	1284.8	1296.0	1394.2	1367.4	1337.1
37.5°	1220.8	1243.8	1319.4	1242.2	1207.4
40°	1173.8	1212.1	1255.4	1140.3	1100.3
42.5°	1116.3	1177.6	1170.5	1023.8	974.9
45°	1025.2	1108.2	1017.0	857.5	803.1
47.5°	917.8	1003.0	853.8	711.3	660.6
50°	847.3	916.0	755.8	622.3	566.5
52.5°	775.4	825.0	672.3	538.9	488.1
55°	664.4	690.0	555.1	428.6	393.5
57.5°	562.6	578.8	453.5	346.2	320.3
60°	501.2	512.3	386.9	303.2	282.5
62.5°	445.0	453.7	333.4	266.7	251.1
65°	365.6	373.7	271.0	220.1	209.0
67.5°	302.7	306.8	223.1	182.9	172.4
70°	266.1	267.8	194.3	158.2	150.2
72.5°	233.5	231.2	166.8	137.4	132.0
75°	184.5	179.7	127.3	107.6	104.5
77.5°	137.8	132.6	89.5	83.0	83.0
80°	107.7	101.4	68.6	68.6	68.6
82.5°	80.3	71.4	52.8	52.8	51.6
85°	39.2	31.2	31.0	21.2	16.3
87.5°	10.4	10.4	4.0	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P855105

CATALOG NUMBER: SQ2-PR1-OU-075D-835-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.00	23.50	22.37	23.81	24.13	18.73	20.22	19.09	20.54	20.85
	3H	23.28	24.62	23.66	24.95	25.31	19.84	21.18	20.22	21.51	21.87
	4H	23.76	25.02	24.16	25.37	25.74	20.27	21.52	20.67	21.87	22.25
	6H	24.11	25.27	24.52	25.63	26.03	20.63	21.79	21.04	22.15	22.55
	8H	24.21	25.31	24.64	25.70	26.10	20.73	21.83	21.16	22.22	22.62
	12H	24.26	25.31	24.69	25.69	26.12	20.76	21.81	21.19	22.19	22.62
4H	2H	22.16	23.41	22.56	23.76	24.14	19.37	20.62	19.77	20.97	21.35
	3H	23.69	24.72	24.10	25.12	25.52	20.70	21.73	21.11	22.13	22.53
	4H	24.30	25.23	24.74	25.65	26.09	21.22	22.15	21.66	22.57	23.01
	6H	24.79	25.59	25.25	26.04	26.50	21.69	22.50	22.15	22.94	23.40
	8H	24.93	25.68	25.39	26.13	26.60	21.83	22.58	22.29	23.02	23.49
	12H	25.01	25.68	25.49	26.16	26.63	21.87	22.55	22.36	23.03	23.50
8H	4H	24.37	25.12	24.84	25.57	26.04	21.57	22.33	22.04	22.77	23.24
	6H	24.94	25.56	25.44	26.05	26.53	22.13	22.75	22.63	23.24	23.72
	8H	25.14	25.70	25.65	26.21	26.70	22.31	22.87	22.83	23.38	23.87
	12H	25.27	25.76	25.78	26.26	26.82	22.40	22.90	22.91	23.39	23.96
12H	4H	24.36	25.03	24.84	25.51	25.98	21.62	22.29	22.10	22.77	23.24
	6H	24.93	25.49	25.44	26.00	26.49	22.19	22.75	22.70	23.26	23.75
	8H	25.16	25.66	25.67	26.15	26.72	22.42	22.92	22.93	23.41	23.98