

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854215

Luminaire Tested: SQ2-PR1-100U-100D-935-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P854215  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PR1-100U-100D-935-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8505.9 lumens  
Efficiency: N/A  
Efficacy: 121.2 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 70.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854215

CATALOG NUMBER: SQ2-PR1-100U-100D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854215

CATALOG NUMBER: SQ2-PR1-100U-100D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60	54	54	54	54	
1	99	95	92	88	92	89	85	83	76	74	72	64	63	61	54	53	52	47	47	47	47	
2	91	84	78	73	84	78	73	69	67	64	60	57	55	52	48	46	45	40	40	40	40	
3	83	74	67	62	77	69	63	58	60	55	51	51	48	45	43	41	39	35	35	35	35	
4	77	66	59	53	71	62	55	50	54	48	44	46	42	39	39	36	34	30	30	30	30	
5	70	59	51	46	65	55	48	43	48	43	39	42	37	34	35	32	30	27	27	27	27	
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	24	24	24	24	
7	60	48	41	35	56	45	38	33	40	34	30	34	30	27	30	26	24	21	21	21	21	
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21	19	19	19	19	
9	52	40	33	28	49	38	31	27	33	28	24	29	25	22	25	22	19	17	17	17	17	
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	16	16	16	16	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	30721	30721	30721
5°	30681	30870	31246
10°	31004	31800	32277
15°	30994	31156	31415
20°	30493	30960	31993
25°	30407	31271	33309
30°	30374	31966	33629
35°	30086	32648	31310
40°	29392	31436	27554
45°	27811	27590	21790
50°	25284	22556	16905
55°	22221	18565	13157
60°	19226	14844	10834
65°	16600	12302	9486
70°	14922	10895	8422
75°	13674	9439	7742
80°	11901	7578	7578
85°	8614	6836	3594

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 30065 cd/sqm



TEST NUMBER: P854215

CATALOG NUMBER: SQ2-PR1-100U-100D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.7	2.2
10°-20°	531.9	6.3
20°-30°	822.2	9.7
30°-40°	988.9	11.6
40°-50°	888.0	10.4
50°-60°	594.9	7.0
60°-70°	346.0	4.1
70°-80°	177.7	2.1
80°-90°	45.0	0.5
90°-100°	263.6	3.1
100°-110°	797.1	9.4
110°-120°	778.2	9.1
120°-130°	635.9	7.5
130°-140°	519.0	6.1
140°-150°	404.0	4.8
150°-160°	291.3	3.4
160°-170°	178.3	2.1
170°-180°	60.2	0.7
0°-30°	1537.8	18.1
0°-40°	2526.8	29.7
0°-60°	4009.6	47.1
0°-90°	4578.3	53.8
90°-120°	1838.8	21.6
90°-150°	3397.8	39.9
90°-180°	3928.0	46.2
0°-180°	8505.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1903	1903	1903	1903	1903	
5°	1893	1925	1905	1909	1928	181
15°	1854	1930	1864	1870	1879	521
25°	1707	1775	1755	1820	1870	787
35°	1526	1540	1656	1624	1588	952
45°	1218	1317	1208	1019	954	932
55°	789	820	660	509	467	709
65°	434	444	322	262	248	439
75°	219	214	151	128	124	233
85°	46	37	37	25	19	58
90°	0	2	12	7	6	3
95°	33	103	497	184	116	39
105°	139	195	783	1486	1413	146
115°	247	294	633	1310	1539	244
125°	345	382	624	1034	1218	306
135°	413	457	620	892	1004	320
145°	482	518	620	767	839	302
155°	550	568	624	688	714	253
165°	601	608	627	651	659	169
175°	629	629	630	635	633	60
180°	631	631	631	631	631	

TEST NUMBER: P854215

CATALOG NUMBER: SQ2-PR1-100U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1902.7	1902.7	1902.7	1902.7	1902.7
2.5°	1895.0	1917.7	1896.5	1898.2	1902.7
5°	1893.0	1925.3	1904.7	1909.0	1927.9
7.5°	1892.6	1938.5	1928.7	1940.5	1965.6
10°	1891.1	1946.1	1939.6	1942.1	1968.7
12.5°	1881.8	1945.9	1916.3	1913.9	1928.3
15°	1854.2	1930.1	1863.9	1870.0	1879.4
17.5°	1805.7	1885.0	1822.0	1843.4	1862.0
20°	1774.7	1852.5	1801.9	1829.7	1862.0
22.5°	1746.8	1824.5	1783.2	1822.3	1866.6
25°	1706.8	1775.1	1755.3	1820.4	1869.7
27.5°	1664.9	1705.1	1728.5	1815.8	1850.3
30°	1629.2	1655.8	1714.6	1790.5	1803.8
32.5°	1590.4	1606.4	1696.0	1735.5	1718.5
35°	1526.4	1539.7	1656.4	1624.5	1588.5
37.5°	1450.4	1477.7	1567.6	1475.8	1434.5
40°	1394.5	1440.1	1491.5	1354.7	1307.3
42.5°	1326.3	1399.1	1390.7	1216.3	1158.3
45°	1218.0	1316.7	1208.3	1018.7	954.3
47.5°	1090.4	1191.7	1014.4	845.1	784.7
50°	1006.6	1088.2	898.0	739.4	673.0
52.5°	921.3	980.1	798.7	640.2	579.9
55°	789.4	819.7	659.5	509.2	467.4
57.5°	668.4	687.7	538.8	411.3	380.5
60°	595.4	608.7	459.7	360.2	335.5
62.5°	528.7	539.0	396.1	316.9	298.3
65°	434.5	443.9	322.0	261.5	248.3
67.5°	359.6	364.5	264.9	217.3	204.8
70°	316.1	318.0	230.8	187.9	178.4
72.5°	277.4	274.7	198.2	163.2	156.7
75°	219.2	213.5	151.3	127.9	124.1
77.5°	163.7	157.6	106.3	98.5	98.5
80°	128.0	120.4	81.5	81.5	81.5
82.5°	95.4	84.8	62.8	62.8	61.3
85°	46.5	37.1	36.9	25.1	19.4
87.5°	12.4	12.8	7.0	6.0	5.8
90°	0.0	1.9	11.9	6.9	5.9
92.5°	11.1	44.8	160.9	53.4	38.4
95°	32.7	103.4	497.3	183.7	115.9
97.5°	63.2	131.6	783.8	518.7	315.8
100°	82.2	149.1	875.8	846.7	568.7
102.5°	103.6	168.1	856.8	1187.5	946.7
105°	138.7	194.9	782.7	1486.4	1412.7
107.5°	172.0	225.6	711.3	1515.9	1601.2
110°	194.2	245.5	675.7	1478.7	1633.7



TEST NUMBER: P854215

CATALOG NUMBER: SQ2-PR1-100U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	215.6	265.4	654.3	1416.2	1612.3
115°	246.7	294.1	633.1	1309.9	1538.6
117.5°	277.6	322.5	625.5	1210.4	1444.4
120°	298.2	340.8	623.1	1152.3	1377.1
122.5°	317.2	357.5	623.1	1101.2	1308.9
125°	344.8	382.5	624.1	1034.5	1217.6
127.5°	367.2	406.3	623.1	984.1	1140.3
130°	381.4	422.1	623.1	955.3	1096.7
132.5°	394.1	435.6	622.4	928.9	1059.5
135°	413.1	456.7	620.2	892.2	1003.6
137.5°	434.3	475.8	620.2	853.0	956.2
140°	447.8	488.5	620.2	827.5	925.3
142.5°	461.3	500.4	619.4	804.2	889.6
145°	482.5	518.3	620.2	767.4	839.1
147.5°	503.7	534.1	621.4	737.1	792.2
150°	517.1	545.2	622.2	720.3	766.8
152.5°	529.8	554.8	622.9	705.8	743.8
155°	549.8	568.2	624.1	688.1	714.3
157.5°	567.3	582.2	625.3	675.1	693.3
160°	577.6	590.2	626.1	667.0	680.6
162.5°	587.9	597.4	626.9	659.9	671.1
165°	601.4	608.1	627.1	651.1	658.8
167.5°	612.8	616.3	628.3	644.2	647.5
170°	619.2	621.1	629.1	641.0	642.0
172.5°	623.1	624.3	629.1	637.8	638.0
175°	629.1	629.1	630.1	635.0	633.1
177.5°	631.9	631.1	630.3	632.6	631.1
180°	631.1	631.1	631.1	631.1	631.1

-----

TEST NUMBER: P854215

CATALOG NUMBER: SQ2-PR1-100U-100D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.03	19.88	19.96	20.83	22.05	15.76	16.61	16.69	17.55	18.77
	3H	20.26	21.02	21.21	21.98	23.22	16.82	17.58	17.77	18.53	19.78
	4H	20.72	21.43	21.67	22.39	23.64	17.22	17.94	18.18	18.90	20.15
	6H	21.03	21.69	22.00	22.66	23.92	17.55	18.21	18.52	19.18	20.44
	8H	21.11	21.74	22.09	22.72	23.98	17.64	18.26	18.61	19.24	20.51
	12H	21.14	21.74	22.12	22.71	24.00	17.65	18.24	18.63	19.22	20.50
4H	2H	19.11	19.83	20.07	20.78	22.04	16.32	17.04	17.29	18.00	19.25
	3H	20.58	21.17	21.55	22.16	23.43	17.59	18.18	18.56	19.17	20.44
	4H	21.17	21.72	22.16	22.70	23.99	18.10	18.64	19.08	19.62	20.91
	6H	21.63	22.09	22.62	23.10	24.39	18.53	19.00	19.53	20.00	21.29
	8H	21.76	22.19	22.75	23.19	24.49	18.65	19.09	19.65	20.09	21.39
	12H	21.81	22.20	22.83	23.22	24.53	18.67	19.07	19.69	20.08	21.39
8H	4H	21.20	21.63	22.20	22.63	23.94	18.40	18.84	19.40	19.83	21.14
	6H	21.75	22.11	22.77	23.15	24.45	18.94	19.29	19.96	20.33	21.64
	8H	21.95	22.26	22.97	23.29	24.61	19.12	19.44	20.15	20.46	21.78
	12H	22.05	22.33	23.08	23.35	24.71	19.18	19.46	20.21	20.48	21.85
12H	4H	21.16	21.55	22.17	22.56	23.87	18.42	18.81	19.43	19.82	21.13
	6H	21.73	22.05	22.76	23.08	24.40	19.00	19.31	20.02	20.34	21.66
	8H	21.95	22.23	22.98	23.25	24.61	19.20	19.48	20.23	20.50	21.87