

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855080

Luminaire Tested: SQ2-PW1-075U-100D-835-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855080
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PW1-075U-100D-835-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8467.5 lumens
Efficiency: N/A
Efficacy: 139.0 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.22
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 60.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855080

CATALOG NUMBER: SQ2-PW1-075U-100D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855080

CATALOG NUMBER: SQ2-PW1-075U-100D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66	66	66	66	60	
1	101	97	93	90	94	91	87	85	79	77	75	69	67	66	59	58	57	57	57	57	52	
2	92	85	79	74	86	80	75	71	70	66	63	61	58	56	53	51	49	49	49	49	45	
3	85	76	68	63	79	71	65	60	63	58	54	55	51	48	47	45	42	42	42	42	39	
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	40	37	37	37	37	34	
5	72	60	52	47	67	57	50	45	51	45	41	45	40	37	39	36	33	33	33	33	30	
6	66	54	47	41	62	51	44	39	46	40	36	41	36	32	36	32	29	29	29	29	27	
7	62	49	42	36	58	47	40	35	42	36	32	37	32	29	33	29	26	26	26	26	24	
8	57	45	37	32	54	43	36	31	38	33	28	34	29	26	30	26	24	24	24	24	21	
9	53	41	34	29	50	39	32	28	35	30	26	31	27	24	28	24	21	21	21	21	19	
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	20	20	20	18	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	37210	37210	37210
5°	36961	37246	37601
10°	37030	37461	37930
15°	37020	37717	38158
20°	37036	37675	37412
25°	36836	36873	34762
30°	36584	34742	31428
35°	36299	31970	28381
40°	35576	29145	25073
45°	34182	26213	21902
50°	31810	23431	18746
55°	29101	20701	15198
60°	26085	18006	13110
65°	22812	15511	11656
70°	18652	13785	10565
75°	14516	11909	9719
80°	10814	10209	8573
85°	7317	7744	4891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34182 cd/sqm



TEST NUMBER: P855080

CATALOG NUMBER: SQ2-PW1-075U-100D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.5	2.6
10°-20°	635.9	7.5
20°-30°	935.7	11.1
30°-40°	1023.1	12.1
40°-50°	917.8	10.8
50°-60°	684.6	8.1
60°-70°	432.7	5.1
70°-80°	214.3	2.5
80°-90°	50.7	0.6
90°-100°	204.8	2.4
100°-110°	679.0	8.0
110°-120°	673.9	8.0
120°-130°	548.9	6.5
130°-140°	446.1	5.3
140°-150°	346.5	4.1
150°-160°	249.6	2.9
160°-170°	152.9	1.8
170°-180°	51.6	0.6
0°-30°	1791.1	21.2
0°-40°	2814.1	33.2
0°-60°	4416.5	52.2
0°-90°	5114.2	60.4
90°-120°	1557.7	18.4
90°-150°	2899.1	34.2
90°-180°	3353.0	39.6
0°-180°	8467.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2305	2305	2305	2305	2305	
5°	2280	2317	2298	2301	2320	217
15°	2215	2258	2256	2272	2283	625
25°	2068	2113	2070	1984	1951	952
35°	1842	1822	1622	1481	1440	1149
45°	1497	1377	1148	1004	959	1148
55°	1034	935	735	576	540	923
65°	597	548	406	327	305	592
75°	233	250	191	160	156	256
85°	40	50	42	28	26	50
90°	0	1	3	4	4	3
95°	29	86	371	132	89	33
105°	119	169	680	1282	1199	125
115°	212	254	547	1139	1332	210
125°	296	329	537	895	1055	263
135°	354	390	533	768	867	274
145°	412	442	532	661	723	258
155°	470	486	535	590	612	216
165°	516	521	537	558	564	145
175°	539	539	540	544	543	51
180°	542	542	542	542	542	



TEST NUMBER: P855080

CATALOG NUMBER: SQ2-PW1-075U-100D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2304.6	2304.6	2304.6	2304.6	2304.6
2.5°	2288.9	2318.1	2299.4	2301.4	2306.4
5°	2280.5	2317.1	2298.1	2300.8	2320.0
7.5°	2269.1	2306.0	2292.0	2299.9	2318.8
10°	2258.6	2297.3	2284.9	2296.3	2313.5
12.5°	2244.5	2284.9	2276.1	2289.2	2306.4
15°	2214.7	2257.7	2256.4	2272.0	2282.8
17.5°	2180.0	2222.9	2220.9	2225.0	2230.1
20°	2155.5	2198.4	2192.7	2177.4	2177.4
22.5°	2120.3	2166.7	2152.3	2110.3	2096.6
25°	2067.7	2112.7	2069.8	1983.5	1951.3
27.5°	2006.2	2042.7	1956.5	1834.0	1789.3
30°	1962.3	1990.1	1863.5	1728.6	1685.7
32.5°	1916.6	1927.3	1768.7	1628.5	1582.1
35°	1841.6	1822.2	1622.0	1480.7	1439.9
37.5°	1752.8	1695.3	1481.1	1333.1	1287.9
40°	1687.9	1606.4	1382.8	1234.8	1189.6
42.5°	1615.9	1513.7	1289.8	1141.6	1094.9
45°	1497.0	1376.8	1148.0	1004.2	959.2
47.5°	1363.1	1243.7	1015.3	876.2	837.5
50°	1266.4	1150.6	932.8	793.5	746.3
52.5°	1168.1	1064.3	852.0	708.9	644.5
55°	1033.8	935.1	735.4	576.5	539.9
57.5°	895.5	810.2	629.5	485.3	455.3
60°	807.8	732.6	557.6	436.1	406.0
62.5°	723.5	656.9	487.3	390.5	365.6
65°	597.1	547.6	406.0	326.6	305.1
67.5°	474.1	446.7	337.6	267.9	253.7
70°	395.1	386.5	292.0	234.6	223.8
72.5°	326.6	330.0	248.1	203.1	195.8
75°	232.7	249.9	190.9	160.1	155.8
77.5°	158.4	184.2	141.3	118.5	115.0
80°	116.3	142.1	109.8	92.2	92.2
82.5°	81.3	101.8	78.1	69.4	69.4
85°	39.5	50.2	41.8	28.5	26.4
87.5°	10.5	16.0	7.7	6.1	6.1
90°	0.0	1.1	3.4	4.5	4.5
92.5°	8.9	34.6	102.1	33.0	27.8
95°	29.2	86.1	371.2	132.4	88.6
97.5°	53.6	113.3	647.9	377.9	238.8
100°	70.6	127.7	750.2	644.3	427.2
102.5°	89.5	144.7	743.8	984.7	743.8
105°	118.8	169.3	679.5	1281.9	1198.7
107.5°	148.9	193.9	617.9	1312.3	1375.7
110°	165.9	210.9	586.4	1282.3	1410.6



TEST NUMBER: P855080

CATALOG NUMBER: SQ2-PW1-075U-100D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	183.9	227.9	567.6	1229.3	1392.6
115°	212.0	253.6	547.2	1139.1	1332.1
117.5°	239.7	276.8	539.8	1053.0	1255.4
120°	256.8	293.0	537.1	999.0	1195.3
122.5°	272.1	307.4	537.1	954.8	1136.1
125°	296.0	328.9	537.1	895.0	1055.2
127.5°	315.7	348.0	535.7	849.9	986.7
130°	327.4	361.5	534.8	823.6	946.4
132.5°	338.1	373.0	533.9	801.8	912.2
135°	354.3	390.5	532.6	768.1	866.7
137.5°	371.9	406.7	531.3	735.6	822.6
140°	383.5	417.5	530.4	713.9	793.9
142.5°	394.3	427.3	531.3	692.1	763.4
145°	411.5	442.3	531.5	660.8	723.2
147.5°	430.1	455.8	531.8	634.2	680.6
150°	441.8	464.8	532.6	618.7	658.2
152.5°	452.6	474.7	533.5	606.0	637.6
155°	469.9	486.3	534.8	590.3	612.2
157.5°	486.6	499.4	536.2	579.2	594.7
160°	495.6	506.5	537.1	571.0	583.0
162.5°	504.6	512.9	537.1	565.6	575.0
165°	515.8	521.2	537.1	558.5	564.0
167.5°	526.1	528.9	538.2	552.1	555.1
170°	531.5	532.6	538.2	549.4	550.6
172.5°	535.1	536.2	539.1	546.7	546.9
175°	539.4	539.4	540.5	543.8	542.7
177.5°	541.6	541.6	540.7	542.4	540.7
180°	541.6	541.6	541.6	541.6	541.6



TEST NUMBER: P855080

CATALOG NUMBER: SQ2-PW1-075U-100D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.54	21.46	21.41	22.34	23.46	17.03	17.94	17.90	18.83	19.95
	3H	21.87	22.68	22.75	23.58	24.72	18.24	19.05	19.12	19.95	21.09
	4H	22.24	23.01	23.14	23.92	25.07	18.69	19.46	19.59	20.36	21.51
	6H	22.45	23.16	23.36	24.07	25.23	19.01	19.71	19.92	20.62	21.79
	8H	22.48	23.16	23.40	24.08	25.25	19.08	19.76	20.00	20.68	21.85
	12H	22.48	23.12	23.41	24.04	25.23	19.10	19.74	20.02	20.66	21.85
4H	2H	20.65	21.42	21.56	22.32	23.48	17.72	18.49	18.62	19.39	20.54
	3H	22.20	22.84	23.12	23.77	24.94	19.11	19.75	20.02	20.68	21.85
	4H	22.71	23.29	23.64	24.22	25.42	19.66	20.24	20.58	21.17	22.36
	6H	23.05	23.55	23.99	24.50	25.70	20.06	20.56	21.00	21.52	22.71
	8H	23.13	23.59	24.07	24.54	25.75	20.17	20.64	21.11	21.58	22.79
	12H	23.14	23.56	24.10	24.53	25.74	20.20	20.62	21.16	21.58	22.79
8H	4H	22.75	23.22	23.70	24.17	25.38	19.99	20.46	20.93	21.40	22.61
	6H	23.19	23.58	24.16	24.57	25.77	20.50	20.88	21.46	21.87	23.08
	8H	23.34	23.68	24.31	24.66	25.88	20.66	21.00	21.64	21.98	23.20
	12H	23.41	23.71	24.39	24.68	25.95	20.72	21.02	21.70	21.99	23.27
12H	4H	22.72	23.14	23.68	24.10	25.31	20.01	20.43	20.97	21.39	22.60
	6H	23.18	23.52	24.16	24.50	25.73	20.56	20.90	21.54	21.88	23.11
	8H	23.35	23.65	24.33	24.62	25.89	20.75	21.05	21.73	22.02	23.29