

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854230

Luminaire Tested: SQ2-PR1-125U-125D-935-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P854230  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PR1-125U-125D-935-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10653.2 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 93.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854230  
CATALOG NUMBER: SQ2-PR1-125U-125D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854230

CATALOG NUMBER: SQ2-PR1-125U-125D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54	54	54	54	
1	99	95	92	88	92	88	85	82	76	74	71	64	63	61	54	52	51	46	46	46	46	
2	91	84	78	73	84	78	73	69	67	63	60	57	54	52	48	46	44	40	40	40	40	
3	83	74	67	62	77	69	63	58	60	55	51	51	48	45	43	41	38	35	35	35	35	
4	77	66	58	53	71	62	55	50	54	48	44	46	42	39	39	36	34	30	30	30	30	
5	70	59	51	46	65	55	48	43	48	43	39	41	37	34	35	32	30	27	27	27	27	
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26	23	23	23	23	
7	60	48	40	35	56	45	38	33	40	34	30	34	30	27	29	26	24	21	21	21	21	
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19	19	19	19	
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17	17	17	17	
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	16	16	16	16	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	38253	38253	38253
5°	38203	38438	38908
10°	38605	39595	40189
15°	38593	38795	39117
20°	37969	38550	39837
25°	37860	38936	41475
30°	37820	39802	41874
35°	37462	40653	38985
40°	36598	39144	34307
45°	34632	34356	27131
50°	31483	28087	21049
55°	27668	23113	16383
60°	23941	18484	13491
65°	20669	15316	11809
70°	18586	13567	10489
75°	17024	11753	9644
80°	14821	9428	9428
85°	10745	8503	4483

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 37434 cd/sqm



TEST NUMBER: P854230

CATALOG NUMBER: SQ2-PR1-125U-125D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	228.8	2.1
10°-20°	662.3	6.2
20°-30°	1023.8	9.6
30°-40°	1231.4	11.6
40°-50°	1105.7	10.4
50°-60°	740.7	7.0
60°-70°	430.9	4.0
70°-80°	221.3	2.1
80°-90°	55.5	0.5
90°-100°	307.1	2.9
100°-110°	999.7	9.4
110°-120°	988.9	9.3
120°-130°	808.2	7.6
130°-140°	660.5	6.2
140°-150°	514.5	4.8
150°-160°	370.8	3.5
160°-170°	226.7	2.1
170°-180°	76.5	0.7
0°-30°	1914.9	18.0
0°-40°	3146.2	29.5
0°-60°	4992.6	46.9
0°-90°	5700.2	53.5
90°-120°	2295.8	21.6
90°-150°	4278.9	40.2
90°-180°	4953.0	46.5
0°-180°	10653.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2369	2369	2369	2369	2369	
5°	2357	2397	2372	2377	2401	225
15°	2309	2403	2321	2328	2340	648
25°	2125	2210	2186	2267	2328	980
35°	1901	1917	2062	2023	1978	1185
45°	1517	1639	1505	1268	1188	1160
55°	983	1021	821	634	582	883
65°	541	553	401	326	309	547
75°	273	266	188	159	155	290
85°	58	46	46	31	24	72
90°	0	3	7	6	6	4
95°	42	126	563	201	123	48
105°	170	245	990	1892	1791	181
115°	314	375	807	1663	1956	311
125°	436	487	796	1313	1547	388
135°	527	582	792	1133	1278	407
145°	616	662	790	976	1068	386
155°	703	726	795	874	906	324
165°	767	774	797	827	836	216
175°	800	800	800	806	804	76
180°	803	803	803	803	803	



TEST NUMBER: P854230

CATALOG NUMBER: SQ2-PR1-125U-125D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2369.2	2369.2	2369.2	2369.2	2369.2
2.5°	2359.5	2387.8	2361.4	2363.5	2369.2
5°	2357.1	2397.2	2371.6	2377.0	2400.6
7.5°	2356.6	2413.8	2401.5	2416.2	2447.4
10°	2354.7	2423.2	2415.1	2418.2	2451.3
12.5°	2343.1	2422.9	2386.1	2383.1	2401.0
15°	2308.8	2403.2	2320.9	2328.4	2340.2
17.5°	2248.4	2347.1	2268.7	2295.3	2318.5
20°	2209.8	2306.6	2243.6	2278.3	2318.5
22.5°	2175.0	2271.8	2220.4	2269.0	2324.3
25°	2125.2	2210.3	2185.6	2266.7	2328.1
27.5°	2073.1	2123.1	2152.3	2261.0	2304.0
30°	2028.6	2061.7	2134.9	2229.5	2246.0
32.5°	1980.3	2000.2	2111.7	2161.0	2139.7
35°	1900.6	1917.2	2062.5	2022.8	1977.9
37.5°	1806.0	1840.0	1951.8	1837.7	1786.2
40°	1736.4	1793.1	1857.2	1686.8	1627.7
42.5°	1651.4	1742.1	1731.6	1514.5	1442.3
45°	1516.7	1639.4	1504.6	1268.5	1188.2
47.5°	1357.7	1483.8	1263.1	1052.2	977.1
50°	1253.4	1355.0	1118.2	920.7	838.0
52.5°	1147.2	1220.4	994.5	797.2	722.1
55°	982.9	1020.7	821.1	634.0	582.0
57.5°	832.2	856.3	670.9	512.1	473.8
60°	741.4	758.0	572.4	448.5	417.8
62.5°	658.3	671.1	493.2	394.6	371.4
65°	541.0	552.8	400.9	325.7	309.1
67.5°	447.8	453.9	329.9	270.6	255.0
70°	393.7	396.0	287.4	234.0	222.2
72.5°	345.4	342.0	246.8	203.2	195.1
75°	272.9	265.8	188.4	159.3	154.6
77.5°	203.8	196.3	132.3	122.7	122.7
80°	159.4	149.9	101.4	101.4	101.4
82.5°	118.8	105.6	78.2	78.2	76.3
85°	58.0	46.2	45.9	31.2	24.2
87.5°	15.5	16.0	7.2	7.0	7.0
90°	0.0	2.9	6.9	5.9	5.9
92.5°	14.2	51.1	163.3	53.8	41.5
95°	41.5	126.4	562.8	200.7	123.4
97.5°	78.0	164.5	955.2	581.8	355.1
100°	101.7	186.7	1102.9	983.5	637.9
102.5°	128.6	210.4	1084.8	1455.0	1106.3
105°	169.8	245.1	990.4	1891.6	1791.2
107.5°	214.5	285.3	900.7	1929.4	2035.8
110°	246.9	311.5	858.1	1882.4	2074.6



TEST NUMBER: P854230

CATALOG NUMBER: SQ2-PR1-125U-125D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	273.7	337.6	831.2	1797.6	2045.3
115°	314.0	374.8	806.7	1662.6	1956.1
117.5°	355.5	410.3	797.2	1538.9	1831.1
120°	379.2	433.2	794.9	1462.9	1745.7
122.5°	402.1	455.4	795.7	1396.9	1660.4
125°	436.4	486.6	795.9	1312.7	1547.3
127.5°	465.9	517.2	795.7	1249.6	1445.2
130°	484.8	537.0	794.9	1213.5	1388.3
132.5°	501.4	555.9	794.1	1180.1	1344.1
135°	527.3	582.3	791.9	1132.9	1277.7
137.5°	552.6	608.0	789.7	1084.9	1213.5
140°	570.7	623.8	788.9	1052.4	1174.0
142.5°	588.1	638.9	788.9	1021.3	1129.8
145°	616.1	661.5	789.9	975.7	1068.4
147.5°	643.4	682.8	791.3	936.9	1008.5
150°	661.6	696.3	792.9	913.7	974.6
152.5°	679.7	708.3	793.7	896.1	944.6
155°	703.0	726.2	794.9	873.6	906.4
157.5°	725.2	741.8	796.1	857.0	880.0
160°	738.6	752.1	796.8	846.6	865.0
162.5°	750.4	760.9	796.8	837.8	851.5
165°	767.2	774.0	796.8	826.7	836.3
167.5°	779.1	783.3	797.0	818.3	823.3
170°	787.0	788.9	797.8	812.7	814.6
172.5°	792.5	793.7	799.4	809.5	809.1
175°	799.8	799.8	799.8	805.7	803.8
177.5°	802.8	802.0	801.2	805.1	802.0
180°	802.8	802.8	802.8	802.8	802.8



TEST NUMBER: P854230

CATALOG NUMBER: SQ2-PR1-125U-125D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.76	20.61	20.70	21.56	22.78	16.49	17.34	17.42	18.29	19.51
	3H	21.00	21.76	21.94	22.71	23.96	17.55	18.31	18.50	19.27	20.52
	4H	21.45	22.16	22.41	23.12	24.38	17.95	18.67	18.92	19.63	20.89
	6H	21.77	22.42	22.74	23.39	24.66	18.28	18.94	19.26	19.91	21.18
	8H	21.85	22.47	22.83	23.46	24.72	18.37	19.00	19.35	19.98	21.24
	12H	21.88	22.47	22.86	23.45	24.74	18.38	18.97	19.36	19.95	21.24
4H	2H	19.84	20.56	20.81	21.52	22.77	17.06	17.77	18.02	18.73	19.99
	3H	21.31	21.91	22.29	22.90	24.17	18.32	18.92	19.30	19.91	21.18
	4H	21.91	22.45	22.89	23.43	24.73	18.83	19.37	19.81	20.35	21.65
	6H	22.36	22.82	23.36	23.83	25.12	19.26	19.73	20.26	20.73	22.03
	8H	22.49	22.92	23.49	23.93	25.23	19.39	19.82	20.38	20.82	22.13
	12H	22.54	22.94	23.56	23.95	25.26	19.41	19.80	20.42	20.81	22.13
8H	4H	21.93	22.37	22.93	23.37	24.67	19.13	19.57	20.13	20.57	21.87
	6H	22.48	22.84	23.50	23.88	25.19	19.67	20.03	20.69	21.07	22.37
	8H	22.68	22.99	23.71	24.02	25.35	19.85	20.17	20.88	21.20	22.52
	12H	22.78	23.06	23.82	24.08	25.45	19.92	20.19	20.95	21.22	22.59
12H	4H	21.89	22.28	22.91	23.30	24.61	19.15	19.54	20.17	20.56	21.87
	6H	22.47	22.78	23.50	23.81	25.14	19.73	20.04	20.76	21.07	22.40
	8H	22.68	22.96	23.71	23.98	25.35	19.94	20.21	20.97	21.24	22.60