

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855073

Luminaire Tested: SQ2-PW1-100U-075D-835-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855073
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G2-2308-131-8)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PW1-100U-075D-835-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8269.5 lumens
Efficiency: N/A
Efficacy: 139.5 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.22
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855073

CATALOG NUMBER: SQ2-PW1-100U-075D-835-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855073

CATALOG NUMBER: SQ2-PW1-100U-075D-835-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46				46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45				40	
2	89	82	76	71	82	76	71	66	64	60	57	52	50	48	42	40	39				34	
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34				30	
4	75	65	57	51	69	60	53	48	51	46	42	42	38	35	34	32	30				26	
5	69	58	50	44	63	53	47	41	45	40	36	38	34	31	31	28	26				23	
6	64	52	44	39	58	48	41	36	41	36	32	34	30	27	28	25	23				20	
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21				18	
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19				16	
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17				15	
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	15				14	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27676	27676	27676
5°	27490	27704	27968
10°	27540	27862	28211
15°	27534	28053	28379
20°	27545	28020	27825
25°	27396	27426	25857
30°	27210	25842	23375
35°	26997	23781	21108
40°	26460	21678	18649
45°	25421	19495	16290
50°	23662	17427	13943
55°	21647	15395	11305
60°	19401	13388	9752
65°	16967	11538	8669
70°	13874	10253	7860
75°	10792	8858	7230
80°	8052	7587	6378
85°	5446	5743	3631

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25421 cd/sqm



TEST NUMBER: P855073

CATALOG NUMBER: SQ2-PW1-100U-075D-835-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.2	2.0
10°-20°	472.9	5.7
20°-30°	696.0	8.4
30°-40°	760.9	9.2
40°-50°	682.6	8.3
50°-60°	509.2	6.2
60°-70°	321.8	3.9
70°-80°	159.4	1.9
80°-90°	38.6	0.5
90°-100°	299.6	3.6
100°-110°	906.1	11.0
110°-120°	884.6	10.7
120°-130°	722.8	8.7
130°-140°	590.0	7.1
140°-150°	459.3	5.6
150°-160°	331.1	4.0
160°-170°	202.7	2.5
170°-180°	68.4	0.8
0°-30°	1332.1	16.1
0°-40°	2093.0	25.3
0°-60°	3284.9	39.7
0°-90°	3804.7	46.0
90°-120°	2090.4	25.3
90°-150°	3862.5	46.7
90°-180°	4465.0	54.0
0°-180°	8269.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1714	1714	1714	1714	1714	
5°	1696	1723	1709	1711	1726	161
15°	1647	1679	1678	1690	1698	465
25°	1538	1571	1540	1475	1451	708
35°	1370	1355	1206	1101	1071	854
45°	1113	1024	854	747	713	854
55°	769	696	547	429	402	687
65°	444	407	302	243	227	440
75°	173	186	142	119	116	191
85°	29	37	31	21	20	37
90°	0	2	14	8	7	3
95°	37	118	565	209	132	44
105°	158	222	890	1690	1606	166
115°	280	334	720	1489	1749	277
125°	392	435	710	1176	1384	348
135°	470	519	705	1014	1141	364
145°	548	589	705	872	954	343
155°	625	646	710	782	812	288
165°	684	691	713	740	749	193
175°	715	715	716	722	720	68
180°	717	717	717	717	717	



TEST NUMBER: P855073

CATALOG NUMBER: SQ2-PW1-100U-075D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1714.1	1714.1	1714.1	1714.1	1714.1
2.5°	1702.4	1724.1	1710.3	1711.6	1715.5
5°	1696.1	1723.3	1709.3	1711.2	1725.6
7.5°	1687.7	1715.1	1704.6	1710.5	1724.5
10°	1679.8	1708.6	1699.4	1707.9	1720.7
12.5°	1669.4	1699.4	1693.0	1702.7	1715.5
15°	1647.2	1679.2	1678.3	1689.8	1697.8
17.5°	1621.4	1653.4	1651.8	1654.8	1658.7
20°	1603.1	1635.0	1630.8	1619.4	1619.4
22.5°	1577.0	1611.5	1600.9	1569.6	1559.4
25°	1537.8	1571.3	1539.5	1475.2	1451.4
27.5°	1492.1	1519.3	1455.2	1364.0	1330.8
30°	1459.5	1480.2	1386.1	1285.7	1253.8
32.5°	1425.6	1433.5	1315.4	1211.2	1176.7
35°	1369.7	1355.3	1206.5	1101.2	1070.9
37.5°	1303.7	1260.9	1101.7	991.5	958.0
40°	1255.4	1194.7	1028.5	918.3	884.8
42.5°	1201.8	1125.9	959.3	849.1	814.3
45°	1113.3	1024.0	853.8	746.9	713.4
47.5°	1013.7	925.0	755.2	651.7	623.0
50°	942.0	855.8	693.8	590.2	555.1
52.5°	868.8	791.6	633.7	527.2	479.3
55°	769.0	695.5	546.9	428.8	401.6
57.5°	666.1	602.5	468.2	360.9	338.6
60°	600.8	544.9	414.6	324.3	302.0
62.5°	538.1	488.5	362.5	290.5	271.9
65°	444.1	407.3	302.0	242.9	226.9
67.5°	352.6	332.1	251.1	199.3	188.8
70°	293.9	287.4	217.2	174.5	166.5
72.5°	243.0	245.5	184.5	151.1	145.6
75°	173.0	185.8	142.0	119.1	115.9
77.5°	117.9	137.0	105.1	88.0	85.6
80°	86.6	105.7	81.6	68.6	68.6
82.5°	60.4	75.7	58.2	51.6	51.6
85°	29.4	37.3	31.0	21.2	19.6
87.5°	7.8	12.1	7.9	5.5	5.3
90°	0.0	2.2	13.5	7.8	6.8
92.5°	12.6	50.9	182.9	60.7	43.7
95°	37.1	117.6	565.4	208.9	131.7
97.5°	71.9	149.6	891.1	589.6	359.1
100°	93.5	169.4	995.5	962.5	646.4
102.5°	117.8	191.1	973.9	1350.0	1076.2
105°	157.6	221.6	889.7	1689.7	1605.9
107.5°	195.6	256.5	808.6	1723.3	1820.2
110°	220.8	279.1	768.1	1681.0	1857.1



TEST NUMBER: P855073

CATALOG NUMBER: SQ2-PW1-100U-075D-835-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	245.1	301.7	743.7	1609.9	1832.8
115°	280.4	334.4	719.6	1489.2	1749.0
117.5°	315.5	366.7	711.1	1376.0	1642.0
120°	338.9	387.5	708.4	1309.9	1565.4
122.5°	360.7	406.4	708.4	1251.8	1487.9
125°	391.9	434.9	709.6	1176.0	1384.1
127.5°	417.4	461.8	708.4	1118.8	1296.2
130°	433.5	479.8	708.4	1085.9	1246.8
132.5°	448.0	495.1	707.5	1056.0	1204.3
135°	469.6	519.2	705.0	1014.2	1140.8
137.5°	493.7	540.8	705.0	969.6	1087.0
140°	509.0	555.3	705.0	940.6	1051.9
142.5°	524.4	568.9	704.1	914.2	1011.4
145°	548.5	589.3	705.0	872.4	953.9
147.5°	572.5	607.1	706.4	838.0	900.5
150°	587.9	619.8	707.3	818.9	871.7
152.5°	602.3	630.7	708.2	802.3	845.6
155°	625.0	646.0	709.6	782.2	812.0
157.5°	644.8	661.8	710.9	767.4	788.1
160°	656.6	670.9	711.8	758.3	773.7
162.5°	668.2	679.1	712.6	750.1	762.9
165°	683.6	691.3	712.8	740.1	748.9
167.5°	696.7	700.6	714.2	732.3	736.0
170°	703.9	706.0	715.1	728.7	729.8
172.5°	708.4	709.7	715.1	725.1	725.3
175°	715.1	715.1	716.2	721.9	719.6
177.5°	718.3	717.4	716.5	719.2	717.4
180°	717.4	717.4	717.4	717.4	717.4



TEST NUMBER: P855073

CATALOG NUMBER: SQ2-PW1-100U-075D-835-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.21	19.00	19.20	20.00	21.33	14.69	15.48	15.69	16.49	17.82
	3H	19.52	20.23	20.53	21.24	22.60	15.89	16.60	16.90	17.61	18.96
	4H	19.89	20.56	20.92	21.58	22.94	16.34	17.01	17.36	18.02	19.38
	6H	20.09	20.71	21.13	21.73	23.10	16.65	17.27	17.68	18.29	19.66
	8H	20.12	20.71	21.16	21.75	23.11	16.72	17.31	17.76	18.35	19.71
	12H	20.12	20.68	21.16	21.71	23.10	16.73	17.29	17.77	18.32	19.71
4H	2H	18.30	18.97	19.33	19.99	21.35	15.37	16.04	16.39	17.05	18.41
	3H	19.84	20.40	20.88	21.44	22.81	16.75	17.30	17.78	18.35	19.72
	4H	20.34	20.85	21.39	21.89	23.28	17.29	17.80	18.33	18.84	20.23
	6H	20.67	21.11	21.73	22.17	23.56	17.69	18.13	18.75	19.19	20.58
	8H	20.75	21.16	21.80	22.21	23.62	17.80	18.20	18.85	19.26	20.66
	12H	20.76	21.13	21.83	22.20	23.61	17.82	18.18	18.89	19.25	20.66
8H	4H	20.38	20.79	21.43	21.84	23.24	17.61	18.02	18.67	19.07	20.48
	6H	20.81	21.15	21.89	22.24	23.65	18.12	18.45	19.19	19.55	20.95
	8H	20.96	21.25	22.04	22.33	23.75	18.28	18.57	19.36	19.65	21.08
	12H	21.02	21.28	22.11	22.35	23.82	18.34	18.60	19.42	19.67	21.13
12H	4H	20.33	20.70	21.41	21.77	23.18	17.63	17.99	18.70	19.06	20.47
	6H	20.80	21.10	21.89	22.18	23.60	18.18	18.48	19.27	19.56	20.98
	8H	20.96	21.22	22.05	22.30	23.76	18.37	18.62	19.45	19.70	21.16