

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853609

Luminaire Tested: SQ2-BBN-0U-050D-935-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853609
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2308-130-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-BBN-0U-050D-935-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2016.8 lumens
Efficiency: N/A
Efficacy: 111.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.62
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 18.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853609

CATALOG NUMBER: SQ2-BBN-0U-050D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853609

CATALOG NUMBER: SQ2-BBN-0U-050D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73
6	90	81	75	71	88	80	75	71	79	74	71	77	73	70	76	73	70	68
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	72	69	66	64
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61
9	78	69	63	60	77	69	63	60	68	63	59	67	62	59	66	62	59	58
10	75	66	60	57	74	65	60	57	64	60	56	64	59	56	63	59	56	55

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	60240	60240	60240
5°	58225	57506	58258
10°	49970	50003	49970
15°	38786	38168	38696
20°	27993	27416	27392
25°	19848	19058	19094
30°	14768	14391	14253
35°	11491	11199	10961
40°	8502	8290	7767
45°	4345	5327	3500
50°	947	2939	693
55°	265	1194	208
60°	42	239	23
65°	0	27	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 5327 cd/sqm



TEST NUMBER: P853609

CATALOG NUMBER: SQ2-BBN-0U-050D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	322.6	16.0
10°-20°	636.1	31.5
20°-30°	513.1	25.4
30°-40°	356.5	17.7
40°-50°	164.7	8.2
50°-60°	23.1	1.1
60°-70°	0.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1471.8	73.0
0°-40°	1828.2	90.6
0°-60°	2016.0	100.0
0°-90°	2016.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2016.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3731	3731	3731	3731	3731	
5°	3592	3573	3548	3592	3594	323
15°	2320	2350	2283	2316	2315	639
25°	1114	1089	1070	1086	1072	522
35°	583	583	568	558	556	365
45°	190	227	233	212	153	154
55°	9	15	42	12	7	12
65°	0	0	1	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P853609

CATALOG NUMBER: SQ2-BBN-0U-050D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3731.0	3731.0	3731.0	3731.0	3731.0
2.5°	3728.9	3715.2	3682.6	3712.0	3703.1
5°	3592.5	3573.4	3548.1	3591.9	3594.5
7.5°	3291.6	3297.7	3274.2	3322.5	3317.4
10°	3047.9	3052.5	3049.9	3065.6	3047.9
12.5°	2765.5	2783.8	2749.2	2773.6	2781.1
15°	2320.4	2350.0	2283.4	2315.7	2315.0
17.5°	1903.0	1899.9	1865.6	1871.6	1869.6
20°	1629.2	1624.6	1595.6	1590.9	1594.2
22.5°	1394.6	1386.9	1376.6	1365.0	1369.4
25°	1114.1	1089.1	1069.8	1085.6	1071.8
27.5°	894.3	893.9	877.9	879.7	882.3
30°	792.1	787.5	771.9	772.4	764.5
32.5°	701.2	704.4	685.3	681.5	673.6
35°	583.0	583.0	568.2	558.0	556.1
37.5°	473.4	472.2	461.7	447.3	442.2
40°	403.4	400.1	393.3	375.7	368.5
42.5°	323.8	332.6	326.1	308.4	297.5
45°	190.3	227.1	233.3	211.8	153.3
47.5°	81.8	122.3	155.7	101.5	52.8
50°	37.7	69.2	117.0	49.9	27.6
52.5°	22.1	37.8	86.9	29.2	17.3
55°	9.4	14.7	42.4	12.0	7.4
57.5°	3.5	6.4	16.0	5.2	2.8
60°	1.3	2.7	7.4	2.0	0.7
62.5°	0.3	1.1	3.6	0.9	0.1
65°	0.0	0.0	0.7	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P853609

CATALOG NUMBER: SQ2-BBN-0U-050D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00