

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855445

Luminaire Tested: SQ2-FA-125U-050D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855445
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FA-125U-050D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8102.9 lumens
Efficiency: N/A
Efficacy: 131.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 0.95 / 0.95
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855445
CATALOG NUMBER: SQ2-FA-125U-050D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855445

CATALOG NUMBER: SQ2-FA-125U-050D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28		
1	93	89	86	83	83	80	77	75	63	61	59	47	46	45	32	32	31	25		
2	86	79	73	69	76	71	66	62	56	53	50	42	40	39	29	28	27	22		
3	79	70	63	58	70	63	58	53	50	46	43	38	36	34	27	25	24	19		
4	72	62	55	50	65	56	50	46	45	41	37	34	32	29	25	23	22	18		
5	67	56	49	43	60	51	44	40	41	36	33	31	28	26	23	21	20	16		
6	62	51	43	38	55	46	39	35	37	32	29	29	26	23	21	19	18	14		
7	57	46	39	33	51	42	35	31	34	29	26	26	23	21	19	18	16	13		
8	53	42	35	30	48	38	32	28	31	26	23	24	21	19	18	16	15	12		
9	49	38	31	27	45	35	29	25	28	24	21	22	19	17	17	15	14	11		
10	46	35	28	24	42	32	26	22	26	22	19	21	18	16	16	14	13	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24950	24950	24950	24950
5°	24819	24857	24725	24838
10°	24781	24686	24686	24686
15°	24700	24448	24506	24448
20°	24510	23469	24330	23689
25°	24187	19807	24022	20222
30°	23964	11363	23705	11516
35°	23544	9763	23246	9625
40°	22894	5134	22255	5084
45°	20808	2208	20064	2208
50°	13730	2665	13026	2489
55°	7676	4921	7282	4462
60°	4140	6923	4066	6210
65°	3652	8416	3828	9574
70°	3413	10069	3248	10617
75°	3200	8652	3269	8939
80°	2706	6174	2706	6499
85°	2371	3446	2167	4094

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20808 cd/sqm



TEST NUMBER: P855445

CATALOG NUMBER: SQ2-FA-125U-050D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.4	1.8
10°-20°	412.6	5.1
20°-30°	562.5	6.9
30°-40°	472.7	5.8
40°-50°	268.5	3.3
50°-60°	142.5	1.8
60°-70°	131.2	1.6
70°-80°	96.3	1.2
80°-90°	26.2	0.3
90°-100°	362.4	4.5
100°-110°	1179.8	14.6
110°-120°	1167.1	14.4
120°-130°	953.7	11.8
130°-140°	779.5	9.6
140°-150°	607.1	7.5
150°-160°	437.6	5.4
160°-170°	267.5	3.3
170°-180°	90.3	1.1
0°-30°	1120.5	13.8
0°-40°	1593.2	19.7
0°-60°	2004.2	24.7
0°-90°	2257.9	27.9
90°-120°	2709.3	33.4
90°-150°	5049.7	62.3
90°-180°	5845.0	72.1
0°-180°	8102.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1545	1545	1545	1545	1545	
5°	1531	1534	1526	1532	1531	146
15°	1478	1463	1466	1463	1478	417
25°	1358	1112	1348	1135	1358	626
35°	1194	495	1179	488	1194	746
45°	911	97	879	97	911	666
55°	273	175	259	158	273	263
65°	96	220	100	251	96	96
75°	51	139	52	143	51	53
85°	13	19	12	22	13	14
90°	0	7	0	7	0	3
95°	49	146	49	146	49	57
105°	200	2114	200	2114	200	214
115°	371	2308	371	2308	371	367
125°	515	1826	515	1826	515	458
135°	622	1508	622	1508	622	481
145°	727	1261	727	1261	727	455
155°	830	1070	830	1070	830	382
165°	905	987	905	987	905	255
175°	944	948	944	948	944	90
180°	947	947	947	947	947	



TEST NUMBER: P855445

CATALOG NUMBER: SQ2-FA-125U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	1545.3	1545.3	1545.3	1545.3	1545.3	1545.3	1545.3	1545.3	1545.3	1545.3	1545.3
2.5°	1536.9	1559.8	1539.7	1537.2	1545.3	1543.5	1540.7	1551.5	1533.2	1551.5	1536.9
5°	1531.3	1557.6	1527.8	1520.0	1533.7	1524.6	1532.5	1548.4	1525.5	1546.0	1523.2
7.5°	1521.8	1545.1	1509.4	1504.4	1517.8	1509.9	1513.2	1535.1	1516.0	1529.4	1508.7
10°	1511.5	1532.0	1496.4	1493.2	1505.7	1497.8	1501.0	1524.0	1505.7	1518.3	1497.5
12.5°	1500.3	1516.3	1480.5	1479.1	1489.8	1484.6	1486.1	1505.3	1490.8	1503.4	1483.6
15°	1477.7	1492.5	1456.8	1451.2	1462.6	1458.0	1460.2	1477.5	1466.1	1474.1	1456.8
17.5°	1449.8	1461.6	1426.0	1409.2	1409.7	1415.4	1426.0	1446.7	1436.5	1447.0	1422.5
20°	1426.5	1440.1	1400.8	1368.2	1365.9	1371.6	1400.8	1421.7	1416.0	1427.4	1392.7
22.5°	1399.4	1408.5	1372.8	1317.7	1309.9	1315.6	1369.1	1393.8	1391.7	1399.5	1356.3
25°	1357.7	1366.8	1301.8	1222.4	1111.8	1215.5	1304.1	1348.4	1348.4	1355.2	1298.3
27.5°	1315.3	1315.5	1197.8	785.0	692.5	756.8	1196.2	1292.2	1303.2	1299.8	1187.8
30°	1285.4	1277.5	1061.7	634.6	609.5	625.5	1062.8	1253.3	1271.5	1259.0	1034.9
32.5°	1250.9	1228.3	783.8	583.4	562.9	577.0	758.0	1206.9	1238.8	1211.7	813.9
35°	1194.5	1135.3	597.9	515.8	495.3	513.5	593.2	1115.6	1179.4	1106.4	617.7
37.5°	1133.7	902.4	526.3	410.8	366.6	401.9	523.7	892.7	1109.0	872.0	525.8
40°	1086.2	709.0	473.2	300.6	243.6	283.4	469.7	676.4	1055.9	727.7	461.5
42.5°	1022.8	622.8	379.9	190.9	149.4	174.7	364.3	608.5	990.6	630.5	367.3
45°	911.3	535.3	224.9	104.7	96.7	101.3	207.4	525.5	878.7	514.1	229.6
47.5°	721.8	408.2	144.5	89.0	97.7	89.0	140.1	395.3	681.8	394.6	144.3
50°	546.6	318.6	111.9	90.1	106.1	90.1	108.4	307.8	518.6	336.3	110.7
52.5°	404.9	266.3	91.4	98.8	127.5	100.6	88.8	259.2	384.3	271.3	86.5
55°	272.7	208.8	73.4	130.4	174.8	133.8	73.4	202.9	258.7	200.6	71.1
57.5°	172.9	155.3	74.4	167.6	199.5	170.8	75.5	149.8	166.0	150.5	65.3
60°	128.2	122.5	82.7	178.0	214.4	180.3	83.9	117.9	125.9	116.8	69.9
62.5°	105.8	96.5	99.5	192.8	222.8	187.7	101.6	92.1	110.0	88.1	77.4
65°	95.6	62.5	117.7	195.2	220.3	195.2	118.9	59.2	100.2	63.7	104.9
67.5°	86.2	46.4	113.7	193.8	221.7	194.3	110.9	44.3	82.7	43.1	107.2
70°	72.3	41.5	107.2	197.3	213.3	190.4	107.2	40.3	68.8	39.2	125.9
72.5°	60.1	39.4	99.8	182.2	189.0	175.4	100.7	39.2	60.4	35.3	118.4
75°	51.3	38.7	95.6	145.6	138.7	138.7	93.2	37.6	52.4	35.3	92.1
77.5°	38.5	34.4	79.2	95.0	89.7	89.7	77.8	33.2	36.6	31.1	74.8
80°	29.1	31.5	65.3	69.8	66.4	66.4	62.9	30.3	29.1	29.1	61.8
82.5°	22.6	26.7	50.3	51.3	48.7	47.8	48.9	26.5	22.6	24.5	47.8
85°	12.8	18.5	26.8	22.0	18.6	17.5	25.6	17.4	11.7	17.4	25.6
87.5°	4.7	9.0	5.4	5.1	5.1	5.1	5.4	9.0	4.7	8.0	6.3
90°	0.0	3.4	8.2	7.0	7.0	7.0	8.2	3.4	0.0	3.4	8.2
92.5°	16.8	60.3	192.8	63.5	48.9	63.5	192.8	60.3	16.8	60.3	192.8
95°	48.9	149.2	664.2	236.8	145.7	236.8	664.2	149.2	48.9	149.2	664.2
97.5°	92.1	194.2	1127.3	686.5	419.1	686.5	1127.3	194.2	92.1	194.2	1127.3
100°	120.0	220.3	1301.6	1160.6	752.7	1160.6	1301.6	220.3	120.0	220.3	1301.6
102.5°	151.7	248.3	1280.2	1717.1	1305.6	1717.1	1280.2	248.3	151.7	248.3	1280.2
105°	200.4	289.3	1168.8	2232.3	2113.8	2232.3	1168.8	289.3	200.4	289.3	1168.8
107.5°	253.1	336.7	1063.0	2277.0	2402.6	2277.0	1063.0	336.7	253.1	336.7	1063.0
110°	291.4	367.7	1012.6	2221.5	2448.3	2221.5	1012.6	367.7	291.4	367.7	1012.6



TEST NUMBER: P855445

CATALOG NUMBER: SQ2-FA-125U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	323.0	398.5	980.9	2121.4	2413.8	2121.4	980.9	398.5	323.0	398.5	980.9
115°	370.6	442.4	952.0	1962.1	2308.4	1962.1	952.0	442.4	370.6	442.4	952.0
117.5°	419.5	484.2	940.8	1816.0	2160.9	1816.0	940.8	484.2	419.5	484.2	940.8
120°	447.5	511.3	938.0	1726.3	2060.2	1726.3	938.0	511.3	447.5	511.3	938.0
122.5°	474.6	537.4	939.0	1648.5	1959.5	1648.5	939.0	537.4	474.6	537.4	939.0
125°	515.0	574.3	939.2	1549.1	1826.0	1549.1	939.2	574.3	515.0	574.3	939.2
127.5°	549.7	610.4	939.0	1474.7	1705.4	1474.7	939.0	610.4	549.7	610.4	939.0
130°	572.1	633.6	938.0	1432.2	1638.3	1432.2	938.0	633.6	572.1	633.6	938.0
132.5°	591.7	656.0	937.1	1392.7	1586.1	1392.7	937.1	656.0	591.7	656.0	937.1
135°	622.2	687.2	934.5	1336.9	1507.9	1336.9	934.5	687.2	622.2	687.2	934.5
137.5°	652.0	717.5	932.0	1280.3	1432.2	1280.3	932.0	717.5	652.0	717.5	932.0
140°	673.5	736.2	931.0	1242.0	1385.5	1242.0	931.0	736.2	673.5	736.2	931.0
142.5°	694.0	754.0	931.0	1205.3	1333.3	1205.3	931.0	754.0	694.0	754.0	931.0
145°	727.1	780.7	932.2	1151.4	1260.8	1151.4	932.2	780.7	727.1	780.7	932.2
147.5°	759.3	805.8	933.8	1105.6	1190.2	1105.6	933.8	805.8	759.3	805.8	933.8
150°	780.7	821.7	935.7	1078.3	1150.1	1078.3	935.7	821.7	780.7	821.7	935.7
152.5°	802.1	835.9	936.6	1057.5	1114.7	1057.5	936.6	835.9	802.1	835.9	936.6
155°	829.6	857.0	938.0	1031.0	1069.7	1031.0	938.0	857.0	829.6	857.0	938.0
157.5°	855.8	875.3	939.4	1011.3	1038.5	1011.3	939.4	875.3	855.8	875.3	939.4
160°	871.6	887.6	940.4	999.1	1020.8	999.1	940.4	887.6	871.6	887.6	940.4
162.5°	885.6	897.9	940.4	988.7	1004.9	988.7	940.4	897.9	885.6	897.9	940.4
165°	905.4	913.4	940.4	975.6	987.0	975.6	940.4	913.4	905.4	913.4	940.4
167.5°	919.4	924.4	940.6	965.7	971.6	965.7	940.6	924.4	919.4	924.4	940.6
170°	928.7	931.0	941.5	959.1	961.3	959.1	941.5	931.0	928.7	931.0	941.5
172.5°	935.2	936.6	943.4	955.3	954.8	955.3	943.4	936.6	935.2	936.6	943.4
175°	943.9	943.9	943.9	950.9	948.5	950.9	943.9	943.9	943.9	943.9	943.9
177.5°	947.4	946.4	945.5	950.0	946.4	950.0	945.5	946.4	947.4	946.4	945.5
180°	947.4	947.4	947.4	947.4	947.4	947.4	947.4	947.4	947.4	947.4	947.4



TEST NUMBER: P855445

CATALOG NUMBER: SQ2-FA-125U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	1545.3	1545.3	1545.3	1545.3	1545.3	1545.3
2.5°	1533.3	1539.7	1539.7	1536.0	1554.3	1536.9
5°	1517.7	1532.5	1525.6	1525.5	1548.5	1531.3
7.5°	1506.7	1520.6	1514.2	1512.9	1535.4	1521.8
10°	1495.4	1505.7	1501.2	1504.5	1525.2	1511.5
12.5°	1479.6	1491.7	1487.2	1492.4	1511.3	1500.3
15°	1452.3	1462.6	1464.9	1467.2	1489.1	1477.7
17.5°	1407.2	1412.2	1423.7	1439.7	1462.6	1449.8
20°	1371.8	1378.7	1385.5	1413.6	1440.1	1426.5
22.5°	1331.6	1329.3	1345.2	1378.2	1411.3	1399.4
25°	1222.9	1135.1	1231.9	1316.9	1361.1	1357.7
27.5°	851.4	738.9	838.5	1215.5	1308.4	1315.3
30°	670.1	617.7	668.9	1085.0	1269.5	1285.4
32.5°	594.9	558.9	590.2	825.8	1220.4	1250.9
35°	513.4	488.3	513.4	617.7	1123.9	1194.5
37.5°	410.9	359.6	410.0	533.8	908.5	1133.7
40°	306.2	241.2	297.1	477.8	726.0	1086.2
42.5°	204.1	155.5	193.1	376.2	628.0	1022.8
45°	110.4	96.7	105.8	227.3	512.5	911.3
47.5°	86.6	91.6	86.6	143.3	392.0	721.8
50°	83.1	99.1	83.1	110.7	324.3	546.6
52.5°	90.6	107.4	89.6	87.4	264.7	404.9
55°	102.7	158.5	103.8	71.1	194.0	272.7
57.5°	146.1	178.3	147.8	67.4	149.5	172.9
60°	150.1	192.3	148.9	71.1	115.6	128.2
62.5°	177.6	238.0	177.4	81.3	86.0	105.8
65°	227.7	250.6	230.1	103.7	61.4	95.6
67.5°	216.2	232.4	214.0	111.2	42.3	86.2
70°	212.3	224.9	210.1	127.0	39.2	72.3
72.5°	198.1	199.7	194.0	117.7	35.3	60.1
75°	153.6	143.3	147.9	101.4	35.3	51.3
77.5°	95.4	91.4	92.1	77.4	31.1	38.5
80°	72.3	69.9	68.8	65.3	29.1	29.1
82.5°	53.6	51.3	50.1	50.3	24.5	22.6
85°	24.5	22.1	21.0	29.1	17.4	12.8
87.5°	6.1	6.1	5.1	6.3	7.2	4.7
90°	7.0	7.0	7.0	8.2	3.4	0.0
92.5°	63.5	48.9	63.5	192.8	60.3	16.8
95°	236.8	145.7	236.8	664.2	149.2	48.9
97.5°	686.5	419.1	686.5	1127.3	194.2	92.1
100°	1160.6	752.7	1160.6	1301.6	220.3	120.0
102.5°	1717.1	1305.6	1717.1	1280.2	248.3	151.7
105°	2232.3	2113.8	2232.3	1168.8	289.3	200.4
107.5°	2277.0	2402.6	2277.0	1063.0	336.7	253.1
110°	2221.5	2448.3	2221.5	1012.6	367.7	291.4



TEST NUMBER: P855445

CATALOG NUMBER: SQ2-FA-125U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	2121.4	2413.8	2121.4	980.9	398.5	323.0
115°	1962.1	2308.4	1962.1	952.0	442.4	370.6
117.5°	1816.0	2160.9	1816.0	940.8	484.2	419.5
120°	1726.3	2060.2	1726.3	938.0	511.3	447.5
122.5°	1648.5	1959.5	1648.5	939.0	537.4	474.6
125°	1549.1	1826.0	1549.1	939.2	574.3	515.0
127.5°	1474.7	1705.4	1474.7	939.0	610.4	549.7
130°	1432.2	1638.3	1432.2	938.0	633.6	572.1
132.5°	1392.7	1586.1	1392.7	937.1	656.0	591.7
135°	1336.9	1507.9	1336.9	934.5	687.2	622.2
137.5°	1280.3	1432.2	1280.3	932.0	717.5	652.0
140°	1242.0	1385.5	1242.0	931.0	736.2	673.5
142.5°	1205.3	1333.3	1205.3	931.0	754.0	694.0
145°	1151.4	1260.8	1151.4	932.2	780.7	727.1
147.5°	1105.6	1190.2	1105.6	933.8	805.8	759.3
150°	1078.3	1150.1	1078.3	935.7	821.7	780.7
152.5°	1057.5	1114.7	1057.5	936.6	835.9	802.1
155°	1031.0	1069.7	1031.0	938.0	857.0	829.6
157.5°	1011.3	1038.5	1011.3	939.4	875.3	855.8
160°	999.1	1020.8	999.1	940.4	887.6	871.6
162.5°	988.7	1004.9	988.7	940.4	897.9	885.6
165°	975.6	987.0	975.6	940.4	913.4	905.4
167.5°	965.7	971.6	965.7	940.6	924.4	919.4
170°	959.1	961.3	959.1	941.5	931.0	928.7
172.5°	955.3	954.8	955.3	943.4	936.6	935.2
175°	950.9	948.5	950.9	943.9	943.9	943.9
177.5°	950.0	946.4	950.0	945.5	946.4	947.4
180°	947.4	947.4	947.4	947.4	947.4	947.4

TEST NUMBER: P855445

CATALOG NUMBER: SQ2-FA-125U-050D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.52	9.16	9.66	10.28	11.84	7.37	8.02	8.51	9.14	10.70
	3H	9.21	9.78	10.36	10.91	12.49	13.52	14.09	14.66	15.22	16.80
	4H	9.61	10.16	10.77	11.29	12.87	14.78	15.33	15.94	16.46	18.04
	6H	9.96	10.46	11.12	11.59	13.18	15.38	15.88	16.55	17.02	18.61
	8H	10.07	10.55	11.24	11.69	13.28	15.50	15.98	16.67	17.13	18.71
	12H	10.14	10.59	11.30	11.73	13.34	15.54	15.99	16.71	17.13	18.74
4H	2H	8.89	9.44	10.06	10.57	12.15	7.89	8.44	9.05	9.57	11.15
	3H	9.88	10.34	11.05	11.49	13.08	14.20	14.66	15.37	15.81	17.41
	4H	10.44	10.86	11.61	12.00	13.61	15.65	16.07	16.82	17.21	18.82
	6H	10.90	11.26	12.08	12.43	14.03	16.38	16.74	17.55	17.90	19.51
	8H	11.07	11.41	12.25	12.57	14.18	16.54	16.88	17.71	18.04	19.65
	12H	11.18	11.48	12.37	12.65	14.28	16.60	16.90	17.78	18.07	19.69
8H	4H	11.53	11.86	12.70	13.02	14.64	15.76	16.10	16.93	17.25	18.87
	6H	12.13	12.41	13.32	13.61	15.22	16.64	16.91	17.83	18.11	19.73
	8H	12.37	12.61	13.56	13.79	15.42	16.89	17.13	18.08	18.31	19.94
	12H	12.53	12.74	13.73	13.92	15.58	17.00	17.21	18.20	18.39	20.05
12H	4H	11.66	11.97	12.85	13.14	14.76	15.71	16.02	16.90	17.19	18.81
	6H	12.41	12.65	13.60	13.83	15.46	16.65	16.89	17.84	18.07	19.70
	8H	12.70	12.91	13.90	14.08	15.75	16.92	17.13	18.12	18.30	19.97