

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855420

Luminaire Tested: SQ2-FB-100U-075D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855420
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-100U-075D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8054.6 lumens
Efficiency: N/A
Efficacy: 135.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855420
CATALOG NUMBER: SQ2-FB-100U-075D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855420

CATALOG NUMBER: SQ2-FB-100U-075D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	44	43	42	36
2	87	80	73	68	79	73	68	63	60	56	53	49	46	44	38	36	35	30
3	79	70	62	56	72	64	57	52	53	48	44	43	39	36	33	31	29	24
4	72	61	53	47	66	56	49	44	47	41	37	38	34	31	29	27	24	21
5	66	54	46	40	60	50	43	37	41	36	32	34	29	26	26	23	21	18
6	61	48	40	34	55	44	37	32	37	31	27	30	26	23	24	20	18	15
7	56	43	35	30	51	40	33	28	33	28	24	27	23	20	21	18	16	13
8	52	39	31	26	47	36	29	24	30	25	21	25	20	17	19	16	14	12
9	48	36	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5646	5646	5646
5°	5504	7629	10000
10°	5155	14773	19461
15°	4665	19221	22397
20°	4131	21146	23457
25°	3654	22611	23840
30°	3229	23288	24134
35°	2884	23692	25945
40°	2624	23918	27566
45°	2418	24032	28866
50°	2281	24493	29391
55°	2224	25129	29627
60°	2280	25462	29479
65°	2376	25112	28646
70°	2459	24283	21663
75°	2726	21815	11959
80°	2817	11260	11093
85°	2816	7799	4668

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 29893 cd/sqm



TEST NUMBER: P855420

CATALOG NUMBER: SQ2-FB-100U-075D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	0.7
10°-20°	267.4	3.3
20°-30°	470.5	5.8
30°-40°	609.0	7.6
40°-50°	671.7	8.3
50°-60°	627.2	7.8
60°-70°	484.7	6.0
70°-80°	223.6	2.8
80°-90°	44.0	0.5
90°-100°	308.5	3.8
100°-110°	933.2	11.6
110°-120°	911.0	11.3
120°-130°	744.4	9.2
130°-140°	607.6	7.5
140°-150°	473.0	5.9
150°-160°	341.0	4.2
160°-170°	208.7	2.6
170°-180°	70.5	0.9
0°-30°	796.5	9.9
0°-40°	1405.6	17.5
0°-60°	2704.4	33.6
0°-90°	3456.8	42.9
90°-120°	2152.7	26.7
90°-150°	3977.7	49.4
90°-180°	4598.0	57.1
0°-180°	8054.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	350	350	350	350	350	
5°	340	389	471	574	617	32
15°	279	550	1150	1287	1340	78
25°	205	739	1269	1325	1338	94
35°	146	713	1202	1244	1316	92
45°	106	546	1052	1208	1264	82
55°	79	326	893	1026	1052	71
65°	62	184	657	737	750	61
75°	44	113	350	188	192	45
85°	15	33	42	29	25	16
90°	0	2	14	8	7	3
95°	38	121	582	215	136	45
105°	162	228	916	1740	1654	171
115°	289	344	741	1534	1801	286
125°	404	448	731	1211	1425	359
135°	484	535	726	1044	1175	374
145°	565	607	726	898	982	354
155°	644	665	731	806	836	296
165°	704	712	734	762	771	198
175°	736	736	738	743	741	70
180°	739	739	739	739	739	

TEST NUMBER: P855420

CATALOG NUMBER: SQ2-FB-100U-075D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	349.7	349.7	349.7	349.7	349.7
2.5°	346.9	361.5	377.9	396.9	404.9
5°	339.6	388.9	470.7	574.3	617.0
7.5°	326.4	426.8	684.6	961.6	1047.0
10°	314.4	454.2	901.1	1140.9	1187.0
12.5°	300.9	490.6	1037.0	1205.5	1252.8
15°	279.1	550.3	1149.9	1287.3	1339.9
17.5°	256.5	617.5	1202.3	1337.9	1366.4
20°	240.4	664.5	1230.7	1347.1	1365.2
22.5°	225.6	699.7	1250.8	1339.0	1358.4
25°	205.1	739.3	1269.2	1325.1	1338.2
27.5°	185.3	749.7	1261.2	1297.8	1310.6
30°	173.2	746.9	1249.1	1276.5	1294.5
32.5°	162.5	738.7	1231.6	1258.1	1297.2
35°	146.3	713.3	1202.0	1244.1	1316.3
37.5°	132.5	672.7	1163.1	1249.1	1318.8
40°	124.5	642.3	1134.8	1248.7	1307.9
42.5°	116.3	606.5	1102.5	1235.3	1294.5
45°	105.9	546.5	1052.5	1208.4	1264.2
47.5°	96.1	478.9	1006.0	1171.0	1211.8
50°	90.8	432.7	975.1	1137.2	1170.1
52.5°	85.4	387.8	944.2	1096.9	1127.1
55°	79.0	325.6	892.7	1026.1	1052.5
57.5°	73.3	272.2	834.2	948.1	969.4
60°	70.6	243.2	788.5	891.5	912.9
62.5°	66.5	216.8	737.3	832.3	852.4
65°	62.2	183.9	657.3	736.7	749.8
67.5°	56.2	159.4	572.3	620.8	596.1
70°	52.1	147.4	514.4	529.7	458.9
72.5°	49.4	134.3	451.2	411.2	277.4
75°	43.7	112.7	349.7	188.3	191.7
77.5°	35.7	87.3	229.9	144.6	147.7
80°	30.3	71.3	121.1	117.7	119.3
82.5°	24.9	55.5	83.4	86.7	84.4
85°	15.2	33.2	42.1	28.6	25.2
87.5°	5.4	12.4	9.6	8.4	8.2
90°	0.0	2.2	13.9	8.0	7.0
92.5°	12.9	52.4	188.3	62.5	45.0
95°	38.2	121.1	582.2	215.1	135.7
97.5°	74.0	154.1	917.6	607.2	369.8
100°	96.3	174.5	1025.2	991.2	665.7
102.5°	121.3	196.8	1002.9	1390.2	1108.3
105°	162.3	228.2	916.2	1740.1	1653.8
107.5°	201.4	264.2	832.7	1774.7	1874.4
110°	227.4	287.4	791.0	1731.1	1912.4



TEST NUMBER: P855420

CATALOG NUMBER: SQ2-FB-100U-075D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.4	310.7	765.9	1657.9	1887.5
115°	288.8	344.4	741.1	1533.6	1801.1
117.5°	324.9	377.6	732.3	1417.0	1691.0
120°	349.0	399.0	729.5	1349.0	1612.1
122.5°	371.4	418.5	729.5	1289.2	1532.3
125°	403.6	447.9	730.7	1211.1	1425.4
127.5°	429.8	475.6	729.5	1152.1	1334.9
130°	446.5	494.1	729.5	1118.3	1283.9
132.5°	461.4	509.9	728.6	1087.4	1240.2
135°	483.6	534.7	726.0	1044.4	1174.8
137.5°	508.5	556.9	726.0	998.5	1119.4
140°	524.2	571.9	726.0	968.7	1083.2
142.5°	540.0	585.8	725.1	941.4	1041.5
145°	564.9	606.8	726.0	898.4	982.3
147.5°	589.6	625.2	727.4	863.0	927.3
150°	605.4	638.3	728.4	843.3	897.7
152.5°	620.2	649.5	729.3	826.3	870.8
155°	643.7	665.2	730.7	805.5	836.2
157.5°	664.0	681.5	732.1	790.3	811.6
160°	676.2	690.8	733.0	780.9	796.8
162.5°	688.2	699.4	733.9	772.4	785.6
165°	704.0	711.9	734.1	762.2	771.3
167.5°	717.4	721.5	735.5	754.1	758.0
170°	724.9	727.1	736.4	750.4	751.6
172.5°	729.5	730.8	736.4	746.7	746.9
175°	736.4	736.4	737.6	743.4	741.1
177.5°	739.7	738.7	737.8	740.6	738.7
180°	738.7	738.7	738.7	738.7	738.7

TEST NUMBER: P855420

CATALOG NUMBER: SQ2-FB-100U-075D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.39	13.21	13.40	14.24	15.60	21.13	21.95	22.14	22.97	24.34
	3H	13.12	13.86	14.14	14.89	16.28	22.75	23.48	23.77	24.52	25.90
	4H	13.42	14.12	14.45	15.15	16.54	22.93	23.62	23.96	24.66	26.05
	6H	13.63	14.27	14.67	15.31	16.72	23.01	23.65	24.05	24.69	26.10
	8H	13.69	14.30	14.74	15.36	16.76	23.01	23.62	24.06	24.68	26.08
	12H	13.72	14.30	14.77	15.35	16.77	22.98	23.56	24.04	24.61	26.04
4H	2H	16.78	17.48	17.82	18.52	19.91	21.57	22.26	22.61	23.30	24.69
	3H	17.71	18.30	18.76	19.36	20.77	23.39	23.97	24.44	25.03	26.44
	4H	17.99	18.53	19.05	19.58	21.01	23.62	24.16	24.68	25.21	26.64
	6H	18.12	18.58	19.19	19.66	21.08	23.77	24.22	24.83	25.30	26.73
	8H	18.14	18.57	19.21	19.64	21.08	23.79	24.22	24.86	25.29	26.73
	12H	18.13	18.52	19.22	19.61	21.05	23.76	24.15	24.85	25.23	26.68
8H	4H	19.17	19.59	20.23	20.66	22.11	23.74	24.17	24.80	25.24	26.68
	6H	19.40	19.75	20.49	20.87	22.31	23.94	24.29	25.03	25.41	26.84
	8H	19.47	19.78	20.57	20.88	22.33	24.00	24.31	25.10	25.41	26.86
	12H	19.50	19.77	20.60	20.86	22.36	23.99	24.27	25.10	25.36	26.85
12H	4H	19.18	19.57	20.27	20.65	22.10	23.69	24.07	24.77	25.16	26.61
	6H	19.50	19.81	20.59	20.90	22.36	23.92	24.23	25.02	25.33	26.79
	8H	19.60	19.87	20.70	20.96	22.46	23.99	24.26	25.09	25.35	26.85