

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853723

Luminaire Tested: SQ2-F-125U-100D-935-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853723
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-125U-100D-935-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8967.4 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 81.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853723
CATALOG NUMBER: SQ2-F-125U-100D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853723

CATALOG NUMBER: SQ2-F-125U-100D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	38	36	31
3	80	70	63	57	73	65	58	53	54	49	45	44	41	38	35	32	30	26
4	73	62	54	48	67	57	50	45	48	43	38	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	38	43	37	33	35	31	28	28	25	23	19
6	62	49	41	36	56	46	38	33	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18	15
8	53	40	33	27	48	37	30	26	32	26	22	26	22	19	21	18	16	13
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	20	27	21	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22985	22985	22985
5°	22822	22885	23073
10°	22768	22832	22991
15°	22629	22695	22922
20°	22495	22527	22728
25°	22287	22287	22425
30°	22057	22057	22130
35°	21790	21715	21867
40°	21503	21420	21503
45°	21169	21080	21169
50°	20851	20657	20705
55°	20366	20310	20200
60°	19853	19730	19604
65°	19266	19045	18819
70°	18128	18038	17670
75°	17062	16700	16213
80°	15146	14784	14245
85°	12208	11134	10411

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 21299 cd/sqm



TEST NUMBER: P853723

CATALOG NUMBER: SQ2-F-125U-100D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.6	1.5
10°-20°	384.5	4.3
20°-30°	578.5	6.5
30°-40°	692.2	7.7
40°-50°	714.2	8.0
50°-60°	644.3	7.2
60°-70°	491.7	5.5
70°-80°	282.7	3.2
80°-90°	74.6	0.8
90°-100°	308.2	3.4
100°-110°	1003.2	11.2
110°-120°	992.4	11.1
120°-130°	811.0	9.0
130°-140°	662.8	7.4
140°-150°	516.3	5.8
150°-160°	372.1	4.1
160°-170°	227.4	2.5
170°-180°	76.7	0.9
0°-30°	1097.6	12.2
0°-40°	1789.8	20.0
0°-60°	3148.3	35.1
0°-90°	3997.3	44.6
90°-120°	2303.8	25.7
90°-150°	4293.8	47.9
90°-180°	4970.0	55.4
0°-180°	8967.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1424	1424	1424	1424	1424	
5°	1408	1427	1412	1414	1424	134
15°	1354	1371	1358	1364	1371	382
25°	1251	1264	1251	1253	1259	576
35°	1106	1113	1102	1106	1109	691
45°	927	933	923	925	927	715
55°	724	727	722	718	718	647
65°	504	502	498	494	493	496
75°	274	272	268	262	260	288
85°	66	62	60	54	56	76
90°	0	3	7	6	6	5
95°	42	127	565	201	124	48
105°	170	246	994	1898	1797	182
115°	315	376	810	1668	1963	312
125°	438	488	799	1317	1553	390
135°	529	584	795	1137	1282	409
145°	618	664	793	979	1072	387
155°	706	729	798	877	910	325
165°	770	777	800	830	839	217
175°	803	803	803	808	806	76
180°	806	806	806	806	806	



TEST NUMBER: P853723

CATALOG NUMBER: SQ2-F-125U-100D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1423.6	1423.6	1423.6	1423.6	1423.6
2.5°	1414.3	1431.0	1417.4	1420.6	1422.1
5°	1408.1	1427.1	1412.0	1414.1	1423.6
7.5°	1396.5	1417.0	1400.4	1404.1	1414.7
10°	1388.7	1407.7	1392.6	1394.7	1402.3
12.5°	1376.3	1395.3	1380.2	1383.8	1391.4
15°	1353.8	1370.9	1357.7	1363.7	1371.3
17.5°	1327.8	1346.0	1331.3	1336.5	1342.9
20°	1309.2	1324.4	1311.1	1313.3	1322.8
22.5°	1285.9	1301.1	1289.4	1290.0	1297.9
25°	1251.0	1264.3	1251.0	1253.1	1258.8
27.5°	1211.1	1222.4	1211.1	1213.1	1218.0
30°	1183.1	1194.5	1183.1	1185.1	1187.0
32.5°	1152.1	1162.0	1150.5	1152.6	1157.5
35°	1105.5	1113.1	1101.7	1105.6	1109.4
37.5°	1055.9	1061.6	1052.0	1054.0	1057.4
40°	1020.2	1025.9	1016.3	1018.3	1020.2
42.5°	984.5	988.7	979.1	981.1	984.5
45°	927.1	932.8	923.2	925.2	927.1
47.5°	868.9	872.3	864.3	862.8	866.2
50°	830.1	832.0	822.4	822.4	824.3
52.5°	788.2	790.1	783.6	780.5	782.4
55°	723.5	727.2	721.5	717.6	717.6
57.5°	658.3	661.7	654.4	652.5	652.1
60°	614.8	616.7	611.0	609.0	607.1
62.5°	571.4	571.8	566.0	564.0	562.1
65°	504.3	502.4	498.5	494.5	492.6
67.5°	429.0	430.9	427.1	420.9	420.9
70°	384.0	385.9	382.1	374.3	374.3
72.5°	340.6	339.4	337.1	330.8	327.8
75°	273.5	271.6	267.7	261.8	259.9
77.5°	206.4	204.5	202.5	195.2	196.7
80°	162.9	161.0	159.0	153.2	153.2
82.5°	124.1	120.7	118.7	112.9	112.9
85°	65.9	62.2	60.1	54.4	56.2
87.5°	18.6	17.7	16.9	13.6	13.6
90°	0.0	2.9	6.9	5.9	5.9
92.5°	14.3	51.3	163.9	54.0	41.6
95°	41.6	126.9	564.8	201.4	123.9
97.5°	78.3	165.1	958.5	583.8	356.3
100°	102.1	187.3	1106.8	986.9	640.1
102.5°	129.0	211.2	1088.5	1460.1	1110.1
105°	170.4	246.0	993.8	1898.2	1797.4
107.5°	215.2	286.3	903.9	1936.2	2042.9
110°	247.7	312.6	861.0	1889.0	2081.8



TEST NUMBER: P853723

CATALOG NUMBER: SQ2-F-125U-100D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.7	338.8	834.1	1803.8	2052.4
115°	315.1	376.1	809.5	1668.3	1962.9
117.5°	356.7	411.7	800.0	1544.3	1837.4
120°	380.5	434.7	797.6	1468.0	1751.8
122.5°	403.5	457.0	798.4	1401.7	1666.2
125°	438.0	488.3	798.6	1317.2	1552.7
127.5°	467.5	519.0	798.4	1253.9	1450.2
130°	486.5	538.8	797.6	1217.8	1393.1
132.5°	503.2	557.8	796.8	1184.2	1348.7
135°	529.1	584.3	794.7	1136.8	1282.2
137.5°	554.5	610.1	792.5	1088.7	1217.8
140°	572.7	626.0	791.7	1056.0	1178.1
142.5°	590.1	641.1	791.7	1024.8	1133.7
145°	618.3	663.8	792.7	979.1	1072.1
147.5°	645.6	685.2	794.1	940.2	1012.1
150°	663.9	698.7	795.7	916.9	978.0
152.5°	682.1	710.8	796.4	899.2	947.8
155°	705.5	728.7	797.6	876.7	909.6
157.5°	727.7	744.3	798.8	860.0	883.0
160°	741.2	754.7	799.6	849.6	868.0
162.5°	753.0	763.5	799.6	840.7	854.5
165°	769.9	776.7	799.6	829.6	839.2
167.5°	781.8	786.0	799.8	821.1	826.2
170°	789.7	791.6	800.6	815.5	817.4
172.5°	795.3	796.4	802.2	812.3	811.9
175°	802.6	802.6	802.6	808.5	806.5
177.5°	805.6	804.8	804.0	807.9	804.8
180°	805.6	805.6	805.6	805.6	805.6



TEST NUMBER: P853723

CATALOG NUMBER: SQ2-F-125U-100D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.34	19.16	19.34	20.18	21.52	18.26	19.08	19.26	20.10	21.44
	3H	20.12	20.86	21.13	21.88	23.24	20.00	20.74	21.01	21.76	23.12
	4H	20.77	21.47	21.80	22.50	23.87	20.62	21.32	21.64	22.35	23.72
	6H	21.24	21.89	22.27	22.91	24.30	21.06	21.70	22.09	22.73	24.12
	8H	21.38	21.99	22.42	23.04	24.42	21.18	21.79	22.21	22.84	24.22
	12H	21.45	22.03	22.49	23.07	24.48	21.23	21.81	22.27	22.85	24.26
4H	2H	18.89	19.59	19.91	20.61	21.98	18.82	19.52	19.85	20.55	21.92
	3H	20.87	21.45	21.91	22.51	23.89	20.76	21.35	21.80	22.40	23.79
	4H	21.66	22.19	22.70	23.24	24.65	21.51	22.05	22.56	23.09	24.50
	6H	22.24	22.71	23.30	23.77	25.18	22.06	22.53	23.12	23.59	25.00
	8H	22.43	22.86	23.49	23.92	25.34	22.23	22.66	23.29	23.72	25.14
	12H	22.53	22.92	23.61	24.00	25.42	22.30	22.69	23.38	23.77	25.19
8H	4H	21.90	22.33	22.96	23.39	24.81	21.78	22.21	22.83	23.27	24.69
	6H	22.62	22.97	23.70	24.08	25.49	22.45	22.81	23.53	23.91	25.33
	8H	22.88	23.20	23.97	24.28	25.72	22.69	23.00	23.78	24.09	25.53
	12H	23.05	23.33	24.14	24.41	25.88	22.82	23.10	23.91	24.18	25.66
12H	4H	21.89	22.28	22.97	23.36	24.78	21.77	22.16	22.85	23.24	24.66
	6H	22.66	22.97	23.75	24.06	25.50	22.50	22.81	23.59	23.90	25.34
	8H	22.95	23.23	24.04	24.31	25.79	22.76	23.04	23.86	24.12	25.60