

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855380

Luminaire Tested: SQ2-PH1-025U-075D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855380
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2308-131-10)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PH1-025U-075D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5080.6 lumens
Efficiency: N/A
Efficacy: 149.0 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 34.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855380
CATALOG NUMBER: SQ2-PH1-025U-075D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855380

CATALOG NUMBER: SQ2-PH1-025U-075D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	98	98	98	89	89	89	81	81	81	77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	71	69	66
2	95	87	81	76	90	84	78	73	76	72	68	70	66	63	64	61	59	55
3	87	77	70	64	83	74	67	61	68	62	58	62	57	54	57	53	50	47
4	80	68	60	54	76	66	58	52	60	54	49	55	50	46	51	47	43	40
5	73	61	53	47	70	59	51	45	54	48	43	50	44	40	46	41	38	35
6	68	55	47	41	64	53	45	40	49	42	37	45	40	35	42	37	33	31
7	63	50	42	36	60	48	40	35	44	38	33	41	36	31	38	33	30	27
8	58	46	37	32	56	44	36	31	41	34	30	38	32	28	35	30	27	25
9	54	42	34	29	52	40	33	28	37	31	27	35	29	25	32	28	24	22
10	51	38	31	26	49	37	30	25	35	28	24	32	27	23	30	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	28530	28530	28530
5°	28691	26976	26075
10°	28032	24558	23704
15°	28159	23099	23239
20°	27153	22386	23426
25°	26657	22283	22882
30°	26077	22223	23068
35°	25882	21969	27039
40°	25901	21827	21439
45°	25912	20998	18466
50°	25551	21411	17314
55°	25225	23237	16608
60°	24974	20360	15581
65°	24539	16504	13551
70°	23174	14044	9682
75°	20661	10593	7342
80°	16885	6881	6881
85°	10578	6243	4668

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25912 cd/sqm



TEST NUMBER: P855380

CATALOG NUMBER: SQ2-PH1-025U-075D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	3.1
10°-20°	409.0	8.0
20°-30°	599.6	11.8
30°-40°	726.2	14.3
40°-50°	714.1	14.1
50°-60°	621.7	12.2
60°-70°	432.2	8.5
70°-80°	204.9	4.0
80°-90°	45.6	0.9
90°-100°	76.4	1.5
100°-110°	237.7	4.7
110°-120°	232.5	4.6
120°-130°	189.8	3.7
130°-140°	155.3	3.1
140°-150°	121.2	2.4
150°-160°	87.5	1.7
160°-170°	53.5	1.1
170°-180°	18.0	0.4
0°-30°	1164.1	22.9
0°-40°	1890.2	37.2
0°-60°	3226.0	63.5
0°-90°	3908.7	76.9
90°-120°	546.6	10.8
90°-150°	1012.9	19.9
90°-180°	1172.0	23.1
0°-180°	5080.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1767	1767	1767	1767	1767	
5°	1770	1769	1664	1612	1609	166
15°	1685	1500	1382	1372	1390	470
25°	1496	1273	1251	1289	1284	688
35°	1313	1061	1115	1211	1372	822
45°	1135	841	920	952	809	872
55°	896	654	826	595	590	801
65°	642	450	432	355	355	631
75°	331	229	170	121	118	351
85°	57	37	34	27	25	77
90°	0	1	4	4	4	2
95°	10	31	140	52	34	12
105°	42	59	234	447	426	44
115°	74	88	190	392	459	73
125°	103	114	188	308	361	91
135°	124	138	186	266	299	96
145°	145	156	186	230	250	91
155°	166	171	188	206	213	76
165°	182	183	189	195	197	51
175°	189	189	189	190	189	18
180°	189	189	189	189	189	



TEST NUMBER: P855380

CATALOG NUMBER: SQ2-PH1-025U-075D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1767.0	1767.0	1767.0	1767.0	1767.0
2.5°	1762.9	1781.3	1740.1	1723.9	1721.2
5°	1770.2	1768.6	1664.4	1612.2	1608.8
7.5°	1738.0	1687.0	1562.5	1504.9	1502.3
10°	1709.8	1632.5	1497.9	1445.8	1445.8
12.5°	1703.0	1581.1	1445.4	1407.0	1414.9
15°	1684.6	1500.5	1381.9	1372.3	1390.3
17.5°	1623.4	1425.1	1332.5	1354.5	1375.5
20°	1580.3	1384.7	1302.9	1343.7	1363.4
22.5°	1544.0	1345.8	1281.4	1326.0	1336.6
25°	1496.3	1272.7	1250.8	1289.4	1284.4
27.5°	1439.0	1205.7	1220.2	1243.8	1246.7
30°	1398.7	1165.3	1192.0	1216.0	1237.3
32.5°	1359.8	1118.4	1161.0	1218.0	1266.9
35°	1313.1	1061.4	1114.6	1210.7	1371.8
37.5°	1263.9	994.3	1067.9	1148.7	1200.0
40°	1228.9	946.2	1035.6	1135.5	1017.2
42.5°	1191.3	908.5	987.2	1116.1	916.2
45°	1134.8	840.6	919.6	951.7	808.7
47.5°	1068.2	787.8	873.9	793.6	737.7
50°	1017.2	752.5	852.4	725.5	689.3
52.5°	967.4	715.9	837.6	669.2	644.9
55°	896.1	654.4	825.5	595.1	590.0
57.5°	820.4	591.9	730.0	530.5	539.0
60°	773.4	551.5	630.5	492.4	482.5
62.5°	723.6	512.2	537.6	443.9	434.1
65°	642.3	449.8	432.0	354.7	354.7
67.5°	552.7	385.0	350.0	290.3	250.8
70°	490.9	343.0	297.5	231.4	205.1
72.5°	425.0	298.1	243.8	189.6	159.4
75°	331.2	229.2	169.8	121.0	117.7
77.5°	239.4	165.1	114.3	89.7	90.1
80°	181.6	125.6	74.0	72.4	74.0
82.5°	127.7	86.4	55.1	57.5	57.8
85°	57.1	37.4	33.7	26.8	25.2
87.5°	12.1	11.1	7.5	7.5	7.5
90°	0.0	1.2	3.5	3.5	3.5
92.5°	3.7	12.9	44.3	14.6	11.8
95°	10.4	30.8	140.2	51.7	33.6
97.5°	19.0	40.1	232.1	144.5	91.0
100°	25.5	44.8	261.7	244.9	163.3
102.5°	31.9	50.3	256.3	349.7	274.6
105°	41.7	58.7	234.0	446.7	426.3
107.5°	51.4	67.2	212.7	454.2	476.5
110°	57.9	73.8	201.5	443.4	487.6



TEST NUMBER: P855380

CATALOG NUMBER: SQ2-PH1-025U-075D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	64.4	79.4	196.0	424.3	480.3
115°	74.1	87.8	190.0	391.9	458.7
117.5°	83.7	96.1	187.4	360.9	429.3
120°	89.2	101.6	186.5	343.2	408.9
122.5°	94.7	107.2	187.4	328.3	388.5
125°	103.1	114.4	187.6	308.1	361.4
127.5°	109.8	121.3	187.6	293.2	338.4
130°	113.5	126.0	187.6	284.7	325.5
132.5°	118.2	130.6	186.7	277.2	315.2
135°	124.0	137.5	186.5	266.1	298.8
137.5°	130.6	143.1	186.5	254.9	284.7
140°	134.4	146.8	186.5	247.3	274.6
142.5°	139.0	150.6	186.5	239.8	264.3
145°	144.7	156.2	186.5	229.8	250.2
147.5°	151.7	161.5	187.6	220.5	236.6
150°	156.4	164.3	187.6	215.7	228.2
152.5°	160.1	167.1	187.6	211.1	221.7
155°	165.6	171.3	187.6	206.4	213.2
157.5°	171.2	175.5	187.6	202.1	206.4
160°	174.9	178.3	187.6	199.3	202.7
162.5°	177.7	180.2	187.6	197.4	200.0
165°	181.8	183.0	188.8	194.6	197.0
167.5°	184.4	184.6	187.6	193.0	194.2
170°	185.3	186.5	187.6	191.1	192.3
172.5°	187.2	187.4	188.6	190.2	190.4
175°	188.8	188.8	188.8	190.0	188.8
177.5°	188.8	188.8	188.8	188.8	188.8
180°	188.8	188.8	188.8	188.8	188.8



TEST NUMBER: P855380

CATALOG NUMBER: SQ2-PH1-025U-075D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.17	22.32	21.85	23.03	23.85	19.84	21.00	20.53	21.70	22.53
	3H	23.21	24.25	23.91	24.96	25.83	20.89	21.93	21.60	22.65	23.51
	4H	23.96	24.94	24.68	25.66	26.53	21.12	22.10	21.84	22.82	23.70
	6H	24.46	25.36	25.19	26.09	26.98	21.28	22.18	22.02	22.92	23.81
	8H	24.59	25.45	25.34	26.20	27.09	21.32	22.18	22.07	22.94	23.83
	12H	24.65	25.46	25.40	26.21	27.13	21.33	22.15	22.08	22.90	23.81
4H	2H	21.58	22.55	22.30	23.28	24.15	20.52	21.49	21.24	22.22	23.09
	3H	23.71	24.52	24.45	25.29	26.18	21.72	22.54	22.46	23.30	24.19
	4H	24.54	25.27	25.29	26.04	26.96	22.01	22.75	22.76	23.51	24.43
	6H	25.14	25.78	25.91	26.56	27.49	22.24	22.87	23.01	23.66	24.59
	8H	25.32	25.91	26.09	26.69	27.63	22.30	22.89	23.07	23.68	24.62
	12H	25.40	25.93	26.19	26.74	27.68	22.32	22.85	23.12	23.66	24.61
8H	4H	24.58	25.17	25.35	25.96	26.90	22.25	22.84	23.02	23.63	24.57
	6H	25.24	25.73	26.05	26.56	27.50	22.53	23.03	23.34	23.85	24.79
	8H	25.47	25.91	26.29	26.73	27.69	22.64	23.08	23.46	23.90	24.86
	12H	25.60	25.98	26.42	26.80	27.81	22.70	23.08	23.52	23.90	24.91
12H	4H	24.54	25.08	25.34	25.89	26.83	22.26	22.79	23.06	23.60	24.55
	6H	25.22	25.66	26.03	26.48	27.44	22.57	23.00	23.38	23.83	24.79
	8H	25.46	25.85	26.28	26.66	27.68	22.70	23.08	23.51	23.90	24.91