

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853795

Luminaire Tested: SQ2-FA-100U-100D-935-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P853795  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G2-2308-131-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FA-100U-100D-935-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7684.7 lumens  
Efficiency: N/A  
Efficacy: 109.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 0.95 / 0.95  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 70.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853795

CATALOG NUMBER: SQ2-FA-100U-100D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853795

CATALOG NUMBER: SQ2-FA-100U-100D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	99	95	91	88	91	87	84	82	74	72	70	62	60	59	50	49	49	43
2	91	84	79	74	84	78	73	69	66	63	60	56	53	51	46	44	43	38
3	84	75	69	63	77	70	64	60	60	56	52	51	48	45	42	40	38	34
4	77	68	60	55	71	63	57	52	54	50	46	46	43	40	39	36	34	31
5	72	61	54	48	66	57	51	46	49	44	41	42	39	36	36	33	31	28
6	67	56	48	43	62	52	45	41	45	40	36	39	35	32	33	30	28	25
7	62	51	43	38	57	48	41	37	42	37	33	36	32	29	31	28	26	23
8	58	47	39	35	54	44	37	33	38	33	30	33	30	27	29	26	24	21
9	54	43	36	31	50	40	34	30	36	31	27	31	27	25	27	24	22	20
10	51	40	33	29	47	38	31	27	33	28	25	29	25	23	25	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	41525	41525	41525	41525
5°	41306	41370	41149	41337
10°	41243	41084	41084	41084
15°	41110	40689	40786	40689
20°	40790	39058	40491	39424
25°	40255	32963	39979	33654
30°	39884	18912	39452	19166
35°	39186	16247	38688	16019
40°	38101	8545	37036	8462
45°	34632	3676	33392	3676
50°	22850	4433	21680	4142
55°	12777	8189	12121	7426
60°	6891	11525	6765	10333
65°	6074	14006	6372	15931
70°	5679	16754	5401	17670
75°	5321	14398	5446	14885
80°	4510	10284	4510	10823
85°	3946	5743	3594	6836

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 34632 cd/sqm



TEST NUMBER: P853795

CATALOG NUMBER: SQ2-FA-100U-100D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	242.0	3.1
10°-20°	686.6	8.9
20°-30°	936.2	12.2
30°-40°	786.7	10.2
40°-50°	446.8	5.8
50°-60°	237.1	3.1
60°-70°	218.3	2.8
70°-80°	160.3	2.1
80°-90°	43.0	0.6
90°-100°	263.6	3.4
100°-110°	797.1	10.4
110°-120°	778.2	10.1
120°-130°	635.9	8.3
130°-140°	519.0	6.8
140°-150°	404.0	5.3
150°-160°	291.3	3.8
160°-170°	178.3	2.3
170°-180°	60.2	0.8
0°-30°	1864.9	24.3
0°-40°	2651.6	34.5
0°-60°	3335.6	43.4
0°-90°	3757.1	48.9
90°-120°	1838.8	23.9
90°-150°	3397.8	44.2
90°-180°	3928.0	51.1
0°-180°	7684.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2572	2572	2572	2572	2572	
5°	2549	2552	2539	2550	2549	242
15°	2459	2434	2440	2434	2459	693
25°	2260	1850	2244	1889	2260	1042
35°	1988	824	1963	813	1988	1241
45°	1517	161	1462	161	1517	1109
55°	454	291	431	264	454	437
65°	159	367	167	417	159	160
75°	85	231	87	239	85	88
85°	21	31	19	37	21	24
90°	0	6	0	6	0	3
95°	33	116	33	116	33	39
105°	139	1413	139	1413	139	146
115°	247	1539	247	1539	247	244
125°	345	1218	345	1218	345	306
135°	413	1004	413	1004	413	320
145°	482	839	482	839	482	302
155°	550	714	550	714	550	253
165°	601	659	601	659	601	169
175°	629	633	629	633	629	60
180°	631	631	631	631	631	



TEST NUMBER: P853795

CATALOG NUMBER: SQ2-FA-100U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9
2.5°	2557.9	2595.8	2562.6	2558.2	2571.9	2568.8	2564.1	2582.0	2551.7	2582.0	2557.9
5°	2548.6	2592.2	2542.8	2529.7	2552.5	2537.3	2550.5	2576.8	2538.9	2573.0	2535.0
7.5°	2532.7	2571.4	2512.1	2503.7	2526.1	2512.8	2518.3	2554.8	2523.0	2545.4	2511.0
10°	2515.6	2549.7	2490.4	2485.1	2505.9	2492.6	2498.2	2536.3	2505.9	2526.8	2492.3
12.5°	2497.0	2523.5	2464.0	2461.7	2479.5	2470.8	2473.3	2505.4	2481.1	2502.0	2469.1
15°	2459.4	2484.0	2424.5	2415.2	2434.2	2426.6	2430.3	2458.9	2440.0	2453.2	2424.5
17.5°	2412.8	2432.5	2373.2	2345.3	2346.1	2355.6	2373.2	2407.8	2390.7	2408.2	2367.4
20°	2374.0	2396.8	2331.4	2277.0	2273.2	2282.7	2331.4	2366.1	2356.6	2375.5	2317.8
22.5°	2329.0	2344.2	2284.8	2193.0	2180.1	2189.6	2278.6	2319.6	2316.2	2329.1	2257.3
25°	2259.6	2274.8	2166.5	2034.3	1850.3	2022.9	2170.4	2244.1	2244.1	2255.5	2160.7
27.5°	2189.0	2189.4	1993.5	1306.5	1152.5	1259.4	1990.8	2150.6	2168.8	2163.1	1976.8
30°	2139.3	2126.1	1766.9	1056.1	1014.4	1040.9	1768.9	2085.7	2116.1	2095.2	1722.3
32.5°	2081.9	2044.4	1304.6	970.9	936.8	960.3	1261.5	2008.7	2061.8	2016.6	1354.6
35°	1988.1	1889.4	995.0	858.5	824.3	854.7	987.2	1856.6	1962.8	1841.5	1028.0
37.5°	1886.8	1501.8	875.9	683.8	610.2	669.0	871.6	1485.7	1845.7	1451.2	875.1
40°	1807.7	1179.9	787.5	500.2	405.4	471.7	781.6	1125.7	1757.2	1211.1	768.1
42.5°	1702.2	1036.5	632.3	317.7	248.7	290.8	606.3	1012.6	1648.6	1049.3	611.4
45°	1516.7	890.9	374.3	174.3	161.0	168.6	345.2	874.5	1462.4	855.6	382.1
47.5°	1201.4	679.5	240.5	148.1	162.5	148.1	233.1	657.9	1134.6	656.7	240.1
50°	909.7	530.4	186.2	149.9	176.5	149.9	180.4	512.3	863.1	559.7	184.3
52.5°	673.8	443.2	152.1	164.4	212.2	167.4	147.8	431.4	639.7	451.5	143.9
55°	453.9	347.7	122.2	217.0	290.9	222.7	122.2	337.7	430.6	333.9	118.3
57.5°	287.8	258.6	123.7	279.0	332.1	284.3	125.7	249.3	276.2	250.4	108.6
60°	213.4	203.9	137.7	296.2	356.9	300.0	139.6	196.2	209.5	194.3	116.4
62.5°	176.1	160.6	165.6	320.8	370.8	312.4	169.1	153.1	183.1	146.7	128.8
65°	159.0	104.0	195.9	324.9	366.6	324.9	197.8	98.5	166.8	106.1	174.6
67.5°	143.5	77.2	189.3	322.6	368.9	323.4	184.6	73.6	137.7	71.7	178.4
70°	120.3	69.0	178.4	328.4	354.9	317.0	178.4	67.0	114.4	65.1	209.5
72.5°	100.1	65.6	166.0	303.2	314.6	291.8	167.6	65.2	100.5	58.7	197.1
75°	85.3	64.5	159.0	242.2	230.8	230.8	155.2	62.6	87.3	58.8	153.2
77.5°	64.0	57.2	131.9	158.1	149.3	149.3	129.6	55.2	60.9	51.8	124.5
80°	48.5	52.3	108.6	116.2	110.6	110.6	104.7	50.4	48.5	48.5	102.8
82.5°	37.6	44.5	83.8	85.2	81.1	79.6	81.5	44.1	37.6	40.7	79.5
85°	21.3	30.8	44.6	36.7	31.0	29.1	42.7	28.9	19.4	28.9	42.7
87.5°	7.8	14.2	8.6	7.6	7.4	7.6	8.6	14.2	7.8	12.7	10.1
90°	0.0	1.9	11.9	6.9	5.9	6.9	11.9	1.9	0.0	1.9	11.9
92.5°	11.1	44.8	160.9	53.4	38.4	53.4	160.9	44.8	11.1	44.8	160.9
95°	32.7	103.4	497.3	183.7	115.9	183.7	497.3	103.4	32.7	103.4	497.3
97.5°	63.2	131.6	783.8	518.7	315.8	518.7	783.8	131.6	63.2	131.6	783.8
100°	82.2	149.1	875.8	846.7	568.7	846.7	875.8	149.1	82.2	149.1	875.8
102.5°	103.6	168.1	856.8	1187.5	946.7	1187.5	856.8	168.1	103.6	168.1	856.8
105°	138.7	194.9	782.7	1486.4	1412.7	1486.4	782.7	194.9	138.7	194.9	782.7
107.5°	172.0	225.6	711.3	1515.9	1601.2	1515.9	711.3	225.6	172.0	225.6	711.3
110°	194.2	245.5	675.7	1478.7	1633.7	1478.7	675.7	245.5	194.2	245.5	675.7



TEST NUMBER: P853795

CATALOG NUMBER: SQ2-FA-100U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	215.6	265.4	654.3	1416.2	1612.3	1416.2	654.3	265.4	215.6	265.4	654.3
115°	246.7	294.1	633.1	1309.9	1538.6	1309.9	633.1	294.1	246.7	294.1	633.1
117.5°	277.6	322.5	625.5	1210.4	1444.4	1210.4	625.5	322.5	277.6	322.5	625.5
120°	298.2	340.8	623.1	1152.3	1377.1	1152.3	623.1	340.8	298.2	340.8	623.1
122.5°	317.2	357.5	623.1	1101.2	1308.9	1101.2	623.1	357.5	317.2	357.5	623.1
125°	344.8	382.5	624.1	1034.5	1217.6	1034.5	624.1	382.5	344.8	382.5	624.1
127.5°	367.2	406.3	623.1	984.1	1140.3	984.1	623.1	406.3	367.2	406.3	623.1
130°	381.4	422.1	623.1	955.3	1096.7	955.3	623.1	422.1	381.4	422.1	623.1
132.5°	394.1	435.6	622.4	928.9	1059.5	928.9	622.4	435.6	394.1	435.6	622.4
135°	413.1	456.7	620.2	892.2	1003.6	892.2	620.2	456.7	413.1	456.7	620.2
137.5°	434.3	475.8	620.2	853.0	956.2	853.0	620.2	475.8	434.3	475.8	620.2
140°	447.8	488.5	620.2	827.5	925.3	827.5	620.2	488.5	447.8	488.5	620.2
142.5°	461.3	500.4	619.4	804.2	889.6	804.2	619.4	500.4	461.3	500.4	619.4
145°	482.5	518.3	620.2	767.4	839.1	767.4	620.2	518.3	482.5	518.3	620.2
147.5°	503.7	534.1	621.4	737.1	792.2	737.1	621.4	534.1	503.7	534.1	621.4
150°	517.1	545.2	622.2	720.3	766.8	720.3	622.2	545.2	517.1	545.2	622.2
152.5°	529.8	554.8	622.9	705.8	743.8	705.8	622.9	554.8	529.8	554.8	622.9
155°	549.8	568.2	624.1	688.1	714.3	688.1	624.1	568.2	549.8	568.2	624.1
157.5°	567.3	582.2	625.3	675.1	693.3	675.1	625.3	582.2	567.3	582.2	625.3
160°	577.6	590.2	626.1	667.0	680.6	667.0	626.1	590.2	577.6	590.2	626.1
162.5°	587.9	597.4	626.9	659.9	671.1	659.9	626.9	597.4	587.9	597.4	626.9
165°	601.4	608.1	627.1	651.1	658.8	651.1	627.1	608.1	601.4	608.1	627.1
167.5°	612.8	616.3	628.3	644.2	647.5	644.2	628.3	616.3	612.8	616.3	628.3
170°	619.2	621.1	629.1	641.0	642.0	641.0	629.1	621.1	619.2	621.1	629.1
172.5°	623.1	624.3	629.1	637.8	638.0	637.8	629.1	624.3	623.1	624.3	629.1
175°	629.1	629.1	630.1	635.0	633.1	635.0	630.1	629.1	629.1	629.1	630.1
177.5°	631.9	631.1	630.3	632.6	631.1	632.6	630.3	631.1	631.9	631.1	630.3
180°	631.1	631.1	631.1	631.1	631.1	631.1	631.1	631.1	631.1	631.1	631.1



TEST NUMBER: P853795

CATALOG NUMBER: SQ2-FA-100U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
0°	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9
2.5°	2551.9	2562.6	2562.6	2556.3	2586.7	2557.9
5°	2525.9	2550.5	2539.1	2538.9	2577.0	2548.6
7.5°	2507.6	2530.7	2520.1	2517.9	2555.4	2532.7
10°	2488.8	2505.9	2498.3	2504.0	2538.4	2515.6
12.5°	2462.5	2482.6	2475.1	2483.8	2515.2	2497.0
15°	2417.1	2434.2	2437.9	2441.9	2478.3	2459.4
17.5°	2342.0	2350.4	2369.3	2396.1	2434.1	2412.8
20°	2283.1	2294.5	2305.9	2352.7	2396.8	2374.0
22.5°	2216.1	2212.3	2238.8	2293.7	2348.8	2329.0
25°	2035.2	1889.1	2050.3	2191.7	2265.3	2259.6
27.5°	1417.1	1229.7	1395.4	2023.0	2177.6	2189.0
30°	1115.2	1028.0	1113.3	1805.7	2112.8	2139.3
32.5°	990.1	930.2	982.2	1374.4	2031.1	2081.9
35°	854.4	812.7	854.4	1028.0	1870.5	1988.1
37.5°	683.9	598.5	682.4	888.3	1512.1	1886.8
40°	509.6	401.5	494.4	795.2	1208.4	1807.7
42.5°	339.5	258.7	321.3	626.1	1045.2	1702.2
45°	183.7	161.0	176.2	378.2	853.0	1516.7
47.5°	144.1	152.4	144.1	238.6	652.5	1201.4
50°	138.3	164.9	138.3	184.3	539.8	909.7
52.5°	150.8	178.8	149.2	145.5	440.5	673.8
55°	170.9	263.8	172.8	118.3	323.0	453.9
57.5°	243.3	296.8	245.9	112.1	248.8	287.8
60°	249.9	320.0	248.0	118.3	192.5	213.4
62.5°	295.5	396.1	295.2	135.4	143.1	176.1
65°	379.1	417.0	382.9	172.6	102.2	159.0
67.5°	359.8	386.7	356.0	185.0	70.3	143.5
70°	353.5	374.3	349.7	211.4	65.3	120.3
72.5°	329.8	332.4	323.0	195.9	58.7	100.1
75°	255.6	238.6	246.2	168.7	58.8	85.3
77.5°	158.9	152.1	153.2	128.8	51.9	64.0
80°	120.2	116.4	114.5	108.6	48.5	48.5
82.5°	89.1	85.3	83.4	83.8	40.7	37.6
85°	40.6	36.9	35.0	48.5	28.9	21.3
87.5°	9.1	8.9	7.6	10.1	11.2	7.8
90°	6.9	5.9	6.9	11.9	1.9	0.0
92.5°	53.4	38.4	53.4	160.9	44.8	11.1
95°	183.7	115.9	183.7	497.3	103.4	32.7
97.5°	518.7	315.8	518.7	783.8	131.6	63.2
100°	846.7	568.7	846.7	875.8	149.1	82.2
102.5°	1187.5	946.7	1187.5	856.8	168.1	103.6
105°	1486.4	1412.7	1486.4	782.7	194.9	138.7
107.5°	1515.9	1601.2	1515.9	711.3	225.6	172.0
110°	1478.7	1633.7	1478.7	675.7	245.5	194.2





TEST NUMBER: P853795

CATALOG NUMBER: SQ2-FA-100U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	1416.2	1612.3	1416.2	654.3	265.4	215.6
115°	1309.9	1538.6	1309.9	633.1	294.1	246.7
117.5°	1210.4	1444.4	1210.4	625.5	322.5	277.6
120°	1152.3	1377.1	1152.3	623.1	340.8	298.2
122.5°	1101.2	1308.9	1101.2	623.1	357.5	317.2
125°	1034.5	1217.6	1034.5	624.1	382.5	344.8
127.5°	984.1	1140.3	984.1	623.1	406.3	367.2
130°	955.3	1096.7	955.3	623.1	422.1	381.4
132.5°	928.9	1059.5	928.9	622.4	435.6	394.1
135°	892.2	1003.6	892.2	620.2	456.7	413.1
137.5°	853.0	956.2	853.0	620.2	475.8	434.3
140°	827.5	925.3	827.5	620.2	488.5	447.8
142.5°	804.2	889.6	804.2	619.4	500.4	461.3
145°	767.4	839.1	767.4	620.2	518.3	482.5
147.5°	737.1	792.2	737.1	621.4	534.1	503.7
150°	720.3	766.8	720.3	622.2	545.2	517.1
152.5°	705.8	743.8	705.8	622.9	554.8	529.8
155°	688.1	714.3	688.1	624.1	568.2	549.8
157.5°	675.1	693.3	675.1	625.3	582.2	567.3
160°	667.0	680.6	667.0	626.1	590.2	577.6
162.5°	659.9	671.1	659.9	626.9	597.4	587.9
165°	651.1	658.8	651.1	627.1	608.1	601.4
167.5°	644.2	647.5	644.2	628.3	616.3	612.8
170°	641.0	642.0	641.0	629.1	621.1	619.2
172.5°	637.8	638.0	637.8	629.1	624.3	623.1
175°	635.0	633.1	635.0	630.1	629.1	629.1
177.5°	632.6	631.1	632.6	630.3	631.1	631.9
180°	631.1	631.1	631.1	631.1	631.1	631.1



TEST NUMBER: P853795

CATALOG NUMBER: SQ2-FA-100U-100D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.76	13.51	13.75	14.49	15.79	11.61	12.37	12.60	13.35	14.65
	3H	13.45	14.13	14.45	15.12	16.44	17.76	18.43	18.76	19.43	20.75
	4H	13.86	14.50	14.87	15.49	16.82	19.03	19.67	20.04	20.67	21.99
	6H	14.21	14.80	15.23	15.80	17.14	19.64	20.22	20.66	21.23	22.56
	8H	14.33	14.88	15.35	15.90	17.23	19.76	20.32	20.78	21.33	22.67
	12H	14.40	14.92	15.42	15.94	17.29	19.80	20.33	20.83	21.34	22.69
4H	2H	13.14	13.78	14.16	14.78	16.10	12.14	12.78	13.16	13.77	15.10
	3H	14.14	14.67	15.16	15.69	17.03	18.46	18.99	19.48	20.02	21.35
	4H	14.70	15.18	15.73	16.20	17.56	19.91	20.39	20.94	21.41	22.77
	6H	15.17	15.59	16.21	16.63	17.99	20.64	21.06	21.68	22.10	23.46
	8H	15.34	15.73	16.38	16.76	18.13	20.81	21.20	21.85	22.23	23.60
	12H	15.45	15.80	16.51	16.85	18.23	20.87	21.22	21.92	22.27	23.64
8H	4H	15.79	16.18	16.83	17.22	18.59	20.03	20.42	21.07	21.45	22.82
	6H	16.40	16.72	17.46	17.79	19.16	20.90	21.22	21.97	22.30	23.67
	8H	16.63	16.91	17.70	17.98	19.36	21.15	21.43	22.23	22.50	23.88
	12H	16.80	17.05	17.87	18.10	19.53	21.27	21.52	22.34	22.57	24.01
12H	4H	15.93	16.28	16.99	17.33	18.71	19.98	20.33	21.04	21.38	22.76
	6H	16.67	16.95	17.74	18.02	19.40	20.91	21.19	21.98	22.26	23.64
	8H	16.97	17.21	18.04	18.27	19.70	21.19	21.44	22.26	22.49	23.92