

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853807

Luminaire Tested: SQ2-FA-125U-100D-935-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P853807  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FA-125U-100D-935-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8727.0 lumens  
Efficiency: N/A  
Efficacy: 107.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 0.95 / 0.95  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 81.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P853807

CATALOG NUMBER: SQ2-FA-125U-100D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P853807

CATALOG NUMBER: SQ2-FA-125U-100D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	97	93	90	87	89	85	82	80	71	69	67	58	56	55	45	44	44	38
2	89	83	77	72	82	76	71	67	63	60	57	52	50	48	41	40	39	34
3	82	74	67	62	75	68	62	58	57	53	50	47	44	42	38	36	34	30
4	76	66	59	54	70	61	55	50	52	47	44	43	40	37	35	33	31	27
5	70	60	52	47	64	55	49	44	47	42	39	39	36	33	32	30	28	25
6	65	54	47	41	60	50	44	39	43	38	34	36	33	30	30	27	25	22
7	61	49	42	37	56	46	40	35	39	35	31	33	30	27	28	25	23	20
8	57	45	38	33	52	42	36	31	36	31	28	31	27	25	26	23	21	19
9	53	42	35	30	49	39	33	29	34	29	25	29	25	23	24	21	20	17
10	50	38	32	27	46	36	30	26	31	27	23	27	23	21	23	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	41525	41525	41525	41525
5°	41306	41370	41149	41337
10°	41243	41084	41084	41084
15°	41110	40689	40786	40689
20°	40790	39058	40491	39424
25°	40255	32963	39979	33654
30°	39884	18912	39452	19166
35°	39186	16247	38688	16019
40°	38101	8545	37036	8462
45°	34632	3676	33392	3676
50°	22850	4433	21680	4142
55°	12777	8189	12121	7426
60°	6891	11525	6765	10333
65°	6074	14006	6372	15931
70°	5679	16754	5401	17670
75°	5321	14398	5446	14885
80°	4510	10284	4510	10823
85°	3946	5743	3594	6836

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 34632 cd/sqm



TEST NUMBER: P853807

CATALOG NUMBER: SQ2-FA-125U-100D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	242.0	2.8
10°-20°	686.6	7.9
20°-30°	936.2	10.7
30°-40°	786.7	9.0
40°-50°	446.8	5.1
50°-60°	237.1	2.7
60°-70°	218.3	2.5
70°-80°	160.3	1.8
80°-90°	42.8	0.5
90°-100°	308.2	3.5
100°-110°	1003.2	11.5
110°-120°	992.4	11.4
120°-130°	811.0	9.3
130°-140°	662.8	7.6
140°-150°	516.3	5.9
150°-160°	372.1	4.3
160°-170°	227.4	2.6
170°-180°	76.7	0.9
0°-30°	1864.9	21.4
0°-40°	2651.6	30.4
0°-60°	3335.6	38.2
0°-90°	3756.9	43.0
90°-120°	2303.8	26.4
90°-150°	4293.8	49.2
90°-180°	4970.0	56.9
0°-180°	8727.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2572	2572	2572	2572	2572	
5°	2549	2552	2539	2550	2549	242
15°	2459	2434	2440	2434	2459	693
25°	2260	1850	2244	1889	2260	1042
35°	1988	824	1963	813	1988	1241
45°	1517	161	1462	161	1517	1109
55°	454	291	431	264	454	437
65°	159	367	167	417	159	160
75°	85	231	87	239	85	88
85°	21	31	19	37	21	24
90°	0	6	0	6	0	3
95°	42	124	42	124	42	48
105°	170	1797	170	1797	170	182
115°	315	1963	315	1963	315	312
125°	438	1553	438	1553	438	390
135°	529	1282	529	1282	529	409
145°	618	1072	618	1072	618	387
155°	706	910	706	910	706	325
165°	770	839	770	839	770	217
175°	803	806	803	806	803	76
180°	806	806	806	806	806	



TEST NUMBER: P853807

CATALOG NUMBER: SQ2-FA-125U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9
2.5°	2557.9	2595.8	2562.6	2558.2	2571.9	2568.8	2564.1	2582.0	2551.7	2582.0	2557.9
5°	2548.6	2592.2	2542.8	2529.7	2552.5	2537.3	2550.5	2576.8	2538.9	2573.0	2535.0
7.5°	2532.7	2571.4	2512.1	2503.7	2526.1	2512.8	2518.3	2554.8	2523.0	2545.4	2511.0
10°	2515.6	2549.7	2490.4	2485.1	2505.9	2492.6	2498.2	2536.3	2505.9	2526.8	2492.3
12.5°	2497.0	2523.5	2464.0	2461.7	2479.5	2470.8	2473.3	2505.4	2481.1	2502.0	2469.1
15°	2459.4	2484.0	2424.5	2415.2	2434.2	2426.6	2430.3	2458.9	2440.0	2453.2	2424.5
17.5°	2412.8	2432.5	2373.2	2345.3	2346.1	2355.6	2373.2	2407.8	2390.7	2408.2	2367.4
20°	2374.0	2396.8	2331.4	2277.0	2273.2	2282.7	2331.4	2366.1	2356.6	2375.5	2317.8
22.5°	2329.0	2344.2	2284.8	2193.0	2180.1	2189.6	2278.6	2319.6	2316.2	2329.1	2257.3
25°	2259.6	2274.8	2166.5	2034.3	1850.3	2022.9	2170.4	2244.1	2244.1	2255.5	2160.7
27.5°	2189.0	2189.4	1993.5	1306.5	1152.5	1259.4	1990.8	2150.6	2168.8	2163.1	1976.8
30°	2139.3	2126.1	1766.9	1056.1	1014.4	1040.9	1768.9	2085.7	2116.1	2095.2	1722.3
32.5°	2081.9	2044.4	1304.6	970.9	936.8	960.3	1261.5	2008.7	2061.8	2016.6	1354.6
35°	1988.1	1889.4	995.0	858.5	824.3	854.7	987.2	1856.6	1962.8	1841.5	1028.0
37.5°	1886.8	1501.8	875.9	683.8	610.2	669.0	871.6	1485.7	1845.7	1451.2	875.1
40°	1807.7	1179.9	787.5	500.2	405.4	471.7	781.6	1125.7	1757.2	1211.1	768.1
42.5°	1702.2	1036.5	632.3	317.7	248.7	290.8	606.3	1012.6	1648.6	1049.3	611.4
45°	1516.7	890.9	374.3	174.3	161.0	168.6	345.2	874.5	1462.4	855.6	382.1
47.5°	1201.4	679.5	240.5	148.1	162.5	148.1	233.1	657.9	1134.6	656.7	240.1
50°	909.7	530.4	186.2	149.9	176.5	149.9	180.4	512.3	863.1	559.7	184.3
52.5°	673.8	443.2	152.1	164.4	212.2	167.4	147.8	431.4	639.7	451.5	143.9
55°	453.9	347.7	122.2	217.0	290.9	222.7	122.2	337.7	430.6	333.9	118.3
57.5°	287.8	258.6	123.7	279.0	332.1	284.3	125.7	249.3	276.2	250.4	108.6
60°	213.4	203.9	137.7	296.2	356.9	300.0	139.6	196.2	209.5	194.3	116.4
62.5°	176.1	160.6	165.6	320.8	370.8	312.4	169.1	153.1	183.1	146.7	128.8
65°	159.0	104.0	195.9	324.9	366.6	324.9	197.8	98.5	166.8	106.1	174.6
67.5°	143.5	77.2	189.3	322.6	368.9	323.4	184.6	73.6	137.7	71.7	178.4
70°	120.3	69.0	178.4	328.4	354.9	317.0	178.4	67.0	114.4	65.1	209.5
72.5°	100.1	65.6	166.0	303.2	314.6	291.8	167.6	65.2	100.5	58.7	197.1
75°	85.3	64.5	159.0	242.2	230.8	230.8	155.2	62.6	87.3	58.8	153.2
77.5°	64.0	57.2	131.9	158.1	149.3	149.3	129.6	55.2	60.9	51.8	124.5
80°	48.5	52.3	108.6	116.2	110.6	110.6	104.7	50.4	48.5	48.5	102.8
82.5°	37.6	44.5	83.8	85.2	81.1	79.6	81.5	44.1	37.6	40.7	79.5
85°	21.3	30.8	44.6	36.7	31.0	29.1	42.7	28.9	19.4	28.9	42.7
87.5°	7.8	14.4	7.6	7.4	7.4	7.4	7.6	14.4	7.8	12.9	9.1
90°	0.0	2.9	6.9	5.9	5.9	5.9	6.9	2.9	0.0	2.9	6.9
92.5°	14.3	51.3	163.9	54.0	41.6	54.0	163.9	51.3	14.3	51.3	163.9
95°	41.6	126.9	564.8	201.4	123.9	201.4	564.8	126.9	41.6	126.9	564.8
97.5°	78.3	165.1	958.5	583.8	356.3	583.8	958.5	165.1	78.3	165.1	958.5
100°	102.1	187.3	1106.8	986.9	640.1	986.9	1106.8	187.3	102.1	187.3	1106.8
102.5°	129.0	211.2	1088.5	1460.1	1110.1	1460.1	1088.5	211.2	129.0	211.2	1088.5
105°	170.4	246.0	993.8	1898.2	1797.4	1898.2	993.8	246.0	170.4	246.0	993.8
107.5°	215.2	286.3	903.9	1936.2	2042.9	1936.2	903.9	286.3	215.2	286.3	903.9
110°	247.7	312.6	861.0	1889.0	2081.8	1889.0	861.0	312.6	247.7	312.6	861.0



TEST NUMBER: P853807

CATALOG NUMBER: SQ2-FA-125U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	274.7	338.8	834.1	1803.8	2052.4	1803.8	834.1	338.8	274.7	338.8	834.1
115°	315.1	376.1	809.5	1668.3	1962.9	1668.3	809.5	376.1	315.1	376.1	809.5
117.5°	356.7	411.7	800.0	1544.3	1837.4	1544.3	800.0	411.7	356.7	411.7	800.0
120°	380.5	434.7	797.6	1468.0	1751.8	1468.0	797.6	434.7	380.5	434.7	797.6
122.5°	403.5	457.0	798.4	1401.7	1666.2	1401.7	798.4	457.0	403.5	457.0	798.4
125°	438.0	488.3	798.6	1317.2	1552.7	1317.2	798.6	488.3	438.0	488.3	798.6
127.5°	467.5	519.0	798.4	1253.9	1450.2	1253.9	798.4	519.0	467.5	519.0	798.4
130°	486.5	538.8	797.6	1217.8	1393.1	1217.8	797.6	538.8	486.5	538.8	797.6
132.5°	503.2	557.8	796.8	1184.2	1348.7	1184.2	796.8	557.8	503.2	557.8	796.8
135°	529.1	584.3	794.7	1136.8	1282.2	1136.8	794.7	584.3	529.1	584.3	794.7
137.5°	554.5	610.1	792.5	1088.7	1217.8	1088.7	792.5	610.1	554.5	610.1	792.5
140°	572.7	626.0	791.7	1056.0	1178.1	1056.0	791.7	626.0	572.7	626.0	791.7
142.5°	590.1	641.1	791.7	1024.8	1133.7	1024.8	791.7	641.1	590.1	641.1	791.7
145°	618.3	663.8	792.7	979.1	1072.1	979.1	792.7	663.8	618.3	663.8	792.7
147.5°	645.6	685.2	794.1	940.2	1012.1	940.2	794.1	685.2	645.6	685.2	794.1
150°	663.9	698.7	795.7	916.9	978.0	916.9	795.7	698.7	663.9	698.7	795.7
152.5°	682.1	710.8	796.4	899.2	947.8	899.2	796.4	710.8	682.1	710.8	796.4
155°	705.5	728.7	797.6	876.7	909.6	876.7	797.6	728.7	705.5	728.7	797.6
157.5°	727.7	744.3	798.8	860.0	883.0	860.0	798.8	744.3	727.7	744.3	798.8
160°	741.2	754.7	799.6	849.6	868.0	849.6	799.6	754.7	741.2	754.7	799.6
162.5°	753.0	763.5	799.6	840.7	854.5	840.7	799.6	763.5	753.0	763.5	799.6
165°	769.9	776.7	799.6	829.6	839.2	829.6	799.6	776.7	769.9	776.7	799.6
167.5°	781.8	786.0	799.8	821.1	826.2	821.1	799.8	786.0	781.8	786.0	799.8
170°	789.7	791.6	800.6	815.5	817.4	815.5	800.6	791.6	789.7	791.6	800.6
172.5°	795.3	796.4	802.2	812.3	811.9	812.3	802.2	796.4	795.3	796.4	802.2
175°	802.6	802.6	802.6	808.5	806.5	808.5	802.6	802.6	802.6	802.6	802.6
177.5°	805.6	804.8	804.0	807.9	804.8	807.9	804.0	804.8	805.6	804.8	804.0
180°	805.6	805.6	805.6	805.6	805.6	805.6	805.6	805.6	805.6	805.6	805.6



TEST NUMBER: P853807

CATALOG NUMBER: SQ2-FA-125U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
0°	2571.9	2571.9	2571.9	2571.9	2571.9	2571.9
2.5°	2551.9	2562.6	2562.6	2556.3	2586.7	2557.9
5°	2525.9	2550.5	2539.1	2538.9	2577.0	2548.6
7.5°	2507.6	2530.7	2520.1	2517.9	2555.4	2532.7
10°	2488.8	2505.9	2498.3	2504.0	2538.4	2515.6
12.5°	2462.5	2482.6	2475.1	2483.8	2515.2	2497.0
15°	2417.1	2434.2	2437.9	2441.9	2478.3	2459.4
17.5°	2342.0	2350.4	2369.3	2396.1	2434.1	2412.8
20°	2283.1	2294.5	2305.9	2352.7	2396.8	2374.0
22.5°	2216.1	2212.3	2238.8	2293.7	2348.8	2329.0
25°	2035.2	1889.1	2050.3	2191.7	2265.3	2259.6
27.5°	1417.1	1229.7	1395.4	2023.0	2177.6	2189.0
30°	1115.2	1028.0	1113.3	1805.7	2112.8	2139.3
32.5°	990.1	930.2	982.2	1374.4	2031.1	2081.9
35°	854.4	812.7	854.4	1028.0	1870.5	1988.1
37.5°	683.9	598.5	682.4	888.3	1512.1	1886.8
40°	509.6	401.5	494.4	795.2	1208.4	1807.7
42.5°	339.5	258.7	321.3	626.1	1045.2	1702.2
45°	183.7	161.0	176.2	378.2	853.0	1516.7
47.5°	144.1	152.4	144.1	238.6	652.5	1201.4
50°	138.3	164.9	138.3	184.3	539.8	909.7
52.5°	150.8	178.8	149.2	145.5	440.5	673.8
55°	170.9	263.8	172.8	118.3	323.0	453.9
57.5°	243.3	296.8	245.9	112.1	248.8	287.8
60°	249.9	320.0	248.0	118.3	192.5	213.4
62.5°	295.5	396.1	295.2	135.4	143.1	176.1
65°	379.1	417.0	382.9	172.6	102.2	159.0
67.5°	359.8	386.7	356.0	185.0	70.3	143.5
70°	353.5	374.3	349.7	211.4	65.3	120.3
72.5°	329.8	332.4	323.0	195.9	58.7	100.1
75°	255.6	238.6	246.2	168.7	58.8	85.3
77.5°	158.9	152.1	153.2	128.8	51.9	64.0
80°	120.2	116.4	114.5	108.6	48.5	48.5
82.5°	89.1	85.3	83.4	83.8	40.7	37.6
85°	40.6	36.9	35.0	48.5	28.9	21.3
87.5°	8.9	8.9	7.4	9.1	11.4	7.8
90°	5.9	5.9	5.9	6.9	2.9	0.0
92.5°	54.0	41.6	54.0	163.9	51.3	14.3
95°	201.4	123.9	201.4	564.8	126.9	41.6
97.5°	583.8	356.3	583.8	958.5	165.1	78.3
100°	986.9	640.1	986.9	1106.8	187.3	102.1
102.5°	1460.1	1110.1	1460.1	1088.5	211.2	129.0
105°	1898.2	1797.4	1898.2	993.8	246.0	170.4
107.5°	1936.2	2042.9	1936.2	903.9	286.3	215.2
110°	1889.0	2081.8	1889.0	861.0	312.6	247.7





TEST NUMBER: P853807

CATALOG NUMBER: SQ2-FA-125U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	1803.8	2052.4	1803.8	834.1	338.8	274.7
115°	1668.3	1962.9	1668.3	809.5	376.1	315.1
117.5°	1544.3	1837.4	1544.3	800.0	411.7	356.7
120°	1468.0	1751.8	1468.0	797.6	434.7	380.5
122.5°	1401.7	1666.2	1401.7	798.4	457.0	403.5
125°	1317.2	1552.7	1317.2	798.6	488.3	438.0
127.5°	1253.9	1450.2	1253.9	798.4	519.0	467.5
130°	1217.8	1393.1	1217.8	797.6	538.8	486.5
132.5°	1184.2	1348.7	1184.2	796.8	557.8	503.2
135°	1136.8	1282.2	1136.8	794.7	584.3	529.1
137.5°	1088.7	1217.8	1088.7	792.5	610.1	554.5
140°	1056.0	1178.1	1056.0	791.7	626.0	572.7
142.5°	1024.8	1133.7	1024.8	791.7	641.1	590.1
145°	979.1	1072.1	979.1	792.7	663.8	618.3
147.5°	940.2	1012.1	940.2	794.1	685.2	645.6
150°	916.9	978.0	916.9	795.7	698.7	663.9
152.5°	899.2	947.8	899.2	796.4	710.8	682.1
155°	876.7	909.6	876.7	797.6	728.7	705.5
157.5°	860.0	883.0	860.0	798.8	744.3	727.7
160°	849.6	868.0	849.6	799.6	754.7	741.2
162.5°	840.7	854.5	840.7	799.6	763.5	753.0
165°	829.6	839.2	829.6	799.6	776.7	769.9
167.5°	821.1	826.2	821.1	799.8	786.0	781.8
170°	815.5	817.4	815.5	800.6	791.6	789.7
172.5°	812.3	811.9	812.3	802.2	796.4	795.3
175°	808.5	806.5	808.5	802.6	802.6	802.6
177.5°	807.9	804.8	807.9	804.0	804.8	805.6
180°	805.6	805.6	805.6	805.6	805.6	805.6



TEST NUMBER: P853807

CATALOG NUMBER: SQ2-FA-125U-100D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.16	12.88	13.20	13.91	15.29	11.02	11.74	12.06	12.77	14.14
	3H	12.86	13.50	13.90	14.54	15.93	17.17	17.81	18.21	18.85	20.24
	4H	13.26	13.87	14.32	14.91	16.31	18.44	19.05	19.49	20.09	21.49
	6H	13.61	14.17	14.68	15.22	16.63	19.04	19.60	20.10	20.64	22.06
	8H	13.73	14.26	14.80	15.32	16.73	19.16	19.69	20.23	20.75	22.16
	12H	13.80	14.30	14.87	15.35	16.78	19.20	19.70	20.27	20.76	22.19
4H	2H	12.55	13.16	13.61	14.20	15.60	11.54	12.15	12.61	13.19	14.59
	3H	13.54	14.05	14.61	15.11	16.53	17.86	18.37	18.93	19.43	20.85
	4H	14.10	14.56	15.17	15.62	17.06	19.31	19.77	20.38	20.83	22.27
	6H	14.57	14.97	15.65	16.05	17.48	20.04	20.44	21.12	21.52	22.95
	8H	14.74	15.11	15.82	16.18	17.63	20.21	20.58	21.29	21.65	23.10
	12H	14.85	15.18	15.94	16.27	17.72	20.26	20.60	21.36	21.69	23.14
8H	4H	15.19	15.56	16.27	16.64	18.08	19.43	19.80	20.51	20.87	22.32
	6H	15.80	16.10	16.90	17.22	18.66	20.30	20.61	21.40	21.72	23.17
	8H	16.03	16.30	17.14	17.40	18.86	20.55	20.82	21.66	21.92	23.38
	12H	16.20	16.43	17.31	17.53	19.03	20.67	20.90	21.78	22.00	23.50
12H	4H	15.33	15.67	16.43	16.75	18.20	19.38	19.72	20.48	20.80	22.25
	6H	16.07	16.34	17.18	17.44	18.90	20.31	20.58	21.42	21.68	23.14
	8H	16.37	16.60	17.48	17.69	19.20	20.59	20.82	21.70	21.92	23.42