

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855327

Luminaire Tested: SQ2-PP3-150U-100D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855327
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-14, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PP3-150U-100D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12315.7 lumens
Efficiency: N/A
Efficacy: 130.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 94.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855327

CATALOG NUMBER: SQ2-PP3-150U-100D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855327

CATALOG NUMBER: SQ2-PP3-150U-100D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	93	89	86	89	85	82	79	71	69	67	57	56	55	45	44	43	38
2	89	82	76	71	81	75	70	66	62	59	56	51	48	46	40	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	40	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	41	41	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16	13
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	34525	34525	34525
5°	34255	34546	34877
10°	34428	34687	35131
15°	34345	34684	35214
20°	34099	34916	35924
25°	33905	35356	37812
30°	33715	36074	38602
35°	33236	36177	38672
40°	32349	36113	35732
45°	31383	34477	27202
50°	30147	29411	22654
55°	28059	24752	16287
60°	24161	21241	11677
65°	20378	16409	11488
70°	16966	12911	10990
75°	14379	11135	10293
80°	12190	9670	9242
85°	9633	7966	5039

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 34477 cd/sqm



TEST NUMBER: P855327

CATALOG NUMBER: SQ2-PP3-150U-100D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.6	1.7
10°-20°	589.3	4.8
20°-30°	923.2	7.5
30°-40°	1138.8	9.2
40°-50°	1072.2	8.7
50°-60°	759.2	6.2
60°-70°	432.6	3.5
70°-80°	214.0	1.7
80°-90°	53.6	0.4
90°-100°	427.8	3.5
100°-110°	1400.7	11.4
110°-120°	1384.8	11.2
120°-130°	1132.0	9.2
130°-140°	923.8	7.5
140°-150°	718.9	5.8
150°-160°	517.6	4.2
160°-170°	316.7	2.6
170°-180°	107.0	0.9
0°-30°	1716.0	13.9
0°-40°	2854.8	23.2
0°-60°	4686.2	38.1
0°-90°	5386.4	43.7
90°-120°	3213.3	26.1
90°-150°	5988.0	48.6
90°-180°	6929.0	56.3
0°-180°	12315.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2138	2138	2138	2138	2138	
5°	2114	2151	2132	2136	2152	201
15°	2055	2083	2075	2096	2107	579
25°	1903	1952	1985	2065	2122	877
35°	1686	1733	1835	1940	1962	1052
45°	1374	1478	1510	1280	1191	1058
55°	997	1057	879	663	579	879
65°	533	562	430	303	301	536
75°	230	255	178	167	165	250
85°	52	48	43	34	27	61
90°	1	3	9	8	9	5
95°	60	174	778	277	180	68
105°	244	347	1390	2642	2510	256
115°	438	524	1130	2334	2740	433
125°	610	680	1113	1841	2162	543
135°	735	813	1104	1588	1790	569
145°	860	923	1102	1366	1496	539
155°	980	1012	1109	1222	1269	451
165°	1070	1080	1113	1156	1169	301
175°	1118	1118	1119	1127	1125	106
180°	1123	1123	1123	1123	1123	



TEST NUMBER: P855327

CATALOG NUMBER: SQ2-PP3-150U-100D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2138.3	2138.3	2138.3	2138.3	2138.3
2.5°	2122.1	2152.1	2132.9	2136.5	2140.1
5°	2113.5	2151.0	2131.5	2136.4	2151.9
7.5°	2105.3	2143.8	2124.8	2132.9	2151.9
10°	2099.9	2133.0	2115.7	2127.3	2142.8
12.5°	2083.6	2115.0	2099.5	2114.6	2128.4
15°	2054.7	2083.4	2075.0	2095.6	2106.7
17.5°	2015.3	2050.3	2050.2	2079.3	2090.8
20°	1984.6	2026.6	2032.1	2068.7	2090.8
22.5°	1952.0	2001.1	2010.3	2065.4	2103.5
25°	1903.2	1951.8	1984.6	2065.0	2122.5
27.5°	1846.2	1894.5	1962.0	2052.0	2097.6
30°	1808.4	1854.7	1934.9	2028.5	2070.5
32.5°	1761.3	1809.5	1895.1	1995.9	2034.3
35°	1686.2	1732.6	1835.4	1939.9	1962.0
37.5°	1599.9	1652.5	1767.6	1826.0	1827.2
40°	1534.8	1603.4	1713.4	1724.0	1695.3
42.5°	1471.6	1559.4	1637.4	1589.7	1462.0
45°	1374.4	1478.2	1509.9	1279.6	1191.3
47.5°	1270.8	1373.3	1322.7	1073.2	1012.2
50°	1200.2	1297.6	1170.9	959.4	901.9
52.5°	1120.6	1207.4	1035.2	850.2	762.6
55°	996.8	1056.6	879.3	662.6	578.6
57.5°	847.6	889.7	751.8	497.4	403.2
60°	748.2	781.3	657.8	408.1	361.6
62.5°	657.8	687.4	560.1	354.5	338.2
65°	533.4	562.2	429.5	302.9	300.7
67.5°	424.6	455.9	329.6	264.4	261.7
70°	359.4	392.5	273.5	237.3	232.8
72.5°	305.1	336.6	231.9	208.4	205.7
75°	230.5	254.9	178.5	167.2	165.0
77.5°	167.2	182.7	132.9	127.0	124.8
80°	131.1	137.8	104.0	101.6	99.4
82.5°	98.6	96.4	78.7	76.3	72.4
85°	52.0	47.5	43.0	33.8	27.2
87.5°	16.5	17.0	9.1	7.0	7.2
90°	1.2	3.4	9.2	8.2	9.2
92.5°	19.6	71.6	219.7	71.4	57.2
95°	60.0	174.0	777.7	277.0	180.1
97.5°	109.0	229.5	1334.3	807.2	500.3
100°	143.1	258.1	1543.8	1378.7	913.8
102.5°	181.8	294.3	1520.7	2031.4	1574.8
105°	243.5	347.3	1390.3	2641.6	2509.6
107.5°	304.2	399.4	1263.2	2698.6	2843.7
110°	343.8	436.3	1202.3	2632.3	2901.8



TEST NUMBER: P855327

CATALOG NUMBER: SQ2-PP3-150U-100D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	381.7	471.5	1165.4	2516.7	2862.2
115°	438.4	524.2	1129.6	2334.2	2740.3
117.5°	493.7	573.7	1116.0	2154.8	2567.3
120°	529.6	605.2	1112.3	2050.3	2451.9
122.5°	562.0	635.7	1112.3	1960.1	2332.8
125°	610.3	680.4	1113.4	1840.8	2162.3
127.5°	651.5	722.8	1112.0	1752.8	2032.6
130°	677.3	749.5	1111.1	1699.6	1952.3
132.5°	700.4	774.4	1108.4	1653.8	1883.1
135°	735.0	812.9	1104.2	1587.6	1789.6
137.5°	771.5	848.6	1101.7	1518.6	1701.3
140°	797.3	871.7	1100.7	1475.0	1647.6
142.5°	823.1	893.0	1100.7	1428.5	1584.9
145°	859.6	922.8	1101.9	1365.6	1496.5
147.5°	897.9	950.5	1103.5	1311.0	1409.8
150°	921.9	968.2	1105.4	1279.1	1362.7
152.5°	946.0	986.7	1106.3	1253.0	1322.0
155°	979.6	1012.3	1108.9	1221.8	1269.2
157.5°	1009.8	1033.5	1111.3	1197.3	1231.6
160°	1029.2	1048.4	1112.3	1183.3	1210.4
162.5°	1045.8	1061.4	1112.3	1172.0	1191.9
165°	1069.6	1079.7	1113.4	1156.4	1168.8
167.5°	1089.7	1094.7	1114.8	1144.3	1151.1
170°	1100.7	1103.1	1115.8	1137.8	1140.0
172.5°	1109.1	1110.4	1118.6	1133.1	1133.5
175°	1118.1	1118.1	1119.3	1127.3	1125.0
177.5°	1122.6	1121.8	1120.9	1126.2	1122.6
180°	1122.6	1122.6	1122.6	1122.6	1122.6



TEST NUMBER: P855327

CATALOG NUMBER: SQ2-PP3-150U-100D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.23	20.02	20.25	21.04	22.40	15.63	16.41	16.64	17.43	18.79
	3H	20.32	21.02	21.35	22.05	23.43	16.73	17.43	17.75	18.45	19.84
	4H	20.66	21.32	21.70	22.35	23.74	17.19	17.85	18.23	18.88	20.27
	6H	20.87	21.48	21.92	22.51	23.92	17.53	18.14	18.58	19.17	20.57
	8H	20.92	21.50	21.97	22.55	23.94	17.61	18.19	18.66	19.24	20.64
	12H	20.93	21.48	21.99	22.52	23.94	17.62	18.17	18.68	19.22	20.64
4H	2H	19.33	19.99	20.38	21.02	22.41	16.33	16.99	17.38	18.02	19.41
	3H	20.63	21.18	21.69	22.24	23.64	17.58	18.12	18.63	19.18	20.59
	4H	21.10	21.60	22.16	22.66	24.08	18.13	18.63	19.19	19.68	21.10
	6H	21.44	21.87	22.51	22.94	24.36	18.56	18.99	19.63	20.07	21.49
	8H	21.53	21.93	22.60	23.00	24.43	18.68	19.08	19.75	20.15	21.58
	12H	21.56	21.92	22.65	23.00	24.44	18.71	19.07	19.79	20.15	21.59
8H	4H	21.12	21.52	22.18	22.58	24.02	18.40	18.80	19.46	19.86	21.30
	6H	21.54	21.88	22.64	22.98	24.42	18.94	19.27	20.03	20.38	21.81
	8H	21.70	21.99	22.80	23.08	24.53	19.12	19.41	20.22	20.51	21.96
	12H	21.78	22.04	22.89	23.13	24.62	19.19	19.45	20.30	20.54	22.03
12H	4H	21.07	21.43	22.16	22.51	23.95	18.40	18.76	19.49	19.84	21.28
	6H	21.53	21.82	22.63	22.92	24.37	18.99	19.28	20.09	20.37	21.82
	8H	21.70	21.96	22.80	23.04	24.53	19.20	19.45	20.30	20.54	22.03