

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855284

Luminaire Tested: SQ2-PW1-0U-075D-840-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P855284  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PW1-0U-075D-840-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 750 LUMENS PER FOOT  
DIRECT ONLY  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3916.8 lumens  
Efficiency: N/A  
Efficacy: 146.7 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.11 / 1.22  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P855284

CATALOG NUMBER: SQ2-PW1-0U-075D-840-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P855284

CATALOG NUMBER: SQ2-PW1-0U-075D-840-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	85	82	78	82	79	76	74
3	93	84	76	70	91	82	75	70	79	73	69	77	72	67	74	70	66	64
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	46	41	39
8	64	52	44	38	63	51	43	38	50	43	38	48	42	37	47	42	37	35
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32
10	57	44	37	32	55	44	36	31	43	36	31	42	36	31	41	35	31	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	28501	28501	28501
5°	28310	28528	28801
10°	28362	28693	29052
15°	28356	28889	29227
20°	28366	28857	28654
25°	28214	28244	26626
30°	28021	26612	24071
35°	27802	24488	21737
40°	27248	22323	19205
45°	26179	20078	16776
50°	24367	17947	14358
55°	22292	15854	11643
60°	19979	13789	10043
65°	17471	11882	8928
70°	14290	10556	8091
75°	11117	9127	7442
80°	8294	7810	6564
85°	5613	5910	3742

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 26179 cd/sqm



TEST NUMBER: P855284

CATALOG NUMBER: SQ2-PW1-0U-075D-840-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.1	4.3
10°-20°	487.0	12.4
20°-30°	716.7	18.3
30°-40°	783.6	20.0
40°-50°	703.0	17.9
50°-60°	524.4	13.4
60°-70°	331.4	8.5
70°-80°	164.2	4.2
80°-90°	38.4	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1371.8	35.0
0°-40°	2155.4	55.0
0°-60°	3382.8	86.4
0°-90°	3916.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3916.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1765	1765	1765	1765	1765	
5°	1747	1775	1760	1762	1777	166
15°	1696	1729	1728	1740	1748	479
25°	1584	1618	1585	1519	1495	729
35°	1410	1396	1242	1134	1103	880
45°	1146	1055	879	769	735	879
55°	792	716	563	442	414	707
65°	457	419	311	250	234	453
75°	178	191	146	123	119	196
85°	30	38	32	22	20	39
90°	0	0	0	0	0	



TEST NUMBER: P855284

CATALOG NUMBER: SQ2-PW1-0U-075D-840-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1765.2	1765.2	1765.2	1765.2	1765.2
2.5°	1753.1	1775.5	1761.3	1762.7	1766.6
5°	1746.7	1774.7	1760.2	1762.2	1777.0
7.5°	1738.0	1766.3	1755.4	1761.5	1776.0
10°	1729.9	1759.5	1750.1	1758.8	1772.0
12.5°	1719.2	1750.1	1743.4	1753.5	1766.6
15°	1696.4	1729.2	1728.3	1740.2	1748.5
17.5°	1669.8	1702.7	1701.0	1704.2	1708.1
20°	1650.9	1683.8	1679.5	1667.7	1667.7
22.5°	1624.0	1659.5	1648.6	1616.4	1605.9
25°	1583.7	1618.2	1585.4	1519.2	1494.6
27.5°	1536.6	1564.6	1498.6	1404.7	1370.5
30°	1503.0	1524.3	1427.4	1324.0	1291.1
32.5°	1468.1	1476.2	1354.7	1247.3	1211.8
35°	1410.5	1395.7	1242.4	1134.1	1102.8
37.5°	1342.5	1298.5	1134.5	1021.0	986.5
40°	1292.8	1230.3	1059.1	945.7	911.2
42.5°	1237.7	1159.5	987.9	874.4	838.6
45°	1146.5	1054.6	879.3	769.2	734.7
47.5°	1044.0	952.6	777.7	671.2	641.6
50°	970.1	881.3	714.5	607.8	571.6
52.5°	894.7	815.2	652.6	543.0	493.5
55°	791.9	716.3	563.2	441.6	413.6
57.5°	686.0	620.5	482.1	371.6	348.7
60°	618.7	561.1	427.0	334.0	311.0
62.5°	554.1	503.1	373.3	299.2	280.0
65°	457.3	419.4	311.0	250.1	233.7
67.5°	363.1	342.0	258.6	205.2	194.4
70°	302.7	296.0	223.6	179.7	171.4
72.5°	250.2	252.8	190.0	155.6	150.0
75°	178.2	191.4	146.3	122.6	119.3
77.5°	121.4	141.1	108.3	90.7	88.1
80°	89.2	108.8	84.0	70.6	70.6
82.5°	62.2	78.0	59.9	53.1	53.1
85°	30.3	38.5	31.9	21.8	20.2
87.5°	8.0	12.0	5.4	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P855284

CATALOG NUMBER: SQ2-PW1-0U-075D-840-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.61	24.11	22.97	24.43	24.74	19.10	20.60	19.46	20.91	21.23
	3H	23.98	25.32	24.36	25.65	26.01	20.35	21.69	20.72	22.02	22.38
	4H	24.38	25.64	24.78	25.99	26.37	20.82	22.08	21.22	22.43	22.81
	6H	24.61	25.78	25.03	26.15	26.54	21.17	22.33	21.58	22.70	23.09
	8H	24.66	25.77	25.09	26.16	26.56	21.26	22.37	21.69	22.76	23.16
	12H	24.68	25.74	25.11	26.12	26.55	21.29	22.35	21.72	22.73	23.16
4H	2H	22.79	24.05	23.19	24.40	24.78	19.85	21.11	20.25	21.46	21.84
	3H	24.39	25.43	24.80	25.83	26.23	21.30	22.34	21.71	22.74	23.14
	4H	24.92	25.86	25.35	26.27	26.71	21.87	22.80	22.30	23.22	23.66
	6H	25.28	26.10	25.74	26.54	27.00	22.30	23.12	22.76	23.56	24.02
	8H	25.37	26.14	25.84	26.58	27.05	22.42	23.18	22.88	23.62	24.09
	12H	25.42	26.10	25.90	26.58	27.05	22.47	23.15	22.95	23.63	24.10
8H	4H	25.00	25.76	25.47	26.21	26.68	22.24	23.00	22.70	23.44	23.91
	6H	25.46	26.09	25.96	26.58	27.06	22.76	23.39	23.26	23.88	24.36
	8H	25.61	26.17	26.12	26.68	27.17	22.93	23.49	23.44	24.00	24.49
	12H	25.70	26.20	26.21	26.69	27.26	23.02	23.51	23.53	24.01	24.57
12H	4H	24.99	25.67	25.47	26.15	26.62	22.28	22.96	22.76	23.44	23.91
	6H	25.45	26.02	25.97	26.53	27.02	22.83	23.39	23.34	23.90	24.39
	8H	25.64	26.14	26.15	26.63	27.20	23.04	23.54	23.55	24.03	24.60