

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853879

Luminaire Tested: SQ2-FB-100U-100D-935-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853879
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-12, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-100U-100D-935-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1000 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7915.1 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 70.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853879

CATALOG NUMBER: SQ2-FB-100U-100D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853879

CATALOG NUMBER: SQ2-FB-100U-100D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	71	68	61	59	57	50	48	47	42
2	89	81	75	69	81	75	69	65	64	59	56	53	50	47	43	41	39	35
3	81	71	63	57	74	66	59	54	56	51	46	46	43	40	38	35	33	29
4	73	62	54	48	67	58	50	45	49	43	39	41	37	33	33	30	28	24
5	67	55	47	41	62	51	44	38	43	38	33	36	32	28	30	26	24	21
6	62	49	41	35	57	46	38	33	39	33	29	33	28	25	27	23	21	18
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18	15
8	53	40	32	26	48	37	30	25	32	26	22	27	22	19	22	19	16	14
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14	12
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	19	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6513	6513	6513
5°	6350	8802	11537
10°	5946	17044	22450
15°	5382	22176	25839
20°	4766	24395	27060
25°	4215	26088	27505
30°	3725	26867	27844
35°	3325	27334	29934
40°	3025	27594	31805
45°	2790	27725	33305
50°	2630	28256	33907
55°	2567	28991	34179
60°	2632	29376	34010
65°	2743	28974	33047
70°	2837	28018	24996
75°	3144	25165	13793
80°	3245	12980	12803
85°	3242	8985	5391

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 34487 cd/sqm



TEST NUMBER: P853879

CATALOG NUMBER: SQ2-FB-100U-100D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.6	0.9
10°-20°	308.5	3.9
20°-30°	542.8	6.9
30°-40°	702.6	8.9
40°-50°	774.9	9.8
50°-60°	723.5	9.1
60°-70°	559.2	7.1
70°-80°	257.9	3.3
80°-90°	50.4	0.6
90°-100°	263.6	3.3
100°-110°	797.1	10.1
110°-120°	778.2	9.8
120°-130°	635.9	8.0
130°-140°	519.0	6.6
140°-150°	404.0	5.1
150°-160°	291.3	3.7
160°-170°	178.3	2.3
170°-180°	60.2	0.8
0°-30°	918.9	11.6
0°-40°	1621.6	20.5
0°-60°	3120.1	39.4
0°-90°	3987.6	50.4
90°-120°	1838.8	23.2
90°-150°	3397.8	42.9
90°-180°	3928.0	49.6
0°-180°	7915.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	403	403	403	403	403	
5°	392	449	543	662	712	36
15°	322	635	1327	1485	1546	90
25°	237	853	1464	1529	1544	109
35°	169	823	1387	1435	1519	106
45°	122	630	1214	1394	1459	95
55°	91	376	1030	1184	1214	82
65°	72	212	758	850	865	70
75°	50	130	403	217	221	52
85°	18	38	48	33	29	18
90°	0	2	12	7	6	2
95°	33	103	497	184	116	39
105°	139	195	783	1486	1413	146
115°	247	294	633	1310	1539	244
125°	345	382	624	1034	1218	306
135°	413	457	620	892	1004	320
145°	482	518	620	767	839	302
155°	550	568	624	688	714	253
165°	601	608	627	651	659	169
175°	629	629	630	635	633	60
180°	631	631	631	631	631	



TEST NUMBER: P853879

CATALOG NUMBER: SQ2-FB-100U-100D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	403.4	403.4	403.4	403.4	403.4
2.5°	400.3	417.0	436.0	457.9	467.0
5°	391.8	448.7	543.1	662.5	711.8
7.5°	376.7	492.3	789.8	1109.3	1208.0
10°	362.7	523.9	1039.6	1316.2	1369.3
12.5°	347.2	566.0	1196.3	1390.7	1445.4
15°	322.0	634.9	1326.7	1485.1	1545.8
17.5°	296.0	712.4	1387.2	1543.5	1576.5
20°	277.4	766.6	1419.8	1554.1	1574.9
22.5°	260.3	807.2	1443.0	1544.8	1567.2
25°	236.6	853.0	1464.4	1528.7	1543.9
27.5°	213.7	865.0	1455.1	1497.3	1512.1
30°	199.8	861.6	1441.1	1472.6	1493.5
32.5°	187.4	852.3	1420.9	1451.4	1496.6
35°	168.7	823.0	1386.8	1435.2	1518.7
37.5°	152.8	776.0	1341.8	1441.0	1521.4
40°	143.5	740.9	1309.2	1440.7	1509.0
42.5°	134.2	699.7	1272.0	1425.2	1493.5
45°	122.2	630.4	1214.2	1394.1	1458.6
47.5°	110.9	552.4	1160.6	1351.0	1398.0
50°	104.7	499.2	1124.9	1312.0	1349.9
52.5°	98.5	447.5	1089.3	1265.4	1300.3
55°	91.2	375.6	1029.9	1183.8	1214.2
57.5°	84.6	314.0	962.4	1093.7	1118.4
60°	81.5	280.6	909.7	1028.5	1053.2
62.5°	76.8	250.1	850.7	960.2	983.4
65°	71.8	212.1	758.4	849.9	865.0
67.5°	64.8	183.9	660.2	716.2	687.8
70°	60.1	170.1	593.5	611.0	529.5
72.5°	57.0	154.9	520.6	474.4	320.0
75°	50.4	130.1	403.4	217.3	221.1
77.5°	41.1	100.7	265.3	166.9	170.3
80°	34.9	82.3	139.6	135.8	137.7
82.5°	28.7	64.0	96.2	100.0	97.4
85°	17.5	38.3	48.5	32.9	29.1
87.5°	6.2	14.2	10.1	9.1	8.9
90°	0.0	1.9	11.9	6.9	5.9
92.5°	11.1	44.8	160.9	53.4	38.4
95°	32.7	103.4	497.3	183.7	115.9
97.5°	63.2	131.6	783.8	518.7	315.8
100°	82.2	149.1	875.8	846.7	568.7
102.5°	103.6	168.1	856.8	1187.5	946.7
105°	138.7	194.9	782.7	1486.4	1412.7
107.5°	172.0	225.6	711.3	1515.9	1601.2
110°	194.2	245.5	675.7	1478.7	1633.7



TEST NUMBER: P853879

CATALOG NUMBER: SQ2-FB-100U-100D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.6	265.4	654.3	1416.2	1612.3
115°	246.7	294.1	633.1	1309.9	1538.6
117.5°	277.6	322.5	625.5	1210.4	1444.4
120°	298.2	340.8	623.1	1152.3	1377.1
122.5°	317.2	357.5	623.1	1101.2	1308.9
125°	344.8	382.5	624.1	1034.5	1217.6
127.5°	367.2	406.3	623.1	984.1	1140.3
130°	381.4	422.1	623.1	955.3	1096.7
132.5°	394.1	435.6	622.4	928.9	1059.5
135°	413.1	456.7	620.2	892.2	1003.6
137.5°	434.3	475.8	620.2	853.0	956.2
140°	447.8	488.5	620.2	827.5	925.3
142.5°	461.3	500.4	619.4	804.2	889.6
145°	482.5	518.3	620.2	767.4	839.1
147.5°	503.7	534.1	621.4	737.1	792.2
150°	517.1	545.2	622.2	720.3	766.8
152.5°	529.8	554.8	622.9	705.8	743.8
155°	549.8	568.2	624.1	688.1	714.3
157.5°	567.3	582.2	625.3	675.1	693.3
160°	577.6	590.2	626.1	667.0	680.6
162.5°	587.9	597.4	626.9	659.9	671.1
165°	601.4	608.1	627.1	651.1	658.8
167.5°	612.8	616.3	628.3	644.2	647.5
170°	619.2	621.1	629.1	641.0	642.0
172.5°	623.1	624.3	629.1	637.8	638.0
175°	629.1	629.1	630.1	635.0	633.1
177.5°	631.9	631.1	630.3	632.6	631.1
180°	631.1	631.1	631.1	631.1	631.1



TEST NUMBER: P853879

CATALOG NUMBER: SQ2-FB-100U-100D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.61	14.50	14.56	15.47	16.73	22.34	23.24	23.29	24.20	25.47
	3H	14.34	15.14	15.30	16.12	17.40	23.97	24.77	24.93	25.75	27.03
	4H	14.64	15.40	15.62	16.38	17.68	24.15	24.91	25.13	25.89	27.18
	6H	14.86	15.56	15.85	16.54	17.85	24.24	24.94	25.22	25.92	27.23
	8H	14.92	15.58	15.91	16.59	17.89	24.24	24.91	25.24	25.91	27.22
	12H	14.95	15.58	15.95	16.58	17.91	24.22	24.85	25.21	25.85	27.18
4H	2H	18.01	18.77	18.99	19.75	21.04	22.79	23.55	23.77	24.53	25.82
	3H	18.95	19.58	19.94	20.59	21.90	24.62	25.25	25.61	26.26	27.57
	4H	19.23	19.81	20.23	20.81	22.14	24.86	25.44	25.86	26.44	27.77
	6H	19.37	19.86	20.38	20.89	22.22	25.01	25.50	26.02	26.53	27.86
	8H	19.39	19.85	20.40	20.87	22.22	25.03	25.50	26.05	26.52	27.86
	12H	19.38	19.80	20.41	20.83	22.19	25.01	25.43	26.04	26.46	27.81
8H	4H	20.41	20.87	21.42	21.89	23.24	24.98	25.44	25.99	26.46	27.81
	6H	20.65	21.03	21.69	22.09	23.44	25.19	25.57	26.22	26.63	27.97
	8H	20.72	21.06	21.76	22.10	23.47	25.25	25.58	26.29	26.63	27.99
	12H	20.75	21.04	21.80	22.09	23.49	25.24	25.54	26.29	26.58	27.99
12H	4H	20.43	20.85	21.46	21.88	23.23	24.93	25.35	25.97	26.39	27.74
	6H	20.74	21.08	21.79	22.13	23.49	25.17	25.51	26.22	26.55	27.92
	8H	20.85	21.14	21.90	22.19	23.59	25.24	25.53	26.29	26.58	27.98