

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853667

Luminaire Tested: SQ2-F-025U-125D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853667
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-025U-125D-940-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6326.7 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 56.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853667
CATALOG NUMBER: SQ2-F-025U-125D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853667

CATALOG NUMBER: SQ2-F-025U-125D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	115	115	115	115	110	110	110	110	102	102	102	94	94	94	87	87	87	83				
1	105	100	96	92	101	96	93	89	89	86	83	82	80	78	76	74	73	70				
2	95	87	81	75	91	84	78	73	78	73	69	72	68	65	67	64	61	58				
3	87	77	69	62	83	74	67	61	68	62	58	64	59	54	59	55	52	49				
4	80	68	59	53	76	65	58	51	61	54	49	57	51	47	53	48	44	42				
5	73	61	52	45	70	58	50	44	54	48	42	51	45	40	47	42	38	36				
6	67	54	46	39	64	53	44	39	49	42	37	46	40	35	43	38	34	31				
7	62	49	41	35	60	48	40	34	45	38	33	42	36	31	39	34	30	28				
8	58	45	37	31	56	43	36	30	41	34	29	38	32	28	36	31	27	25				
9	54	41	33	28	52	40	32	27	37	31	26	35	29	25	33	28	24	22				
10	51	38	30	25	49	37	29	25	35	28	24	33	27	23	31	26	22	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	30273	30273	30273
5°	30058	30141	30389
10°	29988	30072	30280
15°	29805	29890	30190
20°	29627	29672	29935
25°	29354	29354	29535
30°	29052	29052	29147
35°	28700	28600	28801
40°	28321	28214	28321
45°	27882	27766	27882
50°	27462	27206	27271
55°	26821	26750	26607
60°	26150	25985	25820
65°	25375	25081	24791
70°	23877	23755	23273
75°	22470	21990	21354
80°	19954	19479	18763
85°	16098	14672	13727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 28053 cd/sqm



TEST NUMBER: P853667

CATALOG NUMBER: SQ2-F-025U-125D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.2	2.8
10°-20°	506.4	8.0
20°-30°	762.0	12.0
30°-40°	911.7	14.4
40°-50°	940.7	14.9
50°-60°	848.6	13.4
60°-70°	647.6	10.2
70°-80°	372.3	5.9
80°-90°	97.6	1.5
90°-100°	69.3	1.1
100°-110°	215.5	3.4
110°-120°	210.9	3.3
120°-130°	172.1	2.7
130°-140°	140.8	2.2
140°-150°	109.9	1.7
150°-160°	79.3	1.3
160°-170°	48.5	0.8
170°-180°	16.3	0.3
0°-30°	1445.6	22.8
0°-40°	2357.3	37.3
0°-60°	4146.6	65.5
0°-90°	5264.0	83.2
90°-120°	495.7	7.8
90°-150°	918.5	14.5
90°-180°	1063.0	16.8
0°-180°	6326.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1875	1875	1875	1875	1875	
5°	1855	1880	1860	1862	1875	176
15°	1783	1806	1788	1796	1806	503
25°	1648	1665	1648	1650	1658	759
35°	1456	1466	1451	1456	1461	910
45°	1221	1229	1216	1219	1221	942
55°	953	958	950	945	945	852
65°	664	662	656	651	649	653
75°	360	358	352	345	342	380
85°	87	82	79	72	74	101
90°	0	1	3	3	3	4
95°	10	28	127	47	30	11
105°	38	53	212	405	387	40
115°	67	80	172	355	416	66
125°	94	104	170	280	328	83
135°	112	125	169	241	271	87
145°	131	142	169	208	227	82
155°	150	155	170	187	193	69
165°	165	166	171	176	179	46
175°	171	171	171	172	171	16
180°	171	171	171	171	171	



TEST NUMBER: P853667

CATALOG NUMBER: SQ2-F-025U-125D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1875.0	1875.0	1875.0	1875.0	1875.0
2.5°	1862.8	1884.8	1866.9	1871.0	1873.0
5°	1854.6	1879.6	1859.7	1862.5	1875.0
7.5°	1839.3	1866.2	1844.4	1849.3	1863.3
10°	1829.1	1854.0	1834.2	1836.9	1846.9
12.5°	1812.7	1837.7	1817.8	1822.6	1832.6
15°	1783.1	1805.6	1788.2	1796.1	1806.1
17.5°	1748.8	1772.8	1753.4	1760.3	1768.8
20°	1724.3	1744.3	1726.9	1729.7	1742.2
22.5°	1693.7	1713.6	1698.3	1699.0	1709.5
25°	1647.7	1665.2	1647.7	1650.4	1657.9
27.5°	1595.1	1610.0	1595.1	1597.8	1604.3
30°	1558.3	1573.3	1558.3	1560.9	1563.4
32.5°	1517.4	1530.4	1515.4	1518.1	1524.6
35°	1456.1	1466.1	1451.0	1456.2	1461.2
37.5°	1390.7	1398.2	1385.6	1388.2	1392.7
40°	1343.7	1351.2	1338.6	1341.2	1343.7
42.5°	1296.7	1302.2	1289.5	1292.2	1296.7
45°	1221.1	1228.6	1216.0	1218.6	1221.1
47.5°	1144.4	1148.9	1138.3	1136.4	1140.9
50°	1093.3	1095.8	1083.1	1083.2	1085.7
52.5°	1038.2	1040.7	1032.0	1028.0	1030.5
55°	952.8	957.8	950.3	945.2	945.2
57.5°	867.0	871.5	861.9	859.3	858.8
60°	809.8	812.3	804.7	802.1	799.6
62.5°	752.6	753.1	745.4	742.8	740.3
65°	664.2	661.7	656.5	651.4	648.9
67.5°	565.1	567.6	562.5	554.3	554.3
70°	505.8	508.3	503.2	493.0	493.0
72.5°	448.6	447.1	444.0	435.7	431.7
75°	360.2	357.7	352.5	344.8	342.3
77.5°	271.8	269.3	266.7	257.0	259.0
80°	214.6	212.1	209.5	201.8	201.8
82.5°	163.5	159.0	156.3	148.7	148.7
85°	86.9	81.9	79.2	71.6	74.1
87.5°	24.5	22.7	21.1	17.0	17.0
90°	0.0	1.0	3.2	3.2	3.2
92.5°	3.4	11.8	40.1	13.2	10.7
95°	9.5	27.9	127.1	46.9	30.5
97.5°	17.2	36.3	210.5	131.0	82.6
100°	23.1	40.6	237.4	222.1	148.1
102.5°	29.0	45.6	232.4	317.2	249.0
105°	37.8	53.2	212.2	405.1	386.6
107.5°	46.6	61.0	192.9	411.8	432.2
110°	52.5	66.9	182.8	402.2	442.2



TEST NUMBER: P853667

CATALOG NUMBER: SQ2-F-025U-125D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	58.4	72.0	177.7	384.8	435.5
115°	67.2	79.6	172.3	355.4	416.0
117.5°	75.8	87.1	170.0	327.3	389.3
120°	80.9	92.2	169.1	311.2	370.8
122.5°	85.9	97.2	170.0	297.7	352.3
125°	93.5	103.8	170.2	279.5	327.7
127.5°	99.6	110.1	170.2	265.9	306.9
130°	102.9	114.2	170.2	258.2	295.2
132.5°	107.1	118.4	169.3	251.4	285.9
135°	112.4	124.7	169.1	241.2	271.0
137.5°	118.5	129.8	169.1	231.1	258.2
140°	121.9	133.2	169.1	224.3	249.0
142.5°	126.1	136.5	169.1	217.5	239.7
145°	131.3	141.6	169.1	208.4	226.9
147.5°	137.6	146.4	170.2	199.9	214.5
150°	141.8	149.0	170.2	195.6	206.9
152.5°	145.2	151.5	170.2	191.4	201.1
155°	150.2	155.4	170.2	187.1	193.3
157.5°	155.3	159.2	170.2	183.3	187.2
160°	158.6	161.7	170.2	180.8	183.8
162.5°	161.1	163.4	170.2	179.1	181.3
165°	164.9	166.0	171.2	176.5	178.6
167.5°	167.2	167.4	170.2	175.0	176.1
170°	168.1	169.1	170.2	173.4	174.4
172.5°	169.8	170.0	171.0	172.5	172.7
175°	171.2	171.2	171.2	172.3	171.2
177.5°	171.2	171.2	171.2	171.2	171.2
180°	171.2	171.2	171.2	171.2	171.2



TEST NUMBER: P853667

CATALOG NUMBER: SQ2-F-025U-125D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	22.44	23.73	23.05	24.35	25.05	22.37	23.66	22.97	24.27	24.97
	3H	24.25	25.42	24.87	26.05	26.78	24.13	25.30	24.75	25.93	26.66
	4H	24.93	26.03	25.57	26.67	27.42	24.78	25.88	25.42	26.52	27.27
	6H	25.42	26.44	26.08	27.09	27.85	25.24	26.25	25.89	26.90	27.67
	8H	25.57	26.54	26.24	27.22	27.98	25.37	26.34	26.04	27.01	27.78
	12H	25.66	26.59	26.33	27.25	28.05	25.44	26.36	26.11	27.03	27.83
4H	2H	23.04	24.14	23.69	24.78	25.53	22.98	24.08	23.62	24.72	25.47
	3H	25.07	25.99	25.72	26.67	27.44	24.96	25.88	25.62	26.56	27.33
	4H	25.88	26.71	26.55	27.40	28.20	25.73	26.57	26.41	27.25	28.05
	6H	26.49	27.22	27.18	27.93	28.74	26.31	27.04	27.00	27.75	28.56
	8H	26.69	27.37	27.39	28.07	28.90	26.49	27.17	27.18	27.87	28.70
	12H	26.81	27.42	27.53	28.15	28.98	26.58	27.19	27.30	27.93	28.75
8H	4H	26.16	26.84	26.86	27.54	28.37	26.03	26.71	26.73	27.42	28.24
	6H	26.89	27.46	27.62	28.21	29.03	26.73	27.29	27.46	28.04	28.87
	8H	27.17	27.67	27.91	28.42	29.26	26.97	27.48	27.72	28.23	29.07
	12H	27.36	27.80	28.10	28.54	29.44	27.13	27.57	27.87	28.31	29.22
12H	4H	26.17	26.78	26.89	27.52	28.34	26.05	26.66	26.77	27.39	28.22
	6H	26.94	27.45	27.68	28.20	29.04	26.78	27.29	27.52	28.04	28.88
	8H	27.26	27.70	28.00	28.44	29.34	27.07	27.51	27.81	28.25	29.16