

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854059

Luminaire Tested: SQ2-PH1-125U-100D-935-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P854059  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PH1-125U-100D-935-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9479.9 lumens  
Efficiency: N/A  
Efficacy: 116.3 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 81.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854059

CATALOG NUMBER: SQ2-PH1-125U-100D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854059

CATALOG NUMBER: SQ2-PH1-125U-100D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48		48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41		41
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39	34		34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33	29		29
4	74	64	56	50	68	59	52	47	50	45	40	41	38	35	34	31	29	25		25
5	68	57	49	43	62	52	45	40	45	39	35	37	33	30	30	27	25	22		22
6	63	51	43	37	58	47	40	35	40	35	30	34	29	26	28	24	22	19		19
7	58	46	38	32	53	43	36	31	36	31	27	31	26	23	25	22	20	17		17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15		15
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16	14		14
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14	12		12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	32913	32913	32913
5°	33102	31122	30084
10°	32339	28334	27347
15°	32485	26649	26812
20°	31326	25828	27027
25°	30752	25707	26398
30°	30085	25639	26614
35°	29857	25346	31196
40°	29883	25183	24732
45°	29894	24224	21302
50°	29474	24702	19974
55°	29101	26807	19164
60°	28811	23486	17977
65°	28306	19045	15633
70°	26738	16206	11169
75°	23836	12221	8472
80°	19479	7931	7931
85°	12208	7188	5391

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29894 cd/sqm



TEST NUMBER: P854059

CATALOG NUMBER: SQ2-PH1-125U-100D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	179.4	1.9
10°-20°	471.8	5.0
20°-30°	691.8	7.3
30°-40°	837.8	8.8
40°-50°	823.9	8.7
50°-60°	717.2	7.6
60°-70°	498.6	5.3
70°-80°	236.4	2.5
80°-90°	53.0	0.6
90°-100°	308.2	3.3
100°-110°	1003.2	10.6
110°-120°	992.4	10.5
120°-130°	811.0	8.6
130°-140°	662.8	7.0
140°-150°	516.3	5.4
150°-160°	372.1	3.9
160°-170°	227.4	2.4
170°-180°	76.7	0.8
0°-30°	1343.0	14.2
0°-40°	2180.8	23.0
0°-60°	3721.8	39.3
0°-90°	4509.8	47.6
90°-120°	2303.8	24.3
90°-150°	4293.8	45.3
90°-180°	4970.0	52.4
0°-180°	9479.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2038	2038	2038	2038	2038	
5°	2042	2040	1920	1860	1856	192
15°	1943	1731	1594	1583	1604	542
25°	1726	1468	1443	1488	1482	794
35°	1515	1225	1286	1397	1583	949
45°	1309	970	1061	1098	933	1006
55°	1034	755	952	686	681	924
65°	741	519	498	409	409	728
75°	382	264	196	140	136	405
85°	66	43	39	31	29	88
90°	0	3	7	6	6	4
95°	42	127	565	201	124	48
105°	170	246	994	1898	1797	182
115°	315	376	810	1668	1963	312
125°	438	488	799	1317	1553	390
135°	529	584	795	1137	1282	409
145°	618	664	793	979	1072	387
155°	706	729	798	877	910	325
165°	770	777	800	830	839	217
175°	803	803	803	808	806	76
180°	806	806	806	806	806	



TEST NUMBER: P854059

CATALOG NUMBER: SQ2-PH1-125U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2038.5	2038.5	2038.5	2038.5	2038.5
2.5°	2033.8	2055.1	2007.4	1988.8	1985.7
5°	2042.4	2040.5	1920.2	1860.0	1856.2
7.5°	2005.1	1946.3	1802.6	1736.2	1733.2
10°	1972.5	1883.4	1728.2	1668.0	1668.0
12.5°	1964.8	1824.1	1667.6	1623.2	1632.3
15°	1943.4	1731.0	1594.3	1583.2	1604.0
17.5°	1872.8	1644.1	1537.3	1562.7	1587.0
20°	1823.2	1597.5	1503.2	1550.2	1573.0
22.5°	1781.3	1552.6	1478.3	1529.8	1542.0
25°	1726.2	1468.3	1443.0	1487.5	1481.8
27.5°	1660.3	1391.0	1407.7	1435.0	1438.4
30°	1613.7	1344.4	1375.2	1402.9	1427.5
32.5°	1568.7	1290.3	1339.5	1405.1	1461.7
35°	1514.8	1224.6	1285.9	1396.8	1582.7
37.5°	1458.2	1147.1	1232.0	1325.3	1384.5
40°	1417.8	1091.6	1194.8	1310.0	1173.4
42.5°	1374.4	1048.2	1138.9	1287.7	1057.1
45°	1309.2	969.7	1060.9	1097.9	932.9
47.5°	1232.4	908.9	1008.2	915.6	851.1
50°	1173.4	868.1	983.4	836.9	795.2
52.5°	1116.0	825.9	966.3	772.1	744.0
55°	1033.8	755.0	952.3	686.5	680.8
57.5°	946.5	682.9	842.2	612.0	621.8
60°	892.2	636.2	727.3	568.0	556.7
62.5°	834.8	590.9	620.3	512.2	500.8
65°	740.9	519.0	498.5	409.2	409.2
67.5°	637.7	444.3	403.8	334.9	289.4
70°	566.4	395.7	343.3	267.0	236.6
72.5°	490.3	343.9	281.2	218.8	183.9
75°	382.1	264.5	195.9	139.6	135.8
77.5°	276.2	190.5	131.9	103.6	104.0
80°	209.5	145.0	85.3	83.4	85.3
82.5°	147.4	99.6	63.6	66.3	66.7
85°	65.9	43.2	38.8	31.0	29.1
87.5°	14.0	13.0	9.1	8.9	8.9
90°	0.0	2.9	6.9	5.9	5.9
92.5°	14.3	51.3	163.9	54.0	41.6
95°	41.6	126.9	564.8	201.4	123.9
97.5°	78.3	165.1	958.5	583.8	356.3
100°	102.1	187.3	1106.8	986.9	640.1
102.5°	129.0	211.2	1088.5	1460.1	1110.1
105°	170.4	246.0	993.8	1898.2	1797.4
107.5°	215.2	286.3	903.9	1936.2	2042.9
110°	247.7	312.6	861.0	1889.0	2081.8



TEST NUMBER: P854059

CATALOG NUMBER: SQ2-PH1-125U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	274.7	338.8	834.1	1803.8	2052.4
115°	315.1	376.1	809.5	1668.3	1962.9
117.5°	356.7	411.7	800.0	1544.3	1837.4
120°	380.5	434.7	797.6	1468.0	1751.8
122.5°	403.5	457.0	798.4	1401.7	1666.2
125°	438.0	488.3	798.6	1317.2	1552.7
127.5°	467.5	519.0	798.4	1253.9	1450.2
130°	486.5	538.8	797.6	1217.8	1393.1
132.5°	503.2	557.8	796.8	1184.2	1348.7
135°	529.1	584.3	794.7	1136.8	1282.2
137.5°	554.5	610.1	792.5	1088.7	1217.8
140°	572.7	626.0	791.7	1056.0	1178.1
142.5°	590.1	641.1	791.7	1024.8	1133.7
145°	618.3	663.8	792.7	979.1	1072.1
147.5°	645.6	685.2	794.1	940.2	1012.1
150°	663.9	698.7	795.7	916.9	978.0
152.5°	682.1	710.8	796.4	899.2	947.8
155°	705.5	728.7	797.6	876.7	909.6
157.5°	727.7	744.3	798.8	860.0	883.0
160°	741.2	754.7	799.6	849.6	868.0
162.5°	753.0	763.5	799.6	840.7	854.5
165°	769.9	776.7	799.6	829.6	839.2
167.5°	781.8	786.0	799.8	821.1	826.2
170°	789.7	791.6	800.6	815.5	817.4
172.5°	795.3	796.4	802.2	812.3	811.9
175°	802.6	802.6	802.6	808.5	806.5
177.5°	805.6	804.8	804.0	807.9	804.8
180°	805.6	805.6	805.6	805.6	805.6



TEST NUMBER: P854059

CATALOG NUMBER: SQ2-PH1-125U-100D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.24	20.07	20.22	21.06	22.37	17.91	18.74	18.89	19.74	21.04
	3H	21.26	22.01	22.25	23.01	24.33	18.94	19.69	19.93	20.69	22.02
	4H	21.99	22.70	22.99	23.70	25.04	19.15	19.86	20.16	20.86	22.20
	6H	22.47	23.12	23.49	24.13	25.48	19.30	19.95	20.31	20.96	22.30
	8H	22.60	23.22	23.62	24.24	25.59	19.33	19.95	20.35	20.97	22.32
	12H	22.64	23.23	23.67	24.25	25.62	19.33	19.91	20.35	20.93	22.30
4H	2H	19.61	20.32	20.62	21.32	22.65	18.55	19.25	19.56	20.26	21.59
	3H	21.71	22.30	22.73	23.33	24.68	19.73	20.31	20.74	21.35	22.69
	4H	22.53	23.06	23.55	24.09	25.46	20.00	20.54	21.03	21.56	22.93
	6H	23.11	23.57	24.15	24.62	25.99	20.21	20.67	21.24	21.72	23.08
	8H	23.28	23.71	24.32	24.75	26.13	20.26	20.69	21.30	21.73	23.12
	12H	23.35	23.73	24.40	24.79	26.18	20.27	20.66	21.32	21.71	23.10
8H	4H	22.54	22.97	23.58	24.01	25.40	20.21	20.64	21.25	21.68	23.07
	6H	23.19	23.55	24.26	24.63	26.01	20.48	20.84	21.55	21.92	23.30
	8H	23.42	23.73	24.49	24.80	26.20	20.59	20.90	21.66	21.97	23.37
	12H	23.53	23.80	24.60	24.87	26.31	20.63	20.90	21.70	21.97	23.41
12H	4H	22.49	22.88	23.55	23.94	25.33	20.21	20.60	21.27	21.65	23.04
	6H	23.17	23.48	24.24	24.55	25.95	20.51	20.83	21.58	21.89	23.29
	8H	23.40	23.67	24.47	24.73	26.18	20.63	20.90	21.70	21.97	23.41