

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853736

Luminaire Tested: SQ2-F-150U-100D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853736
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-14, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-150U-100D-940-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10517.8 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 94.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853736

CATALOG NUMBER: SQ2-F-150U-100D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853736

CATALOG NUMBER: SQ2-F-150U-100D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR	0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40	40	
	1	95	91	87	84	87	83	80	77	68	66	64	54	53	51	41	40	40	34	34	
	2	87	79	73	68	79	72	67	63	59	56	52	47	45	43	36	35	33	28	28	
	3	79	70	62	57	72	64	57	52	52	48	44	42	39	36	32	30	28	24	24	
	4	72	62	54	48	65	56	49	44	46	41	37	37	33	31	29	26	24	20	20	
	5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	26	23	21	17	17	
	6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15	15	
	7	56	44	36	31	51	40	33	29	34	28	24	27	23	20	21	18	16	13	13	
	8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	17	14	12	12	
	9	48	36	29	24	44	33	27	22	28	23	19	23	19	16	18	15	13	11	11	
	10	45	33	26	21	41	31	24	20	26	21	17	21	17	14	17	14	12	10	10	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24314	24314	24314
5°	24141	24208	24407
10°	24082	24150	24319
15°	23936	24005	24246
20°	23794	23830	24041
25°	23575	23575	23721
30°	23332	23332	23409
35°	23049	22969	23130
40°	22744	22658	22744
45°	22393	22299	22393
50°	22057	21851	21901
55°	21540	21484	21368
60°	21003	20870	20734
65°	20378	20145	19908
70°	19176	19081	18694
75°	18047	17661	17149
80°	16020	15639	15072
85°	12931	11782	11023

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 22530 cd/sqm



TEST NUMBER: P853736

CATALOG NUMBER: SQ2-F-150U-100D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.3	1.4
10°-20°	406.7	3.9
20°-30°	611.9	5.8
30°-40°	732.2	7.0
40°-50°	755.5	7.2
50°-60°	681.5	6.5
60°-70°	520.1	4.9
70°-80°	299.0	2.8
80°-90°	79.1	0.8
90°-100°	388.3	3.7
100°-110°	1271.3	12.1
110°-120°	1256.9	12.0
120°-130°	1027.5	9.8
130°-140°	838.5	8.0
140°-150°	652.5	6.2
150°-160°	469.8	4.5
160°-170°	287.4	2.7
170°-180°	97.1	0.9
0°-30°	1161.0	11.0
0°-40°	1893.2	18.0
0°-60°	3330.2	31.7
0°-90°	4228.4	40.2
90°-120°	2916.5	27.7
90°-150°	5435.0	51.7
90°-180°	6289.0	59.8
0°-180°	10517.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1506	1506	1506	1506	1506	
5°	1490	1510	1494	1496	1506	141
15°	1432	1450	1436	1442	1450	404
25°	1323	1337	1323	1326	1332	609
35°	1169	1177	1165	1170	1174	731
45°	981	987	977	979	981	757
55°	765	769	763	759	759	684
65°	533	531	527	523	521	524
75°	289	287	283	277	275	305
85°	70	66	64	58	60	81
90°	1	3	8	7	8	5
95°	54	158	706	251	163	62
105°	221	315	1262	2398	2278	233
115°	398	476	1025	2119	2487	393
125°	554	618	1011	1671	1963	493
135°	667	738	1002	1441	1624	516
145°	780	838	1000	1240	1358	489
155°	889	919	1006	1109	1152	409
165°	971	980	1011	1050	1061	274
175°	1015	1015	1016	1023	1021	96
180°	1019	1019	1019	1019	1019	

TEST NUMBER: P853736

CATALOG NUMBER: SQ2-F-150U-100D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1505.9	1505.9	1505.9	1505.9	1505.9
2.5°	1496.0	1513.7	1499.3	1502.6	1504.2
5°	1489.5	1509.5	1493.6	1495.8	1505.9
7.5°	1477.1	1498.8	1481.2	1485.2	1496.4
10°	1468.9	1489.0	1473.0	1475.3	1483.3
12.5°	1455.8	1475.9	1459.9	1463.8	1471.8
15°	1432.0	1450.1	1436.1	1442.5	1450.5
17.5°	1404.5	1423.8	1408.2	1413.7	1420.5
20°	1384.8	1400.9	1386.9	1389.2	1399.2
22.5°	1360.2	1376.3	1363.9	1364.5	1372.9
25°	1323.3	1337.3	1323.3	1325.5	1331.5
27.5°	1281.0	1293.0	1281.0	1283.2	1288.4
30°	1251.5	1263.5	1251.5	1253.6	1255.6
32.5°	1218.6	1229.1	1217.0	1219.2	1224.4
35°	1169.4	1177.4	1165.3	1169.5	1173.5
37.5°	1116.9	1122.9	1112.8	1114.9	1118.5
40°	1079.1	1085.2	1075.0	1077.1	1079.1
42.5°	1041.4	1045.8	1035.6	1037.8	1041.4
45°	980.7	986.7	976.6	978.7	980.7
47.5°	919.1	922.7	914.2	912.6	916.2
50°	878.1	880.1	869.9	869.9	871.9
52.5°	833.8	835.8	828.8	825.6	827.6
55°	765.2	769.3	763.2	759.1	759.1
57.5°	696.3	699.9	692.2	690.1	689.7
60°	650.4	652.4	646.3	644.2	642.1
62.5°	604.4	604.8	598.7	596.6	594.6
65°	533.4	531.4	527.3	523.1	521.1
67.5°	453.8	455.8	451.8	445.2	445.2
70°	406.2	408.2	404.2	396.0	396.0
72.5°	360.3	359.1	356.6	349.9	346.7
75°	289.3	287.3	283.1	276.9	274.9
77.5°	218.3	216.3	214.2	206.4	208.0
80°	172.3	170.3	168.2	162.1	162.1
82.5°	131.3	127.7	125.6	119.4	119.4
85°	69.8	65.7	63.6	57.5	59.5
87.5°	19.9	18.7	18.1	14.6	14.8
90°	1.0	3.1	8.4	7.4	8.4
92.5°	17.8	64.9	199.4	64.8	51.9
95°	54.5	157.9	705.9	251.4	163.4
97.5°	98.9	208.2	1211.1	732.6	454.1
100°	129.9	234.3	1401.2	1251.3	829.4
102.5°	165.0	267.0	1380.3	1843.8	1429.3
105°	221.0	315.2	1262.0	2397.6	2277.8
107.5°	276.1	362.5	1146.5	2449.4	2581.1
110°	312.1	396.1	1091.3	2389.1	2633.9



TEST NUMBER: P853736

CATALOG NUMBER: SQ2-F-150U-100D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	346.4	427.9	1057.7	2284.3	2597.8
115°	398.0	475.8	1025.3	2118.6	2487.3
117.5°	448.0	520.7	1012.9	1955.8	2330.2
120°	480.7	549.3	1009.6	1860.9	2225.4
122.5°	510.0	577.0	1009.6	1779.0	2117.4
125°	554.0	617.5	1010.6	1670.7	1962.6
127.5°	591.3	656.0	1009.4	1590.9	1844.9
130°	614.7	680.3	1008.5	1542.6	1772.0
132.5°	635.7	702.9	1006.0	1501.1	1709.1
135°	667.1	737.8	1002.2	1441.0	1624.3
137.5°	700.2	770.2	999.9	1378.4	1544.1
140°	723.7	791.2	999.1	1338.8	1495.5
142.5°	747.1	810.6	999.1	1296.6	1438.5
145°	780.2	837.6	1000.1	1239.5	1358.3
147.5°	815.0	862.7	1001.6	1189.8	1279.5
150°	836.8	878.7	1003.3	1161.0	1236.8
152.5°	858.5	895.6	1004.1	1137.3	1200.0
155°	889.1	918.8	1006.4	1109.0	1152.0
157.5°	916.6	938.1	1008.7	1086.7	1117.9
160°	934.2	951.6	1009.6	1074.0	1098.6
162.5°	949.2	963.4	1009.6	1063.8	1081.8
165°	970.8	980.0	1010.6	1049.6	1060.9
167.5°	989.0	993.5	1011.9	1038.6	1044.8
170°	999.1	1001.1	1012.7	1032.7	1034.7
172.5°	1006.6	1007.9	1015.2	1028.4	1028.8
175°	1014.8	1014.8	1015.8	1023.1	1021.1
177.5°	1019.0	1018.2	1017.3	1022.3	1019.0
180°	1019.0	1019.0	1019.0	1019.0	1019.0

TEST NUMBER: P853736

CATALOG NUMBER: SQ2-F-150U-100D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.08	18.87	19.12	19.91	21.31	18.00	18.79	19.04	19.83	21.24
	3H	19.85	20.56	20.90	21.61	23.04	19.74	20.44	20.78	21.49	22.92
	4H	20.51	21.18	21.57	22.23	23.66	20.36	21.03	21.41	22.08	23.51
	6H	20.98	21.59	22.04	22.65	24.09	20.79	21.41	21.86	22.47	23.91
	8H	21.11	21.70	22.18	22.77	24.21	20.91	21.50	21.98	22.57	24.01
	12H	21.18	21.74	22.26	22.81	24.27	20.96	21.52	22.04	22.59	24.05
4H	2H	18.62	19.29	19.69	20.35	21.78	18.56	19.23	19.62	20.28	21.71
	3H	20.60	21.16	21.67	22.24	23.69	20.49	21.05	21.57	22.14	23.58
	4H	21.39	21.90	22.47	22.97	24.44	21.25	21.76	22.32	22.83	24.30
	6H	21.97	22.42	23.06	23.51	24.97	21.79	22.24	22.88	23.33	24.79
	8H	22.16	22.57	23.25	23.66	25.13	21.96	22.37	23.05	23.46	24.93
	12H	22.26	22.63	23.36	23.73	25.21	22.03	22.40	23.14	23.51	24.99
8H	4H	21.63	22.04	22.72	23.13	24.60	21.50	21.92	22.59	23.00	24.48
	6H	22.34	22.68	23.45	23.81	25.29	22.18	22.52	23.29	23.65	25.12
	8H	22.61	22.91	23.73	24.02	25.51	22.42	22.72	23.53	23.83	25.32
	12H	22.78	23.04	23.90	24.15	25.67	22.55	22.81	23.67	23.92	25.45
12H	4H	21.62	21.99	22.72	23.09	24.57	21.50	21.87	22.60	22.97	24.45
	6H	22.39	22.69	23.50	23.80	25.29	22.23	22.53	23.34	23.64	25.13
	8H	22.68	22.94	23.80	24.05	25.58	22.49	22.75	23.61	23.86	25.39