

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854095

Luminaire Tested: SQ2-PP3-050U-100D-935-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P854095  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-10, G2-2308-131-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PP3-050U-100D-935-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6577.9 lumens  
Efficiency: N/A  
Efficacy: 125.5 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 52.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854095

CATALOG NUMBER: SQ2-PP3-050U-100D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854095

CATALOG NUMBER: SQ2-PP3-050U-100D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70				
1	103	99	95	92	97	94	91	88	84	82	80	75	74	72	67	66	65	61				
2	94	87	81	76	89	83	78	73	75	71	67	67	64	61	60	58	56	52				
3	87	77	70	64	82	74	67	62	66	61	57	60	56	52	54	51	48	45				
4	80	69	61	55	75	66	59	53	59	54	49	54	49	45	48	45	42	39				
5	73	62	54	48	69	59	52	46	54	47	43	49	44	40	44	40	37	34				
6	68	56	47	42	64	53	46	40	48	42	38	44	39	35	40	36	33	30				
7	63	50	42	37	59	48	41	36	44	38	33	40	35	31	37	32	29	27				
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	34	29	26	24				
9	54	42	34	29	52	40	33	29	37	31	27	34	29	25	31	27	24	22				
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	25	21	20				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	29624	29624	29624
5°	29392	29644	29927
10°	29542	29763	30145
15°	29471	29762	30216
20°	29259	29960	30826
25°	29094	30337	32446
30°	28929	30954	33122
35°	28519	31042	33183
40°	27758	30987	30661
45°	26928	29583	23341
50°	25870	25237	19439
55°	24076	21239	13976
60°	20731	18225	10020
65°	17486	14078	9857
70°	14559	11080	9432
75°	12339	9557	8833
80°	10460	8294	7931
85°	8262	6836	4316

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 29583 cd/sqm



TEST NUMBER: P854095

CATALOG NUMBER: SQ2-PP3-050U-100D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	174.7	2.7
10°-20°	505.6	7.7
20°-30°	792.1	12.0
30°-40°	977.2	14.9
40°-50°	920.0	14.0
50°-60°	651.4	9.9
60°-70°	371.2	5.6
70°-80°	183.6	2.8
80°-90°	45.3	0.7
90°-100°	125.5	1.9
100°-110°	398.1	6.1
110°-120°	390.3	5.9
120°-130°	317.6	4.8
130°-140°	259.0	3.9
140°-150°	201.9	3.1
150°-160°	145.5	2.2
160°-170°	88.9	1.4
170°-180°	30.0	0.5
0°-30°	1472.5	22.4
0°-40°	2449.7	37.2
0°-60°	4021.1	61.1
0°-90°	4621.2	70.3
90°-120°	913.9	13.9
90°-150°	1692.4	25.7
90°-180°	1957.0	29.8
0°-180°	6577.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1835	1835	1835	1835	1835	
5°	1814	1846	1829	1833	1846	173
15°	1763	1788	1780	1798	1808	497
25°	1633	1675	1703	1772	1821	752
35°	1447	1487	1575	1665	1684	902
45°	1179	1268	1296	1098	1022	908
55°	855	907	754	569	496	755
65°	458	482	368	260	258	460
75°	198	219	153	144	142	214
85°	45	41	37	29	23	52
90°	0	1	3	3	3	3
95°	17	51	228	84	54	19
105°	69	98	392	747	716	73
115°	124	147	317	659	775	122
125°	171	192	312	516	608	153
135°	207	227	310	444	500	160
145°	242	260	310	383	417	151
155°	276	285	311	342	356	127
165°	300	303	312	324	327	85
175°	314	313	314	316	315	30
180°	315	315	315	315	315	



TEST NUMBER: P854095

CATALOG NUMBER: SQ2-PP3-050U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1834.8	1834.8	1834.8	1834.8	1834.8
2.5°	1820.9	1846.7	1830.2	1833.3	1836.4
5°	1813.5	1845.7	1829.0	1833.2	1846.5
7.5°	1806.5	1839.5	1823.2	1830.2	1846.5
10°	1801.9	1830.3	1815.4	1825.4	1838.7
12.5°	1787.9	1814.8	1801.5	1814.5	1826.3
15°	1763.1	1787.7	1780.5	1798.2	1807.7
17.5°	1729.3	1759.3	1759.2	1784.2	1794.1
20°	1702.9	1739.0	1743.7	1775.1	1794.1
22.5°	1675.0	1717.1	1725.0	1772.3	1805.0
25°	1633.1	1674.8	1702.9	1771.9	1821.3
27.5°	1584.2	1625.6	1683.5	1760.8	1799.9
30°	1551.7	1591.5	1660.3	1740.6	1776.6
32.5°	1511.3	1552.7	1626.1	1712.6	1745.6
35°	1446.9	1486.7	1574.9	1664.6	1683.5
37.5°	1372.8	1418.0	1516.7	1566.8	1567.9
40°	1317.0	1375.8	1470.2	1479.3	1454.7
42.5°	1262.7	1338.1	1405.0	1364.1	1254.5
45°	1179.3	1268.4	1295.6	1098.0	1022.2
47.5°	1090.4	1178.4	1135.0	920.9	868.5
50°	1029.9	1113.4	1004.7	823.2	773.9
52.5°	961.6	1036.0	888.3	729.5	654.4
55°	855.3	906.6	754.5	568.6	496.5
57.5°	727.3	763.4	645.1	426.8	346.0
60°	642.0	670.4	564.4	350.2	310.3
62.5°	564.4	589.8	480.6	304.2	290.2
65°	457.7	482.4	368.5	259.9	258.0
67.5°	364.3	391.2	282.8	226.9	224.6
70°	308.4	336.8	234.7	203.6	199.8
72.5°	261.8	288.8	199.0	178.8	176.5
75°	197.8	218.7	153.2	143.5	141.6
77.5°	143.5	156.8	114.0	109.0	107.1
80°	112.5	118.2	89.2	87.2	85.3
82.5°	84.6	82.7	67.5	65.5	62.1
85°	44.6	40.8	36.9	29.0	23.3
87.5°	14.0	14.2	6.8	5.2	5.2
90°	0.0	1.0	3.0	3.0	3.0
92.5°	5.5	22.0	70.4	23.4	16.4
95°	16.8	50.8	227.9	84.5	54.5
97.5°	31.3	65.8	386.0	241.2	148.0
100°	41.6	74.6	439.9	401.1	260.6
102.5°	52.7	84.1	430.4	589.0	450.8
105°	69.4	97.5	392.4	747.4	716.4
107.5°	86.0	112.0	356.1	763.9	805.8
110°	97.1	122.3	337.9	744.9	822.4



TEST NUMBER: P854095

CATALOG NUMBER: SQ2-PP3-050U-100D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	108.2	131.8	327.6	712.1	810.5
115°	123.9	147.1	317.1	658.6	774.9
117.5°	139.1	161.2	312.9	607.1	724.3
120°	148.6	169.9	312.1	575.3	688.7
122.5°	158.1	178.7	312.1	549.8	655.4
125°	171.4	191.8	312.1	516.4	608.4
127.5°	183.1	202.7	312.1	490.5	569.0
130°	190.2	210.6	312.1	475.2	546.0
132.5°	197.4	217.7	311.3	463.2	526.9
135°	207.1	227.4	310.1	444.2	500.4
137.5°	216.6	237.9	309.9	426.0	476.2
140°	222.9	244.3	309.2	413.2	458.8
142.5°	230.9	251.4	309.9	400.5	442.9
145°	241.8	260.2	310.1	383.2	417.2
147.5°	252.7	268.4	310.3	368.0	395.8
150°	260.6	273.2	311.1	359.2	381.5
152.5°	266.9	278.0	311.1	352.0	370.4
155°	275.5	285.2	311.1	342.2	355.7
157.5°	284.6	291.2	312.1	336.1	345.4
160°	289.3	295.1	312.1	332.1	339.9
162.5°	294.1	298.4	312.1	328.9	334.3
165°	300.2	303.1	312.1	324.1	327.0
167.5°	306.0	306.8	313.1	320.7	323.2
170°	309.2	309.2	313.1	319.1	320.1
172.5°	310.7	311.5	313.1	317.5	317.7
175°	314.1	313.1	314.1	316.1	315.1
177.5°	315.1	314.3	314.3	315.9	314.3
180°	315.1	315.1	315.1	315.1	315.1

-----



TEST NUMBER: P854095

CATALOG NUMBER: SQ2-PP3-050U-100D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.03	22.06	21.80	22.84	23.79	17.42	18.45	18.19	19.24	20.19
	3H	22.14	23.05	22.92	23.85	24.83	18.54	19.46	19.32	20.25	21.24
	4H	22.49	23.35	23.29	24.15	25.15	19.01	19.88	19.81	20.68	21.67
	6H	22.71	23.51	23.52	24.32	25.33	19.37	20.16	20.18	20.97	21.98
	8H	22.76	23.52	23.59	24.35	25.36	19.46	20.21	20.28	21.04	22.05
	12H	22.78	23.50	23.61	24.33	25.36	19.48	20.20	20.30	21.02	22.06
4H	2H	21.16	22.02	21.96	22.82	23.82	18.16	19.02	18.96	19.83	20.82
	3H	22.48	23.20	23.30	24.03	25.05	19.43	20.14	20.24	20.98	21.99
	4H	22.96	23.61	23.79	24.45	25.49	19.99	20.63	20.82	21.47	22.51
	6H	23.31	23.87	24.16	24.73	25.77	20.44	20.99	21.28	21.86	22.90
	8H	23.40	23.93	24.25	24.78	25.84	20.56	21.08	21.41	21.94	22.99
	12H	23.45	23.92	24.32	24.79	25.86	20.60	21.06	21.46	21.94	23.00
8H	4H	22.99	23.51	23.84	24.37	25.43	20.27	20.79	21.12	21.65	22.71
	6H	23.43	23.86	24.31	24.76	25.82	20.82	21.25	21.70	22.15	23.21
	8H	23.59	23.97	24.47	24.86	25.94	21.01	21.39	21.90	22.29	23.36
	12H	23.68	24.02	24.57	24.90	26.03	21.09	21.43	21.98	22.31	23.44
12H	4H	22.96	23.43	23.83	24.30	25.37	20.29	20.76	21.16	21.63	22.69
	6H	23.42	23.80	24.31	24.70	25.77	20.88	21.26	21.76	22.15	23.23
	8H	23.60	23.93	24.49	24.82	25.95	21.09	21.43	21.98	22.31	23.44