

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853784

Luminaire Tested: SQ2-FA-0U-100D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853784
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-11)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FA-0U-100D-940-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3972.9 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 0.95 / 0.95
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853784

CATALOG NUMBER: SQ2-FA-0U-100D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853784

CATALOG NUMBER: SQ2-FA-0U-100D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78				78
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70				70
4	90	80	73	68	88	79	72	67	77	71	66	74	70	65	72	68	65	63				63
5	84	74	66	61	82	73	66	60	71	65	60	69	64	59	67	62	59	57				57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52				52
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48				48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44				44
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41				41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38				38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	43923	43923	43923	43923
5°	43692	43759	43527	43726
10°	43625	43458	43458	43458
15°	43483	43039	43141	43039
20°	43148	41314	42830	41701
25°	42580	34867	42287	35600
30°	42189	20005	41730	20273
35°	41449	17186	40923	16943
40°	40301	9038	39178	8951
45°	36634	3889	35321	3889
50°	24169	4690	22933	4381
55°	13515	8662	12822	7854
60°	7288	12190	7156	10931
65°	6426	14816	6739	16852
70°	6005	17722	5712	18694
75°	5633	15228	5758	15739
80°	4770	10869	4770	11446
85°	4187	6076	3798	7225

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 36634 cd/sqm



TEST NUMBER: P853784

CATALOG NUMBER: SQ2-FA-0U-100D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.0	6.4
10°-20°	726.3	18.3
20°-30°	990.3	24.9
30°-40°	832.2	20.9
40°-50°	472.7	11.9
50°-60°	250.8	6.3
60°-70°	230.9	5.8
70°-80°	169.5	4.3
80°-90°	44.3	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1972.6	49.7
0°-40°	2804.8	70.6
0°-60°	3528.2	88.8
0°-90°	3972.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3972.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2720	2720	2720	2720	2720	
5°	2696	2700	2686	2698	2696	256
15°	2601	2575	2581	2575	2601	733
25°	2390	1957	2374	1998	2390	1102
35°	2103	872	2076	860	2103	1313
45°	1604	170	1547	170	1604	1173
55°	480	308	456	279	480	462
65°	168	388	176	441	168	169
75°	90	244	92	252	90	93
85°	23	33	20	39	23	26
90°	0	0	0	0	0	



TEST NUMBER: P853784

CATALOG NUMBER: SQ2-FA-0U-100D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	2720.4	2720.4	2720.4	2720.4	2720.4	2720.4	2720.4	2720.4	2720.4	2720.4	2720.4
2.5°	2705.7	2745.8	2710.6	2706.0	2720.4	2717.2	2712.2	2731.2	2699.1	2731.2	2705.7
5°	2695.8	2741.9	2689.7	2675.8	2699.9	2683.9	2697.9	2725.7	2685.6	2721.7	2681.4
7.5°	2679.0	2719.9	2657.2	2648.3	2672.0	2658.0	2663.8	2702.4	2668.7	2692.4	2656.0
10°	2660.9	2697.0	2634.3	2628.6	2650.7	2636.6	2642.5	2682.8	2650.7	2672.7	2636.3
12.5°	2641.2	2669.3	2606.4	2603.9	2622.8	2613.5	2616.2	2650.1	2624.4	2646.5	2611.7
15°	2601.4	2627.5	2564.5	2554.7	2574.8	2566.7	2570.7	2601.0	2580.9	2595.0	2564.5
17.5°	2552.2	2573.1	2510.3	2480.8	2481.6	2491.7	2510.3	2546.9	2528.8	2547.3	2504.2
20°	2511.2	2535.2	2466.0	2408.5	2404.5	2414.5	2466.0	2502.7	2492.7	2512.8	2451.7
22.5°	2463.6	2479.6	2416.8	2319.6	2306.0	2316.0	2410.2	2453.6	2450.0	2463.7	2387.7
25°	2390.1	2406.2	2291.6	2151.8	1957.2	2139.8	2295.7	2373.7	2373.7	2385.7	2285.5
27.5°	2315.4	2315.8	2108.6	1382.0	1219.1	1332.2	2105.8	2274.8	2294.1	2288.1	2091.0
30°	2262.9	2248.9	1869.0	1117.1	1073.0	1101.1	1871.1	2206.2	2238.3	2216.2	1821.8
32.5°	2202.2	2162.5	1379.9	1027.0	990.9	1015.8	1334.4	2124.7	2180.9	2133.1	1432.8
35°	2102.9	1998.6	1052.5	908.0	871.9	904.0	1044.3	1963.9	2076.2	1947.8	1087.4
37.5°	1995.8	1588.6	926.5	723.3	645.4	707.6	922.0	1571.6	1952.3	1535.1	925.7
40°	1912.1	1248.1	833.0	529.1	428.8	499.0	826.8	1190.8	1858.8	1281.0	812.4
42.5°	1800.5	1096.4	668.8	336.0	263.0	307.5	641.3	1071.0	1743.9	1110.0	646.7
45°	1604.4	942.4	396.0	184.3	170.3	178.3	365.2	925.0	1546.9	905.0	404.2
47.5°	1270.8	718.7	254.4	156.7	171.9	156.7	246.6	695.9	1200.2	694.7	254.0
50°	962.2	561.0	197.0	158.6	186.7	158.6	190.8	541.9	913.0	592.0	194.9
52.5°	712.7	468.8	160.8	173.9	224.4	177.1	156.3	456.4	676.6	477.6	152.2
55°	480.1	367.7	129.3	229.5	307.7	235.5	129.3	357.2	455.5	353.1	125.1
57.5°	304.5	273.6	130.9	295.1	351.2	300.7	132.9	263.7	292.1	264.9	114.9
60°	225.7	215.6	145.7	313.3	377.5	317.3	147.7	207.5	221.6	205.5	123.1
62.5°	186.3	169.8	175.2	339.3	392.3	330.5	178.9	162.0	193.7	155.2	136.2
65°	168.2	110.1	207.2	343.6	387.8	343.6	209.3	104.2	176.4	112.2	184.6
67.5°	151.8	81.6	200.2	341.3	390.2	342.1	195.3	77.9	145.7	75.9	188.7
70°	127.2	73.0	188.7	347.4	375.4	335.3	188.7	70.9	121.0	68.9	221.6
72.5°	105.9	69.4	175.6	320.7	332.8	308.7	177.3	69.0	106.3	62.1	208.4
75°	90.3	68.2	168.2	256.2	244.1	244.1	164.1	66.2	92.3	62.2	162.1
77.5°	67.7	60.5	139.5	167.2	158.0	158.0	137.0	58.4	64.4	54.8	131.7
80°	51.3	55.3	114.9	123.0	116.9	116.9	110.8	53.3	51.3	51.3	108.7
82.5°	39.8	47.0	88.6	90.2	85.8	84.2	86.2	46.6	39.8	43.0	84.1
85°	22.6	32.6	47.2	38.8	32.8	30.8	45.1	30.5	20.5	30.5	45.1
87.5°	8.2	14.6	6.6	6.6	6.6	6.6	6.6	14.6	8.2	13.0	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P853784

CATALOG NUMBER: SQ2-FA-0U-100D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	2720.4	2720.4	2720.4	2720.4	2720.4	2720.4
2.5°	2699.3	2710.6	2710.6	2704.0	2736.1	2705.7
5°	2671.8	2697.9	2685.8	2685.6	2725.9	2695.8
7.5°	2652.5	2676.9	2665.7	2663.4	2703.1	2679.0
10°	2632.6	2650.7	2642.7	2648.6	2685.0	2660.9
12.5°	2604.8	2626.1	2618.0	2627.3	2660.5	2641.2
15°	2556.7	2574.8	2578.8	2583.0	2621.5	2601.4
17.5°	2477.3	2486.1	2506.2	2534.6	2574.7	2552.2
20°	2415.0	2427.0	2439.1	2488.6	2535.2	2511.2
22.5°	2344.1	2340.1	2368.1	2426.2	2484.4	2463.6
25°	2152.7	1998.3	2168.8	2318.3	2396.1	2390.1
27.5°	1498.9	1300.7	1476.0	2139.8	2303.4	2315.4
30°	1179.6	1087.4	1177.6	1910.0	2234.8	2262.9
32.5°	1047.3	984.0	1038.9	1453.8	2148.4	2202.2
35°	903.8	859.6	903.8	1087.4	1978.5	2102.9
37.5°	723.4	633.1	721.8	939.6	1599.4	1995.8
40°	539.0	424.7	523.0	841.2	1278.2	1912.1
42.5°	359.1	273.7	339.9	662.3	1105.6	1800.5
45°	194.4	170.3	186.3	400.1	902.3	1604.4
47.5°	152.4	161.3	152.4	252.3	690.2	1270.8
50°	146.3	174.4	146.3	194.9	571.0	962.2
52.5°	159.5	189.2	157.9	153.9	466.0	712.7
55°	180.7	279.0	182.7	125.1	341.7	480.1
57.5°	257.3	313.9	260.1	118.6	263.1	304.5
60°	264.3	338.5	262.3	125.1	203.6	225.7
62.5°	312.6	418.9	312.2	143.2	151.4	186.3
65°	401.0	441.1	405.0	182.6	108.1	168.2
67.5°	380.6	409.1	376.6	195.7	74.4	151.8
70°	373.9	396.0	369.9	223.6	69.0	127.2
72.5°	348.8	351.6	341.6	207.2	62.1	105.9
75°	270.4	252.3	260.4	178.5	62.2	90.3
77.5°	168.1	160.8	162.0	136.2	54.9	67.7
80°	127.1	123.1	121.1	114.9	51.3	51.3
82.5°	94.3	90.3	88.3	88.6	43.0	39.8
85°	43.0	39.0	37.0	51.3	30.6	22.6
87.5°	8.2	8.2	6.6	8.2	11.4	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P853784

CATALOG NUMBER: SQ2-FA-0U-100D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.14	18.45	17.51	18.77	19.08	16.00	17.31	16.36	17.62	17.94
	3H	17.87	19.04	18.25	19.37	19.73	22.17	23.35	22.55	23.68	24.04
	4H	18.29	19.39	18.70	19.74	20.12	23.47	24.57	23.87	24.92	25.30
	6H	18.67	19.68	19.08	20.05	20.44	24.09	25.10	24.51	25.47	25.87
	8H	18.79	19.75	19.22	20.15	20.55	24.23	25.19	24.66	25.58	25.98
	12H	18.88	19.80	19.31	20.18	20.61	24.28	25.20	24.71	25.58	26.01
4H	2H	17.58	18.68	17.98	19.03	19.41	16.57	17.67	16.97	18.02	18.40
	3H	18.60	19.51	19.02	19.92	20.32	22.93	23.84	23.34	24.24	24.64
	4H	19.17	20.00	19.61	20.41	20.86	24.39	25.21	24.82	25.63	26.07
	6H	19.67	20.38	20.13	20.83	21.29	25.14	25.85	25.60	26.30	26.77
	8H	19.85	20.51	20.31	20.96	21.43	25.31	25.98	25.78	26.43	26.90
	12H	19.98	20.57	20.47	21.05	21.53	25.40	25.98	25.88	26.47	26.94
8H	4H	20.30	20.96	20.77	21.41	21.88	24.53	25.20	25.00	25.65	26.12
	6H	20.92	21.46	21.42	21.96	22.44	25.42	25.97	25.93	26.46	26.95
	8H	21.15	21.64	21.67	22.15	22.65	25.67	26.16	26.19	26.67	27.17
	12H	21.35	21.77	21.86	22.27	22.84	25.82	26.24	26.33	26.74	27.31
12H	4H	20.46	21.05	20.95	21.54	22.01	24.51	25.10	25.00	25.59	26.06
	6H	21.19	21.68	21.71	22.19	22.69	25.43	25.92	25.95	26.43	26.92
	8H	21.51	21.94	22.03	22.43	23.00	25.73	26.16	26.25	26.66	27.23