

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P853895

Luminaire Tested: SQ2-FB-125U-125D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P853895
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-125U-125D-940-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10490.5 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 93.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P853895

CATALOG NUMBER: SQ2-FB-125U-125D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P853895

CATALOG NUMBER: SQ2-FB-125U-125D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	42
2	89	81	75	69	81	75	69	65	63	59	56	53	50	47	43	41	39	34
3	80	71	63	57	74	65	59	54	55	50	46	46	43	39	38	35	33	29
4	73	62	54	48	67	58	50	45	49	43	39	41	37	33	33	30	28	24
5	67	55	47	41	61	51	44	38	43	38	33	36	32	28	30	26	24	20
6	62	49	41	35	56	46	38	33	39	33	29	33	28	25	27	23	21	18
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18	15
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16	13
9	49	36	29	23	45	34	27	22	29	23	19	24	20	17	20	17	14	12
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8578	8578	8578
5°	8363	11593	15195
10°	7832	22448	29568
15°	7089	29207	34033
20°	6277	32129	35641
25°	5553	34360	36225
30°	4905	35386	36672
35°	4380	36001	39425
40°	3984	36343	41890
45°	3674	36516	43863
50°	3464	37216	44661
55°	3381	38185	45017
60°	3465	38689	44792
65°	3610	38158	43526
70°	3739	36902	32922
75°	4142	33144	18166
80°	4277	17099	16867
85°	4261	11838	7095

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 45422 cd/sqm



TEST NUMBER: P853895

CATALOG NUMBER: SQ2-FB-125U-125D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.0	0.8
10°-20°	406.4	3.9
20°-30°	714.9	6.8
30°-40°	925.4	8.8
40°-50°	1020.7	9.7
50°-60°	953.0	9.1
60°-70°	736.5	7.0
70°-80°	339.7	3.2
80°-90°	65.8	0.6
90°-100°	324.8	3.1
100°-110°	1057.5	10.1
110°-120°	1046.1	10.0
120°-130°	854.9	8.1
130°-140°	698.7	6.7
140°-150°	544.2	5.2
150°-160°	392.3	3.7
160°-170°	239.8	2.3
170°-180°	80.9	0.8
0°-30°	1210.3	11.5
0°-40°	2135.7	20.4
0°-60°	4109.4	39.2
0°-90°	5251.5	50.1
90°-120°	2428.4	23.1
90°-150°	4526.1	43.1
90°-180°	5239.0	49.9
0°-180°	10490.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	531	531	531	531	531	
5°	516	591	715	873	938	48
15°	424	836	1747	1956	2036	118
25°	312	1123	1929	2014	2033	143
35°	222	1084	1826	1890	2000	140
45°	161	830	1599	1836	1921	125
55°	120	495	1356	1559	1599	108
65°	94	279	999	1119	1139	93
75°	66	171	531	286	291	68
85°	23	50	64	43	38	24
90°	0	3	7	6	6	3
95°	44	134	595	212	131	51
105°	180	259	1048	2001	1895	192
115°	332	396	853	1759	2069	329
125°	462	515	842	1388	1637	411
135°	558	616	838	1198	1352	431
145°	652	700	836	1032	1130	408
155°	744	768	841	924	959	343
165°	812	819	843	874	885	229
175°	846	846	846	852	850	80
180°	849	849	849	849	849	



TEST NUMBER: P853895

CATALOG NUMBER: SQ2-FB-125U-125D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	531.3	531.3	531.3	531.3	531.3
2.5°	527.3	549.2	574.3	603.1	615.1
5°	516.0	591.0	715.3	872.6	937.5
7.5°	496.1	648.5	1040.2	1461.1	1591.0
10°	477.7	690.0	1369.2	1733.6	1803.5
12.5°	457.3	745.5	1575.7	1831.7	1903.7
15°	424.1	836.2	1747.3	1956.1	2036.0
17.5°	389.8	938.3	1827.0	2032.9	2076.3
20°	365.3	1009.7	1869.9	2046.8	2074.3
22.5°	342.8	1063.2	1900.6	2034.6	2064.1
25°	311.7	1123.4	1928.7	2013.5	2033.4
27.5°	281.5	1139.3	1916.4	1972.1	1991.5
30°	263.1	1134.9	1898.0	1939.5	1967.0
32.5°	246.8	1122.5	1871.5	1911.7	1971.1
35°	222.2	1084.0	1826.5	1890.3	2000.2
37.5°	201.3	1022.1	1767.2	1897.9	2003.8
40°	189.0	975.8	1724.3	1897.5	1987.5
42.5°	176.8	921.6	1675.3	1877.1	1967.0
45°	160.9	830.3	1599.2	1836.1	1921.0
47.5°	146.1	727.6	1528.7	1779.4	1841.3
50°	137.9	657.5	1481.6	1728.0	1778.0
52.5°	129.8	589.4	1434.6	1666.6	1712.6
55°	120.1	494.7	1356.5	1559.2	1599.2
57.5°	111.4	413.6	1267.6	1440.5	1473.0
60°	107.3	369.6	1198.1	1354.7	1387.1
62.5°	101.2	329.5	1120.4	1264.7	1295.2
65°	94.5	279.4	998.8	1119.4	1139.3
67.5°	85.3	242.2	869.6	943.3	905.8
70°	79.2	224.1	781.7	804.8	697.4
72.5°	75.1	204.0	685.6	624.8	421.5
75°	66.4	171.3	531.3	286.2	291.2
77.5°	54.2	132.6	349.5	219.8	224.3
80°	46.0	108.4	183.9	178.9	181.4
82.5°	37.8	84.3	126.7	131.7	128.2
85°	23.0	50.5	63.9	43.3	38.3
87.5°	8.2	18.8	11.7	11.5	11.5
90°	0.0	3.1	7.3	6.3	6.3
92.5°	15.0	54.1	172.8	56.9	43.9
95°	43.9	133.7	595.3	212.3	130.6
97.5°	82.5	174.0	1010.4	615.4	375.6
100°	107.6	197.4	1166.7	1040.3	674.7
102.5°	136.0	222.6	1147.4	1539.1	1170.2
105°	179.6	259.3	1047.6	2000.8	1894.6
107.5°	226.9	301.8	952.7	2040.9	2153.4
110°	261.1	329.5	907.6	1991.2	2194.4



TEST NUMBER: P853895

CATALOG NUMBER: SQ2-FB-125U-125D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	289.5	357.1	879.2	1901.4	2163.5
115°	332.1	396.5	853.3	1758.6	2069.1
117.5°	376.0	434.0	843.3	1627.8	1936.8
120°	401.1	458.3	840.8	1547.4	1846.6
122.5°	425.3	481.7	841.6	1477.5	1756.3
125°	461.6	514.8	841.8	1388.5	1636.7
127.5°	492.8	547.1	841.6	1321.8	1528.7
130°	512.8	568.0	840.8	1283.7	1468.5
132.5°	530.4	588.0	839.9	1248.3	1421.7
135°	557.7	615.9	837.6	1198.3	1351.5
137.5°	584.5	643.1	835.4	1147.6	1283.6
140°	603.7	659.9	834.5	1113.2	1241.9
142.5°	622.1	675.8	834.5	1080.3	1195.1
145°	651.7	699.7	835.6	1032.1	1130.1
147.5°	680.6	722.2	837.0	991.0	1066.8
150°	699.8	736.5	838.7	966.5	1030.9
152.5°	719.0	749.2	839.5	947.9	999.1
155°	743.6	768.2	840.8	924.1	958.8
157.5°	767.0	784.6	842.0	906.5	930.8
160°	781.2	795.5	842.9	895.5	914.9
162.5°	793.8	804.8	842.9	886.2	900.7
165°	811.5	818.7	842.9	874.4	884.6
167.5°	824.1	828.6	843.1	865.6	870.9
170°	832.4	834.5	843.9	859.6	861.7
172.5°	838.3	839.5	845.6	856.2	855.8
175°	846.0	846.0	846.0	852.2	850.2
177.5°	849.1	848.3	847.5	851.6	848.3
180°	849.1	849.1	849.1	849.1	849.1

TEST NUMBER: P853895

CATALOG NUMBER: SQ2-FB-125U-125D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.54	15.42	15.49	16.40	17.66	23.27	24.16	24.22	25.13	26.40
	3H	15.27	16.07	16.23	17.05	18.34	24.90	25.69	25.86	26.67	27.96
	4H	15.57	16.33	16.55	17.31	18.61	25.08	25.83	26.06	26.82	28.12
	6H	15.79	16.48	16.78	17.47	18.79	25.17	25.86	26.15	26.85	28.16
	8H	15.85	16.51	16.84	17.52	18.82	25.17	25.83	26.17	26.84	28.15
	12H	15.88	16.51	16.88	17.51	18.84	25.14	25.77	26.14	26.77	28.11
4H	2H	18.94	19.69	19.92	20.68	21.98	23.72	24.47	24.70	25.46	26.76
	3H	19.87	20.50	20.87	21.52	22.83	25.55	26.18	26.54	27.19	28.50
	4H	20.16	20.73	21.16	21.74	23.08	25.79	26.36	26.79	27.37	28.70
	6H	20.29	20.79	21.31	21.82	23.15	25.93	26.43	26.95	27.46	28.79
	8H	20.31	20.78	21.33	21.80	23.15	25.96	26.42	26.97	27.44	28.79
	12H	20.31	20.72	21.34	21.76	23.12	25.93	26.35	26.97	27.39	28.74
8H	4H	21.34	21.80	22.35	22.82	24.17	25.91	26.37	26.92	27.39	28.74
	6H	21.57	21.96	22.61	23.02	24.37	26.11	26.49	27.15	27.56	28.91
	8H	21.65	21.98	22.69	23.03	24.40	26.18	26.51	27.22	27.56	28.93
	12H	21.67	21.97	22.73	23.01	24.42	26.17	26.46	27.22	27.51	28.92
12H	4H	21.36	21.77	22.39	22.81	24.16	25.86	26.28	26.89	27.32	28.67
	6H	21.67	22.00	22.72	23.05	24.42	26.10	26.43	27.14	27.48	28.85
	8H	21.77	22.07	22.83	23.11	24.52	26.17	26.46	27.22	27.50	28.91