

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854060

Luminaire Tested: SQ2-PH1-125U-100D-940-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P854060  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PH1-125U-100D-940-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10027.6 lumens  
Efficiency: N/A  
Efficacy: 123.0 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 81.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854060  
CATALOG NUMBER: SQ2-PH1-125U-100D-940-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854060

CATALOG NUMBER: SQ2-PH1-125U-100D-940-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				48
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39				34	
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33				29	
4	74	64	56	50	68	59	52	47	50	45	40	41	38	35	34	31	29				25	
5	68	57	49	43	62	52	45	40	45	39	35	37	33	30	30	27	25				22	
6	63	51	43	37	58	47	40	35	40	35	30	34	29	26	28	24	22				19	
7	58	46	38	32	53	43	36	31	36	31	27	31	26	23	25	22	20				17	
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18				15	
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16				14	
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14				12	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	34814	34814	34814
5°	35013	32919	31822
10°	34208	29970	28927
15°	34362	28189	28361
20°	33136	27319	28589
25°	32528	27193	27923
30°	31823	27119	28152
35°	31582	26810	32997
40°	31609	26637	26161
45°	31620	25624	22532
50°	31177	26128	21130
55°	30781	28355	20270
60°	30474	24845	19013
65°	29941	20145	16539
70°	28282	17141	11816
75°	25215	12926	8958
80°	20604	8396	8396
85°	12931	7595	5706

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 31620 cd/sqm



TEST NUMBER: P854060

CATALOG NUMBER: SQ2-PH1-125U-100D-940-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	189.7	1.9
10°-20°	499.1	5.0
20°-30°	731.8	7.3
30°-40°	886.2	8.8
40°-50°	871.5	8.7
50°-60°	758.6	7.6
60°-70°	527.4	5.3
70°-80°	250.1	2.5
80°-90°	56.1	0.6
90°-100°	325.9	3.3
100°-110°	1061.2	10.6
110°-120°	1049.7	10.5
120°-130°	857.8	8.6
130°-140°	701.1	7.0
140°-150°	546.1	5.4
150°-160°	393.6	3.9
160°-170°	240.6	2.4
170°-180°	81.2	0.8
0°-30°	1420.6	14.2
0°-40°	2306.7	23.0
0°-60°	3936.8	39.3
0°-90°	4770.3	47.6
90°-120°	2436.8	24.3
90°-150°	4541.8	45.3
90°-180°	5257.0	52.4
0°-180°	10027.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2156	2156	2156	2156	2156	
5°	2160	2158	2031	1967	1963	203
15°	2056	1831	1686	1675	1697	573
25°	1826	1553	1526	1573	1567	840
35°	1602	1295	1360	1478	1674	1004
45°	1385	1026	1122	1161	987	1064
55°	1094	799	1007	726	720	977
65°	784	549	527	433	433	770
75°	404	280	207	148	144	428
85°	70	46	41	33	31	93
90°	0	3	7	6	6	4
95°	44	134	597	213	131	51
105°	180	260	1051	2008	1901	192
115°	333	398	856	1765	2076	330
125°	463	516	845	1393	1642	412
135°	560	618	841	1202	1356	432
145°	654	702	838	1036	1134	409
155°	746	771	844	927	962	344
165°	814	822	846	878	888	229
175°	849	849	849	855	853	81
180°	852	852	852	852	852	



TEST NUMBER: P854060

CATALOG NUMBER: SQ2-PH1-125U-100D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2156.2	2156.2	2156.2	2156.2	2156.2
2.5°	2151.3	2173.8	2123.4	2103.6	2100.4
5°	2160.3	2158.3	2031.1	1967.4	1963.4
7.5°	2121.0	2058.8	1906.8	1836.5	1833.3
10°	2086.5	1992.2	1828.0	1764.4	1764.4
12.5°	2078.3	1929.4	1764.0	1717.0	1726.6
15°	2055.7	1831.0	1686.4	1674.6	1696.7
17.5°	1981.0	1739.1	1626.1	1652.9	1678.6
20°	1928.5	1689.8	1590.0	1639.8	1663.9
22.5°	1884.2	1642.3	1563.7	1618.2	1631.0
25°	1825.9	1553.1	1526.4	1573.4	1567.4
27.5°	1756.2	1471.3	1489.1	1517.9	1521.5
30°	1706.9	1422.1	1454.6	1483.9	1510.0
32.5°	1659.3	1364.9	1416.8	1486.3	1546.1
35°	1602.3	1295.4	1360.2	1477.5	1674.1
37.5°	1542.4	1213.4	1303.2	1401.8	1464.4
40°	1499.7	1154.7	1263.8	1385.7	1241.2
42.5°	1453.8	1108.7	1204.7	1362.1	1118.1
45°	1384.8	1025.8	1122.2	1161.3	986.8
47.5°	1303.6	961.4	1066.4	968.4	900.2
50°	1241.2	918.3	1040.2	885.3	841.2
52.5°	1180.5	873.6	1022.1	816.7	787.0
55°	1093.5	798.6	1007.3	726.1	720.1
57.5°	1001.2	722.3	890.8	647.3	657.7
60°	943.7	672.9	769.4	600.8	588.8
62.5°	883.0	625.0	656.1	541.8	529.7
65°	783.7	549.0	527.3	432.9	432.9
67.5°	674.6	470.0	427.1	354.2	306.1
70°	599.1	418.5	363.1	282.4	250.3
72.5°	518.6	363.8	297.5	231.4	194.5
75°	404.2	279.8	207.2	147.6	143.6
77.5°	292.1	201.5	139.5	109.6	110.0
80°	221.6	153.4	90.3	88.3	90.3
82.5°	155.9	105.4	67.3	70.2	70.6
85°	69.8	45.7	41.0	32.8	30.8
87.5°	14.8	13.8	9.7	9.5	9.5
90°	0.0	3.1	7.3	6.3	6.3
92.5°	15.1	54.2	173.4	57.1	44.0
95°	44.0	134.2	597.4	213.0	131.0
97.5°	82.8	174.6	1013.9	617.5	376.9
100°	108.0	198.1	1170.7	1043.9	677.1
102.5°	136.5	223.4	1151.4	1544.4	1174.3
105°	180.3	260.2	1051.2	2007.8	1901.2
107.5°	227.6	302.9	956.1	2048.0	2160.9
110°	262.0	330.7	910.8	1998.1	2202.0



TEST NUMBER: P854060

CATALOG NUMBER: SQ2-PH1-125U-100D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	290.5	358.4	882.3	1908.0	2171.0
115°	333.3	397.9	856.3	1764.7	2076.3
117.5°	377.3	435.5	846.2	1633.5	1943.6
120°	402.5	459.9	843.7	1552.7	1853.0
122.5°	426.8	483.3	844.5	1482.7	1762.5
125°	463.3	516.5	844.8	1393.3	1642.3
127.5°	494.5	549.0	844.5	1326.4	1534.0
130°	514.6	569.9	843.7	1288.1	1473.6
132.5°	532.2	590.0	842.9	1252.6	1426.7
135°	559.7	618.1	840.6	1202.5	1356.2
137.5°	586.5	645.3	838.3	1151.6	1288.1
140°	605.8	662.2	837.4	1117.0	1246.2
142.5°	624.2	678.1	837.4	1084.0	1199.2
145°	654.0	702.2	838.5	1035.6	1134.0
147.5°	682.9	724.7	839.9	994.5	1070.5
150°	702.2	739.1	841.6	969.9	1034.5
152.5°	721.5	751.8	842.5	951.2	1002.6
155°	746.2	770.8	843.7	927.3	962.1
157.5°	769.7	787.3	845.0	909.7	934.1
160°	784.0	798.3	845.8	898.7	918.1
162.5°	796.5	807.6	845.8	889.3	903.9
165°	814.4	821.5	845.8	877.5	887.7
167.5°	826.9	831.4	846.0	868.6	873.9
170°	835.3	837.4	846.9	862.6	864.7
172.5°	841.2	842.4	848.5	859.2	858.8
175°	848.9	848.9	848.9	855.2	853.1
177.5°	852.1	851.3	850.4	854.5	851.3
180°	852.1	852.1	852.1	852.1	852.1



TEST NUMBER: P854060

CATALOG NUMBER: SQ2-PH1-125U-100D-940-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.43	20.27	20.41	21.26	22.56	18.11	18.94	19.08	19.93	21.24
	3H	21.46	22.20	22.45	23.20	24.53	19.14	19.88	20.13	20.88	22.21
	4H	22.19	22.89	23.19	23.89	25.23	19.35	20.06	20.35	21.06	22.40
	6H	22.67	23.32	23.68	24.33	25.68	19.49	20.14	20.51	21.15	22.50
	8H	22.79	23.41	23.81	24.44	25.78	19.52	20.14	20.54	21.17	22.51
	12H	22.84	23.42	23.86	24.44	25.81	19.52	20.11	20.55	21.13	22.50
4H	2H	19.80	20.51	20.81	21.51	22.85	18.74	19.45	19.75	20.45	21.79
	3H	21.91	22.50	22.93	23.53	24.88	19.92	20.51	20.94	21.54	22.89
	4H	22.72	23.26	23.75	24.28	25.66	20.20	20.73	21.22	21.76	23.13
	6H	23.31	23.77	24.34	24.81	26.18	20.40	20.86	21.44	21.91	23.28
	8H	23.47	23.90	24.51	24.95	26.33	20.46	20.89	21.50	21.93	23.31
	12H	23.54	23.93	24.60	24.99	26.37	20.46	20.85	21.52	21.91	23.30
8H	4H	22.74	23.17	23.78	24.21	25.59	20.41	20.84	21.45	21.88	23.26
	6H	23.39	23.74	24.45	24.83	26.21	20.68	21.03	21.74	22.12	23.50
	8H	23.61	23.93	24.68	24.99	26.39	20.78	21.09	21.85	22.16	23.56
	12H	23.73	24.00	24.80	25.06	26.50	20.83	21.10	21.90	22.16	23.60
12H	4H	22.69	23.08	23.74	24.13	25.52	20.40	20.79	21.46	21.85	23.24
	6H	23.36	23.67	24.43	24.74	26.14	20.71	21.02	21.78	22.09	23.49
	8H	23.59	23.87	24.67	24.93	26.37	20.82	21.10	21.90	22.16	23.60