

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854221

Luminaire Tested: SQ2-PR1-125U-050D-935-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P854221  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PR1-125U-050D-935-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7376.3 lumens  
Efficiency: N/A  
Efficacy: 119.6 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 61.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854221

CATALOG NUMBER: SQ2-PR1-125U-050D-935-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854221

CATALOG NUMBER: SQ2-PR1-125U-050D-935-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	85	81	78	76	65	63	61	50	48	47	36	35	34	28
2	86	79	73	69	77	71	67	63	57	54	51	44	42	40	32	31	29	24
3	79	70	63	57	71	63	57	53	51	47	43	39	36	34	28	27	25	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	29	26	24	22	18
5	66	55	47	42	59	50	43	39	40	36	32	32	28	26	23	21	19	16
6	61	49	42	36	55	45	38	33	36	32	28	29	25	23	21	19	17	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15	13
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	11
9	49	37	30	25	44	34	27	23	28	23	19	22	18	16	16	14	12	10
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15839	15839	15839
5°	15819	15916	16110
10°	15985	16395	16641
15°	15980	16064	16197
20°	15722	15962	16495
25°	15677	16123	17174
30°	15661	16481	17339
35°	15512	16833	16143
40°	15154	16208	14206
45°	14340	14225	11234
50°	13036	11630	8716
55°	11457	9571	6784
60°	9914	7653	5586
65°	8558	6342	4890
70°	7695	5618	4343
75°	7049	4866	3992
80°	6137	3905	3905
85°	4446	3520	1853

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 15502 cd/sqm



TEST NUMBER: P854221

CATALOG NUMBER: SQ2-PR1-125U-050D-935-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	94.7	1.3
10°-20°	274.2	3.7
20°-30°	423.9	5.7
30°-40°	509.9	6.9
40°-50°	457.8	6.2
50°-60°	306.7	4.2
60°-70°	178.4	2.4
70°-80°	91.6	1.2
80°-90°	23.5	0.3
90°-100°	311.0	4.2
100°-110°	1012.4	13.7
110°-120°	1001.4	13.6
120°-130°	818.4	11.1
130°-140°	668.9	9.1
140°-150°	521.0	7.1
150°-160°	375.5	5.1
160°-170°	229.5	3.1
170°-180°	77.4	1.0
0°-30°	792.9	10.7
0°-40°	1302.8	17.7
0°-60°	2067.3	28.0
0°-90°	2360.8	32.0
90°-120°	2324.8	31.5
90°-150°	4333.0	58.7
90°-180°	5015.0	68.0
0°-180°	7376.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	981	981	981	981	981	
5°	976	993	982	984	994	93
15°	956	995	961	964	969	268
25°	880	915	905	939	964	406
35°	787	794	854	838	819	491
45°	628	679	623	525	492	480
55°	407	423	340	262	241	366
65°	224	229	166	135	128	227
75°	113	110	78	66	64	120
85°	24	19	19	13	10	30
90°	0	3	7	6	6	3
95°	42	128	570	203	125	49
105°	172	248	1003	1916	1814	183
115°	318	380	817	1684	1981	315
125°	442	493	806	1329	1567	393
135°	534	590	802	1147	1294	412
145°	624	670	800	988	1082	391
155°	712	735	805	885	918	328
165°	777	784	807	837	847	219
175°	810	810	810	816	814	77
180°	813	813	813	813	813	



TEST NUMBER: P854221

CATALOG NUMBER: SQ2-PR1-125U-050D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	981.0	981.0	981.0	981.0	981.0
2.5°	977.0	988.7	977.8	978.7	981.0
5°	976.0	992.6	982.0	984.2	994.0
7.5°	975.8	999.5	994.4	1000.5	1013.4
10°	975.0	1003.4	1000.0	1001.3	1015.0
12.5°	970.2	1003.3	988.0	986.8	994.2
15°	956.0	995.1	961.0	964.1	969.0
17.5°	931.0	971.9	939.4	950.4	960.0
20°	915.0	955.1	929.0	943.4	960.0
22.5°	900.6	940.7	919.4	939.5	962.4
25°	880.0	915.2	905.0	938.6	964.0
27.5°	858.4	879.1	891.2	936.2	954.0
30°	840.0	853.7	884.0	923.2	930.0
32.5°	820.0	828.2	874.4	894.8	886.0
35°	787.0	793.9	854.0	837.6	819.0
37.5°	747.8	761.9	808.2	760.9	739.6
40°	719.0	742.5	769.0	698.5	674.0
42.5°	683.8	721.4	717.0	627.1	597.2
45°	628.0	678.9	623.0	525.2	492.0
47.5°	562.2	614.4	523.0	435.7	404.6
50°	519.0	561.0	463.0	381.2	347.0
52.5°	475.0	505.3	411.8	330.1	299.0
55°	407.0	422.6	340.0	262.5	241.0
57.5°	344.6	354.6	277.8	212.0	196.2
60°	307.0	313.8	237.0	185.7	173.0
62.5°	272.6	277.9	204.2	163.4	153.8
65°	224.0	228.9	166.0	134.8	128.0
67.5°	185.4	187.9	136.6	112.1	105.6
70°	163.0	164.0	119.0	96.9	92.0
72.5°	143.0	141.6	102.2	84.1	80.8
75°	113.0	110.1	78.0	66.0	64.0
77.5°	84.4	81.3	54.8	50.8	50.8
80°	66.0	62.1	42.0	42.0	42.0
82.5°	49.2	43.7	32.4	32.4	31.6
85°	24.0	19.1	19.0	12.9	10.0
87.5°	6.4	7.0	3.8	3.6	3.6
90°	0.0	2.9	7.0	6.0	6.0
92.5°	14.4	51.7	165.4	54.5	42.0
95°	42.0	128.0	569.9	203.2	125.0
97.5°	79.0	166.6	967.3	589.1	359.6
100°	103.0	189.0	1116.9	995.9	645.9
102.5°	130.2	213.1	1098.5	1473.4	1120.3
105°	172.0	248.2	1002.9	1915.5	1813.8
107.5°	217.2	288.9	912.1	1953.8	2061.6
110°	250.0	315.5	868.9	1906.2	2100.8



TEST NUMBER: P854221

CATALOG NUMBER: SQ2-PR1-125U-050D-935-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	277.2	341.9	841.7	1820.3	2071.2
115°	318.0	379.6	816.9	1683.6	1980.8
117.5°	360.0	415.5	807.3	1558.3	1854.2
120°	384.0	438.7	804.9	1481.3	1767.8
122.5°	407.2	461.1	805.7	1414.5	1681.4
125°	441.9	492.8	805.9	1329.2	1566.8
127.5°	471.7	523.8	805.7	1265.4	1463.4
130°	490.9	543.7	804.9	1228.9	1405.8
132.5°	507.7	562.9	804.1	1195.0	1361.0
135°	533.9	589.7	801.9	1147.2	1293.9
137.5°	559.5	615.7	799.7	1098.6	1228.9
140°	577.9	631.7	798.9	1065.7	1188.9
142.5°	595.5	647.0	798.9	1034.2	1144.1
145°	623.9	669.9	799.9	988.0	1081.9
147.5°	651.5	691.4	801.3	948.7	1021.3
150°	669.9	705.1	802.9	925.3	986.9
152.5°	688.3	717.3	803.7	907.4	956.5
155°	711.9	735.4	804.9	884.7	917.9
157.5°	734.3	751.1	806.1	867.8	891.1
160°	747.9	761.6	806.9	857.3	875.9
162.5°	759.9	770.5	806.9	848.4	862.3
165°	776.9	783.8	806.9	837.1	846.9
167.5°	788.9	793.2	807.1	828.6	833.7
170°	796.9	798.9	807.9	823.0	824.9
172.5°	802.5	803.7	809.5	819.7	819.3
175°	809.9	809.9	809.9	815.9	813.9
177.5°	812.9	812.1	811.3	815.2	812.1
180°	812.9	812.9	812.9	812.9	812.9



TEST NUMBER: P854221

CATALOG NUMBER: SQ2-PR1-125U-050D-935-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.41	15.11	15.52	16.20	17.71	11.14	11.83	12.24	12.93	14.44
	3H	15.63	16.25	16.74	17.36	18.88	12.19	12.81	13.30	13.92	15.44
	4H	16.08	16.67	17.20	17.77	19.30	12.58	13.17	13.70	14.28	15.81
	6H	16.38	16.93	17.52	18.04	19.58	12.90	13.45	14.04	14.56	16.10
	8H	16.46	16.98	17.60	18.10	19.64	12.99	13.50	14.12	14.62	16.16
	12H	16.49	16.98	17.62	18.09	19.65	12.99	13.48	14.13	14.59	16.15
4H	2H	14.47	15.06	15.60	16.16	17.70	11.68	12.27	12.81	13.38	14.91
	3H	15.93	16.42	17.06	17.55	19.09	12.94	13.43	14.07	14.56	16.10
	4H	16.51	16.96	17.65	18.08	19.65	13.44	13.89	14.57	15.01	16.57
	6H	16.96	17.34	18.10	18.49	20.04	13.86	14.25	15.01	15.39	16.95
	8H	17.09	17.45	18.23	18.58	20.15	13.98	14.34	15.13	15.48	17.05
	12H	17.13	17.46	18.29	18.61	20.18	14.00	14.32	15.16	15.47	17.05
8H	4H	16.53	16.89	17.67	18.02	19.60	13.73	14.09	14.87	15.22	16.80
	6H	17.07	17.37	18.24	18.55	20.12	14.26	14.56	15.42	15.73	17.30
	8H	17.27	17.53	18.44	18.69	20.27	14.44	14.70	15.61	15.86	17.45
	12H	17.37	17.60	18.54	18.75	20.37	14.50	14.73	15.67	15.88	17.51
12H	4H	16.48	16.80	17.64	17.95	19.53	13.74	14.06	14.90	15.21	16.79
	6H	17.06	17.32	18.23	18.47	20.06	14.32	14.58	15.49	15.74	17.32
	8H	17.26	17.49	18.44	18.65	20.27	14.52	14.75	15.69	15.90	17.53