

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854236

Luminaire Tested: SQ2-PR1-150U-075D-935-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854236
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-14, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PR1-150U-075D-935-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9390.2 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 83.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854236

CATALOG NUMBER: SQ2-PR1-150U-075D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854236

CATALOG NUMBER: SQ2-PR1-150U-075D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36
1	95	91	87	84	86	83	80	77	67	65	63	52	51	50	39	38	38	31
2	87	80	74	69	79	73	68	64	59	56	53	47	44	42	35	34	32	27
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	31	30	28	23
4	73	63	55	50	66	57	51	46	47	42	38	37	34	31	28	26	24	20
5	67	56	48	43	61	51	44	39	42	37	33	34	30	27	26	23	21	18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19	16
7	57	45	38	32	52	42	35	30	34	29	26	28	24	21	21	19	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14	12
10	46	34	27	23	42	32	25	21	26	22	18	21	18	15	17	14	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22850	22850	22850
5°	22820	22960	23240
10°	23059	23651	24005
15°	23052	23173	23366
20°	22680	23027	23795
25°	22616	23257	24773
30°	22592	23774	25012
35°	22377	24283	23288
40°	21861	23381	20493
45°	20685	20521	16205
50°	18806	16777	12574
55°	16527	13807	9788
60°	14302	11041	8060
65°	12344	9150	7056
70°	11098	8105	6264
75°	10168	7018	5758
80°	8852	5635	5635
85°	6410	5076	2668

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 22361 cd/sqm



TEST NUMBER: P854236

CATALOG NUMBER: SQ2-PR1-150U-075D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.7	1.5
10°-20°	395.6	4.2
20°-30°	611.5	6.5
30°-40°	735.5	7.8
40°-50°	660.4	7.0
50°-60°	442.5	4.7
60°-70°	257.4	2.7
70°-80°	132.2	1.4
80°-90°	33.7	0.4
90°-100°	369.5	3.9
100°-110°	1209.8	12.9
110°-120°	1196.0	12.7
120°-130°	977.7	10.4
130°-140°	797.9	8.5
140°-150°	620.9	6.6
150°-160°	447.1	4.8
160°-170°	273.5	2.9
170°-180°	92.4	1.0
0°-30°	1143.8	12.2
0°-40°	1879.3	20.0
0°-60°	2982.2	31.8
0°-90°	3405.5	36.3
90°-120°	2775.3	29.6
90°-150°	5171.8	55.1
90°-180°	5985.0	63.7
0°-180°	9390.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1415	1415	1415	1415	1415	
5°	1408	1432	1417	1420	1434	134
15°	1379	1436	1386	1391	1398	387
25°	1270	1320	1306	1354	1391	585
35°	1135	1145	1232	1208	1182	708
45°	906	979	899	758	710	693
55°	587	610	490	379	348	528
65°	323	330	240	194	185	327
75°	163	159	112	95	92	173
85°	35	28	27	19	14	43
90°	1	3	8	7	8	4
95°	52	150	672	239	156	59
105°	210	300	1201	2282	2168	222
115°	379	453	976	2016	2367	374
125°	527	588	962	1590	1868	469
135°	635	702	954	1371	1546	491
145°	742	797	952	1180	1292	465
155°	846	874	958	1055	1096	390
165°	924	933	962	999	1010	260
175°	966	966	967	974	972	92
180°	970	970	970	970	970	



TEST NUMBER: P854236

CATALOG NUMBER: SQ2-PR1-150U-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1415.2	1415.2	1415.2	1415.2	1415.2
2.5°	1409.4	1426.3	1410.6	1411.8	1415.2
5°	1408.0	1431.9	1416.6	1419.8	1433.9
7.5°	1407.7	1441.8	1434.5	1443.3	1461.9
10°	1406.5	1447.4	1442.6	1444.5	1464.2
12.5°	1399.6	1447.3	1425.3	1423.5	1434.2
15°	1379.1	1435.5	1386.3	1390.8	1397.9
17.5°	1343.0	1402.0	1355.2	1371.1	1384.9
20°	1320.0	1377.8	1340.2	1360.9	1384.9
22.5°	1299.2	1357.0	1326.3	1355.3	1388.3
25°	1269.5	1320.2	1305.5	1354.0	1390.6
27.5°	1238.3	1268.2	1285.6	1350.6	1376.2
30°	1211.8	1231.5	1275.2	1331.7	1341.6
32.5°	1182.9	1194.8	1261.4	1290.8	1278.1
35°	1135.3	1145.2	1232.0	1208.3	1181.5
37.5°	1078.8	1099.1	1165.9	1097.7	1066.9
40°	1037.2	1071.1	1109.3	1007.6	972.3
42.5°	986.4	1040.6	1034.3	904.7	861.5
45°	905.9	979.3	898.7	757.7	709.7
47.5°	811.0	886.3	754.5	628.5	583.7
50°	748.7	809.4	667.9	549.9	500.6
52.5°	685.2	729.0	594.1	476.2	431.3
55°	587.1	609.7	490.5	378.7	347.7
57.5°	497.1	511.5	400.7	305.9	283.0
60°	442.9	452.7	341.9	267.9	249.6
62.5°	393.2	400.9	294.6	235.7	221.9
65°	323.1	330.2	239.5	194.5	184.7
67.5°	267.5	271.1	197.1	161.6	152.3
70°	235.1	236.6	171.7	139.8	132.7
72.5°	206.3	204.3	147.4	121.4	116.6
75°	163.0	158.8	112.5	95.1	92.3
77.5°	121.8	117.2	79.1	73.3	73.3
80°	95.2	89.6	60.6	60.6	60.6
82.5°	71.0	63.1	46.7	46.7	45.6
85°	34.6	27.6	27.4	18.7	14.4
87.5°	9.4	9.8	5.1	4.9	5.1
90°	1.0	2.9	8.0	7.0	8.0
92.5°	16.9	61.8	189.7	61.7	49.4
95°	51.8	150.2	671.7	239.3	155.5
97.5°	94.1	198.1	1152.4	697.1	432.1
100°	123.6	223.0	1333.4	1190.7	789.3
102.5°	157.1	254.1	1313.5	1754.5	1360.1
105°	210.3	299.9	1200.8	2281.5	2167.5
107.5°	262.7	344.9	1091.0	2330.8	2456.1
110°	297.0	376.9	1038.4	2273.4	2506.3



TEST NUMBER: P854236

CATALOG NUMBER: SQ2-PR1-150U-075D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	329.7	407.2	1006.5	2173.7	2472.0
115°	378.7	452.7	975.6	2016.0	2366.8
117.5°	426.3	495.5	963.9	1861.1	2217.3
120°	457.4	522.7	960.7	1770.8	2117.7
122.5°	485.3	549.0	960.7	1692.9	2014.8
125°	527.2	587.6	961.7	1589.8	1867.5
127.5°	562.7	624.2	960.5	1513.9	1755.5
130°	585.0	647.3	959.7	1467.9	1686.2
132.5°	604.9	668.8	957.3	1428.4	1626.4
135°	634.8	702.0	953.7	1371.2	1545.6
137.5°	666.3	732.9	951.5	1311.7	1469.3
140°	688.6	752.9	950.7	1274.0	1423.1
142.5°	710.9	771.4	950.7	1233.8	1368.9
145°	742.4	797.0	951.7	1179.5	1292.5
147.5°	775.5	820.9	953.1	1132.2	1217.6
150°	796.2	836.2	954.7	1104.8	1176.9
152.5°	817.0	852.2	955.5	1082.2	1141.8
155°	846.1	874.3	957.7	1055.3	1096.2
157.5°	872.2	892.6	959.9	1034.1	1063.7
160°	888.9	905.5	960.7	1022.0	1045.4
162.5°	903.3	916.7	960.7	1012.3	1029.4
165°	923.8	932.6	961.7	998.8	1009.5
167.5°	941.1	945.4	962.9	988.3	994.2
170°	950.7	952.7	963.7	982.6	984.6
172.5°	957.9	959.1	966.1	978.6	979.0
175°	965.7	965.7	966.7	973.6	971.6
177.5°	969.6	968.9	968.0	972.8	969.6
180°	969.6	969.6	969.6	969.6	969.6



TEST NUMBER: P854236

CATALOG NUMBER: SQ2-PR1-150U-075D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.21	16.94	17.29	18.01	19.46	12.94	13.66	14.01	14.73	16.19
	3H	17.44	18.08	18.52	19.16	20.64	13.99	14.64	15.08	15.72	17.19
	4H	17.88	18.49	18.98	19.57	21.06	14.39	15.00	15.48	16.08	17.56
	6H	18.19	18.75	19.29	19.84	21.33	14.71	15.27	15.81	16.36	17.85
	8H	18.27	18.80	19.38	19.90	21.39	14.79	15.33	15.90	16.43	17.91
	12H	18.29	18.80	19.41	19.89	21.40	14.80	15.30	15.91	16.40	17.91
4H	2H	16.27	16.89	17.38	17.97	19.45	13.49	14.10	14.59	15.18	16.66
	3H	17.73	18.24	18.84	19.35	20.84	14.74	15.25	15.85	16.36	17.85
	4H	18.32	18.79	19.43	19.89	21.40	15.24	15.71	16.36	16.81	18.32
	6H	18.77	19.17	19.89	20.29	21.80	15.67	16.07	16.79	17.19	18.70
	8H	18.90	19.27	20.02	20.38	21.91	15.79	16.16	16.91	17.28	18.80
	12H	18.95	19.28	20.08	20.41	21.94	15.81	16.14	16.94	17.27	18.80
8H	4H	18.34	18.71	19.46	19.82	21.35	15.54	15.91	16.66	17.02	18.55
	6H	18.88	19.19	20.02	20.34	21.87	16.07	16.38	17.21	17.53	19.05
	8H	19.08	19.35	20.23	20.48	22.03	16.26	16.52	17.40	17.66	19.20
	12H	19.18	19.42	20.33	20.55	22.12	16.31	16.55	17.46	17.68	19.26
12H	4H	18.29	18.63	19.43	19.75	21.28	15.55	15.89	16.69	17.01	18.54
	6H	18.87	19.14	20.02	20.27	21.81	16.13	16.40	17.28	17.53	19.07
	8H	19.08	19.31	20.23	20.44	22.02	16.33	16.57	17.48	17.70	19.28