

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854353

Luminaire Tested: SQ2-WBM-075U-050D-935-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854353
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G3-2104-222-5)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-WBM-075U-050D-935-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5183.0 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.19 / 1.17
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 41.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854353

CATALOG NUMBER: SQ2-WBM-075U-050D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854353

CATALOG NUMBER: SQ2-WBM-075U-050D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	98	94	91	88	89	86	83	81	71	70	68	58	57	56	46	45	44	39
2	90	84	79	74	82	77	73	69	65	61	59	53	51	49	42	41	40	35
3	83	75	69	64	76	69	64	60	58	55	51	48	46	44	39	37	36	32
4	77	68	61	55	71	63	57	52	53	49	45	44	41	39	36	34	32	29
5	71	61	54	49	65	57	50	46	48	44	40	40	37	35	33	31	29	26
6	66	55	48	43	61	52	45	41	44	39	36	37	34	31	31	28	27	24
7	62	51	43	38	57	47	41	36	40	36	32	34	31	28	28	26	24	22
8	57	46	39	34	53	43	37	33	37	32	29	32	28	26	26	24	22	20
9	54	42	36	31	49	40	34	29	34	30	26	29	26	23	25	22	20	18
10	50	39	33	28	46	37	31	27	32	27	24	27	24	21	23	21	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22491	22491	22491
5°	22739	22447	22707
10°	23002	22756	22953
15°	23435	23101	23000
20°	23557	23041	22646
25°	23017	22447	22019
30°	21888	21310	20732
35°	19671	19297	18607
40°	16166	15829	15365
45°	10229	11485	9225
50°	3969	6757	3642
55°	1914	3068	1942
60°	904	1518	840
65°	802	879	764
70°	803	803	755
75°	749	811	686
80°	744	744	651
85°	741	741	556

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 11485 cd/sqm



TEST NUMBER: P854353

CATALOG NUMBER: SQ2-WBM-075U-050D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.4	2.6
10°-20°	391.4	7.6
20°-30°	579.5	11.2
30°-40°	600.3	11.6
40°-50°	360.8	7.0
50°-60°	86.3	1.7
60°-70°	23.5	0.5
70°-80°	13.1	0.3
80°-90°	4.7	0.1
90°-100°	182.6	3.5
100°-110°	605.5	11.7
110°-120°	600.9	11.6
120°-130°	489.5	9.4
130°-140°	397.8	7.7
140°-150°	308.9	6.0
150°-160°	222.6	4.3
160°-170°	136.3	2.6
170°-180°	46.0	0.9
0°-30°	1104.3	21.3
0°-40°	1704.6	32.9
0°-60°	2151.7	41.5
0°-90°	2192.9	42.3
90°-120°	1389.0	26.8
90°-150°	2585.2	49.9
90°-180°	2990.0	57.7
0°-180°	5183.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1393	1393	1393	1393	1393	
5°	1403	1398	1385	1403	1401	134
15°	1402	1411	1382	1383	1376	395
25°	1292	1304	1260	1244	1236	591
35°	998	996	979	961	944	614
45°	448	503	503	476	404	343
55°	68	78	109	73	69	69
65°	21	22	23	21	20	21
75°	12	13	13	12	11	13
85°	4	4	4	4	3	4
90°	0	1	3	4	4	1
95°	26	77	331	118	79	30
105°	106	151	606	1143	1069	112
115°	189	226	488	1016	1188	187
125°	264	293	479	798	941	235
135°	316	348	475	685	773	245
145°	367	394	474	589	645	230
155°	419	434	477	526	546	193
165°	460	465	479	498	503	130
175°	481	481	482	485	484	46
180°	483	483	483	483	483	

TEST NUMBER: P854353

CATALOG NUMBER: SQ2-WBM-075U-050D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1393.0	1393.0	1393.0	1393.0	1393.0
2.5°	1401.0	1396.3	1385.0	1397.7	1394.6
5°	1403.0	1398.1	1385.0	1403.0	1401.0
7.5°	1403.0	1399.9	1388.8	1403.7	1400.8
10°	1403.0	1403.0	1388.0	1402.9	1400.0
12.5°	1403.8	1407.7	1387.2	1398.1	1393.6
15°	1402.0	1410.8	1382.0	1382.8	1376.0
17.5°	1387.0	1400.7	1361.0	1353.0	1343.6
20°	1371.0	1384.7	1341.0	1325.8	1318.0
22.5°	1343.0	1357.5	1310.6	1296.2	1287.6
25°	1292.0	1303.7	1260.0	1243.8	1236.0
27.5°	1224.4	1229.7	1191.8	1176.6	1168.0
30°	1174.0	1173.0	1143.0	1123.7	1112.0
32.5°	1109.2	1110.6	1083.0	1064.4	1048.8
35°	998.0	996.0	979.0	960.6	944.0
37.5°	865.4	866.8	848.6	829.1	822.6
40°	767.0	769.9	751.0	730.0	729.0
42.5°	647.0	668.7	655.0	633.1	629.0
45°	448.0	502.8	503.0	476.4	404.0
47.5°	249.2	317.6	358.6	282.8	211.4
50°	158.0	203.0	269.0	169.4	145.0
52.5°	112.4	134.7	199.4	120.9	105.8
55°	68.0	77.8	109.0	72.9	69.0
57.5°	41.6	50.2	63.8	49.4	41.2
60°	28.0	35.8	47.0	31.9	26.0
62.5°	24.8	27.1	36.6	25.6	23.6
65°	21.0	22.0	23.0	21.0	20.0
67.5°	18.6	19.6	19.4	18.6	17.6
70°	17.0	18.0	17.0	17.0	16.0
72.5°	15.4	15.6	15.4	14.6	14.4
75°	12.0	13.0	13.0	12.0	11.0
77.5°	9.6	10.4	9.6	9.6	8.6
80°	8.0	8.0	8.0	8.0	7.0
82.5°	6.4	6.4	6.4	6.4	5.4
85°	4.0	4.0	4.0	4.0	3.0
87.5°	1.6	1.8	2.2	1.6	1.6
90°	0.0	1.0	3.0	4.0	4.0
92.5°	8.0	30.9	91.0	29.5	24.8
95°	26.0	76.8	331.0	118.1	79.0
97.5°	47.8	101.0	577.7	336.9	213.0
100°	63.0	113.8	668.9	574.5	381.0
102.5°	79.8	129.1	663.3	878.0	663.3
105°	106.0	151.0	605.9	1143.2	1068.9
107.5°	132.8	172.9	550.9	1170.1	1226.6
110°	148.0	188.1	522.9	1143.5	1257.8



TEST NUMBER: P854353

CATALOG NUMBER: SQ2-WBM-075U-050D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.0	203.3	506.1	1096.2	1241.8
115°	189.0	226.1	487.9	1015.8	1187.9
117.5°	213.8	246.8	481.3	939.0	1119.5
120°	229.0	261.2	478.9	890.9	1065.9
122.5°	242.6	274.1	478.9	851.4	1013.1
125°	264.0	293.3	478.9	798.1	940.9
127.5°	281.6	310.3	477.7	757.9	879.9
130°	292.0	322.3	476.9	734.4	843.9
132.5°	301.6	332.7	476.1	715.0	813.5
135°	316.0	348.2	474.9	684.9	772.9
137.5°	331.6	362.6	473.7	655.9	733.5
140°	342.0	372.3	472.9	636.5	707.9
142.5°	351.6	381.1	473.7	617.2	680.7
145°	367.0	394.3	473.9	589.2	644.9
147.5°	383.6	406.4	474.1	565.5	606.9
150°	394.0	414.5	474.9	551.7	586.9
152.5°	403.5	423.3	475.7	540.4	568.5
155°	418.9	433.6	476.9	526.4	545.9
157.5°	433.9	445.3	478.1	516.5	530.3
160°	441.9	451.7	478.9	509.2	519.9
162.5°	449.9	457.4	478.9	504.3	512.7
165°	459.9	464.8	478.9	498.0	502.9
167.5°	469.1	471.7	479.9	492.4	494.9
170°	473.9	474.9	479.9	490.0	490.9
172.5°	477.1	478.1	480.7	487.5	487.7
175°	480.9	480.9	481.9	484.9	483.9
177.5°	482.9	482.9	482.1	483.7	482.1
180°	482.9	482.9	482.9	482.9	482.9

TEST NUMBER: P854353

CATALOG NUMBER: SQ2-WBM-075U-050D-935-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.95	3.63	4.00	4.66	6.05	2.54	3.23	3.59	4.26	5.65
	3H	3.46	4.06	4.51	5.10	6.51	3.06	3.66	4.12	4.71	6.11
	4H	3.70	4.27	4.77	5.32	6.73	3.29	3.86	4.36	4.91	6.32
	6H	3.91	4.43	4.99	5.48	6.91	3.48	4.00	4.56	5.05	6.48
	8H	3.98	4.48	5.07	5.54	6.96	3.53	4.03	4.62	5.09	6.51
	12H	4.03	4.50	5.11	5.56	7.00	3.55	4.03	4.64	5.08	6.53
4H	2H	2.95	3.52	4.03	4.57	5.98	2.58	3.16	3.66	4.20	5.62
	3H	3.68	4.15	4.76	5.22	6.65	3.31	3.79	4.40	4.86	6.29
	4H	4.06	4.49	5.15	5.56	7.01	3.68	4.11	4.77	5.18	6.63
	6H	4.41	4.77	5.50	5.86	7.31	4.01	4.38	5.10	5.47	6.91
	8H	4.54	4.88	5.63	5.96	7.42	4.12	4.47	5.22	5.55	7.00
	12H	4.63	4.93	5.73	6.03	7.49	4.18	4.49	5.29	5.58	7.04
8H	4H	4.15	4.49	5.24	5.57	7.03	3.80	4.14	4.89	5.22	6.68
	6H	4.61	4.89	5.72	6.01	7.47	4.26	4.54	5.37	5.66	7.11
	8H	4.82	5.07	5.95	6.18	7.65	4.46	4.70	5.58	5.81	7.28
	12H	5.00	5.21	6.12	6.31	7.83	4.60	4.82	5.72	5.91	7.43
12H	4H	4.12	4.42	5.22	5.52	6.98	3.77	4.08	4.88	5.17	6.63
	6H	4.63	4.88	5.75	5.98	7.46	4.29	4.53	5.41	5.64	7.11
	8H	4.87	5.09	5.99	6.19	7.70	4.52	4.74	5.64	5.83	7.35