

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854201

Luminaire Tested: SQ2-PR1-0U-075D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854201
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PR1-0U-075D-940-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
DIRECT ONLY
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3601.0 lumens
Efficiency: N/A
Efficacy: 134.9 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 26.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854201

CATALOG NUMBER: SQ2-PR1-0U-075D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854201

CATALOG NUMBER: SQ2-PR1-0U-075D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	90	89	87				87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	80	77	75				75
3	93	84	77	71	91	82	76	70	80	74	69	77	72	68	74	70	67	65				65
4	86	75	67	61	84	74	66	61	72	65	60	69	64	59	67	62	58	56				56
5	80	68	60	53	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				44
7	69	56	48	42	67	55	47	42	54	47	42	52	46	41	51	45	41	39				39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35				35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24169	24169	24169
5°	24138	24285	24584
10°	24392	25017	25392
15°	24384	24511	24715
20°	23990	24357	25170
25°	23922	24602	26206
30°	23897	25148	26457
35°	23670	25685	24632
40°	23123	24732	21678
45°	21882	21706	17141
50°	19891	17746	13300
55°	17481	14604	10351
60°	15129	11677	8525
65°	13058	9677	7461
70°	11740	8573	6628
75°	10755	7424	6095
80°	9363	5960	5960
85°	6780	5372	2834

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 23653 cd/sqm

TEST NUMBER: P854201

CATALOG NUMBER: SQ2-PR1-OU-075D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	4.0
10°-20°	418.5	11.6
20°-30°	646.9	18.0
30°-40°	778.0	21.6
40°-50°	698.6	19.4
50°-60°	468.0	13.0
60°-70°	272.2	7.6
70°-80°	139.8	3.9
80°-90°	34.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1209.9	33.6
0°-40°	1987.9	55.2
0°-60°	3154.5	87.6
0°-90°	3601.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3601.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1497	1497	1497	1497	1497	
5°	1489	1515	1498	1502	1517	142
15°	1459	1518	1466	1471	1479	410
25°	1343	1396	1381	1432	1471	619
35°	1201	1211	1303	1278	1250	749
45°	958	1036	951	802	751	733
55°	621	645	519	401	368	558
65°	342	349	253	206	195	346
75°	172	168	119	101	98	183
85°	37	29	29	20	15	47
90°	0	0	0	0	0	



TEST NUMBER: P854201

CATALOG NUMBER: SQ2-PR1-OU-075D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1496.9	1496.9	1496.9	1496.9	1496.9
2.5°	1490.8	1508.7	1492.0	1493.3	1496.9
5°	1489.3	1514.7	1498.4	1501.8	1516.8
7.5°	1489.0	1525.1	1517.4	1526.7	1546.4
10°	1487.8	1531.0	1525.9	1527.9	1548.8
12.5°	1480.4	1530.9	1507.6	1505.7	1517.1
15°	1458.8	1518.5	1466.4	1471.1	1478.6
17.5°	1420.6	1483.0	1433.4	1450.3	1464.9
20°	1396.2	1457.4	1417.6	1439.5	1464.9
22.5°	1374.2	1435.4	1402.9	1433.6	1468.5
25°	1342.8	1396.5	1381.0	1432.2	1471.0
27.5°	1309.8	1341.5	1359.9	1428.6	1455.7
30°	1281.8	1302.7	1348.9	1408.7	1419.1
32.5°	1251.2	1263.8	1334.3	1365.4	1352.0
35°	1200.9	1211.3	1303.1	1278.1	1249.7
37.5°	1141.1	1162.6	1233.2	1161.1	1128.6
40°	1097.1	1132.9	1173.4	1065.8	1028.5
42.5°	1043.4	1100.7	1094.1	956.9	911.3
45°	958.3	1035.9	950.6	801.5	750.7
47.5°	857.9	937.5	798.1	664.8	617.4
50°	791.9	856.1	706.5	581.7	529.5
52.5°	724.8	771.1	628.4	503.7	456.2
55°	621.0	644.9	518.8	400.6	367.7
57.5°	525.8	541.0	423.9	323.6	299.4
60°	468.5	478.9	361.6	283.4	264.0
62.5°	416.0	424.0	311.6	249.3	234.7
65°	341.8	349.3	253.3	205.8	195.3
67.5°	282.9	286.8	208.4	171.0	161.1
70°	248.7	250.2	181.6	147.8	140.4
72.5°	218.2	216.1	155.9	128.4	123.3
75°	172.4	168.0	119.0	100.6	97.7
77.5°	128.8	124.0	83.6	77.5	77.5
80°	100.7	94.7	64.1	64.1	64.1
82.5°	75.1	66.7	49.4	49.4	48.2
85°	36.6	29.2	29.0	19.7	15.3
87.5°	9.8	9.8	3.7	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P854201

CATALOG NUMBER: SQ2-PR1-OU-075D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	21.77	23.27	22.13	23.58	23.89	18.49	19.99	18.86	20.30	20.62
	3H	23.05	24.39	23.43	24.71	25.08	19.61	20.94	19.98	21.27	21.63
	4H	23.53	24.78	23.93	25.13	25.51	20.03	21.29	20.44	21.64	22.02
	6H	23.88	25.03	24.29	25.40	25.79	20.40	21.55	20.81	21.92	22.31
	8H	23.98	25.07	24.40	25.46	25.87	20.50	21.60	20.93	21.99	22.39
	12H	24.02	25.07	24.45	25.46	25.89	20.53	21.58	20.96	21.96	22.39
4H	2H	21.92	23.17	22.32	23.52	23.90	19.14	20.39	19.54	20.74	21.12
	3H	23.45	24.48	23.86	24.88	25.29	20.46	21.49	20.87	21.89	22.30
	4H	24.07	25.00	24.50	25.41	25.85	20.99	21.92	21.42	22.33	22.77
	6H	24.55	25.36	25.01	25.80	26.26	21.46	22.26	21.91	22.71	23.17
	8H	24.70	25.45	25.16	25.89	26.36	21.59	22.34	22.05	22.79	23.26
	12H	24.78	25.45	25.26	25.93	26.40	21.64	22.31	22.12	22.79	23.26
8H	4H	24.14	24.89	24.60	25.33	25.80	21.34	22.09	21.80	22.54	23.00
	6H	24.71	25.33	25.20	25.82	26.30	21.89	22.52	22.39	23.01	23.49
	8H	24.90	25.46	25.42	25.97	26.46	22.08	22.64	22.59	23.15	23.64
	12H	25.03	25.53	25.54	26.02	26.59	22.17	22.66	22.68	23.15	23.72
12H	4H	24.12	24.79	24.60	25.27	25.74	21.38	22.05	21.86	22.53	23.00
	6H	24.69	25.25	25.21	25.76	26.25	21.95	22.51	22.47	23.02	23.51
	8H	24.93	25.43	25.44	25.92	26.48	22.19	22.68	22.70	23.17	23.74