

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855473

Luminaire Tested: SQ2-F-125U-050D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855473
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-125U-050D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8247.4 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855473
CATALOG NUMBER: SQ2-F-125U-050D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855473

CATALOG NUMBER: SQ2-F-125U-050D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	60	59	47	46	44	32	32	31	24				
2	85	77	71	66	76	70	64	60	55	51	48	41	39	37	28	27	26	20				
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17				
4	70	60	52	46	63	54	47	42	43	38	34	32	29	26	22	20	19	15				
5	64	53	45	39	57	48	41	36	38	33	29	29	25	23	20	18	16	13				
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11				
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	17	14	13	10				
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	9				
9	47	35	28	23	42	32	25	21	25	21	17	20	16	14	14	12	10	8				
10	44	32	25	20	39	29	23	19	23	19	16	18	15	12	13	11	9	7				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13811	13811	13811
5°	13713	13750	13864
10°	13680	13719	13814
15°	13598	13636	13772
20°	13515	13536	13656
25°	13392	13392	13473
30°	13254	13254	13297
35°	13094	13046	13139
40°	12920	12872	12920
45°	12721	12666	12721
50°	12529	12411	12441
55°	12237	12203	12138
60°	11929	11854	11780
65°	11576	11442	11308
70°	10891	10839	10617
75°	10249	10031	9744
80°	9103	8889	8563
85°	7336	6688	6262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 12796 cd/sqm



TEST NUMBER: P855473

CATALOG NUMBER: SQ2-F-125U-050D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.9	1.0
10°-20°	231.0	2.8
20°-30°	347.6	4.2
30°-40°	415.9	5.0
40°-50°	429.1	5.2
50°-60°	387.1	4.7
60°-70°	295.4	3.6
70°-80°	169.8	2.1
80°-90°	45.4	0.6
90°-100°	362.4	4.4
100°-110°	1179.8	14.3
110°-120°	1167.1	14.2
120°-130°	953.7	11.6
130°-140°	779.5	9.5
140°-150°	607.1	7.4
150°-160°	437.6	5.3
160°-170°	267.5	3.2
170°-180°	90.3	1.1
0°-30°	659.5	8.0
0°-40°	1075.4	13.0
0°-60°	1891.7	22.9
0°-90°	2402.3	29.1
90°-120°	2709.3	32.9
90°-150°	5049.7	61.2
90°-180°	5845.0	70.9
0°-180°	8247.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	855	855	855	855	855	
5°	846	858	848	850	855	80
15°	814	824	816	819	824	229
25°	752	760	752	753	756	346
35°	664	669	662	664	667	415
45°	557	560	555	556	557	430
55°	435	437	434	431	431	389
65°	303	302	300	297	296	298
75°	164	163	161	157	156	173
85°	40	37	36	33	34	46
90°	0	3	8	7	7	4
95°	49	149	664	237	146	57
105°	200	289	1169	2232	2114	214
115°	371	442	952	1962	2308	367
125°	515	574	939	1549	1826	458
135°	622	687	934	1337	1508	481
145°	727	781	932	1151	1261	455
155°	830	857	938	1031	1070	382
165°	905	913	940	976	987	255
175°	944	944	944	951	948	90
180°	947	947	947	947	947	



TEST NUMBER: P855473

CATALOG NUMBER: SQ2-F-125U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	855.4	855.4	855.4	855.4	855.4
2.5°	849.8	859.8	851.7	853.5	854.5
5°	846.1	857.5	848.4	849.7	855.4
7.5°	839.1	851.4	841.4	843.6	850.0
10°	834.4	845.8	836.8	838.0	842.6
12.5°	827.0	838.4	829.3	831.5	836.1
15°	813.5	823.7	815.8	819.4	823.9
17.5°	797.8	808.8	799.9	803.1	806.9
20°	786.6	795.7	787.8	789.1	794.8
22.5°	772.7	781.8	774.8	775.1	779.9
25°	751.7	759.6	751.7	753.0	756.3
27.5°	727.7	734.6	727.7	729.0	731.9
30°	710.9	717.8	710.9	712.1	713.2
32.5°	692.2	698.2	691.3	692.6	695.5
35°	664.3	668.8	661.9	664.3	666.6
37.5°	634.4	637.8	632.1	633.3	635.4
40°	613.0	616.4	610.7	611.8	613.0
42.5°	591.6	594.1	588.3	589.5	591.6
45°	557.1	560.4	554.7	555.9	557.1
47.5°	522.1	524.2	519.3	518.4	520.5
50°	498.8	500.0	494.1	494.1	495.3
52.5°	473.6	474.8	470.8	469.0	470.1
55°	434.7	437.0	433.5	431.2	431.2
57.5°	395.5	397.6	393.2	392.0	391.8
60°	369.4	370.6	367.1	365.9	364.8
62.5°	343.3	343.6	340.1	338.9	337.7
65°	303.0	301.8	299.5	297.2	296.0
67.5°	257.8	259.0	256.6	252.9	252.9
70°	230.7	231.9	229.6	224.9	224.9
72.5°	204.6	203.9	202.5	198.8	197.0
75°	164.3	163.2	160.8	157.3	156.2
77.5°	124.0	122.8	121.7	117.2	118.2
80°	97.9	96.7	95.6	92.1	92.1
82.5°	74.6	72.5	71.3	67.8	67.8
85°	39.6	37.3	36.1	32.6	33.8
87.5°	11.2	11.0	11.0	8.9	8.9
90°	0.0	3.4	8.2	7.0	7.0
92.5°	16.8	60.3	192.8	63.5	48.9
95°	48.9	149.2	664.2	236.8	145.7
97.5°	92.1	194.2	1127.3	686.5	419.1
100°	120.0	220.3	1301.6	1160.6	752.7
102.5°	151.7	248.3	1280.2	1717.1	1305.6
105°	200.4	289.3	1168.8	2232.3	2113.8
107.5°	253.1	336.7	1063.0	2277.0	2402.6
110°	291.4	367.7	1012.6	2221.5	2448.3



TEST NUMBER: P855473

CATALOG NUMBER: SQ2-F-125U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	323.0	398.5	980.9	2121.4	2413.8
115°	370.6	442.4	952.0	1962.1	2308.4
117.5°	419.5	484.2	940.8	1816.0	2160.9
120°	447.5	511.3	938.0	1726.3	2060.2
122.5°	474.6	537.4	939.0	1648.5	1959.5
125°	515.0	574.3	939.2	1549.1	1826.0
127.5°	549.7	610.4	939.0	1474.7	1705.4
130°	572.1	633.6	938.0	1432.2	1638.3
132.5°	591.7	656.0	937.1	1392.7	1586.1
135°	622.2	687.2	934.5	1336.9	1507.9
137.5°	652.0	717.5	932.0	1280.3	1432.2
140°	673.5	736.2	931.0	1242.0	1385.5
142.5°	694.0	754.0	931.0	1205.3	1333.3
145°	727.1	780.7	932.2	1151.4	1260.8
147.5°	759.3	805.8	933.8	1105.6	1190.2
150°	780.7	821.7	935.7	1078.3	1150.1
152.5°	802.1	835.9	936.6	1057.5	1114.7
155°	829.6	857.0	938.0	1031.0	1069.7
157.5°	855.8	875.3	939.4	1011.3	1038.5
160°	871.6	887.6	940.4	999.1	1020.8
162.5°	885.6	897.9	940.4	988.7	1004.9
165°	905.4	913.4	940.4	975.6	987.0
167.5°	919.4	924.4	940.6	965.7	971.6
170°	928.7	931.0	941.5	959.1	961.3
172.5°	935.2	936.6	943.4	955.3	954.8
175°	943.9	943.9	943.9	950.9	948.5
177.5°	947.4	946.4	945.5	950.0	946.4
180°	947.4	947.4	947.4	947.4	947.4



TEST NUMBER: P855473

CATALOG NUMBER: SQ2-F-125U-050D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.76	15.47	15.88	16.58	18.12	14.69	15.39	15.80	16.50	18.04
	3H	16.53	17.17	17.66	18.29	19.84	16.41	17.05	17.54	18.17	19.72
	4H	17.18	17.79	18.32	18.91	20.47	17.03	17.63	18.17	18.75	20.32
	6H	17.65	18.20	18.79	19.32	20.90	17.46	18.01	18.60	19.14	20.71
	8H	17.78	18.31	18.92	19.44	21.01	17.58	18.10	18.72	19.24	20.81
	12H	17.85	18.35	19.00	19.48	21.07	17.63	18.12	18.78	19.26	20.85
4H	2H	15.30	15.90	16.44	17.02	18.58	15.23	15.84	16.38	16.96	18.52
	3H	17.27	17.77	18.42	18.92	20.49	17.16	17.66	18.31	18.81	20.38
	4H	18.05	18.51	19.20	19.65	21.24	17.91	18.37	19.06	19.51	21.10
	6H	18.63	19.03	19.79	20.19	21.77	18.45	18.85	19.61	20.01	21.59
	8H	18.82	19.19	19.97	20.34	21.94	18.62	18.98	19.77	20.13	21.74
	12H	18.91	19.25	20.08	20.41	22.01	18.68	19.02	19.86	20.18	21.79
8H	4H	18.29	18.66	19.44	19.81	21.41	18.16	18.53	19.32	19.68	21.28
	6H	19.00	19.30	20.17	20.49	22.09	18.83	19.14	20.01	20.33	21.93
	8H	19.26	19.53	20.44	20.70	22.32	19.07	19.34	20.25	20.51	22.13
	12H	19.42	19.66	20.61	20.82	22.48	19.20	19.43	20.38	20.60	22.25
12H	4H	18.27	18.61	19.44	19.77	21.38	18.15	18.49	19.32	19.65	21.25
	6H	19.04	19.30	20.22	20.48	22.09	18.88	19.15	20.06	20.32	21.94
	8H	19.32	19.56	20.51	20.73	22.38	19.14	19.37	20.32	20.54	22.19