

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855471

Luminaire Tested: SQ2-F-125U-100D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855471
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-13)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-F-125U-100D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10450.6 lumens
Efficiency: N/A
Efficacy: 128.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.25 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 81.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855471
CATALOG NUMBER: SQ2-F-125U-100D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855471

CATALOG NUMBER: SQ2-F-125U-100D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43	37
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	38	36	31
3	80	70	63	57	73	65	58	53	54	49	45	44	41	38	35	32	30	26
4	73	62	54	48	67	57	50	45	48	43	38	39	35	32	31	28	26	22
5	67	55	47	41	61	51	44	38	43	37	33	35	31	28	28	25	23	19
6	62	49	41	36	56	46	38	33	38	33	29	32	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18	15
8	53	40	33	27	48	37	30	26	32	26	22	26	22	19	21	18	16	13
9	49	37	29	24	45	34	27	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	20	27	21	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26788	26788	26788
5°	26597	26669	26890
10°	26534	26607	26793
15°	26372	26449	26713
20°	26215	26254	26488
25°	25972	25972	26135
30°	25706	25706	25790
35°	25395	25306	25484
40°	25058	24963	25058
45°	24669	24567	24669
50°	24300	24074	24129
55°	23736	23668	23541
60°	23137	22995	22846
65°	22453	22197	21933
70°	21125	21021	20592
75°	19881	19463	18896
80°	17648	17229	16597
85°	14227	12968	12134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 24822 cd/sqm



TEST NUMBER: P855471

CATALOG NUMBER: SQ2-F-125U-100D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	1.5
10°-20°	448.1	4.3
20°-30°	674.2	6.5
30°-40°	806.7	7.7
40°-50°	832.3	8.0
50°-60°	750.9	7.2
60°-70°	573.0	5.5
70°-80°	329.4	3.2
80°-90°	87.0	0.8
90°-100°	359.1	3.4
100°-110°	1169.2	11.2
110°-120°	1156.5	11.1
120°-130°	945.1	9.0
130°-140°	772.4	7.4
140°-150°	601.7	5.8
150°-160°	433.7	4.1
160°-170°	265.1	2.5
170°-180°	89.4	0.9
0°-30°	1279.1	12.2
0°-40°	2085.8	20.0
0°-60°	3669.0	35.1
0°-90°	4658.4	44.6
90°-120°	2684.8	25.7
90°-150°	5004.0	47.9
90°-180°	5792.0	55.4
0°-180°	10450.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1659	1659	1659	1659	1659	
5°	1641	1663	1646	1648	1659	156
15°	1578	1598	1582	1589	1598	445
25°	1458	1473	1458	1460	1467	671
35°	1288	1297	1284	1288	1293	806
45°	1080	1087	1076	1078	1080	834
55°	843	848	841	836	836	754
65°	588	586	581	576	574	578
75°	319	316	312	305	303	336
85°	77	72	70	63	66	89
90°	0	3	8	7	7	5
95°	48	148	658	235	144	56
105°	199	287	1158	2212	2095	212
115°	367	438	943	1944	2288	363
125°	510	569	931	1535	1810	454
135°	617	681	926	1325	1494	476
145°	721	774	924	1141	1249	451
155°	822	849	930	1022	1060	379
165°	897	905	932	967	978	253
175°	935	935	935	942	940	89
180°	939	939	939	939	939	



TEST NUMBER: P855471

CATALOG NUMBER: SQ2-F-125U-100D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1659.1	1659.1	1659.1	1659.1	1659.1
2.5°	1648.2	1667.7	1651.8	1655.6	1657.3
5°	1641.0	1663.1	1645.5	1648.0	1659.1
7.5°	1627.5	1651.4	1632.0	1636.3	1648.7
10°	1618.4	1640.5	1622.9	1625.4	1634.2
12.5°	1603.9	1626.1	1608.5	1612.7	1621.5
15°	1577.7	1597.6	1582.3	1589.3	1598.1
17.5°	1547.4	1568.6	1551.5	1557.6	1565.0
20°	1525.7	1543.5	1528.0	1530.5	1541.6
22.5°	1498.6	1516.3	1502.7	1503.4	1512.6
25°	1457.9	1473.4	1457.9	1460.4	1467.0
27.5°	1411.4	1424.6	1411.4	1413.7	1419.5
30°	1378.8	1392.1	1378.8	1381.1	1383.3
32.5°	1342.7	1354.2	1340.8	1343.2	1349.0
35°	1288.4	1297.2	1283.9	1288.5	1292.9
37.5°	1230.5	1237.2	1226.0	1228.3	1232.3
40°	1188.9	1195.6	1184.4	1186.7	1188.9
42.5°	1147.3	1152.2	1141.0	1143.4	1147.3
45°	1080.4	1087.1	1075.9	1078.2	1080.4
47.5°	1012.6	1016.6	1007.3	1005.5	1009.5
50°	967.4	969.6	958.4	958.4	960.6
52.5°	918.6	920.8	913.2	909.6	911.8
55°	843.2	847.5	840.8	836.3	836.3
57.5°	767.2	771.1	762.6	760.4	760.0
60°	716.5	718.7	712.1	709.7	707.5
62.5°	665.9	666.4	659.6	657.3	655.1
65°	587.7	585.5	581.0	576.3	574.1
67.5°	500.0	502.2	497.7	490.5	490.5
70°	447.5	449.7	445.3	436.2	436.2
72.5°	396.9	395.5	392.9	385.5	382.0
75°	318.7	316.5	312.0	305.1	302.9
77.5°	240.5	238.3	236.0	227.5	229.2
80°	189.8	187.6	185.3	178.5	178.5
82.5°	144.6	140.7	138.3	131.6	131.6
85°	76.8	72.5	70.0	63.4	65.5
87.5°	21.7	20.6	19.7	15.8	15.8
90°	0.0	3.4	8.0	6.9	6.9
92.5°	16.7	59.8	191.0	62.9	48.5
95°	48.5	147.9	658.2	234.7	144.4
97.5°	91.3	192.4	1117.0	680.4	415.2
100°	119.0	218.3	1289.9	1150.1	746.0
102.5°	150.3	246.1	1268.5	1701.6	1293.7
105°	198.6	286.7	1158.2	2212.2	2094.7
107.5°	250.8	333.7	1053.4	2256.4	2380.8
110°	288.7	364.3	1003.4	2201.4	2426.1



TEST NUMBER: P855471

CATALOG NUMBER: SQ2-F-125U-100D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	320.1	394.8	972.1	2102.2	2391.9
115°	367.2	438.3	943.4	1944.2	2287.6
117.5°	415.7	479.8	932.3	1799.7	2141.3
120°	443.4	506.6	929.5	1710.8	2041.5
122.5°	470.2	532.6	930.5	1633.5	1941.8
125°	510.4	569.1	930.7	1535.1	1809.5
127.5°	544.8	604.8	930.5	1461.3	1690.1
130°	567.0	627.9	929.5	1419.2	1623.5
132.5°	586.4	650.1	928.6	1380.1	1571.8
135°	616.6	680.9	926.1	1324.8	1494.3
137.5°	646.2	711.0	923.6	1268.8	1419.2
140°	667.4	729.5	922.6	1230.7	1373.0
142.5°	687.7	747.1	922.6	1194.3	1321.2
145°	720.6	773.6	923.8	1141.0	1249.4
147.5°	752.4	798.5	925.4	1095.7	1179.5
150°	773.7	814.3	927.3	1068.6	1139.8
152.5°	794.9	828.4	928.1	1047.9	1104.6
155°	822.2	849.2	929.5	1021.7	1060.0
157.5°	848.1	867.4	930.9	1002.2	1029.0
160°	863.8	879.5	931.9	990.1	1011.6
162.5°	877.5	889.8	931.9	979.8	995.8
165°	897.2	905.2	931.9	966.8	978.0
167.5°	911.1	916.0	932.1	956.9	962.9
170°	920.3	922.5	933.0	950.4	952.6
172.5°	926.8	928.1	934.9	946.7	946.2
175°	935.4	935.4	935.4	942.2	939.9
177.5°	938.8	937.9	937.0	941.5	937.9
180°	938.8	938.8	938.8	938.8	938.8



TEST NUMBER: P855471

CATALOG NUMBER: SQ2-F-125U-100D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.87	19.69	19.87	20.71	22.05	18.79	19.62	19.79	20.63	21.97
	3H	20.65	21.39	21.66	22.41	23.77	20.53	21.27	21.54	22.29	23.66
	4H	21.31	22.01	22.33	23.03	24.40	21.15	21.85	22.18	22.88	24.25
	6H	21.77	22.42	22.81	23.45	24.83	21.59	22.23	22.62	23.26	24.65
	8H	21.91	22.52	22.95	23.57	24.95	21.71	22.32	22.75	23.37	24.75
	12H	21.98	22.57	23.03	23.61	25.01	21.76	22.34	22.80	23.38	24.79
4H	2H	19.42	20.12	20.45	21.14	22.52	19.36	20.06	20.39	21.08	22.45
	3H	21.40	21.99	22.44	23.04	24.43	21.29	21.88	22.33	22.93	24.32
	4H	22.19	22.73	23.23	23.77	25.18	22.05	22.58	23.09	23.63	25.04
	6H	22.78	23.24	23.83	24.31	25.71	22.60	23.06	23.65	24.13	25.53
	8H	22.96	23.39	24.02	24.45	25.87	22.76	23.19	23.82	24.25	25.67
	12H	23.06	23.45	24.14	24.53	25.95	22.84	23.23	23.91	24.30	25.73
8H	4H	22.43	22.86	23.49	23.92	25.35	22.31	22.74	23.36	23.80	25.22
	6H	23.15	23.51	24.23	24.61	26.03	22.98	23.34	24.06	24.44	25.86
	8H	23.42	23.73	24.50	24.81	26.25	23.22	23.54	24.31	24.62	26.06
	12H	23.58	23.86	24.67	24.94	26.42	23.35	23.63	24.45	24.71	26.19
12H	4H	22.43	22.81	23.50	23.89	25.32	22.30	22.69	23.38	23.77	25.19
	6H	23.19	23.51	24.28	24.59	26.03	23.03	23.35	24.12	24.43	25.87
	8H	23.48	23.76	24.57	24.84	26.32	23.30	23.57	24.39	24.65	26.13