

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854234

Luminaire Tested: SQ2-PR1-150U-050D-940-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P854234
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-14, G2-2308-131-9)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PR1-150U-050D-940-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8849.4 lumens
Efficiency: N/A
Efficacy: 118.9 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.34 / 1.36
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 74.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P854234

CATALOG NUMBER: SQ2-PR1-150U-050D-940-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P854234

CATALOG NUMBER: SQ2-PR1-150U-050D-940-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	32	32	31	24
2	85	78	73	68	76	70	66	61	55	52	49	42	40	38	29	28	27	21
3	78	69	62	57	69	62	56	52	49	45	42	37	34	32	26	24	23	18
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	22	20	16
5	65	54	47	41	58	49	43	38	39	34	31	30	27	24	21	19	18	14
6	60	49	41	36	54	44	38	33	35	30	27	27	24	21	19	17	16	12
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16755	16755	16755
5°	16733	16835	17041
10°	16908	17343	17602
15°	16903	16991	17133
20°	16631	16885	17448
25°	16582	17054	18166
30°	16565	17434	18340
35°	16409	17804	17075
40°	16029	17144	15026
45°	15168	15047	11883
50°	13790	12303	9218
55°	12118	10123	7175
60°	10485	8096	5909
65°	9051	6709	5173
70°	8139	5943	4593
75°	7455	5147	4223
80°	6490	4128	4128
85°	4705	3724	1964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 16397 cd/sqm



TEST NUMBER: P854234

CATALOG NUMBER: SQ2-PR1-150U-050D-940-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	1.1
10°-20°	290.1	3.3
20°-30°	448.4	5.1
30°-40°	539.3	6.1
40°-50°	484.3	5.5
50°-60°	324.4	3.7
60°-70°	188.7	2.1
70°-80°	96.9	1.1
80°-90°	25.1	0.3
90°-100°	392.1	4.4
100°-110°	1284.0	14.5
110°-120°	1269.4	14.3
120°-130°	1037.7	11.7
130°-140°	846.8	9.6
140°-150°	659.0	7.4
150°-160°	474.5	5.4
160°-170°	290.3	3.3
170°-180°	98.1	1.1
0°-30°	838.7	9.5
0°-40°	1378.0	15.6
0°-60°	2186.7	24.7
0°-90°	2497.4	28.2
90°-120°	2945.6	33.3
90°-150°	5489.1	62.0
90°-180°	6352.0	71.8
0°-180°	8849.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1038	1038	1038	1038	1038	
5°	1032	1050	1039	1041	1051	99
15°	1011	1053	1016	1020	1025	284
25°	931	968	957	993	1020	429
35°	832	840	903	886	866	519
45°	664	718	659	556	520	508
55°	430	447	360	278	255	387
65°	237	242	176	143	135	240
75°	120	116	82	70	68	127
85°	25	20	20	14	11	31
90°	1	3	8	7	8	4
95°	55	160	713	254	165	62
105°	223	318	1274	2422	2300	235
115°	402	480	1036	2140	2512	397
125°	560	624	1021	1687	1982	498
135°	674	745	1012	1455	1640	521
145°	788	846	1010	1252	1372	494
155°	898	928	1016	1120	1164	413
165°	980	990	1021	1060	1071	276
175°	1025	1025	1026	1033	1031	97
180°	1029	1029	1029	1029	1029	

TEST NUMBER: P854234

CATALOG NUMBER: SQ2-PR1-150U-050D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1037.7	1037.7	1037.7	1037.7	1037.7
2.5°	1033.4	1045.9	1034.3	1035.2	1037.7
5°	1032.4	1050.0	1038.7	1041.1	1051.4
7.5°	1032.2	1057.2	1051.9	1058.3	1071.9
10°	1031.3	1061.3	1057.8	1059.2	1073.6
12.5°	1026.3	1061.2	1045.1	1043.8	1051.6
15°	1011.2	1052.6	1016.5	1019.8	1025.0
17.5°	984.8	1028.0	993.7	1005.3	1015.5
20°	967.9	1010.3	982.7	997.9	1015.5
22.5°	952.6	995.0	972.5	993.8	1018.0
25°	930.8	968.1	957.3	992.8	1019.7
27.5°	908.0	929.9	942.7	990.3	1009.1
30°	888.5	903.0	935.1	976.5	983.7
32.5°	867.4	876.1	924.9	946.5	937.2
35°	832.5	839.7	903.3	886.0	866.3
37.5°	791.0	805.9	854.9	804.9	782.3
40°	760.5	785.4	813.4	738.8	712.9
42.5°	723.3	763.0	758.4	663.4	631.7
45°	664.3	718.1	659.0	555.6	520.4
47.5°	594.7	649.9	553.2	460.9	428.0
50°	549.0	593.5	489.8	403.2	367.0
52.5°	502.4	534.5	435.6	349.2	316.3
55°	430.5	447.1	359.6	277.7	254.9
57.5°	364.5	375.1	293.9	224.3	207.5
60°	324.7	332.0	250.7	196.4	183.0
62.5°	288.3	293.9	216.0	172.8	162.7
65°	236.9	242.1	175.6	142.6	135.4
67.5°	196.1	198.8	144.5	118.5	111.7
70°	172.4	173.5	125.9	102.5	97.3
72.5°	151.3	149.8	108.1	89.0	85.5
75°	119.5	116.4	82.5	69.8	67.7
77.5°	89.3	86.0	58.0	53.7	53.7
80°	69.8	65.7	44.4	44.4	44.4
82.5°	52.0	46.3	34.3	34.3	33.4
85°	25.4	20.2	20.1	13.7	10.6
87.5°	7.0	7.4	4.2	4.0	4.2
90°	1.1	3.1	8.5	7.4	8.5
92.5°	18.0	65.6	201.4	65.5	52.5
95°	55.0	159.5	712.9	253.9	165.0
97.5°	99.8	210.3	1223.1	739.9	458.6
100°	131.2	236.6	1415.2	1263.8	837.7
102.5°	166.7	269.7	1394.0	1862.2	1443.5
105°	223.2	318.3	1274.5	2421.5	2300.5
107.5°	278.8	366.1	1158.0	2473.8	2606.8
110°	315.2	400.0	1102.1	2412.9	2660.1



TEST NUMBER: P854234

CATALOG NUMBER: SQ2-PR1-150U-050D-940-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	349.9	432.2	1068.3	2307.0	2623.7
115°	401.9	480.5	1035.5	2139.7	2512.0
117.5°	452.5	525.9	1023.0	1975.3	2353.4
120°	485.5	554.8	1019.6	1879.4	2247.6
122.5°	515.1	582.7	1019.6	1796.7	2138.4
125°	559.5	623.6	1020.7	1687.4	1982.1
127.5°	597.2	662.5	1019.4	1606.7	1863.2
130°	620.9	687.1	1018.6	1558.0	1789.6
132.5°	642.0	709.9	1016.0	1516.0	1726.1
135°	673.7	745.1	1012.2	1455.4	1640.5
137.5°	707.2	777.9	1009.9	1392.1	1559.5
140°	730.9	799.1	1009.0	1352.2	1510.4
142.5°	754.6	818.7	1009.0	1309.5	1452.8
145°	788.0	845.9	1010.1	1251.9	1371.8
147.5°	823.1	871.3	1011.6	1201.7	1292.3
150°	845.1	887.5	1013.3	1172.6	1249.1
152.5°	867.1	904.5	1014.1	1148.6	1211.9
155°	898.0	928.0	1016.4	1120.0	1163.5
157.5°	925.7	947.4	1018.8	1097.5	1129.0
160°	943.5	961.0	1019.6	1084.7	1109.5
162.5°	958.7	973.0	1019.6	1074.4	1092.6
165°	980.5	989.8	1020.7	1060.1	1071.4
167.5°	998.9	1003.4	1021.9	1048.9	1055.2
170°	1009.0	1011.1	1022.8	1042.9	1045.0
172.5°	1016.7	1017.9	1025.3	1038.7	1039.1
175°	1024.9	1024.9	1026.0	1033.3	1031.2
177.5°	1029.1	1028.3	1027.4	1032.4	1029.1
180°	1029.1	1029.1	1029.1	1029.1	1029.1

TEST NUMBER: P854234

CATALOG NUMBER: SQ2-PR1-150U-050D-940-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.09	14.76	15.22	15.88	17.44	10.81	11.49	11.94	12.60	14.16
	3H	15.31	15.91	16.44	17.04	18.61	11.86	12.47	13.00	13.59	15.16
	4H	15.75	16.32	16.90	17.45	19.02	12.25	12.83	13.40	13.95	15.53
	6H	16.06	16.58	17.21	17.71	19.30	12.58	13.10	13.73	14.23	15.82
	8H	16.13	16.63	17.29	17.78	19.36	12.66	13.16	13.81	14.30	15.88
	12H	16.16	16.63	17.32	17.77	19.37	12.66	13.13	13.82	14.27	15.87
4H	2H	14.14	14.71	15.30	15.84	17.42	11.36	11.93	12.51	13.06	14.63
	3H	15.60	16.07	16.76	17.22	18.81	12.61	13.08	13.77	14.23	15.82
	4H	16.18	16.62	17.35	17.76	19.37	13.11	13.54	14.27	14.68	16.29
	6H	16.63	17.00	17.79	18.16	19.76	13.53	13.90	14.70	15.07	16.67
	8H	16.76	17.10	17.92	18.26	19.87	13.65	14.00	14.82	15.15	16.77
	12H	16.80	17.12	17.98	18.28	19.90	13.66	13.98	14.85	15.15	16.76
8H	4H	16.20	16.55	17.36	17.70	19.31	13.40	13.75	14.56	14.90	16.52
	6H	16.74	17.03	17.93	18.23	19.83	13.93	14.21	15.11	15.41	17.02
	8H	16.94	17.19	18.13	18.36	19.99	14.11	14.36	15.30	15.54	17.17
	12H	17.03	17.25	18.23	18.43	20.09	14.17	14.39	15.36	15.56	17.22
12H	4H	16.15	16.46	17.33	17.63	19.25	13.41	13.72	14.59	14.89	16.51
	6H	16.73	16.98	17.92	18.15	19.78	13.99	14.24	15.18	15.41	17.04
	8H	16.93	17.15	18.12	18.32	19.99	14.19	14.41	15.38	15.58	17.24