

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855437

Luminaire Tested: SQ2-FB-025U-050D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855437
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-FB-025U-050D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3574.3 lumens
Efficiency: N/A
Efficacy: 141.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 25.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855437
CATALOG NUMBER: SQ2-FB-025U-050D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855437

CATALOG NUMBER: SQ2-FB-025U-050D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																		
RCR	0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67																																			
	1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	62	60	56																																			
	2	92	84	77	72	86	79	74	69	71	66	62	62	59	56	55	52	50	46																																			
	3	83	73	65	59	78	69	62	57	62	56	51	55	50	47	48	45	42	38																																			
	4	76	64	56	50	71	61	53	47	54	48	43	48	43	39	42	39	35	32																																			
	5	70	57	48	42	65	54	46	40	48	42	37	43	38	34	38	34	30	27																																			
	6	64	51	42	36	60	48	40	35	43	37	32	38	33	29	34	30	26	24																																			
	7	59	46	37	31	55	43	36	30	39	32	28	35	29	25	31	26	23	20																																			
	8	54	41	33	27	51	39	32	26	35	29	24	32	26	22	28	24	20	18																																			
	9	51	38	30	24	48	36	28	23	32	26	22	29	24	20	26	21	18	16																																			
	10	47	34	27	22	44	33	26	21	30	23	19	27	21	18	24	19	16	14																																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3914	3914	3914
5°	3815	5289	6932
10°	3572	10242	13490
15°	3234	13324	15525
20°	2864	14658	16259
25°	2533	15675	16527
30°	2237	16144	16731
35°	1999	16425	17986
40°	1817	16579	19110
45°	1676	16657	20011
50°	1580	16978	20374
55°	1543	17419	20535
60°	1579	17651	20434
65°	1647	17410	19859
70°	1704	16834	15021
75°	1890	15122	8291
80°	1953	7801	7689
85°	1945	5391	3242

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 52.5°
 Luminance: 20722 cd/sqm



TEST NUMBER: P855437

CATALOG NUMBER: SQ2-FB-025U-050D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.6	1.1
10°-20°	185.4	5.2
20°-30°	326.2	9.1
30°-40°	422.2	11.8
40°-50°	465.6	13.0
50°-60°	434.8	12.2
60°-70°	336.0	9.4
70°-80°	155.0	4.3
80°-90°	30.1	0.8
90°-100°	76.8	2.1
100°-110°	239.0	6.7
110°-120°	233.8	6.5
120°-130°	190.9	5.3
130°-140°	156.2	4.4
140°-150°	121.9	3.4
150°-160°	88.0	2.5
160°-170°	53.8	1.5
170°-180°	18.1	0.5
0°-30°	552.2	15.4
0°-40°	974.3	27.3
0°-60°	1874.7	52.4
0°-90°	2395.8	67.0
90°-120°	549.7	15.4
90°-150°	1018.7	28.5
90°-180°	1179.0	33.0
0°-180°	3574.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	242	242	242	242	242	
5°	235	270	326	398	428	22
15°	194	381	797	892	929	54
25°	142	512	880	919	928	65
35°	101	494	833	862	912	64
45°	73	379	730	838	876	57
55°	55	226	619	711	730	49
65°	43	128	456	511	520	42
75°	30	78	242	130	133	31
85°	10	23	29	20	18	11
90°	0	1	4	4	4	1
95°	10	31	141	52	34	12
105°	42	59	235	449	429	44
115°	75	88	191	394	461	74
125°	104	115	189	310	364	92
135°	125	138	188	268	301	97
145°	146	157	188	231	252	91
155°	167	172	189	208	214	77
165°	183	184	190	196	198	51
175°	190	190	190	191	190	18
180°	190	190	190	190	190	



TEST NUMBER: P855437

CATALOG NUMBER: SQ2-FB-025U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	242.4	242.4	242.4	242.4	242.4
2.5°	240.5	250.6	262.0	275.2	280.6
5°	235.4	269.6	326.3	398.1	427.7
7.5°	226.3	295.8	474.6	666.6	725.8
10°	217.9	314.8	624.7	790.8	822.8
12.5°	208.6	340.1	718.8	835.6	868.5
15°	193.5	381.4	797.1	892.3	928.8
17.5°	177.8	428.1	833.5	927.4	947.2
20°	166.7	460.7	853.1	933.8	946.3
22.5°	156.4	485.0	867.1	928.2	941.6
25°	142.2	512.5	879.9	918.6	927.7
27.5°	128.4	519.8	874.3	899.7	908.5
30°	120.0	517.7	865.9	884.9	897.4
32.5°	112.6	512.1	853.8	872.1	899.2
35°	101.4	494.5	833.3	862.4	912.5
37.5°	91.8	466.3	806.2	865.8	914.1
40°	86.2	445.2	786.6	865.7	906.7
42.5°	80.6	420.5	764.3	856.3	897.4
45°	73.4	378.8	729.5	837.7	876.4
47.5°	66.7	331.9	697.4	811.8	840.0
50°	62.9	300.0	675.9	788.3	811.1
52.5°	59.2	268.9	654.5	760.3	781.3
55°	54.8	225.7	618.8	711.4	729.5
57.5°	50.8	188.7	578.3	657.2	672.0
60°	48.9	168.6	546.6	618.0	632.8
62.5°	46.1	150.3	511.1	577.0	590.9
65°	43.1	127.5	455.7	510.7	519.8
67.5°	38.9	110.5	396.7	430.4	413.3
70°	36.1	102.2	356.6	367.1	318.2
72.5°	34.3	93.1	312.8	285.1	192.3
75°	30.3	78.2	242.4	130.5	132.9
77.5°	24.7	60.5	159.4	100.2	102.3
80°	21.0	49.4	83.9	81.6	82.7
82.5°	17.2	38.5	57.8	60.1	58.5
85°	10.5	23.1	29.1	19.8	17.5
87.5°	3.7	8.5	5.4	5.4	5.4
90°	0.0	1.2	3.5	3.5	3.5
92.5°	3.7	13.1	44.5	14.6	11.9
95°	10.5	31.0	141.0	52.0	33.8
97.5°	19.1	40.3	233.4	145.3	91.6
100°	25.6	45.0	263.3	246.2	164.3
102.5°	32.2	50.6	257.7	351.7	276.1
105°	42.0	59.1	235.3	449.3	428.8
107.5°	51.7	67.7	213.9	456.7	479.3
110°	58.3	74.2	202.7	446.0	490.5



TEST NUMBER: P855437

CATALOG NUMBER: SQ2-FB-025U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	64.8	79.8	197.1	426.8	483.1
115°	74.6	88.2	191.0	394.1	461.4
117.5°	84.1	96.6	188.4	362.9	431.8
120°	89.7	102.2	187.5	345.2	411.3
122.5°	95.3	107.8	188.4	330.2	390.8
125°	103.7	115.0	188.7	310.0	363.5
127.5°	110.5	122.0	188.7	294.8	340.4
130°	114.2	126.7	188.7	286.3	327.4
132.5°	118.9	131.3	187.7	278.9	317.1
135°	124.7	138.3	187.5	267.6	300.6
137.5°	131.5	143.9	187.5	256.3	286.3
140°	135.2	147.7	187.5	248.8	276.1
142.5°	139.8	151.4	187.5	241.2	265.8
145°	145.7	157.0	187.5	231.1	251.6
147.5°	152.7	162.5	188.7	221.8	237.9
150°	157.3	165.3	188.7	217.0	229.5
152.5°	161.1	168.1	188.7	212.2	222.9
155°	166.7	172.2	188.7	207.6	214.3
157.5°	172.2	176.6	188.7	203.2	207.6
160°	176.0	179.4	188.7	200.4	203.8
162.5°	178.7	181.2	188.7	198.6	201.0
165°	182.9	184.0	189.8	195.8	198.0
167.5°	185.4	185.6	188.7	194.2	195.2
170°	186.3	187.5	188.7	192.3	193.3
172.5°	188.2	188.4	189.6	191.4	191.5
175°	189.8	189.8	189.8	191.0	189.8
177.5°	189.8	189.8	189.8	189.8	189.8
180°	189.8	189.8	189.8	189.8	189.8



TEST NUMBER: P855437

CATALOG NUMBER: SQ2-FB-025U-050D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.23	14.30	14.01	15.12	16.12	21.96	23.04	22.75	23.86	24.86
	3H	13.97	14.94	14.78	15.77	16.80	23.60	24.57	24.40	25.40	26.43
	4H	14.28	15.20	15.10	16.03	17.08	23.79	24.71	24.61	25.54	26.58
	6H	14.51	15.36	15.35	16.20	17.26	23.89	24.73	24.72	25.58	26.63
	8H	14.58	15.38	15.42	16.24	17.30	23.90	24.71	24.74	25.57	26.62
	12H	14.61	15.38	15.46	16.23	17.32	23.88	24.65	24.73	25.50	26.59
4H	2H	17.65	18.57	18.48	19.40	20.44	22.43	23.35	23.26	24.18	25.22
	3H	18.61	19.37	19.44	20.24	21.30	24.28	25.04	25.12	25.91	26.97
	4H	18.90	19.59	19.75	20.46	21.55	24.53	25.22	25.38	26.09	27.17
	6H	19.04	19.64	19.91	20.53	21.62	24.69	25.29	25.55	26.18	27.27
	8H	19.07	19.63	19.94	20.52	21.62	24.72	25.28	25.59	26.16	27.26
	12H	19.07	19.58	19.96	20.48	21.59	24.70	25.20	25.59	26.11	27.22
8H	4H	20.09	20.65	20.96	21.54	22.64	24.66	25.22	25.53	26.11	27.21
	6H	20.34	20.80	21.24	21.73	22.83	24.88	25.34	25.78	26.27	27.37
	8H	20.41	20.82	21.32	21.74	22.86	24.94	25.35	25.85	26.27	27.39
	12H	20.45	20.81	21.36	21.72	22.90	24.95	25.31	25.86	26.22	27.39
12H	4H	20.12	20.63	21.01	21.53	22.64	24.63	25.13	25.52	26.04	27.14
	6H	20.44	20.85	21.35	21.77	22.89	24.86	25.28	25.77	26.19	27.32
	8H	20.55	20.91	21.46	21.82	23.00	24.94	25.30	25.86	26.22	27.39