

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P854360

Luminaire Tested: SQ2-WBM-075U-100D-940-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P854360  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G3-2104-222-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-WBM-075U-100D-940-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7746.2 lumens  
Efficiency: N/A  
Efficacy: 126.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.18 / 1.17  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P854360

CATALOG NUMBER: SQ2-WBM-075U-100D-940-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P854360

CATALOG NUMBER: SQ2-WBM-075U-100D-940-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60				
1	102	98	95	92	95	92	90	87	81	79	77	70	69	68	61	60	59	54				
2	95	89	84	79	89	83	79	75	74	70	68	65	62	60	56	55	53	49				
3	88	80	74	69	82	76	70	66	67	63	60	59	56	54	52	50	48	45				
4	82	73	66	61	77	69	63	58	61	57	53	54	51	48	48	46	43	40				
5	76	66	59	54	71	63	56	52	56	51	47	50	46	43	44	42	39	37				
6	71	60	53	48	67	57	51	46	51	46	43	46	42	39	41	38	36	33				
7	66	55	48	43	62	52	46	42	47	42	39	43	39	36	38	35	33	31				
8	62	51	44	39	58	48	42	38	44	39	35	40	36	33	36	32	30	28				
9	58	47	40	35	55	45	38	34	41	36	32	37	33	30	33	30	28	26				
10	54	43	37	32	51	41	35	31	38	33	29	34	30	27	31	28	26	24				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	47180	47180	47180
5°	47686	47188	47496
10°	48237	47803	48063
15°	49091	48455	48084
20°	49462	48318	47245
25°	48515	47101	46198
30°	46236	44836	43121
35°	41837	40627	39356
40°	33970	33280	31809
45°	21758	24172	19559
50°	8528	14318	7676
55°	4020	6550	4020
60°	1912	3178	1741
65°	1738	1819	1616
70°	1648	1699	1548
75°	1647	1647	1516
80°	1571	1571	1478
85°	1371	1371	1371

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°  
 Vertical Angle: 45°  
 Luminance: 24332 cd/sqm



TEST NUMBER: P854360

CATALOG NUMBER: SQ2-WBM-075U-100D-940-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	279.9	3.6
10°-20°	820.3	10.6
20°-30°	1217.4	15.7
30°-40°	1264.5	16.3
40°-50°	761.0	9.8
50°-60°	182.4	2.4
60°-70°	49.5	0.6
70°-80°	27.8	0.4
80°-90°	9.2	0.1
90°-100°	191.4	2.5
100°-110°	634.6	8.2
110°-120°	629.9	8.1
120°-130°	513.0	6.6
130°-140°	417.0	5.4
140°-150°	323.8	4.2
150°-160°	233.3	3.0
160°-170°	142.9	1.8
170°-180°	48.3	0.6
0°-30°	2317.6	29.9
0°-40°	3582.1	46.2
0°-60°	4525.6	58.4
0°-90°	4612.0	59.5
90°-120°	1456.0	18.8
90°-150°	2709.8	35.0
90°-180°	3134.0	40.5
0°-180°	7746.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2922	2922	2922	2922	2922	
5°	2942	2935	2912	2942	2930	281
15°	2937	2958	2899	2897	2877	828
25°	2723	2742	2644	2609	2593	1246
35°	2123	2103	2061	2020	1997	1300
45°	953	1066	1059	1008	857	728
55°	143	161	233	155	143	147
65°	46	46	48	45	42	45
75°	26	28	26	25	24	27
85°	7	8	7	7	7	8
90°	0	1	3	4	4	1
95°	27	80	347	124	83	31
105°	111	158	635	1198	1120	117
115°	198	237	512	1065	1245	196
125°	277	307	502	837	986	246
135°	331	365	498	718	810	256
145°	385	413	497	618	676	241
155°	439	454	500	552	572	202
165°	482	487	502	522	527	136
175°	504	504	505	508	507	48
180°	506	506	506	506	506	

TEST NUMBER: P854360

CATALOG NUMBER: SQ2-WBM-075U-100D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2922.1	2922.1	2922.1	2922.1	2922.1
2.5°	2936.5	2929.9	2908.6	2932.0	2922.1
5°	2942.2	2934.9	2911.5	2941.9	2930.5
7.5°	2943.0	2943.4	2915.7	2942.5	2929.9
10°	2942.2	2948.4	2915.7	2940.9	2931.6
12.5°	2943.0	2953.4	2912.4	2930.6	2916.4
15°	2936.9	2957.6	2898.8	2897.3	2876.6
17.5°	2910.0	2935.7	2856.1	2831.6	2807.2
20°	2878.7	2903.5	2812.1	2776.6	2749.7
22.5°	2824.6	2850.2	2749.5	2711.6	2692.2
25°	2723.3	2741.9	2643.9	2608.7	2593.2
27.5°	2590.0	2596.0	2510.7	2469.7	2443.2
30°	2480.0	2485.2	2404.9	2358.4	2312.9
32.5°	2354.0	2345.1	2283.9	2233.2	2186.0
35°	2122.6	2102.9	2061.2	2019.5	1996.7
37.5°	1829.2	1824.2	1793.9	1743.7	1716.4
40°	1611.7	1628.3	1579.0	1542.3	1509.2
42.5°	1379.1	1419.6	1376.8	1324.9	1296.8
45°	952.9	1065.6	1058.6	1007.6	856.6
47.5°	529.8	671.7	757.0	593.8	439.3
50°	339.5	436.7	570.0	358.4	305.6
52.5°	238.0	291.3	421.1	254.0	225.3
55°	142.8	161.4	232.7	155.2	142.8
57.5°	86.3	104.3	132.2	104.0	84.4
60°	59.2	74.7	98.4	69.4	53.9
62.5°	51.6	57.2	76.4	54.4	48.9
65°	45.5	46.5	47.6	45.4	42.3
67.5°	39.1	41.2	40.2	39.3	37.0
70°	34.9	37.0	36.0	35.9	32.8
72.5°	31.5	33.6	32.6	31.7	29.4
75°	26.4	27.5	26.4	25.4	24.3
77.5°	20.3	21.3	21.2	20.3	19.2
80°	16.9	18.0	16.9	16.9	15.9
82.5°	13.5	13.7	13.5	12.7	12.5
85°	7.4	8.4	7.4	7.4	7.4
87.5°	2.5	2.7	3.2	3.4	3.4
90°	0.0	1.0	3.1	4.2	4.2
92.5°	8.4	32.4	95.4	30.9	26.0
95°	27.2	80.5	346.9	123.8	82.8
97.5°	50.1	105.8	605.6	353.2	223.2
100°	66.0	119.3	701.2	602.2	399.3
102.5°	83.6	135.3	695.3	920.3	695.3
105°	111.1	158.2	635.1	1198.3	1120.4
107.5°	139.2	181.2	577.5	1226.5	1285.8
110°	155.1	197.1	548.1	1198.6	1318.5



TEST NUMBER: P854360

CATALOG NUMBER: SQ2-WBM-075U-100D-940-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	171.9	213.1	530.5	1149.0	1301.7
115°	198.1	237.0	511.5	1064.8	1245.1
117.5°	224.1	258.7	504.5	984.2	1173.4
120°	240.0	273.8	502.0	933.8	1117.2
122.5°	254.3	287.3	502.0	892.4	1061.9
125°	276.7	307.4	502.0	836.6	986.2
127.5°	295.1	325.3	500.8	794.4	922.3
130°	306.0	337.8	499.9	769.8	884.6
132.5°	316.1	348.7	499.1	749.4	852.7
135°	331.2	365.0	497.8	717.9	810.2
137.5°	347.5	380.1	496.6	687.5	768.9
140°	358.4	390.2	495.7	667.2	742.0
142.5°	368.5	399.5	496.6	646.9	713.5
145°	384.6	413.3	496.8	617.6	676.0
147.5°	402.0	426.0	497.0	592.7	636.2
150°	412.9	434.5	497.8	578.3	615.2
152.5°	423.0	443.7	498.7	566.4	595.9
155°	439.1	454.5	499.9	551.8	572.2
157.5°	454.9	466.8	501.2	541.3	555.9
160°	463.2	473.5	502.0	533.7	545.0
162.5°	471.6	479.4	502.0	528.6	537.5
165°	482.1	487.2	502.0	522.1	527.2
167.5°	491.8	494.4	503.1	516.1	518.8
170°	496.8	497.8	503.1	513.6	514.6
172.5°	500.1	501.2	503.9	511.0	511.3
175°	504.1	504.1	505.2	508.3	507.3
177.5°	506.2	506.2	505.4	507.0	505.4
180°	506.2	506.2	506.2	506.2	506.2



TEST NUMBER: P854360

CATALOG NUMBER: SQ2-WBM-075U-100D-940-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.15	7.93	8.06	8.83	9.97	6.87	7.64	7.78	8.54	9.68
	3H	7.67	8.35	8.58	9.26	10.43	7.38	8.06	8.29	8.97	10.14
	4H	7.93	8.58	8.87	9.49	10.67	7.62	8.26	8.55	9.18	10.36
	6H	8.17	8.76	9.11	9.68	10.86	7.84	8.43	8.78	9.35	10.54
	8H	8.24	8.80	9.19	9.73	10.92	7.91	8.47	8.86	9.40	10.59
	12H	8.27	8.80	9.23	9.73	10.94	7.95	8.48	8.90	9.41	10.62
4H	2H	7.16	7.81	8.10	8.72	9.90	6.91	7.55	7.84	8.46	9.64
	3H	7.89	8.42	8.84	9.37	10.55	7.63	8.16	8.57	9.10	10.29
	4H	8.30	8.78	9.25	9.72	10.94	8.01	8.49	8.96	9.43	10.64
	6H	8.68	9.09	9.64	10.05	11.27	8.36	8.77	9.33	9.74	10.95
	8H	8.81	9.19	9.78	10.15	11.38	8.49	8.87	9.46	9.83	11.06
	12H	8.88	9.23	9.87	10.20	11.43	8.57	8.91	9.55	9.88	11.11
8H	4H	8.38	8.77	9.35	9.72	10.95	8.11	8.50	9.08	9.45	10.68
	6H	8.89	9.20	9.88	10.20	11.43	8.59	8.91	9.59	9.91	11.13
	8H	9.11	9.38	10.10	10.37	11.62	8.80	9.08	9.80	10.07	11.31
	12H	9.26	9.50	10.26	10.48	11.78	8.95	9.19	9.95	10.17	11.47
12H	4H	8.36	8.70	9.34	9.67	10.91	8.09	8.43	9.08	9.41	10.64
	6H	8.91	9.18	9.91	10.17	11.42	8.62	8.90	9.62	9.89	11.13
	8H	9.15	9.39	10.15	10.37	11.67	8.86	9.10	9.86	10.08	11.38