

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855428

Luminaire Tested: SQ2-FB-075U-075D-840-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P855428  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-11, G2-2308-131-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-FB-075U-075D-840-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 750 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6924.9 lumens  
Efficiency: N/A  
Efficacy: 138.5 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 2.98 / 2.56  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 50  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P855428

CATALOG NUMBER: SQ2-FB-075U-075D-840-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P855428

CATALOG NUMBER: SQ2-FB-075U-075D-840-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50				
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47	42				
2	89	81	75	69	81	75	69	65	63	59	56	53	50	47	43	41	39	34				
3	80	71	63	57	74	65	59	53	55	50	46	46	42	39	38	35	33	28				
4	73	62	54	48	67	58	50	45	49	43	39	41	37	33	33	30	28	24				
5	67	55	47	41	61	51	44	38	43	38	33	36	32	28	30	26	24	20				
6	62	49	41	35	56	46	38	33	39	33	29	32	28	24	27	23	20	18				
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18	15				
8	52	40	32	26	48	37	30	25	32	26	22	27	22	19	22	18	16	13				
9	49	36	28	23	45	34	27	22	29	23	19	24	20	17	20	17	14	12				
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	13	11				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5646	5646	5646
5°	5504	7629	10000
10°	5155	14773	19461
15°	4665	19221	22397
20°	4131	21146	23457
25°	3654	22611	23840
30°	3229	23288	24134
35°	2884	23692	25945
40°	2624	23918	27566
45°	2418	24032	28866
50°	2281	24493	29391
55°	2224	25129	29627
60°	2280	25462	29479
65°	2376	25112	28646
70°	2459	24283	21663
75°	2726	21815	11959
80°	2817	11260	11093
85°	2816	7799	4668

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 52.5°  
 Luminance: 29893 cd/sqm



TEST NUMBER: P855428

CATALOG NUMBER: SQ2-FB-075U-075D-840-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.6	0.8
10°-20°	267.4	3.9
20°-30°	470.5	6.8
30°-40°	609.0	8.8
40°-50°	671.7	9.7
50°-60°	627.2	9.1
60°-70°	484.7	7.0
70°-80°	223.6	3.2
80°-90°	43.3	0.6
90°-100°	211.9	3.1
100°-110°	702.4	10.1
110°-120°	697.1	10.1
120°-130°	567.8	8.2
130°-140°	461.5	6.7
140°-150°	358.4	5.2
150°-160°	258.2	3.7
160°-170°	158.1	2.3
170°-180°	53.4	0.8
0°-30°	796.5	11.5
0°-40°	1405.6	20.3
0°-60°	2704.4	39.1
0°-90°	3456.0	49.9
90°-120°	1611.4	23.3
90°-150°	2999.1	43.3
90°-180°	3469.0	50.1
0°-180°	6924.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	350	350	350	350	350	
5°	340	389	471	574	617	32
15°	279	550	1150	1287	1340	78
25°	205	739	1269	1325	1338	94
35°	146	713	1202	1244	1316	92
45°	106	546	1052	1208	1264	82
55°	79	326	893	1026	1052	71
65°	62	184	657	737	750	61
75°	44	113	350	188	192	45
85°	15	33	42	29	25	16
90°	0	1	4	5	5	2
95°	30	89	384	137	92	35
105°	123	175	703	1326	1240	130
115°	219	262	566	1178	1378	217
125°	306	340	556	926	1092	272
135°	366	404	551	795	897	284
145°	426	457	550	684	748	267
155°	486	503	553	611	633	224
165°	534	539	556	578	583	150
175°	558	558	559	562	561	53
180°	560	560	560	560	560	



TEST NUMBER: P855428

CATALOG NUMBER: SQ2-FB-075U-075D-840-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	349.7	349.7	349.7	349.7	349.7
2.5°	346.9	361.5	377.9	396.9	404.9
5°	339.6	388.9	470.7	574.3	617.0
7.5°	326.4	426.8	684.6	961.6	1047.0
10°	314.4	454.2	901.1	1140.9	1187.0
12.5°	300.9	490.6	1037.0	1205.5	1252.8
15°	279.1	550.3	1149.9	1287.3	1339.9
17.5°	256.5	617.5	1202.3	1337.9	1366.4
20°	240.4	664.5	1230.7	1347.1	1365.2
22.5°	225.6	699.7	1250.8	1339.0	1358.4
25°	205.1	739.3	1269.2	1325.1	1338.2
27.5°	185.3	749.7	1261.2	1297.8	1310.6
30°	173.2	746.9	1249.1	1276.5	1294.5
32.5°	162.5	738.7	1231.6	1258.1	1297.2
35°	146.3	713.3	1202.0	1244.1	1316.3
37.5°	132.5	672.7	1163.1	1249.1	1318.8
40°	124.5	642.3	1134.8	1248.7	1307.9
42.5°	116.3	606.5	1102.5	1235.3	1294.5
45°	105.9	546.5	1052.5	1208.4	1264.2
47.5°	96.1	478.9	1006.0	1171.0	1211.8
50°	90.8	432.7	975.1	1137.2	1170.1
52.5°	85.4	387.8	944.2	1096.9	1127.1
55°	79.0	325.6	892.7	1026.1	1052.5
57.5°	73.3	272.2	834.2	948.1	969.4
60°	70.6	243.2	788.5	891.5	912.9
62.5°	66.5	216.8	737.3	832.3	852.4
65°	62.2	183.9	657.3	736.7	749.8
67.5°	56.2	159.4	572.3	620.8	596.1
70°	52.1	147.4	514.4	529.7	458.9
72.5°	49.4	134.3	451.2	411.2	277.4
75°	43.7	112.7	349.7	188.3	191.7
77.5°	35.7	87.3	229.9	144.6	147.7
80°	30.3	71.3	121.1	117.7	119.3
82.5°	24.9	55.5	83.4	86.7	84.4
85°	15.2	33.2	42.1	28.6	25.2
87.5°	5.4	12.2	7.5	7.7	7.7
90°	0.0	1.2	3.5	4.7	4.7
92.5°	9.3	35.8	105.6	34.3	28.8
95°	30.2	89.2	384.0	137.1	91.6
97.5°	55.5	117.1	670.2	390.9	247.1
100°	73.1	132.0	776.0	666.5	441.9
102.5°	92.5	149.8	769.5	1018.6	769.5
105°	122.9	175.2	703.0	1326.2	1240.0
107.5°	154.1	200.6	639.1	1357.5	1423.1
110°	171.7	218.2	606.7	1326.5	1459.2



TEST NUMBER: P855428

CATALOG NUMBER: SQ2-FB-075U-075D-840-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	190.2	235.9	587.1	1271.7	1440.7
115°	219.2	262.3	566.0	1178.5	1378.0
117.5°	248.0	286.3	558.3	1089.3	1298.7
120°	265.6	303.0	555.7	1033.5	1236.5
122.5°	281.4	317.9	555.7	987.7	1175.3
125°	306.3	340.3	555.7	925.9	1091.5
127.5°	326.7	360.0	554.3	879.2	1020.8
130°	338.7	373.9	553.3	851.9	978.9
132.5°	349.9	385.9	552.4	829.4	943.7
135°	366.5	403.9	551.0	794.6	896.7
137.5°	384.6	420.7	549.6	760.9	851.0
140°	396.7	431.9	548.7	738.4	821.3
142.5°	407.9	442.0	549.6	716.0	789.7
145°	425.7	457.4	549.8	683.5	748.2
147.5°	445.0	471.5	550.1	656.0	704.1
150°	457.1	480.8	551.0	640.0	680.9
152.5°	468.1	491.1	551.9	626.9	659.5
155°	486.0	503.0	553.3	610.7	633.3
157.5°	503.5	516.6	554.7	599.1	615.2
160°	512.7	524.1	555.7	590.7	603.2
162.5°	522.0	530.6	555.7	585.0	594.8
165°	533.5	539.2	555.7	577.8	583.4
167.5°	544.2	547.2	556.8	571.3	574.2
170°	549.8	551.0	556.8	568.4	569.5
172.5°	553.6	554.6	557.6	565.6	565.8
175°	557.9	557.9	559.0	562.5	561.4
177.5°	560.2	560.2	559.3	561.1	559.3
180°	560.2	560.2	560.2	560.2	560.2

TEST NUMBER: P855428

CATALOG NUMBER: SQ2-FB-075U-075D-840-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.07	13.96	14.02	14.93	16.20	21.81	22.69	22.76	23.66	24.93
	3H	13.80	14.60	14.76	15.58	16.87	23.43	24.23	24.39	25.21	26.50
	4H	14.10	14.86	15.08	15.84	17.14	23.61	24.36	24.59	25.35	26.65
	6H	14.32	15.01	15.31	16.00	17.32	23.70	24.39	24.69	25.38	26.70
	8H	14.38	15.04	15.37	16.05	17.36	23.70	24.36	24.70	25.37	26.68
	12H	14.41	15.04	15.41	16.04	17.38	23.68	24.30	24.68	25.31	26.64
4H	2H	17.47	18.22	18.45	19.21	20.51	22.25	23.00	23.24	23.99	25.29
	3H	18.41	19.03	19.40	20.05	21.36	24.08	24.71	25.07	25.72	27.04
	4H	18.69	19.26	19.69	20.27	21.61	24.32	24.89	25.32	25.90	27.24
	6H	18.82	19.32	19.84	20.35	21.68	24.47	24.96	25.48	25.99	27.33
	8H	18.85	19.31	19.86	20.33	21.68	24.49	24.95	25.51	25.98	27.33
	12H	18.84	19.25	19.87	20.29	21.65	24.47	24.88	25.50	25.92	27.28
8H	4H	19.87	20.33	20.88	21.35	22.70	24.44	24.90	25.46	25.92	27.28
	6H	20.11	20.49	21.15	21.55	22.90	24.65	25.03	25.69	26.09	27.44
	8H	20.18	20.51	21.23	21.56	22.93	24.71	25.04	25.76	26.09	27.46
	12H	20.21	20.50	21.26	21.55	22.96	24.70	25.00	25.75	26.04	27.45
12H	4H	19.89	20.30	20.92	21.34	22.70	24.39	24.81	25.43	25.85	27.20
	6H	20.20	20.54	21.25	21.59	22.95	24.63	24.96	25.68	26.01	27.38
	8H	20.31	20.60	21.36	21.65	23.06	24.70	24.99	25.75	26.04	27.45