

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936923

Luminaire Tested: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936923
REPORT IS A COMBINATION OF REPORTS P933480 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7003.1 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936923
CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P936923

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67	67	67	67
1	101	96	92	88	95	91	87	83	80	78	75	71	69	67	62	61	59	55	55	55	55
2	91	83	76	71	86	78	72	67	70	65	61	61	58	55	54	51	49	45	45	45	45
3	83	72	64	58	77	68	61	55	61	55	50	54	49	45	47	44	41	37	37	37	37
4	75	64	55	48	70	60	52	46	53	47	42	47	42	38	42	38	34	31	31	31	31
5	69	56	47	41	64	53	45	39	47	41	36	42	37	32	37	33	29	26	26	26	26
6	63	50	41	35	59	47	39	34	42	36	31	38	32	28	33	29	25	23	23	23	23
7	58	45	36	30	55	43	35	29	38	32	27	34	29	24	30	26	22	20	20	20	20
8	54	41	32	27	51	39	31	26	35	28	24	31	26	22	27	23	20	17	17	17	17
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17	15	15	15	15
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3760	3760	3760
5°	3672	4345	5054
10°	3330	6332	8380
15°	2829	8271	10118
20°	2302	9582	10312
25°	1919	10025	10102
30°	1618	10086	10083
35°	1430	9916	10344
40°	1246	9695	10613
45°	1127	9532	10655
50°	1032	9386	10478
55°	988	9173	10014
60°	1010	8767	9280
65°	1050	8149	8273
70°	1116	7102	6989
75°	1231	5786	5454
80°	1334	4008	3675
85°	1169	2123	1882

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10655 cd/sqm



TEST NUMBER: P936923

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.6	1.1
10°-20°	348.5	5.0
20°-30°	609.6	8.7
30°-40°	784.7	11.2
40°-50°	876.5	12.5
50°-60°	839.4	12.0
60°-70°	665.3	9.5
70°-80°	391.2	5.6
80°-90°	110.0	1.6
90°-100°	172.9	2.5
100°-110°	454.6	6.5
110°-120°	471.3	6.7
120°-130°	378.1	5.4
130°-140°	296.6	4.2
140°-150°	227.7	3.3
150°-160°	164.0	2.3
160°-170°	100.3	1.4
170°-180°	33.9	0.5
0°-30°	1036.7	14.8
0°-40°	1821.4	26.0
0°-60°	3537.3	50.5
0°-90°	4703.7	67.2
90°-120°	1098.8	15.7
90°-150°	2001.2	28.6
90°-180°	2299.0	32.8
0°-180°	7003.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	608	608	608	608	608	
5°	592	635	715	809	838	55
15°	444	819	1380	1673	1726	123
25°	283	928	1644	1716	1718	131
35°	192	887	1548	1636	1700	120
45°	131	708	1368	1568	1638	101
55°	94	450	1161	1349	1386	85
65°	74	238	862	969	983	74
75°	55	147	473	520	522	57
85°	20	45	117	129	131	21
90°	2	7	18	9	9	3
95°	23	90	298	154	104	25
105°	82	124	502	763	712	87
115°	146	177	403	803	916	144
125°	202	227	366	619	730	180
135°	241	265	355	499	566	187
145°	280	298	350	426	460	175
155°	316	325	350	384	396	145
165°	341	346	350	364	368	96
175°	355	355	353	357	357	34
180°	355	355	355	355	355	



TEST NUMBER: P936923

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	607.8	607.8	607.8	607.8	607.8	607.8	607.8	607.8	607.8	607.8	607.8
2.5°	607.8	607.8	611.8	613.7	617.6	619.6	623.5	627.4	639.1	641.1	645.0
5°	592.2	600.1	625.5	635.2	662.6	699.7	715.3	740.7	793.6	809.2	819.0
7.5°	568.8	586.4	648.9	664.5	733.0	830.7	871.7	926.5	1010.5	1051.5	1084.8
10°	531.6	568.8	680.1	717.3	828.8	977.3	1053.5	1129.7	1256.8	1313.5	1334.9
12.5°	490.6	551.2	713.4	764.2	924.5	1141.4	1233.3	1317.3	1462.0	1538.2	1549.9
15°	443.7	525.8	744.7	819.0	1026.1	1278.3	1379.9	1483.5	1618.4	1673.1	1686.8
17.5°	402.6	506.2	774.0	852.2	1104.3	1401.4	1505.0	1591.0	1700.5	1737.6	1747.4
20°	351.8	474.9	793.6	895.2	1186.4	1491.3	1591.0	1657.4	1731.7	1755.1	1759.1
22.5°	314.7	441.7	805.3	910.8	1241.2	1546.0	1630.1	1682.8	1733.7	1741.5	1743.4
25°	283.4	404.6	803.3	928.4	1288.1	1579.3	1643.8	1682.8	1712.2	1716.1	1716.1
27.5°	254.1	363.5	795.5	932.3	1323.2	1587.0	1637.9	1665.3	1678.9	1686.8	1686.8
30°	228.7	324.5	775.9	924.5	1338.9	1579.3	1620.3	1634.0	1647.6	1659.4	1665.3
32.5°	209.1	287.3	746.6	908.8	1340.8	1559.7	1589.0	1596.8	1616.4	1643.8	1653.5
35°	191.6	250.2	713.4	887.3	1329.1	1528.4	1548.0	1555.8	1594.9	1635.9	1649.6
37.5°	173.9	222.8	670.4	850.2	1311.5	1491.3	1505.0	1518.7	1579.3	1628.1	1643.8
40°	156.4	199.4	619.6	809.2	1284.1	1446.4	1458.1	1479.6	1559.7	1616.4	1632.0
42.5°	142.7	179.8	564.9	766.2	1248.9	1395.5	1413.1	1444.4	1536.2	1596.8	1614.5
45°	131.0	160.2	506.2	707.6	1204.0	1342.7	1368.1	1411.2	1508.9	1567.6	1583.2
47.5°	119.2	146.6	445.6	647.0	1155.2	1290.0	1323.2	1372.1	1471.8	1528.4	1542.2
50°	109.4	132.9	385.1	582.4	1102.3	1233.3	1272.4	1323.2	1424.9	1477.6	1495.2
52.5°	101.6	121.2	328.3	518.0	1041.7	1174.6	1219.6	1272.4	1368.1	1419.0	1430.7
55°	93.8	111.4	279.5	449.5	979.2	1112.1	1161.0	1211.8	1305.6	1348.7	1356.4
57.5°	89.9	103.6	238.5	385.1	912.8	1041.7	1096.5	1143.4	1231.4	1264.6	1272.4
60°	84.0	97.7	207.2	330.3	840.5	975.3	1022.3	1069.1	1143.4	1170.8	1176.6
62.5°	78.2	93.8	183.7	277.5	766.2	897.1	944.0	987.1	1049.6	1069.1	1076.9
65°	74.3	89.9	166.2	238.5	689.9	815.0	861.9	899.1	949.9	969.4	973.4
67.5°	70.4	86.0	152.5	205.2	613.7	733.0	768.2	803.3	842.4	861.9	863.9
70°	64.5	82.1	140.8	181.8	535.5	639.1	668.4	705.6	736.9	746.6	752.5
72.5°	60.6	76.2	132.9	164.2	455.4	549.2	576.6	598.1	625.5	635.2	635.2
75°	54.7	68.4	125.1	146.6	373.3	449.5	473.0	494.5	516.0	519.9	514.1
77.5°	48.9	60.6	107.5	123.1	291.2	355.7	375.3	387.0	404.6	408.5	410.5
80°	41.0	52.7	84.0	95.8	211.1	261.9	275.6	285.4	301.0	301.0	304.9
82.5°	31.3	41.0	60.6	68.4	142.7	179.8	191.6	197.4	207.2	207.2	207.2
85°	19.6	25.4	39.1	45.0	86.0	109.4	117.3	119.2	127.0	129.0	129.0
87.5°	9.8	13.7	25.4	27.3	45.0	56.7	56.7	60.6	60.6	58.7	56.7
90°	2.4	4.3	6.2	6.7	10.5	15.6	18.1	16.1	12.0	9.0	9.0
92.5°	9.5	25.7	41.9	46.0	64.6	89.5	101.9	89.2	64.1	45.2	43.4
95°	22.9	52.4	82.1	89.5	158.9	251.6	297.8	265.8	201.7	153.5	148.1
97.5°	39.5	65.7	91.8	98.3	214.1	368.5	445.7	425.4	384.8	354.4	344.0
100°	52.4	76.1	99.8	105.7	234.2	405.5	491.1	492.6	495.6	497.8	485.5
102.5°	63.3	85.5	107.6	113.1	243.4	417.1	504.0	529.8	581.4	620.2	609.6
105°	81.9	100.6	119.4	124.0	250.2	418.4	502.5	560.4	676.1	763.0	757.3
107.5°	100.9	118.4	135.8	140.2	251.5	399.8	473.9	554.6	716.1	837.2	838.6
110°	113.8	129.5	145.3	149.2	249.6	383.3	450.1	540.4	721.0	856.3	862.2



TEST NUMBER: P936923

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	126.4	141.4	156.5	160.2	249.6	368.9	428.5	520.9	705.6	844.2	853.2
115°	145.5	159.3	173.2	176.6	251.9	352.4	402.6	491.6	669.5	803.0	815.6
117.5°	164.2	176.9	189.4	192.6	256.6	342.0	384.7	465.0	625.6	746.1	760.1
120°	175.2	187.0	198.9	201.9	260.4	338.5	377.5	450.9	597.7	707.7	721.3
122.5°	186.0	197.9	209.8	212.8	265.9	336.6	372.1	438.1	570.3	669.4	682.8
125°	202.4	213.2	224.1	226.8	273.3	335.2	366.1	422.3	534.5	618.7	631.0
127.5°	215.7	226.7	237.7	240.5	280.7	334.3	361.1	409.3	505.7	578.0	588.4
130°	222.8	234.7	246.6	249.5	286.1	334.8	359.2	402.1	487.9	552.3	561.9
132.5°	230.2	242.1	253.9	256.9	290.4	335.2	357.6	396.0	472.8	530.4	539.0
135°	241.2	251.9	262.7	265.4	295.2	334.9	354.7	386.9	451.2	499.4	506.9
137.5°	252.3	263.0	273.7	276.4	302.3	336.9	354.2	381.4	435.7	476.6	482.6
140°	261.6	271.5	281.3	283.7	306.7	337.3	352.6	376.1	423.0	458.2	463.9
142.5°	268.7	277.8	286.9	289.2	310.3	338.5	352.6	373.2	414.4	445.4	450.3
145°	279.7	287.7	295.6	297.6	315.2	338.5	350.2	367.1	400.8	426.1	429.8
147.5°	290.7	298.4	306.2	308.1	322.1	340.8	350.2	363.4	390.0	409.9	413.0
150°	297.8	304.8	311.8	313.5	325.8	342.0	350.2	361.4	383.8	400.6	403.1
152.5°	305.2	310.5	315.8	317.1	328.1	342.8	350.2	359.7	378.9	393.2	395.1
155°	316.2	320.1	323.9	324.9	333.3	344.6	350.2	357.8	373.1	384.5	385.7
157.5°	324.2	328.0	331.9	332.8	338.6	346.3	350.2	356.1	368.0	376.8	377.7
160°	329.7	332.6	335.6	336.3	341.0	347.1	350.2	355.3	365.4	373.1	373.5
162.5°	335.2	337.4	339.6	340.2	343.5	348.0	350.2	354.5	363.1	369.4	369.9
165°	341.1	343.1	345.1	345.7	347.2	349.2	350.2	353.3	359.4	364.0	364.5
167.5°	346.6	347.5	348.5	348.7	350.0	351.7	352.6	354.6	358.6	361.6	361.8
170°	350.2	351.1	352.1	352.4	352.4	352.5	352.6	354.6	358.6	361.6	361.6
172.5°	352.1	352.4	352.5	352.6	352.6	352.6	352.6	354.1	357.3	359.7	359.5
175°	354.7	354.7	354.7	354.7	354.0	353.0	352.6	353.6	355.6	357.0	357.0
177.5°	354.7	354.7	354.7	354.7	354.2	353.4	353.0	353.8	355.4	356.6	356.4
180°	354.7	354.7	354.7	354.7	354.7	354.7	354.7	354.7	354.7	354.7	354.7



TEST NUMBER: P936923

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	607.8	607.8
2.5°	648.9	645.0
5°	834.6	838.5
7.5°	1123.9	1121.9
10°	1397.5	1415.1
12.5°	1596.8	1600.8
15°	1718.0	1725.9
17.5°	1764.9	1766.9
20°	1766.9	1763.0
22.5°	1745.4	1741.5
25°	1719.9	1718.0
27.5°	1696.5	1698.5
30°	1686.8	1692.6
32.5°	1686.8	1696.5
35°	1690.7	1700.5
37.5°	1688.7	1700.5
40°	1680.9	1694.5
42.5°	1659.4	1669.2
45°	1626.2	1637.9
47.5°	1583.2	1591.0
50°	1528.4	1536.2
52.5°	1460.0	1462.0
55°	1377.9	1385.8
57.5°	1290.0	1291.9
60°	1192.3	1198.1
62.5°	1088.7	1088.7
65°	979.2	983.1
67.5°	865.9	875.6
70°	750.5	752.5
72.5°	637.2	637.2
75°	519.9	521.8
77.5°	408.5	408.5
80°	302.9	304.9
82.5°	209.1	213.1
85°	131.0	131.0
87.5°	60.6	54.7
90°	9.0	9.0
92.5°	36.2	29.0
95°	126.3	104.5
97.5°	302.6	261.2
100°	436.1	386.6
102.5°	567.3	524.9
105°	734.6	711.8
107.5°	844.1	849.6
110°	885.9	909.6



TEST NUMBER: P936923

CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	889.7	926.0
115°	866.0	916.5
117.5°	816.0	872.0
120°	775.7	830.1
122.5°	736.5	790.1
125°	680.4	729.9
127.5°	630.1	671.8
130°	600.4	638.9
132.5°	573.5	608.0
135°	536.6	566.3
137.5°	507.0	531.4
140°	486.6	509.4
142.5°	469.9	489.4
145°	444.7	459.5
147.5°	425.3	437.5
150°	413.1	423.0
152.5°	402.6	410.2
155°	390.7	395.6
157.5°	381.2	384.7
160°	375.5	377.5
162.5°	371.8	373.8
165°	366.5	368.5
167.5°	362.7	363.5
170°	361.6	361.6
172.5°	358.7	358.0
175°	357.0	357.0
177.5°	355.6	354.7
180°	354.7	354.7



TEST NUMBER: P936923
 CATALOG NUMBER: SQ4-FB-050U-125D-927-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.03	8.13	7.82	8.94	9.94	20.19	21.29	20.98	22.11	23.11
	3H	7.75	8.74	8.55	9.57	10.59	22.05	23.03	22.84	23.86	24.89
	4H	8.06	9.00	8.88	9.83	10.87	22.70	23.63	23.51	24.47	25.50
	6H	8.32	9.19	9.15	10.03	11.08	23.14	24.00	23.97	24.84	25.90
	8H	8.40	9.22	9.24	10.08	11.14	23.26	24.09	24.10	24.95	26.00
	12H	8.43	9.21	9.27	10.07	11.15	23.34	24.12	24.18	24.98	26.06
4H	2H	14.26	15.20	15.08	16.03	17.07	20.50	21.43	21.32	22.27	23.30
	3H	15.85	16.64	16.69	17.50	18.56	22.56	23.34	23.39	24.21	25.27
	4H	15.96	16.68	16.81	17.54	18.62	23.33	24.05	24.18	24.91	25.99
	6H	15.98	16.61	16.85	17.49	18.58	23.88	24.50	24.74	25.39	26.48
	8H	15.97	16.55	16.83	17.43	18.53	24.05	24.63	24.91	25.51	26.61
	12H	15.94	16.46	16.82	17.36	18.47	24.15	24.68	25.04	25.58	26.68
8H	4H	17.42	18.00	18.29	18.88	19.98	23.41	24.00	24.28	24.88	25.98
	6H	17.67	18.16	18.57	19.08	20.18	24.05	24.53	24.94	25.46	26.56
	8H	17.70	18.12	18.60	19.04	20.16	24.27	24.70	25.17	25.62	26.73
	12H	17.68	18.05	18.58	18.96	20.13	24.42	24.80	25.33	25.71	26.88
12H	4H	17.58	18.10	18.46	19.00	20.11	23.38	23.90	24.27	24.81	25.91
	6H	17.93	18.36	18.84	19.28	20.40	24.04	24.47	24.94	25.38	26.50
	8H	18.02	18.39	18.92	19.30	20.47	24.28	24.65	25.18	25.56	26.73