

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855360

Luminaire Tested: SQ2-PH1-125U-075D-840-UNV-STD-W-4

Issue Date: 7/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P855360  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2-PH1-125U-075D-840-UNV-STD-W-4  
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 750 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9727.7 lumens  
Efficiency: N/A  
Efficacy: 137.8 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.02 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 70.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P855360  
CATALOG NUMBER: SQ2-PH1-125U-075D-840-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P855360

CATALOG NUMBER: SQ2-PH1-125U-075D-840-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																			
1	96	92	88	84	87	84	80	77	68	66	64	55	53	52	42	41	40	34																			
2	87	80	74	69	79	73	68	64	60	57	53	48	46	43	37	35	34	29																			
3	80	70	63	58	72	64	58	53	53	49	45	43	39	37	33	31	29	25																			
4	73	62	55	49	66	57	50	45	47	42	38	38	34	32	29	27	25	21																			
5	67	55	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18																			
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16																			
7	57	45	37	32	52	41	34	29	34	29	25	28	24	21	22	19	17	14																			
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13																			
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	19	16	14	12																			
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	13	11																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	28530	28530	28530
5°	28691	26976	26075
10°	28032	24558	23704
15°	28159	23099	23239
20°	27153	22386	23426
25°	26657	22283	22882
30°	26077	22223	23068
35°	25882	21969	27039
40°	25901	21827	21439
45°	25912	20998	18466
50°	25551	21411	17314
55°	25225	23237	16608
60°	24974	20360	15581
65°	24539	16504	13551
70°	23174	14044	9682
75°	20661	10593	7342
80°	16885	6881	6881
85°	10578	6243	4668

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25912 cd/sqm



TEST NUMBER: P855360

CATALOG NUMBER: SQ2-PH1-125U-075D-840-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.5	1.6
10°-20°	409.0	4.2
20°-30°	599.6	6.2
30°-40°	726.2	7.5
40°-50°	714.1	7.3
50°-60°	621.7	6.4
60°-70°	432.2	4.4
70°-80°	204.9	2.1
80°-90°	46.2	0.5
90°-100°	360.7	3.7
100°-110°	1174.5	12.1
110°-120°	1161.7	11.9
120°-130°	949.4	9.8
130°-140°	775.9	8.0
140°-150°	604.4	6.2
150°-160°	435.6	4.5
160°-170°	266.3	2.7
170°-180°	89.8	0.9
0°-30°	1164.1	12.0
0°-40°	1890.2	19.4
0°-60°	3226.0	33.2
0°-90°	3909.3	40.2
90°-120°	2696.9	27.7
90°-150°	5026.6	51.7
90°-180°	5818.0	59.8
0°-180°	9727.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1767	1767	1767	1767	1767	
5°	1770	1769	1664	1612	1609	166
15°	1685	1500	1382	1372	1390	470
25°	1496	1273	1251	1289	1284	688
35°	1313	1061	1115	1211	1372	822
45°	1135	841	920	952	809	872
55°	896	654	826	595	590	801
65°	642	450	432	355	355	631
75°	331	229	170	121	118	351
85°	57	37	34	27	25	77
90°	0	3	8	7	7	4
95°	49	148	661	236	145	57
105°	200	288	1163	2222	2104	213
115°	369	440	948	1953	2298	365
125°	513	572	935	1542	1818	456
135°	619	684	930	1331	1501	479
145°	724	777	928	1146	1255	453
155°	826	853	934	1026	1065	380
165°	901	909	936	971	982	254
175°	940	940	940	946	944	89
180°	943	943	943	943	943	



TEST NUMBER: P855360

CATALOG NUMBER: SQ2-PH1-125U-075D-840-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1767.0	1767.0	1767.0	1767.0	1767.0
2.5°	1762.9	1781.3	1740.1	1723.9	1721.2
5°	1770.2	1768.6	1664.4	1612.2	1608.8
7.5°	1738.0	1687.0	1562.5	1504.9	1502.3
10°	1709.8	1632.5	1497.9	1445.8	1445.8
12.5°	1703.0	1581.1	1445.4	1407.0	1414.9
15°	1684.6	1500.5	1381.9	1372.3	1390.3
17.5°	1623.4	1425.1	1332.5	1354.5	1375.5
20°	1580.3	1384.7	1302.9	1343.7	1363.4
22.5°	1544.0	1345.8	1281.4	1326.0	1336.6
25°	1496.3	1272.7	1250.8	1289.4	1284.4
27.5°	1439.0	1205.7	1220.2	1243.8	1246.7
30°	1398.7	1165.3	1192.0	1216.0	1237.3
32.5°	1359.8	1118.4	1161.0	1218.0	1266.9
35°	1313.1	1061.4	1114.6	1210.7	1371.8
37.5°	1263.9	994.3	1067.9	1148.7	1200.0
40°	1228.9	946.2	1035.6	1135.5	1017.2
42.5°	1191.3	908.5	987.2	1116.1	916.2
45°	1134.8	840.6	919.6	951.7	808.7
47.5°	1068.2	787.8	873.9	793.6	737.7
50°	1017.2	752.5	852.4	725.5	689.3
52.5°	967.4	715.9	837.6	669.2	644.9
55°	896.1	654.4	825.5	595.1	590.0
57.5°	820.4	591.9	730.0	530.5	539.0
60°	773.4	551.5	630.5	492.4	482.5
62.5°	723.6	512.2	537.6	443.9	434.1
65°	642.3	449.8	432.0	354.7	354.7
67.5°	552.7	385.0	350.0	290.3	250.8
70°	490.9	343.0	297.5	231.4	205.1
72.5°	425.0	298.1	243.8	189.6	159.4
75°	331.2	229.2	169.8	121.0	117.7
77.5°	239.4	165.1	114.3	89.7	90.1
80°	181.6	125.6	74.0	72.4	74.0
82.5°	127.7	86.4	55.1	57.5	57.8
85°	57.1	37.4	33.7	26.8	25.2
87.5°	12.1	11.4	8.4	8.2	8.2
90°	0.0	3.4	8.2	7.0	7.0
92.5°	16.7	60.0	191.8	63.3	48.7
95°	48.7	148.5	661.1	235.8	145.0
97.5°	91.6	193.2	1122.2	683.4	417.1
100°	119.5	219.3	1295.7	1155.4	749.4
102.5°	151.0	247.2	1274.4	1709.3	1299.7
105°	199.5	288.0	1163.4	2222.1	2104.1
107.5°	252.0	335.2	1058.1	2266.6	2391.6
110°	290.0	365.9	1008.0	2211.3	2437.1



TEST NUMBER: P855360

CATALOG NUMBER: SQ2-PH1-125U-075D-840-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	321.5	396.6	976.5	2111.7	2402.7
115°	368.8	440.3	947.7	1953.1	2297.8
117.5°	417.6	482.0	936.5	1807.8	2151.0
120°	445.4	508.9	933.7	1718.5	2050.8
122.5°	472.3	534.9	934.7	1641.0	1950.5
125°	512.7	571.6	934.9	1542.1	1817.7
127.5°	547.3	607.6	934.7	1467.9	1697.8
130°	569.5	630.8	933.7	1425.6	1630.9
132.5°	589.0	653.0	932.8	1386.4	1578.9
135°	619.4	684.1	930.3	1330.9	1501.0
137.5°	649.1	714.2	927.8	1274.5	1425.6
140°	670.5	732.8	926.8	1236.3	1379.1
142.5°	690.8	750.5	926.8	1199.8	1327.3
145°	723.8	777.1	928.0	1146.2	1255.0
147.5°	755.9	802.1	929.6	1100.6	1184.7
150°	777.2	818.0	931.4	1073.5	1144.9
152.5°	798.5	832.1	932.3	1052.7	1109.6
155°	825.9	853.1	933.7	1026.3	1064.8
157.5°	851.9	871.4	935.1	1006.8	1033.7
160°	867.6	883.5	936.1	994.6	1016.1
162.5°	881.5	893.9	936.1	984.3	1000.4
165°	901.3	909.2	936.1	971.1	982.4
167.5°	915.2	920.2	936.3	961.2	967.2
170°	924.5	926.7	937.2	954.7	956.9
172.5°	931.0	932.3	939.1	951.0	950.5
175°	939.5	939.5	939.5	946.4	944.2
177.5°	943.0	942.1	941.2	945.7	942.1
180°	943.0	943.0	943.0	943.0	943.0

TEST NUMBER: P855360

CATALOG NUMBER: SQ2-PH1-125U-075D-840-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.99	18.76	19.03	19.81	21.21	16.66	17.44	17.70	18.48	19.88
	3H	20.01	20.70	21.06	21.75	23.18	17.69	18.38	18.74	19.43	20.86
	4H	20.73	21.39	21.79	22.44	23.88	17.90	18.55	18.96	19.61	21.04
	6H	21.21	21.82	22.28	22.88	24.32	18.04	18.64	19.11	19.70	21.14
	8H	21.34	21.91	22.41	22.98	24.42	18.07	18.64	19.14	19.72	21.15
	12H	21.38	21.92	22.46	22.99	24.45	18.06	18.61	19.14	19.68	21.14
4H	2H	18.35	19.01	19.42	20.06	21.49	17.29	17.95	18.36	19.00	20.43
	3H	20.45	21.00	21.53	22.08	23.52	18.46	19.01	19.54	20.09	21.54
	4H	21.26	21.76	22.34	22.83	24.30	18.73	19.23	19.82	20.31	21.77
	6H	21.84	22.27	22.93	23.37	24.83	18.94	19.37	20.03	20.46	21.92
	8H	22.01	22.41	23.10	23.50	24.97	18.99	19.39	20.08	20.48	21.96
	12H	22.07	22.43	23.18	23.54	25.02	19.00	19.36	20.10	20.46	21.94
8H	4H	21.27	21.67	22.36	22.76	24.24	18.94	19.34	20.03	20.43	21.91
	6H	21.92	22.25	23.03	23.38	24.85	19.21	19.54	20.32	20.67	22.15
	8H	22.14	22.43	23.26	23.55	25.04	19.31	19.60	20.43	20.72	22.21
	12H	22.25	22.51	23.38	23.62	25.15	19.35	19.61	20.48	20.72	22.25
12H	4H	21.22	21.58	22.33	22.68	24.16	18.94	19.30	20.04	20.40	21.88
	6H	21.89	22.18	23.01	23.29	24.79	19.24	19.53	20.36	20.64	22.14
	8H	22.12	22.38	23.24	23.48	25.01	19.35	19.61	20.48	20.72	22.25