

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519644

Luminaire Tested: **SQ4-025U-0D-830-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519644  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-025U-0D-830-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 911.7 lumens  
Efficiency: N/A  
Efficacy: 154.5 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 5.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519644  
CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P519644

CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10				
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8				
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7				
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6				
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5				
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4				
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4				
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3				
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3				
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3				
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	953	12502	4393
100°	1100	10350	8145
105°	1159	7105	10060
110°	1217	4815	9730
115°	1260	3484	7933
120°	1281	2762	6073
125°	1292	2336	4655
130°	1269	2045	3637
135°	1247	1836	2929
140°	1249	1684	2433
145°	1249	1564	2051
150°	1258	1480	1787
155°	1276	1414	1597
160°	1283	1364	1470
165°	1292	1327	1395
170°	1301	1310	1343
175°	1303	1295	1311



TEST NUMBER: P519644

CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	68.6	7.5
100°-110°	180.2	19.8
110°-120°	186.9	20.5
120°-130°	149.9	16.4
130°-140°	117.6	12.9
140°-150°	90.3	9.9
150°-160°	65.0	7.1
160°-170°	39.8	4.4
170°-180°	13.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	435.7	47.8
90°-150°	793.5	87.0
90°-180°	912.0	100.0
0°-180°	911.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	3	7	4	4	
95°	9	36	118	61	42	11
105°	32	49	199	302	282	34
115°	58	70	160	318	363	57
125°	80	90	145	245	289	71
135°	96	105	141	198	224	74
145°	111	118	139	169	182	69
155°	125	129	139	152	157	58
165°	135	137	139	144	146	38
175°	141	141	140	142	142	13
180°	141	141	141	141	141	



TEST NUMBER: P519644

CATALOG NUMBER: SQ4-025U-0D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	0.9	2.7	7.2	3.6	3.6
92.5°	3.8	18.2	40.4	17.9	11.5
95°	9.0	35.5	118.1	60.9	41.5
97.5°	15.7	39.0	176.7	140.5	103.5
100°	20.7	41.9	194.8	197.4	153.3
102.5°	25.1	44.8	199.8	245.8	208.1
105°	32.5	49.2	199.3	302.5	282.2
107.5°	40.0	55.6	187.9	331.9	336.9
110°	45.1	59.2	178.5	339.5	360.7
112.5°	50.1	63.5	169.9	334.7	367.2
115°	57.7	70.1	159.6	318.4	363.4
117.5°	65.1	76.4	152.6	295.8	345.7
120°	69.4	80.0	149.7	280.6	329.1
122.5°	73.8	84.3	147.5	265.5	313.2
125°	80.3	89.9	145.2	245.4	289.4
127.5°	85.5	95.4	143.2	229.2	266.4
130°	88.4	98.9	142.5	219.0	253.4
132.5°	91.3	101.8	141.7	210.3	241.1
135°	95.6	105.3	140.7	198.1	224.5
137.5°	100.1	109.6	140.5	188.9	210.6
140°	103.7	112.5	139.8	181.7	202.0
142.5°	106.6	114.7	139.8	176.6	194.0
145°	110.9	118.0	138.9	168.9	182.1
147.5°	115.2	122.1	138.9	162.6	173.5
150°	118.1	124.3	138.9	158.9	167.7
152.5°	121.0	125.8	138.9	156.0	162.7
155°	125.3	128.9	138.9	152.5	156.9
157.5°	128.6	131.9	138.9	149.4	152.6
160°	130.7	133.4	138.9	147.9	149.7
162.5°	132.9	134.8	138.9	146.5	148.2
165°	135.3	137.0	138.9	144.3	146.1
167.5°	137.4	138.3	139.8	143.4	144.1
170°	138.9	139.7	139.8	143.4	143.4
172.5°	139.6	139.8	139.8	142.6	141.9
175°	140.7	140.7	139.8	141.6	141.6
177.5°	140.7	140.7	139.9	141.4	140.7
180°	140.7	140.7	140.7	140.7	140.7

(END OF REPORT)