

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519668

Luminaire Tested: **SQ4-050U-0D-830-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519668  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-050U-0D-830-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1880.1 lumens  
Efficiency: N/A  
Efficacy: 152.9 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 12.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519668  
CATALOG NUMBER: SQ4-050U-0D-830-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P519668

CATALOG NUMBER: SQ4-050U-0D-830-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	0
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	0

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	2160	25480	7452
100°	2263	21694	17762
105°	2378	14722	21093
110°	2522	10016	20108
115°	2587	7215	16354
120°	2631	5707	12557
125°	2622	4811	9561
130°	2592	4226	7482
135°	2561	3793	6041
140°	2553	3479	5007
145°	2554	3233	4224
150°	2594	3048	3669
155°	2611	2903	3280
160°	2636	2800	3037
165°	2653	2733	2857
170°	2663	2689	2750
175°	2667	2658	2684



TEST NUMBER: P519668

CATALOG NUMBER: SQ4-050U-0D-830-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	138.2	7.4
100°-110°	375.5	20.0
110°-120°	386.1	20.5
120°-130°	308.7	16.4
130°-140°	242.5	12.9
140°-150°	186.0	9.9
150°-160°	133.7	7.1
160°-170°	81.8	4.4
170°-180°	27.6	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	899.8	47.9
90°-150°	1637.0	87.1
90°-180°	1880.0	100.0
0°-180°	1880.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	1	4	6	8	8	
95°	20	76	241	105	70	23
105°	67	104	413	629	592	71
115°	118	144	330	658	749	117
125°	163	186	299	504	594	145
135°	196	218	291	410	463	152
145°	227	243	287	349	375	142
155°	256	266	285	313	322	118
165°	278	281	286	298	299	78
175°	288	289	287	291	290	27
180°	288	288	288	288	288	



TEST NUMBER: P519668

CATALOG NUMBER: SQ4-050U-0D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	0.9	3.6	6.5	8.3	8.3
92.5°	8.3	37.8	65.7	28.2	23.9
95°	20.4	75.6	240.7	104.8	70.4
97.5°	33.7	83.5	369.1	287.1	201.7
100°	42.6	88.8	408.3	413.9	334.3
102.5°	51.5	94.0	418.7	511.9	441.7
105°	66.7	103.8	413.0	628.8	591.7
107.5°	82.4	115.2	389.1	689.1	699.4
110°	93.5	123.4	371.3	701.0	745.4
112.5°	103.1	131.6	353.5	691.1	757.9
115°	118.5	143.9	330.5	657.6	749.1
117.5°	133.0	157.2	315.9	610.1	713.1
120°	142.6	166.1	309.3	578.2	680.5
122.5°	150.7	174.3	304.8	546.3	645.0
125°	163.0	185.6	299.1	503.9	594.4
127.5°	173.9	196.3	295.9	471.8	549.4
130°	180.6	202.3	294.4	451.6	521.3
132.5°	187.2	208.9	293.0	434.4	496.1
135°	196.3	218.0	290.7	410.4	463.0
137.5°	206.1	225.8	289.6	389.3	433.5
140°	212.0	231.0	288.9	375.9	415.7
142.5°	218.0	235.5	288.1	365.4	398.7
145°	226.8	243.1	287.0	348.7	375.0
147.5°	236.8	250.8	286.1	335.6	356.3
150°	243.5	255.3	286.1	328.1	344.4
152.5°	248.7	259.0	285.4	321.4	334.8
155°	256.5	265.5	285.2	313.2	322.2
157.5°	264.1	271.1	285.2	307.6	314.4
160°	268.5	274.9	285.2	303.8	309.3
162.5°	273.0	277.8	285.9	300.8	304.8
165°	277.8	281.4	286.1	298.2	299.1
167.5°	282.8	284.6	287.0	295.0	295.7
170°	284.3	286.1	287.0	293.5	293.5
172.5°	285.7	286.8	287.0	292.0	292.0
175°	288.0	288.9	287.0	290.7	289.8
177.5°	288.7	288.7	286.5	289.4	288.0
180°	288.0	288.0	288.0	288.0	288.0

(END OF REPORT)