

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855353

Luminaire Tested: SQ2-PP3-025U-050D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855353
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-9, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PP3-025U-050D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3955.5 lumens
Efficiency: N/A
Efficacy: 157.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 25.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855353

CATALOG NUMBER: SQ2-PP3-025U-050D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855353

CATALOG NUMBER: SQ2-PP3-025U-050D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70				
1	103	99	95	92	97	94	91	88	84	82	79	75	74	72	67	66	65	61				
2	94	87	81	76	89	83	78	73	75	71	67	67	64	61	60	58	56	52				
3	87	77	70	64	82	74	67	62	66	61	57	60	56	52	54	51	48	45				
4	80	69	61	55	75	66	59	53	59	54	49	54	49	45	48	45	42	39				
5	73	62	54	48	69	59	51	46	53	47	43	48	44	40	44	40	37	34				
6	68	56	47	42	64	53	46	40	48	42	38	44	39	35	40	36	33	30				
7	63	50	42	37	59	48	41	36	44	38	33	40	35	31	36	32	29	27				
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	34	29	26	24				
9	54	42	34	29	52	40	33	29	37	31	27	34	29	25	31	27	24	22				
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	25	21	20				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17801	17801	17801
5°	17661	17812	17982
10°	17751	17884	18113
15°	17707	17882	18156
20°	17581	18002	18522
25°	17482	18228	19495
30°	17381	18599	19902
35°	17136	18652	19939
40°	16678	18619	18423
45°	16180	17776	14024
50°	15543	15164	11680
55°	14466	12760	8397
60°	12455	10950	6022
65°	10506	8458	5922
70°	8748	6656	5665
75°	7417	5745	5309
80°	6285	4984	4770
85°	4965	4094	2594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 17776 cd/sqm



TEST NUMBER: P855353

CATALOG NUMBER: SQ2-PP3-025U-050D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.0	2.7
10°-20°	303.8	7.7
20°-30°	476.0	12.0
30°-40°	587.1	14.8
40°-50°	552.8	14.0
50°-60°	391.4	9.9
60°-70°	223.0	5.6
70°-80°	110.3	2.8
80°-90°	27.4	0.7
90°-100°	76.8	1.9
100°-110°	239.0	6.0
110°-120°	233.8	5.9
120°-130°	190.9	4.8
130°-140°	156.2	3.9
140°-150°	121.9	3.1
150°-160°	88.0	2.2
160°-170°	53.8	1.4
170°-180°	18.1	0.5
0°-30°	884.8	22.4
0°-40°	1471.9	37.2
0°-60°	2416.1	61.1
0°-90°	2776.9	70.2
90°-120°	549.7	13.9
90°-150°	1018.7	25.8
90°-180°	1179.0	29.8
0°-180°	3955.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1102	1102	1102	1102	1102	
5°	1090	1109	1099	1102	1110	104
15°	1059	1074	1070	1080	1086	299
25°	981	1006	1023	1065	1094	452
35°	869	893	946	1000	1012	542
45°	709	762	778	660	614	545
55°	514	545	453	342	298	453
65°	275	290	221	156	155	276
75°	119	132	92	86	85	129
85°	27	24	22	17	14	31
90°	0	1	4	4	4	2
95°	10	31	141	52	34	12
105°	42	59	235	449	429	44
115°	75	88	191	394	461	74
125°	104	115	189	310	364	92
135°	125	138	188	268	301	97
145°	146	157	188	231	252	91
155°	167	172	189	208	214	77
165°	183	184	190	196	198	51
175°	190	190	190	191	190	18
180°	190	190	190	190	190	



TEST NUMBER: P855353

CATALOG NUMBER: SQ2-PP3-025U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1102.5	1102.5	1102.5	1102.5	1102.5
2.5°	1094.1	1109.6	1099.7	1101.5	1103.4
5°	1089.7	1109.0	1099.0	1101.5	1109.5
7.5°	1085.5	1105.3	1095.5	1099.7	1109.5
10°	1082.7	1099.8	1090.8	1096.9	1104.8
12.5°	1074.3	1090.5	1082.4	1090.2	1097.3
15°	1059.3	1074.2	1069.8	1080.4	1086.2
17.5°	1039.1	1057.1	1057.0	1072.1	1078.0
20°	1023.2	1044.9	1047.7	1066.6	1078.0
22.5°	1006.4	1031.7	1036.5	1064.9	1084.5
25°	981.3	1006.3	1023.2	1064.7	1094.3
27.5°	951.9	976.7	1011.6	1058.1	1081.5
30°	932.3	956.2	997.6	1045.8	1067.5
32.5°	908.1	932.9	977.1	1029.0	1048.9
35°	869.4	893.3	946.3	1000.1	1011.6
37.5°	824.9	852.0	911.3	941.4	942.1
40°	791.3	826.6	883.4	888.9	874.1
42.5°	758.7	804.0	844.2	819.6	753.8
45°	708.6	762.2	778.5	659.7	614.2
47.5°	655.2	708.1	682.0	553.3	521.9
50°	618.8	668.9	603.7	494.6	465.0
52.5°	577.8	622.4	533.8	438.3	393.2
55°	513.9	544.7	453.3	341.7	298.3
57.5°	437.0	458.7	387.6	256.5	207.9
60°	385.7	402.9	339.1	210.4	186.5
62.5°	339.1	354.4	288.8	182.7	174.3
65°	275.0	289.8	221.4	156.2	155.0
67.5°	218.9	235.1	169.9	136.4	135.0
70°	185.3	202.4	141.0	122.4	120.0
72.5°	157.3	173.5	119.6	107.4	106.1
75°	118.9	131.5	92.1	86.2	85.1
77.5°	86.2	94.2	68.5	65.5	64.3
80°	67.6	71.0	53.6	52.4	51.3
82.5°	50.8	49.6	40.6	39.4	37.3
85°	26.8	24.5	22.1	17.4	14.0
87.5°	8.4	8.6	4.4	3.5	3.5
90°	0.0	1.2	3.5	3.5	3.5
92.5°	3.7	13.1	44.5	14.6	11.9
95°	10.5	31.0	141.0	52.0	33.8
97.5°	19.1	40.3	233.4	145.3	91.6
100°	25.6	45.0	263.3	246.2	164.3
102.5°	32.2	50.6	257.7	351.7	276.1
105°	42.0	59.1	235.3	449.3	428.8
107.5°	51.7	67.7	213.9	456.7	479.3
110°	58.3	74.2	202.7	446.0	490.5



TEST NUMBER: P855353

CATALOG NUMBER: SQ2-PP3-025U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	64.8	79.8	197.1	426.8	483.1
115°	74.6	88.2	191.0	394.1	461.4
117.5°	84.1	96.6	188.4	362.9	431.8
120°	89.7	102.2	187.5	345.2	411.3
122.5°	95.3	107.8	188.4	330.2	390.8
125°	103.7	115.0	188.7	310.0	363.5
127.5°	110.5	122.0	188.7	294.8	340.4
130°	114.2	126.7	188.7	286.3	327.4
132.5°	118.9	131.3	187.7	278.9	317.1
135°	124.7	138.3	187.5	267.6	300.6
137.5°	131.5	143.9	187.5	256.3	286.3
140°	135.2	147.7	187.5	248.8	276.1
142.5°	139.8	151.4	187.5	241.2	265.8
145°	145.7	157.0	187.5	231.1	251.6
147.5°	152.7	162.5	188.7	221.8	237.9
150°	157.3	165.3	188.7	217.0	229.5
152.5°	161.1	168.1	188.7	212.2	222.9
155°	166.7	172.2	188.7	207.6	214.3
157.5°	172.2	176.6	188.7	203.2	207.6
160°	176.0	179.4	188.7	200.4	203.8
162.5°	178.7	181.2	188.7	198.6	201.0
165°	182.9	184.0	189.8	195.8	198.0
167.5°	185.4	185.6	188.7	194.2	195.2
170°	186.3	187.5	188.7	192.3	193.3
172.5°	188.2	188.4	189.6	191.4	191.5
175°	189.8	189.8	189.8	191.0	189.8
177.5°	189.8	189.8	189.8	189.8	189.8
180°	189.8	189.8	189.8	189.8	189.8



TEST NUMBER: P855353

CATALOG NUMBER: SQ2-PP3-025U-050D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	19.25	20.28	20.02	21.07	22.02	15.65	16.68	16.42	17.46	18.42
	3H	20.36	21.28	21.14	22.08	23.06	16.77	17.69	17.55	18.48	19.47
	4H	20.71	21.58	21.51	22.38	23.38	17.24	18.10	18.04	18.91	19.90
	6H	20.94	21.73	21.75	22.54	23.55	17.59	18.39	18.41	19.20	20.21
	8H	20.99	21.75	21.81	22.58	23.59	17.68	18.44	18.51	19.27	20.28
	12H	21.01	21.73	21.84	22.55	23.59	17.70	18.42	18.53	19.25	20.28
4H	2H	19.38	20.25	20.19	21.05	22.05	16.38	17.25	17.19	18.05	19.05
	3H	20.71	21.42	21.52	22.26	23.27	17.65	18.37	18.47	19.20	20.22
	4H	21.19	21.84	22.02	22.67	23.71	18.21	18.86	19.04	19.70	20.74
	6H	21.53	22.09	22.38	22.96	24.00	18.66	19.22	19.51	20.08	21.13
	8H	21.63	22.15	22.48	23.01	24.07	18.79	19.31	19.64	20.16	21.22
	12H	21.67	22.14	22.54	23.02	24.08	18.82	19.29	19.69	20.17	21.23
8H	4H	21.22	21.74	22.07	22.60	23.65	18.50	19.02	19.35	19.88	20.93
	6H	21.66	22.09	22.53	22.99	24.04	19.05	19.48	19.93	20.38	21.44
	8H	21.81	22.20	22.70	23.09	24.16	19.23	19.62	20.12	20.51	21.59
	12H	21.91	22.24	22.80	23.13	24.26	19.32	19.65	20.21	20.54	21.67
12H	4H	21.18	21.65	22.05	22.53	23.59	18.51	18.98	19.38	19.86	20.92
	6H	21.64	22.03	22.53	22.92	24.00	19.10	19.49	19.99	20.38	21.45
	8H	21.82	22.16	22.71	23.05	24.17	19.32	19.66	20.21	20.54	21.67