

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P519764

Luminaire Tested: **SQ4-150U-0D-830-1D-UNV-STD-W-4**

Issue Date: 4/29/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P519764  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 4/29/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-150U-0D-830-1D-UNV-STD-W-4  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5686.0 lumens  
Efficiency: N/A  
Efficacy: 143.9 lumens/watt  
N/A  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 39.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P519764  
CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P519764

CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0																
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0																
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0																
3	72	63	57	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0																
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0																
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0																
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0																
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0																
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0																
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0																
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
95°	6733	72153	22209
100°	6960	62743	52908
105°	7343	43821	61994
110°	7707	30423	58464
115°	7916	22259	48640
120°	8023	17570	38064
125°	7986	14781	29303
130°	7861	12971	22960
135°	7766	11667	18493
140°	7751	10701	15321
145°	7794	9933	12991
150°	7869	9335	11277
155°	7954	8900	10109
160°	8062	8594	9293
165°	8125	8387	8759
170°	8155	8236	8431
175°	8177	8142	8229



TEST NUMBER: P519764

CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	409.8	7.2
100°-110°	1108.2	19.5
110°-120°	1165.1	20.5
120°-130°	946.4	16.6
130°-140°	742.3	13.1
140°-150°	569.7	10.0
150°-160°	409.7	7.2
160°-170°	250.3	4.4
170°-180°	84.4	1.5
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.0	0.0
90°-120°	2683.1	47.2
90°-150°	4941.5	86.9
90°-180°	5686.0	100.0
0°-180°	5686.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
90°	2	6	12	13	12	
95°	64	223	682	353	210	71
105°	206	318	1229	1813	1739	217
115°	363	443	1020	1974	2228	358
125°	496	569	919	1551	1822	443
135°	595	666	894	1252	1417	460
145°	692	744	882	1072	1153	433
155°	781	812	874	961	993	360
165°	851	859	878	912	917	240
175°	883	882	879	890	888	84
180°	882	882	882	882	882	



TEST NUMBER: P519764

CATALOG NUMBER: SQ4-150U-0D-830-1D-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
90°	1.9	5.6	12.3	13.3	12.3
92.5°	27.0	98.2	193.8	84.2	60.9
95°	63.6	223.3	681.6	352.7	209.8
97.5°	102.1	256.0	1062.5	879.3	645.7
100°	131.0	269.3	1180.9	1231.6	995.8
102.5°	157.6	287.7	1222.7	1498.7	1322.4
105°	206.0	318.3	1229.3	1813.4	1739.1
107.5°	250.8	353.3	1175.6	2009.7	2034.4
110°	285.7	378.6	1127.8	2062.4	2167.3
112.5°	316.9	403.8	1083.7	2051.8	2228.0
115°	362.6	443.4	1019.6	1973.7	2228.0
117.5°	407.4	483.2	977.2	1854.3	2142.6
120°	434.8	509.0	952.2	1768.6	2062.8
122.5°	460.6	533.4	937.0	1676.8	1973.2
125°	496.5	568.9	918.9	1550.7	1821.7
127.5°	529.5	600.6	908.3	1447.8	1686.2
130°	547.7	621.1	903.7	1384.2	1599.6
132.5°	566.7	639.3	899.2	1326.9	1525.2
135°	595.2	665.8	894.2	1252.1	1417.3
137.5°	623.9	690.5	890.1	1191.4	1326.0
140°	643.6	705.8	888.5	1152.3	1272.1
142.5°	662.6	721.1	885.5	1117.1	1221.9
145°	692.0	744.0	881.9	1071.7	1153.4
147.5°	718.8	764.9	877.7	1030.7	1093.4
150°	738.6	779.4	876.2	1008.4	1058.5
152.5°	756.8	792.4	875.4	987.6	1028.9
155°	781.3	811.9	874.3	961.4	993.0
157.5°	806.7	828.1	874.5	943.1	963.9
160°	821.1	838.8	875.3	931.6	946.5
162.5°	832.5	847.2	876.0	922.4	933.5
165°	850.6	858.9	878.1	912.4	917.0
167.5°	862.9	868.7	878.3	903.8	906.0
170°	870.5	873.3	879.1	899.9	899.9
172.5°	876.6	877.1	879.1	895.4	894.6
175°	882.9	881.9	879.1	890.4	888.5
177.5°	884.9	882.7	878.9	886.4	884.2
180°	881.9	881.9	881.9	881.9	881.9

(END OF REPORT)