

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P855333

Luminaire Tested: SQ2-PP3-125U-050D-840-UNV-STD-W-4

Issue Date: 7/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P855333
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2104-222-13, G2-2308-131-7)
Test Lab: INNOVATION CENTER
Issue Date: 7/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2-PP3-125U-050D-840-UNV-STD-W-4
Description: CORELITE SQ2 SUSPENDED LED LUMINAIRE
DOWNLIGHT 500 LUMENS PER FOOT
UPLIGHT 1250 LUMENS PER FOOT
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8622.6 lumens
Efficiency: N/A
Efficacy: 139.7 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.41 / 1.4
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 61.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P855333

CATALOG NUMBER: SQ2-PP3-125U-050D-840-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P855333

CATALOG NUMBER: SQ2-PP3-125U-050D-840-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32				
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				
2	86	79	73	68	77	71	67	62	57	54	51	44	42	40	32	30	29	24				
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25	21				
4	72	62	54	48	65	56	50	45	45	40	37	35	32	29	26	24	22	18				
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19	16				
6	61	49	41	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14				
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12				
8	52	40	33	28	47	37	30	26	30	25	22	24	20	17	18	15	14	11				
9	48	37	29	25	43	33	27	23	27	23	19	22	18	16	16	14	12	10				
10	45	33	26	22	41	31	24	20	25	20	17	20	16	14	15	13	11	9				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17801	17801	17801
5°	17661	17812	17982
10°	17751	17884	18113
15°	17707	17882	18156
20°	17581	18002	18522
25°	17482	18228	19495
30°	17381	18599	19902
35°	17136	18652	19939
40°	16678	18619	18423
45°	16180	17776	14024
50°	15543	15164	11680
55°	14466	12760	8397
60°	12455	10950	6022
65°	10506	8458	5922
70°	8748	6656	5665
75°	7417	5745	5309
80°	6285	4984	4770
85°	4965	4094	2594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 17776 cd/sqm



TEST NUMBER: P855333

CATALOG NUMBER: SQ2-PP3-125U-050D-840-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.0	1.2
10°-20°	303.8	3.5
20°-30°	476.0	5.5
30°-40°	587.1	6.8
40°-50°	552.8	6.4
50°-60°	391.4	4.5
60°-70°	223.0	2.6
70°-80°	110.3	1.3
80°-90°	28.0	0.3
90°-100°	362.4	4.2
100°-110°	1179.8	13.7
110°-120°	1167.1	13.5
120°-130°	953.7	11.1
130°-140°	779.5	9.0
140°-150°	607.1	7.0
150°-160°	437.6	5.1
160°-170°	267.5	3.1
170°-180°	90.3	1.0
0°-30°	884.8	10.3
0°-40°	1471.9	17.1
0°-60°	2416.1	28.0
0°-90°	2777.5	32.2
90°-120°	2709.3	31.4
90°-150°	5049.7	58.6
90°-180°	5845.0	67.8
0°-180°	8622.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1102	1102	1102	1102	1102	
5°	1090	1109	1099	1102	1110	104
15°	1059	1074	1070	1080	1086	299
25°	981	1006	1023	1065	1094	452
35°	869	893	946	1000	1012	542
45°	709	762	778	660	614	545
55°	514	545	453	342	298	453
65°	275	290	221	156	155	276
75°	119	132	92	86	85	129
85°	27	24	22	17	14	31
90°	0	3	8	7	7	3
95°	49	149	664	237	146	57
105°	200	289	1169	2232	2114	214
115°	371	442	952	1962	2308	367
125°	515	574	939	1549	1826	458
135°	622	687	934	1337	1508	481
145°	727	781	932	1151	1261	455
155°	830	857	938	1031	1070	382
165°	905	913	940	976	987	255
175°	944	944	944	951	948	90
180°	947	947	947	947	947	



TEST NUMBER: P855333

CATALOG NUMBER: SQ2-PP3-125U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1102.5	1102.5	1102.5	1102.5	1102.5
2.5°	1094.1	1109.6	1099.7	1101.5	1103.4
5°	1089.7	1109.0	1099.0	1101.5	1109.5
7.5°	1085.5	1105.3	1095.5	1099.7	1109.5
10°	1082.7	1099.8	1090.8	1096.9	1104.8
12.5°	1074.3	1090.5	1082.4	1090.2	1097.3
15°	1059.3	1074.2	1069.8	1080.4	1086.2
17.5°	1039.1	1057.1	1057.0	1072.1	1078.0
20°	1023.2	1044.9	1047.7	1066.6	1078.0
22.5°	1006.4	1031.7	1036.5	1064.9	1084.5
25°	981.3	1006.3	1023.2	1064.7	1094.3
27.5°	951.9	976.7	1011.6	1058.1	1081.5
30°	932.3	956.2	997.6	1045.8	1067.5
32.5°	908.1	932.9	977.1	1029.0	1048.9
35°	869.4	893.3	946.3	1000.1	1011.6
37.5°	824.9	852.0	911.3	941.4	942.1
40°	791.3	826.6	883.4	888.9	874.1
42.5°	758.7	804.0	844.2	819.6	753.8
45°	708.6	762.2	778.5	659.7	614.2
47.5°	655.2	708.1	682.0	553.3	521.9
50°	618.8	668.9	603.7	494.6	465.0
52.5°	577.8	622.4	533.8	438.3	393.2
55°	513.9	544.7	453.3	341.7	298.3
57.5°	437.0	458.7	387.6	256.5	207.9
60°	385.7	402.9	339.1	210.4	186.5
62.5°	339.1	354.4	288.8	182.7	174.3
65°	275.0	289.8	221.4	156.2	155.0
67.5°	218.9	235.1	169.9	136.4	135.0
70°	185.3	202.4	141.0	122.4	120.0
72.5°	157.3	173.5	119.6	107.4	106.1
75°	118.9	131.5	92.1	86.2	85.1
77.5°	86.2	94.2	68.5	65.5	64.3
80°	67.6	71.0	53.6	52.4	51.3
82.5°	50.8	49.6	40.6	39.4	37.3
85°	26.8	24.5	22.1	17.4	14.0
87.5°	8.4	9.1	5.4	4.2	4.2
90°	0.0	3.4	8.2	7.0	7.0
92.5°	16.8	60.3	192.8	63.5	48.9
95°	48.9	149.2	664.2	236.8	145.7
97.5°	92.1	194.2	1127.3	686.5	419.1
100°	120.0	220.3	1301.6	1160.6	752.7
102.5°	151.7	248.3	1280.2	1717.1	1305.6
105°	200.4	289.3	1168.8	2232.3	2113.8
107.5°	253.1	336.7	1063.0	2277.0	2402.6
110°	291.4	367.7	1012.6	2221.5	2448.3



TEST NUMBER: P855333

CATALOG NUMBER: SQ2-PP3-125U-050D-840-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	323.0	398.5	980.9	2121.4	2413.8
115°	370.6	442.4	952.0	1962.1	2308.4
117.5°	419.5	484.2	940.8	1816.0	2160.9
120°	447.5	511.3	938.0	1726.3	2060.2
122.5°	474.6	537.4	939.0	1648.5	1959.5
125°	515.0	574.3	939.2	1549.1	1826.0
127.5°	549.7	610.4	939.0	1474.7	1705.4
130°	572.1	633.6	938.0	1432.2	1638.3
132.5°	591.7	656.0	937.1	1392.7	1586.1
135°	622.2	687.2	934.5	1336.9	1507.9
137.5°	652.0	717.5	932.0	1280.3	1432.2
140°	673.5	736.2	931.0	1242.0	1385.5
142.5°	694.0	754.0	931.0	1205.3	1333.3
145°	727.1	780.7	932.2	1151.4	1260.8
147.5°	759.3	805.8	933.8	1105.6	1190.2
150°	780.7	821.7	935.7	1078.3	1150.1
152.5°	802.1	835.9	936.6	1057.5	1114.7
155°	829.6	857.0	938.0	1031.0	1069.7
157.5°	855.8	875.3	939.4	1011.3	1038.5
160°	871.6	887.6	940.4	999.1	1020.8
162.5°	885.6	897.9	940.4	988.7	1004.9
165°	905.4	913.4	940.4	975.6	987.0
167.5°	919.4	924.4	940.6	965.7	971.6
170°	928.7	931.0	941.5	959.1	961.3
172.5°	935.2	936.6	943.4	955.3	954.8
175°	943.9	943.9	943.9	950.9	948.5
177.5°	947.4	946.4	945.5	950.0	946.4
180°	947.4	947.4	947.4	947.4	947.4



TEST NUMBER: P855333

CATALOG NUMBER: SQ2-PP3-125U-050D-840-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.61	16.31	16.71	17.41	18.92	12.01	12.71	13.11	13.81	15.31
	3H	16.69	17.32	17.80	18.42	19.95	13.10	13.73	14.21	14.83	16.35
	4H	17.03	17.62	18.15	18.73	20.26	13.55	14.15	14.67	15.25	16.78
	6H	17.24	17.78	18.36	18.89	20.43	13.89	14.44	15.02	15.55	17.09
	8H	17.28	17.80	18.41	18.92	20.46	13.97	14.49	15.11	15.62	17.15
	12H	17.29	17.78	18.42	18.90	20.46	13.98	14.48	15.12	15.59	17.15
4H	2H	15.70	16.29	16.83	17.40	18.93	12.70	13.30	13.83	14.40	15.93
	3H	16.99	17.49	18.13	18.62	20.16	13.94	14.43	15.07	15.56	17.10
	4H	17.46	17.91	18.60	19.03	20.60	14.48	14.94	15.62	16.06	17.62
	6H	17.79	18.18	18.93	19.32	20.87	14.92	15.30	16.06	16.45	18.00
	8H	17.88	18.24	19.02	19.38	20.95	15.03	15.40	16.18	16.53	18.10
	12H	17.91	18.24	19.07	19.38	20.96	15.06	15.38	16.21	16.53	18.10
8H	4H	17.47	17.83	18.61	18.96	20.53	14.75	15.11	15.89	16.24	17.81
	6H	17.89	18.19	19.06	19.37	20.93	15.29	15.59	16.45	16.76	18.33
	8H	18.05	18.31	19.22	19.47	21.05	15.47	15.73	16.64	16.89	18.48
	12H	18.13	18.36	19.30	19.51	21.13	15.54	15.77	16.71	16.92	18.54
12H	4H	17.42	17.75	18.58	18.89	20.47	14.75	15.08	15.91	16.22	17.80
	6H	17.88	18.14	19.05	19.30	20.89	15.34	15.60	16.51	16.76	18.34
	8H	18.05	18.28	19.22	19.43	21.05	15.54	15.77	16.71	16.92	18.54